



Position	Count	Description	Unit price
	-1	<p>Product name: DPI differential pressure sensor kit</p>  <p>Product photo could vary from the actual product</p> <p>Product No.: 96611524 Product Number: 96611524 EAN number: 5700834481550</p> <p>Technical: Maximum operating pressure: 232 psi</p> <p>Materials: Material: Stainless steel DIN 1.4305, FKM, PPS</p> <p>Installation: Range of ambient temperature: 14 .. 158 °F Maximum operating pressure: 232 psi Type of connection: 7/16 - 20 UNF Range of differential pressure measurement: 0 .. 23.2 psi</p> <p>Liquid: Liquid temperature range: 14 .. 158 °F</p> <p>Electrical data: Enclosure class (IEC 34-5): 55 Length of cable: 2.95 ft Signal: 4 - 20 mA</p> <p>Others: Net weight: 1.21 lb</p>	On request



96611524 DPI differential pressure sensor kit 60 Hz



Note! All units are in [mm] unless others are stated.
 Disclaimer: This simplified dimensional drawing does not show all details.