

VU30S

FEATURES

Heavy-duty stainless steel construction

Powerful blower options

Bright LED lighting

Dishwasher Safe Filters

Remote Control

Rigorously tested in our U.S. manufacturing facilities for decades of use

Exceptional 24/7 support from our Customer Care team in Madison

ACCESSORIES

Make-Up Air Damper

Recirculating Filters

Remote Control

Internal Blowers

Accessories available through an authorized dealer.


For local dealer information, visit subzero-wolf.com/locator.



BLOWER OPTIONS

- 300 CFM Internal
- 600 CFM Internal

OPENING DIMENSIONS





PRODUCT SPECIFICATIONS

Model	VU30S
Dimensions	27 5/8"W x 13 3/4"H x 11 3/4"D
Weight	45 lbs
Electrical Supply	110/120 VAC, 60 Hz
Electrical Service	15 amp dedicated circuit
Discharge Location	Vertical
Discharge Dimensions	6" Round
Bottom of Hood to Countertop	24" to 36"
Receptacle	3-prong grounding-type

NOTE: Dimensions in parenthesis are in millimeters unless otherwise specified

DIMENSIONS

