# 48" DUAL FUEL RANGE - 4 BURNERS AND FRENCH TOP

**DF484F**



## FEATURES

- 4 dual-stacked burners plus 15,000 Btu French top
- Dual-stacked burners produce up to 20,000 Btu
- Burners capable of delivering less than 300 Btu for premier simmer performance
- 10 cooking modes make meals easy
- Dual convection oven for faster, more consistent cooking
- Second 18" single convection oven
- Continuous cast-iron grates for easy movement of pots and pans
- Rigorously tested in our U.S. manufacturing facilities for decades of use
- Exceptional 24/7 support from our Customer Care team in Madison
- Cobalt blue porcelain interior
- Spark ignition system re-ignites if flame goes out
- Heavy-gauge stainless steel
- Exclusive pivoting control panel
- Red, black or stainless steel control knobs
- Temperature probe lets you know when it's done
- Self clean, delayed start, timed cook, Sabbath mode and more

## ACCESSORIES

- 30" Bake Stone Kit
- 30" Full-Extension Oven Rack
- Broiler Pan
- Dehydration Kit
- Oven Rack Set (3)
- Premier Baking Sheet
- Temperature Probe
- 5" and 10" stainless steel risers, and 20" riser with shelf
- Signature red, black or stainless steel control knobs
- Front Leg Extension Covers


- Cast iron S-grates and wok grate
- Hardwood cutting board
- High altitude conversion kit
- Stainless steel, brass or chrome bezels

Accessories available through an authorized Sub-Zero dealer.
For local dealer information, visit subzero-wolf.com/locator.

## KNOB OPTIONS



## TOP CONFIGURATION




## RANGETOP SPECIFICATIONS


- 1 - 9,200 Btu Burner
- 1 - 15,000 Btu Burner
- 1 - 18,000 Btu Burner
- 1 - 20,000 Btu Burner
- 1 - 15,000 Btu French Top

# 48" DUAL FUEL RANGE - 4 BURNERS AND FRENCH TOP


## PRODUCT SPECIFICATIONS

| | |
|---|---|
| Model | DF484F |
| Dimensions | 47 7/8"W x 36 7/8"H x 29 1/2"D |
| Oven 1 Usable Capacity | 1.5 cu. ft. |
| Oven 1 Overall Capacity | 2.5 cu. ft. |
| Oven 2 Usable Capacity | 2.8 cu. ft. |
| Oven 2 Overall Capacity | 4.5 cu. ft. |
| Door Clearance | 19 1/2" |
| Weight | 750 lbs |
| Electrical Supply | 240/208 VAC, 60 Hz |
| Electrical Service | 50 amp dedicated circuit |
| Gas Supply | 3/4" ID line |
| Gas Inlet | 1/2" NPT female |

## ELECTRICAL





## GAS





## NOTE:

Dimensions in parenthesis are in millimeters unless otherwise specified

## DIMENSIONS




## STANDARD INSTALLATION




**Without ventilation hood, 36" (914) minimum clearance countertop to combustible materials, 44" (118) for charbroiler.*

*NOTE: Shaded area above countertop indicates minimum clearance to combustible surfaces, combustible materials cannot be located within this area.*
*For island installation, 12" (305) minimum clearance back of range to combustible rear wall above countertop.*