

Slice Gate Valves - PVC



VSGV Uni-Body



VSGV 3 piece body



VSGV 3 piece body with union

PVC Slice Gate Valve Features:

- Designed for pool & spa, irrigation, plumbing, waste water and agricultural applications.
- Stainless steel shaft prevent rust and corrosion.
- Ozone & chemical resistant Santoprene[™] materials.
- Santoprene[™] seals are integrated to the paddle to eliminate any chance of torn or punctured gaskets.
- Maximum working pressure 50 psi (through 2").
- Solvent cement traps to catch excess glue.
- Every valve tested at double recommended working pressure.
- Valterra's patent pending triple o-ring neck seal to ensure against any chance of shaft leakage.

Unibody Design

- One piece uni-body design.
- Combination socket ID x spigot OD for installation flexibility.
- Locking handle provides positive shut-off and easy gate opening.

3 Piece body

- Three piece configuration allows for repair or can be used as a union.
- Three piece configuration easily disassembles for inline service.

Part Number	Description	Max PSI	Ctn Qty	List Price
Uni-Body				
VSGV2101	1 1/2" slip x slip	45	30	\$ 18.70
VSGV2201	2" slip x slip	40	20	26.64
* Unibody 2" slip hubs a	are 2" slip or 2 1/2" spig			
Three Piece Body				
VSGV150SL	1 1/2" slip x slip	45	30	19.57
VSGV150FIPTXMIPT	1 1/2" fipt x mipt	45	40	25.32
VSGV150SLU	1 1/2" slip x union slip	45	38	31.93
VSGV150MTU	1 1/2" mipt x union slip	45	38	33.09
VSGV150SP	1 1/2" slip x spigot	45	30	23.98
VSGV150SD	1 1/2" step down pool hose x mipt ABS		40	23.36
VSGV200SL	2" slip x slip	40	20	28.29
VSGV200SP	2" slip x spigot	40	34	28.29
VSGV300SL	3" slip x slip	30	15	39.32
VSGV400SL	4" slip x slip w/ metal handle	20	6	167.22
VSGV600SL	6" slip x slip w/ stainless handle	10	1	696.67
VSGV800SL	8" slip x slip w/ stainless handle	10	1	975.45
VSGV1000SL	10" slip x slip w/ stainless handle	10	1	1778.33
VSGV1200SL	12" slip x slip w/ stainless handle	10	1	1868.19



