

# Installation Accessories - Submersible



**TA48** 



TA6100

SG Series





MG6 WG Series

All torque arrestors, pump guides, cable guards are third party certified to NSF/ANSI 372.



### **Deluxe Torque Arrestor Features:**

- Two piece design, molded from PVC or natural rubber.
- PVC torque arrestor is **40% heavier** than competitors to resist long-term casing abrasion.
- · Field adjustable to hold pump centered in well.
- Fits all well casings from 4" to 8" I.D.
- Torque Arrestor is securely fastened to 1" or 1 1/4" drop pipe
  w/ 2 Ideal all stainless steel clamps included.
- Available bagged or bulk without clamps.

### **Spider Style Torque Arrestor Features:**

- Spider style molded from natural rubber.
- Installs just above discharge of submersible pump.
- · Tabs are easily cut for field alteration.
- 4"-6" casing, 1" center hole.

## **Natural Rubber Pump Guide Features:**

- Installed at the top of the submersible pump discharge.
- Permits the pump to be lowered without damage from abrading against the well casing & ledge while centering the pump in the well.

#### **Cable Guard Features:**

- · Snap-in and self clamping styles.
- · Keeps power cable from abrading against well casing.
- A minimum of three to five should be used; one at the pump, one no further than 15' above the pump, and one between 25' and 30' above the pump.
- Adjustable use in 4", 5" and 6" wells. Available for 1" or 1 1/4" drop pipe.
- · Made of polyethylene and will float.

Part Number	Description		Color	Ctn Qty	List Price
Deluxe PVC Torque Arrestor					
TA48	Bagged, with 2 Ideal all stair	Black	16	\$ 14.61	
TA48G	Bagged, with 2 Ideal all stair	Green	16	16.32	
CTA48	Bulk, no clamps	Black	Bulk	11.92	
CTA48G	Bulk, no clamps	Green	Bulk	13.13	
Deluxe Rubber Torque Arrestor					
TA48R	Bagged with 2 Ideal all stain	Black	16	16.10	
CTA48R	Bulk, No clamps	Black	Bulk	13.93	
Spider Style Rubber Torque Arrestor					
TA6100	6x1		Black	50	27.47
Natural Rubber Pump Guides Fits Casing ID Guide OD			Drop Pipe	<b>:</b>	
SG558-5X1	5-5/8"	5"	1"	Bulk	8.99
SG600-55/8X1	6"	5 5/8"	1"	Bulk	10.31
SG600-55/8X11/4	6"	5 5/8"	1 1/4"	Bulk	10.31
SG625-6X1	6 1/4"	6"	1"	Bulk	11.41
SG625-6X2	6 1/4"	6"	2"	Bulk	11.41
Cable Guard					
MG6	With two cable holes, fits 4"		100	0.96	
WG100	1" Self-clamping style, fits 4		48	2.93	
WG125	1 1/4" Self-clamping style, f		48	4.86	



www.americangranby.com