



Expandable Repair Couplings



118 Series



Flo Span Expandable Repair Coupling Features:

- Double EPDM o-ring seal gives more protection from possible leakage due to deflection of piston in the extended position.
- EPDM o-ring seal also protects against contamination on the cylinder wall.
- Solvent cement trap located in cap to capture excess solvent cement.
- Made from PVC type I grade I material meeting ASTM D-1784
- 118 Series does not have union end.

NEW				
Part Number	IPS Size	Body Length	Ctn Qty	List Price
PVC Flo-Span Expansion Couplings - NO UNION S x SPG				
118-05	1/2"	7 1/2"	28	\$ 7.62
118-07	3/4"	7 3/4"	24	8.45
118-10	1"	9 1/2"	15	9.79
118-12	1-1/4"	10 3/4"	10	18.41
118-15	1-1/2"	12 3/4"	16	20.18
118-20	2"	13 1/2"	12	30.85
118-25	2-1/2"	18 3/4"	3	47.94
118-30	3"	21"	3	59.89
118-40	4"	22 3/4"	3	104.70
QF-6000	6" S x S	26 1/4"	1	520.90



PSC Series




Poly-Stretch Repair Coupling Features:

- For repair of polyethylene irrigation pipe.
- Avoid extra digging and buckled pipe.
- Couplings are made of ABS
- O-ring seal is made of Buna 70
- Pressure rated at 160 psi.
- Designed for irrigation operation pressures of polyethylene pipe and more.

Instructions for Installation:

- Cut out approximately 4" of pipe where repair is needed.
- Place clamps over ends of pipe
- Insert end marked with "END FIRST" arrow by pushing and turning at same time.
- Insert other end by pushing & turning.
- Place clamps over ribbed ends & tighten.

Dimensions:



	A	B	C	D	E
3/4"	4.0	.575	.820	1.50	5.625
1"	4.0	.770	1.075	1.50	5.625
1 1/4"	5.0	1.109	1.415	1.755	6.70
1 1/2"	5.0	1.310	1.63	1.755	6.70
2"	5.0	1.825	2.125	1.755	6.70

Part Number	Description	Ctn Qty	List Price
PSC07	3/4" Poly-stretch coupling	50	\$ 12.47
PSC10	1" Poly-stretch coupling	50	13.05
PSC12	1 1/4" Poly-stretch coupling	25	19.54
PSC15	1 1/2" Poly-stretch coupling	25	22.59
PSC20	2" Poly-stretch coupling	20	35.28