Cast Centerset Faucets 4" Centers





Specification: (example)

- HEAVY DUTY CAST BRASS centerset faucet
- 102mm (4") centers, two handle
- · Polished chrome plated finish with polished underspout
- Metal hold-down package
- Color indexed metal handles with vandal resistant screws
- **CER-TECK**® 1/4 turn ceramic structures

and ... with ... (add product variation required)

with ... (add outlet required) with ... (add handle required)

with ... (add suffix -TI if required - See Back Page)

21C143







Engineer/Architect Approval

Model Specified:

Approval: Date:

- 11
— 1

DESCRIPTION	PRODUCT NO.			
4" Centerset Faucet	21C			



						c Us
	PRODUCT VARIATION		OUTLET		HAN	DLE
		/				✓
o			0		o	
1	Standard Product Less Pop-up (No Pop-up Hole)		1		1 Five Flute Handles	
2	Standard Product With Metal Pop-up		Vandal Resistant 1.5 gpm (5.7 L/min.) Laminar w/Agion® Antimicrobial		102mm (4") Hooded Blade Handles (1)	
3	Standard Product with Cast Open Grid Strainer (No Pop-up Hole)		Vandal Resistant 1.5 gpm (5.7 L/min.) Flow Control Aerator		3 76mm (3") Hooded Lever Handles (1)	Ġ.
4	Standard Product With Cast Offset Open Grid Strainer (No Pop-up Hole)		4 Standard 1.5 gpm (5.7 L/min.) Flow Control Aerator	S Carrier Carr	102mm (4") Blade Handles, Sanitary Hoods (1)	E. S.
5	Standard Product With Chain Stay Less Plug & Chain		Vandal Resistant 0.5 gpm (1.9 L/min.) Non-Aerating Spray Outlet		5 152mm (6") Wrist Handles, Sanitary Hoods	B G.
6			6		6	
7			7		7	
8			8		76mm (3") Self-Closing Hooded Lever Handles	
9			Yandal Resistant 9 0.35 gpm (1.32 L/min.) Non-Aerating Spray Outlet		9 Five Flute Self-Closing Handles	

See Series 27C4, 27C5 for 4" Gooseneck Spout Centersets. (1) H & C Temperature Indicator available. Add suffix -TI. Refer to www.specselect.com for individual models.

 $\label{eq:FlowRates} Flow \mbox{ Rates are at 60 PSI.}$ Note: Use this page front and back as a product submittal sheet.



Approvals:

- CSA certified
- Complies to ASME A112.18.1/CSA B125.1
- Handles No. 2, 3, 4 and 5
 Indicates compliance to ICC/ANSI A117.1
- Outlet options 2, 3 and 4 are EPA WaterSense listed
- Verified compliant with 0.25% weighted average Pb content regulations


(Contact Delta Representative for State and/or Local Approvals.)

HANDLE TEMPERATURE INDICATORS

□ Add suffix "-TI" to Product Number for handle temperature indicators "H" (red), "C" (blue). Availaible on handle options 2, 3 or 4 only.



FLOW RATE vs PRESSURE






CAST SPOUT	"D"		
OUTLET NO.	mm	in.	
2	11	0.45	
3	11	0.45	
4	11	0.45	
5	11	0.45	
9	11	0.45	

Note: Measurements may vary ± 6mm (0.25")

TECK® COMMERCIAL

Cast Centerset Faucets 4" Centers



Refer to www.specselect.com for individual models.

Note: Use this page front and back as a product submittal sheet.