# **Cast Deckmount Sink Faucets** 8" Centers





# Specification: (example)

- HEAVY DUTY CAST BRASS sink faucet
- 203mm (8") center two handle
- Polished chrome plated finish
- **BRASS** swing spout or 3/8" IPS **BRASS PIPE** Rigid/Swivel Gooseneck Spout
- Metal hold-down package
- Color indexed metal handles with vandal resistant screws
- TUF-TECK® compression structures

and ... with ... (add spout required) with ... (add outlet required)

with ... (add handle required)
with ... (add suffix **-LS** if required – See Back Page) with ... (add suffix -TI if required - See Back Page)



Engineer/Architect Approval	
Model Specified:	
Approval:	Date:

DESCRIPTION	PRODUCT NO.			
CAST Deckmount	26T3			



SPOUT	OUTLET HANDLE			
<b>✓</b>	<u> </u>	<u> </u>		
0	<b>o</b>			
203mm (8") Wallform (S2) Swing Spout (2)	1	1 Five Flute Handles		
2 203mm (8") Tubular (S5) Swing Spout (2)	Vandal Resistant 1.5 GPM (5.7 L/min.) Laminar w/Antimicrobial By Agion®	102mm (4") Hooded Blade Handles (5)		
3	3 Vandal Resistant 1.5 GPM (5.7 L/min.) Flow Control Aerator	76mm (3") Lever Blade Handles (5)		
4	Standard 1.5 GPM (5.7 L/min.) Flow Control Aerator	102mm (4") Blade Handles, Sanitary Hoods (5)		
5	Vandal Resistant Non-Aerating Spray Outlet 0.5 GPM (1.9 L/min.)	5 Wrist Handles, Sanitary Hoods		
6	6	6		
7	Smooth End, Laminar Flow Control in Base of Gooseneck Spout 1.0 GPM (3.8 L/min.) (3)	7		
8	8	8		
Heavy Duty 152mm (6") Bend Rigid/Swivel (R4) Gooseneck Spout (1) (4)	9	9		

(1) Available Optional Rigid/Swivel Spouts These spouts can ONLY be added to SPOUT Option No. 9. Note: Use this page front and back as a product submittal sheet. Flow Rates are at 60 PSI (2) Available Optional Swing Spouts. These spouts can ONLY be added to SPOUT Option No. 2. Refer to www.specselect.com for individual models. (3) This outlet can ONLY be added to SPOUT Option No. 9. (4) 120° Limited Swing Spout available. Add Suffix -LS. (5) H/C Temperature Indicator Available. Add Suffix -TI. Flow Rates are at 60 PSI.



#### **Approvals:**

- CSA certified
- Complies to ASME A112.18.1/CSA B125.1
- Handles No. 2, 3, 4, and 5 meet ADA compliance to 1CC/ANSI A117.1/ADA
- Verified compliant with 0.25% weighted average Pb content regulations

(Contact Delta Representative for State and/or Local Approvals.)


#### **HANDLE TEMPERATURE INDICATORS**

☐ Add suffix "-TI" to Product Number for handle temperature indicators "H" (red), "C" (blue).

Availaible on handle options 2, 3 or 4 only.



### FLOW RATE vs PRESSURE



### FOR OPTIONAL **RIGID/SWIVEL & LIMITED SWING SPOUTS**

See DSP-R/S for detailed specification (Found in the "Add-On Option" section when using the printed spec binder)

# **FOR OPTIONAL SWING SPOUTS**

See DSP-S/S for detailed specification

(Found in the "Add-On Option" section when using the printed spec binder)


#### INLETS - 1/2" MIP/Coupling Nuts

± 6mm (0.25")

# Note: Measurements may vary

**TECK®** COMMERCIAL

# **Cast Deckmount Sink Faucets** 8" Centers



#### **LIMITED SWING GOOSENECK**

Add suffix "-LS" to Product Number for 120° Limited Swing

OUTLET	"D"			
NO.	mm	in.		
2	18	0.69		
3	18	0.69		
4	1 <i>7</i>	0.67		
5	18	0.69		

### **GOOSENECK SPOUT ASSEMBLY #9**

	"A"		"C"		"L"	
SPOUT/OUTLET	mm	in.	mm	in.	mm	in.
Gooseneck–Standard (R4) for outlets #2, 3, 4 & 5	152	6	124	4.9	146	5.8
Gooseneck-Standard (R4) for outlet #7	152	6	117	4.6	152	6.0

SWING SPOUT ASSEMBLIES							
SPOUT "A"		Α"	"C"		"L"		
NO.	SPOUT TYPE	mm	in.	mm	in.	mm	in.
1	8" Wallform Spout (S2)	206	8.1	15	0.6	130	5.1
2	8" Tubular Spout (S5)	185	7.3	41	1.6	147	5.8

Refer to www.specselect.com for individual models

Note: Use this page front and back as a product submittal sheet.