DEMD Series **Electronic Lavatory Faucets (Infrared)**

SENSOR, _____

AND BATTERY

65 mm (2.56")

486 mm (19.13")

M4 x 5 set screw used to lock spout to tubular base

DEMD-101LF (BATTERY OPERATED WITH NO MIX)

Ð

F

SENSOR CLEARANCE

For above deck mounted sinks, the sensor requires a clearance.

38 mm (1.50") MAX.

DECK THICKNESS

113 mm (4.46")

116 mm (4.55")

Ø 32 MM (1.25") HOLE SIZE

DECK

175 mm (6.89")

O-RING TO SEAL





SPECIFICATION: (EXAMPLE)

- Deck mount electronic lavatory faucet
 - Sensor detects user's hand to activate water flow
- One 9V lithium battery inside spout (included)
- Above deck battery and electronics •
- Red light indicator blinks when battery is low
- Vandal resistant (wrench flat)
- 0.5 gpm (1.9 L/min) spray outlet

DEMD-101 SERIES

- Electronic faucet for cold or pre-mixed water
- DEMD-101LF (Chrome)

DEMD-101LF-NS (Nickel Stainless)

OPERATION

Sensing Range:

- Factory set to $8.0" \pm 1.5"$ (200 mm \pm 40 mm)
- Adjustable from 3.15" to 11.8" (80 mm to 300 mm) with optional remote control

Maximum Run Time:

90 seconds, adjustable with remote control •


OPTIONAL ACCESSORIES (Order Separately)


060967A

- Remote Control allows adjustment of sensor range, maximum run time, delayed close time, temporary shut-off for cleaning and factory settings reset
- O63256A (Chrome Only)
 - 0.35 gpm (1.32 L/min) spray outlet

O60961A (Chrome)

- 1.0 gpm (3.8 L/min) aerator
- O61118A (Chrome)
 - 1.5 gpm (5.7 L/min) Careguard® laminar outlet





APPROVALS:

- IAPMO certified .
- Complies to ASME A112.18.1/CSA B125.1 Indicates compliance to
- ICC/ANSI A117.1
- Verified compliant with 0.25% weighted average Pb content regulations

(Contact Delta Representative for State and/or Local Approvals.)

Note: Measurements may vary ± 6mm (0.25")

Refer to www.specselect.com for individual models.

For sensor clearance: 38 mm (1.5") maximum sink lip height from deck HARDWIRE CONVERSION OF DEMD-100 SERIES **Requires SEPARATE order of either: (**A) One 060958A DEMD plug in power supply, One 060704A hardwire 20VA transformer OR B output 9VDC (120VAC to 24VAC) PLUS

One 061168A connector kit

- PLUS
- One 060974A DEMD converter (24VAC to 9VDC) PLUS
- One 061168A connector kit

Delta reserves the right (1) to make changes in specifications and materials, and (2) to change or discontinue models, both without notice or obligation. Dimensions are for reference only. See current full-line price book or www.specselect.com for finish options and product availability

Note: Use this page front and back as a product submittal sheet.

DSP-DEMD-100 Rev. J

DEMD Series Electronic Lavatory Faucets (Infrared)



SPECIFICATION: (EXAMPLE)

- Deck mount electronic lavatory faucet
- Sensor detects user's hand to activate water flow
- One 9V lithium battery inside spout (included)
- Above deck battery and electronics
- Red light indicator blinks when battery is low
- Vandal resistant (wrench flat)
- 0.5 gpm (1.9 L/min) spray outlet

DEMD-111 SERIES

- Electronic faucet with mixer to adjust temperature
- DEMD-111LF (Chrome)
- DEMD-111LF-NS (Nickel Stainless)

OPERATION

Sensing Range:

- Factory set to 8.0" ± 1.5" (200 mm ± 40 mm)
- Adjustable from 3.15" to 11.8" (80 mm to 300 mm) with optional remote control
- Maximum Run Time:
- 90 seconds, adjustable with remote control

OPTIONAL ACCESSORIES (Order Separately)

🖵 060967A

 Remote Control – allows adjustment of sensor range, maximum run time, delayed close time, temporary shut-off for cleaning and factory settings reset

□ 063256A (Chrome Only)


• 0.35 gpm (1.32 L/min) spray outlet

O60961A (Chrome)

• 1.0 gpm (3.8 L/min) aerator

O61118A (Chrome)


 1.5 gpm (5.7 L/min) Careguard[®] laminar outlet




- IAPMO certified
 Complian to ASME A11
- Complies to ASME A112.18.1/CSA B125.1
 L Indicates compliance to
- ICC/ANSI A117.1
- Verified compliant with 0.25% weighted average Pb content regulations
- (Contact Delta Representative for State and/or Local Approvals.)

Note: Measurements may vary ± 6mm (0.25")

Refer to www.specselect.com for individual models.





Requires SEPARATE order of either:

- One 060958A DEMD plug in power supply, output 9VDC
- One 061168A connector kit

- One 060704A hardwire 20VA transformer (120VAC to 24VAC)
 PLUS
- One 060974A DEMD converter (24VAC to 9VDC)
- One 061168A connector kit

Note: Use this page front and back as a product submittal sheet.

DSP-DEMD-100 Rev. J

Delta reserves the right (1) to make changes in specifications and materials, and (2) to change or discontinue models, both without notice or obligation. Dimensions are for reference only. See current full-line price book or www.specselect.com for finish options and product availability.

OR