

# SPEAKMAN COMPANY

## Chelsea™ Collection Combination Series SM-10410-P

### DESCRIPTION

Speakman Chelsea™ Collection Combination Series unites the best products included in our Chelsea™ Series. The combination begins with our anti-scald balanced pressure valve with integral volume control and stops, featuring a brass body and adjustable temperature limit stop. The wall plate, handle, and integral volume control handle are designed with definitive Chelsea™ Collection styling. Piston type pressure balancing/ceramic regulating cartridge assembly with built-in check valves. Meets ASME A112.18.1 / CSA B125.1 & ASSE 1016 standards. Also provided is the S-2500 brass 7" shower arm with metal wall flange. The featured product in the Chelsea™ Collection Combination Series is the ANYSTREAM® S-3020 showerhead with a 5-1/4" outer diameter face. Five self-cleaning plunger nozzles resist scale build-up and provide 50 spray streams for a full body coverage pattern. The center core nozzle delivers 12 massaging jets and a combination spray is included. Water-conserving pressure compensating AUTOFLO® device reduces flow to 2.5 GPM / 9.46 LPM maximum, to meet existing ANSI A112.18.1 Standard. 1/2" NPT inlet.

### SPECIFICATIONS

SM-10400-P Anti-Scald Balanced Pressure Valve:

Connections: 1/2" female copper sweat inlets & shower outlet; 1/2" NPT female tub outlet

Flow Rate: For use with showerheads rated at 2.0 GPM (7.6 LPM) or higher.

S-3020 Showerhead:

Supply: 1/2" NPT female

Flow Rate:

2.5 GPM / 9.46 LPM MAX

S-2500 Shower Arm:

Supply: 1/2" NPT male inlet

Outlet: 1/2" NPT male outlet

### INSTRUCTIONS

See individual products for installation of the components and warranty information.

### ROUGH-IN

