


# SUBMITTAL DATA

## LONG STARTING COLLAR — RX12 (no damper) RX13 (damper)



<b>A</b>	<b>B</b>	<b>C</b>	<b>D</b>	<b>GA</b>
<b>4</b>	6	1.75	1.0	30, 28
<b>5</b>	6	1.75	1.0	30, 28
<b>6</b>	6	1.75	1.0	30, 28, 26
<b>7</b>	6	1.75	1.0	30, 28, 26
<b>8</b>	6	1.75	1.0	30, 28, 26
<b>9</b>	6	1.75	1.0	30, 28, 26
<b>10</b>	6	1.75	1.0	30, 28, 26
<b>12</b>	6	1.75	1.0	26
<b>14</b>	6	1.75	1.0	26
<b>16</b>	6	1.75	1.0	26
<b>18</b>	6	1.75	1.0	26
<b>20</b>	6	1.75	1.0	26
<b>22</b>	6	1.75	1.0	26
<b>24</b>	6	1.75	1.0	26, 24
<b>26</b>	6	1.75	1.0	26, 24
<b>28</b>	6	1.75	1.0	26, 24
<b>30</b>	6	1.75	1.0	26, 24
<b>32</b>	6	1.75	1.0	26, 24
<b>34</b>	6	1.75	1.0	26, 24
<b>36</b>	6	1.75	1.0	26, 24

Galvanized Steel, G30/40 coating standard, G90 available. Specify GA  
Metals tabs with 1/4" bead for sheet metal application, crimp one end.

### PART NUMBER DESIGNATIONS

**RX12xx (no damper)**

**RX13xx (with damper)**

XX = Diameter (03-36)

Single and dual hardware damper available

PROJECT: \_\_\_\_\_ COMPANY: \_\_\_\_\_ DATE : \_\_\_\_\_

LOCATION: \_\_\_\_\_ SUBMITTED BY: \_\_\_\_\_