




Westwood ceramic fibre chambers

SOUND ABSORBING • RED HOT IN SECONDS • FIRES DRY • 2,300° - 3,000°F

WET COMBUSTION CHAMBER LINERS - Sealed in a plastic bag and individually boxed*



 No.	Ref. No.	Type		GPH	Description and Representative Picture			
S70-9 S70-10 S70-11 S70-12 S70-13 S70-15	#9 #10 #11 #12 #13 #15	Wet	Westwood <i>Round - Preshaped</i>	.50 - .75 .85 - 1.00 1.10 - 1.25 1.35 - 1.50 1.65 - 1.85 2.00 - 2.50	9" diameter, 12" high 10" diameter, 12" high 11" diameter, 12" high 12" diameter, 12" high 13" diameter, 14" high 15" diameter, 14" high			
S70-25 S70-27	#135 #200			Wet	Westwood <i>Rect. - Preshaped</i>	.75 - 1.35 1.35 - 2.00	14" x 11" x 12" 14" x 12" x 12"	
S70-30 S70-35 S70-40 S70-45	#1 #2 #3 #4					Wet	Westwood <i>Flat sheet(s)</i>	1.25 2.50 2.65 1.25

*Wet chambers have a shelf life and should be ordered such that they are not held in inventory longer than 6 months.

J-M Cerafelt™

Dry Refractory Liners

DRY COMBUSTION CHAMBER LINERS

 No.	Ref. No.	Type		GPH	Description and Representative Picture		
S70-50 S70-51 S70-53	141608 141612 -	Dry	Cerafelt blanket	- - -	1/4" x 16" x 8 ft. 1/4" x 16" x 12 ft. 1/4" x 48" x 20 ft. 		
S70-60	SS Kit			Dry	Cerafelt SS Kit (For lining burned out stainless steel combustion chambers)	.50 - 1.75	(1) - 14" x 48" (1) - 16" x 33" (8) - Stainless Steel Clips 