


UPS 15-35 SUC/SFC



TM03 8850 4412

Flow range:	0 - 21.5 gpm (0 - 4.9 m ³ /h)
Head range:	0-12 ft (0 - 3.7 m)
Motor:	2-pole, single-phase
Max. liquid temperature:	165 °F (74 °C)
Min. liquid temperature:	36 °F (2 °C)
Max. system pressure:	145 psi (10 bar)

Note: If the UP pump is equipped with a timer, the maximum liquid temperature is 150 °F (66 °C).

Model	Speed	Volts	Amps	Watts	Hp	Capacitor
UPS 15-35 SUC/ SFC	3	115	0.95	110	0.15	10 μF / 180 V
	2		0.75	84	0.11	
	1		0.55	61	0.08	


— Without check valve
- - - With check valve

Approvals




Drinking Water System Components
In Accordance with NSF/ANSI 372

UPS 15-35 SFC



TM03 8779 2507

UPS 15-35 SUC/TLC



TM03 8778 2507

Model	Product number 115 V	Dimensions [inches (mm)]						Connection type and size	Shipping weight [lbs (kg)]
		A	B	C	D	E	F		
UPS 15-35 SFC	59896772	6.50 (165)	5.50 (140)	4.13 (105)	3.88 (99)	2.85 (72)	3.13 (80)	GF 15/26	6.0 (2.7)
UPS 15-35 SUC	59896778	5.88 (149)	5.06 (129)	4.13 (105)	3.44 (87)	2.85 (72)	-	GU 125	5.4 (2.5)
UPS 15-35 SUC/TLC	59896780	5.88 (149)	5.06 (129)	4.13 (105)	3.44 (87)	5.33 (135)	-	GU 125	6.2 (2.8)

Note: LC/TLC models have a 6 ft (1.8 m), 3-prong power cord.
Removable check valve.
Dimensions in inches unless otherwise stated.