PRODUCT DIMENSIONS & SPECIFICATIONS



BH SERIES HORIZONTAL COILS

C B

Representative image only. Some models may vary in appearance. Due to continuous product improvement, specifications are subject to change without notice.

GENERAL SPECIFICATIONS

- \bullet Standard refrigerant connections: liquid line 3/8" ODS, suction line 7/8" ODS.
- Two 3/4" MPT condensate drains.
- Powder-painted metal drain pan. Stainless available.
- Five-year limited warranty.
- Flowrater standard. Factory or field-installable TXV available.
- Immersion-tested at 500 psi, then nitrogen-pressurized and sealed.
- \bullet Heavy gauge embossed galvanized cabinet fully lined with 1/2" faced insulation.
- Rifled copper tubing, enhanced aluminum fins.
- ETL listed.

COIL MODEL		DIMENSIONS			
	REPLACES	HEIGHT (B)"	OPENING		LENGTH (EX
			(C)"	(D)"	LENGTH (E)"
BHA SLAB HIGH HORIZON	TAL COILS				•
BHA** 24	N/A	23-1/2	21	16	21-1/2
BHA** 36	N/A	23-1/2	21	24	29-1/2
BHA** 48	N/A	23-1/2	21	29	34-1/2
BHA** 60	N/A	25	21	29	34-1/2
BHC HORIZONTAL COILS					
BHC24 24	RTE524CH	21-1/2	17-1/2	22	27
BHC32 36	RTE536CH	21-1/2	17-1/2	22	27
BHC32 48	RTE48CH, 548CH	21-1/2	17-1/2	28	33
BHC32 60	RTE60CH	25-1/2	21-1/2	28	33
BHL SLAB LOW HORIZON	TAL COILS				
BHL** 24	N/A	17	14-1/2	21-1/2	27
BHL** 36	N/A	17	14-1/2	21-1/2	27
BHL** 48	N/A	17	14-1/2	29	36
BHL** 60	N/A	21	18-1/2	29	36
BHR SLAB HORIZONTAL C	OILS				
BHR24 24	N/A	23-1/2	21	16	21-1/2
BHR32 36	N/A	23-1/2	21	16	21-1/2
BHR32 48	N/A	23-1/2	21	24	29-1/2
BHR32 60	N/A	25-1/2	21	24	29-1/2
BH232 60 SLAB HIGH HO	RIZONTAL COILS				
BH232 60	N/A	23-1/2	21	33-3/4	39-1/4













