



- Efficient, quiet fan
- Warm up in a hurry with a fast-heating element
- Unique compact design is recess mounted into your wall to suit any room
- All metal surfaces are powder-coated paint to remove sharp edges and provide a durable finish
- Easy to install
- Rest easy includes high temperature safety shutoff
- Available with or without built-in thermostat



cadetheat.com 855.CADET.US Vancouver, Washington Get warm on your terms with our most popular wall heater. The Com-Pak is an efficient, affordable way to add warmth without installing ductwork. Our hard wired heaters have proven safety features and multiple installation options, so your family can enjoy safe, sensible warmth for years.

ARCHITECTURAL - ENGINEERING INFORMATION

Fan forced up flow electric air heaters are ETL listed, factory rated at 120V, 208V, and dual field rated 208V/240V. A powder coated 20 gauge wall mounting can with six knockouts and 34 cubic inch wiring compartment is provided with each complete heater. Each complete heater is powder coated, of unitized construction and attaches to the wall can with a single screw and is self-contained and completely separate from the wall mounting can. Element is of nichrome type wire wrapped on mica insulators with a 16 amp rated, at 240V, high temperature manual power reset limit switch, and a one-time over temperature thermal back-up fuse, both located on the element board in the heated air flow for faster response time to abnormal conditions. A two stage centrifugal blower delivering approximately 40 to 55 CFM is driven by an impedance protected motor. The motor is totally isolated from the heating chamber. Metal grill is of one piece, 20-gauge construction and finished with a powder coat paint system.

TECHNICAL INFORMATION

UL safety standards require the heater to be placed a minimum distance of 3/4 inches (1.9 cm) from adjacent surfaces and 4-1/2 inches (11.4 cm) from the floor. Manufacturer recommends installations 12 inches from all surfaces for longer and cleaner performance. All models 1500 watts or less may be ceiling mounted. A 3-foot (91.4 cm) minimum clearance is required for furniture or other objects placed directly in front of the heater.

Electric wall heaters and thermostats work best when installed on an inside wall.





tested to UL standards

Сом-Рак

Grill: 9"W x 12"H x 1"D • Rough-in: 8"W x 10-1/8"H x 4"D Thermostat temperature range 40°F to 85°F


Heater assemblies require a wall can, grill kit, and may require a thermostat

PART	MODEL*	DESCRIPTION	WATTS	VOLTS	AMPS	BTUS V	VT/LB
67508 67580	CSC101TW CSC101TA	Complete unit with stat, wall can & grill, white or almond	1000	120	8.3	3415	7
67509 67581	CSC151TW CSC151TA	n	1500	120	12.5	5120	7
67505 67577	CSC102TW CSC102TA	и	1000/750	240/208	4.2/3.6	3415/2560	7
67506 67578	CSC152TW CSC152TA	и	1500/1125	240/208	6.3/5.4	5120/3840	7
67507 67579	CSC202TW CSC202TA	Π	2000/1500	240/208	8.3/7.2	6825/5120	7
67549	CSC101	Complete unit w/o stat, with wall can & grill	1000	120	8.3	3415	7
67553 67541	CSC151 CSC102	n.	1500 1000	120 240/208	12.5 4.2/3.6	5120 3415/2560	7 7
67543 67544	CSC152 CSC202	u u	1500 2000	240/208 240/208	6.3/5.4 8.3/7.2	5120/3840 6825/5120	7 7
67550 67560	CS051 CS051T	Heater assembly w/o thermostat Heater assembly with thermostat	500	120	4.2	1710	3.5 4
67515 67523	CS101 CS101T	и	1000	120	8.3	3415	3.5 4
67516 67524	CS151 CS151T	и	1500	120	12.5	5120	3.5 4
67563 67573	CS058 CS058T	u	563	208	2.7	1925	3.5 4
67564 67589	CS078 CS078T	п	750	208	3.6	2560	3.5 4
67557 67586	CS108 CS108T	и	1000	208	4.8	3415	3.5 4
67569 67598	CS118 CS118T	u	1125	208	5.4	3840	3.5 4
67571 67599	CS158 CS158T	и	1500	208	7.2	5120	3.5 4
67517 67525	CS208 CS208T	u	2000	208	9.6	6825	4 3.5 4
67584 67585	CS052 CS052 CS052T	и	500/375	240/208	2.1/1.8	1710/1280	4 3.5 4
67510	CS072	а	750/563	240/208	3.1/2.7	2560/1925	3.5
67518 67511	CS072T CS102	а	1000/750	240/208	4.2/3.6	3415/2560	4
57519 57512	CS102T CS122	u .	1250/937	240/208	5.2/4.5	4265/3200	4
57520 57513	CS122T CS152	u	1500/1125	240/208	6.3/5.4	5120/3840	4 3.5
67521 67514	CS152T CS202	n	2000/1500	240/208	8.3/7.2	6825/5120	4 3.5
57522	CS202T		2000/1000	240/200	0.3/7.2	0023/3120	4


WALL HEATER ACCESSORIES (MODEL CS)


PART	MODEL*	DESCRIPTION	VOLTS	AMPS	WT/LBS
67061 67060	CC CC10	Wall can for model CS, single or 10-pack			2.8 22.5
69110 69111 69112	CCSMB CCSMW CCSMA	Surface mount wall can for model CS, black, white or almond			4.4
67079 67081	CGW CGW10	Vertical grill kit for model CS, single or 10-pack, white			1.5 12.3
67075 67080	CGA CGA10	Vertical grill kit for model CS, single or 10-pack, almond			1.5 12.3
65015 65016	CMGA CMGA5	Horizontal grill kit for model CS, single or 5-pack, almond			2.0 7.5
65005 65006	CMGW CMGW5	Horizontal grill kit for model CS, single or 5-pack, white			2.0 7.5
67063 67065	CTT1W CTT1A	Built-in thermostat kit for model CS, single pole, 40°F to 85°F, white or almond	240/208/120	22	.2
67064 67066	CTT2W CTT2A	Built-in thermostat kit for model CS, double pole, 40°F to 85°F, white or almond	240/208/120	22	.2
67067	CTT1P	Built-in thermostat kit, tamper proof for model CS, single pole, 40°F to 85°F	240/208/120	22	.2
67105 67100	CAMW CAMA	Adapter plate for model CS, 18-1/2" w x 22" h, white or almond			3.5
67115 67110	SAMW SAMA	Adapter plate for model CS, $12"wx21\text{-}1/4"h,$ white or almond			2
67088	FWAP	Adapter kit repurposes outdated model FW wall can and grill, use with model CS heater assembly			1







Wall Can Side







ROUGH-IN: 8"W X 10-1/8"H X 4"D



If horizontal mounting is preferred for heater assemblies without thermostat, use model CMGA or CMGW.

*Suffix W or A in model designates color