HEAT PUMPS



The Ameristar line of heating and cooling products offer you flexible and affordable options for HVAC equipment replacement. The Ameristar product line should complement the national brand you are selling and provide an opportunity to capture additional volume and market share with today's budget-conscious consumers.



- Ameristar units are available in 14 SEER (R-410A only) models.
- footprint are ideal for homeowners with limited yard space.

maximum sound level of 76 decibels.

– Units operate quietly, with a

- 24V low-voltage control provides added safety.

- 1.5 5 ton models available.
- Painted, galvanized steel cabinets resist rust and stand up to weather.
- The compact design and small

14 SEER R-410A HP	Compressor	SEER	HSPF	Sound Rating	Dimensions (in.) H x W x D
M4HP4018C1000A	Scroll	14.00	8.2	74	24.94 x 23.63 x 23.63
M4HP4024C1000A	Scroll	14.00	8.2	74	24.94 x 23.63 x 23.63
M4HP4030B1000A	Scroll	14.00	8.5	74	24.94 x 28.00 x 28.00
M4HP4036B1000A	Scroll	14.00	8.5	74	24.94 x 29.13 x 29.13
M4HP4042B1000A	Scroll	14.00	8.5	76	33.19 x 28.00 x 28.00
M4HP4048B1000A	Scroll	14.00	8.2	76	33.19 x 28.00 x 28.00
M4HP4060B1000A	Scroll	14.00	8.5	76	33.19 x 29.13 x 29.13

AMERISTAR WARRANTIES

Registered Limited Warranty terms are applicable if the products are registered within 60 days of installation. Products can be registered online at ameristarac.com or by phone at 866-554-5611, otherwise Ameristar's Base Limited Warranty terms will apply. Base Limited Warranty terms can be found online at ameristarac.com. Warranties are for residential use only; some restrictions may apply. Warranties available include:

- 5-Year Base Limited Parts Warranty 10-Year Registered Parts Warranty



Offer your customers control over their system with a programmable thermostat.