

Panel Filters

StrataDensity® Panel Filters

Product Overview

- Sturdy and economical
- Higher arrestance and dust-holding capacity than typical fiberglass panel filters
- Premium-grade AAF manufactured fiberglass media
- Compression-resistant glass fibers



PANEL FILTERS

Specifications

Filter Depth	1", 2"
Media Type	Fiberglass
Frame Material	Paper Board
Special Size Available	Yes
Max Operating Temperature	150°F (66°C)
Air Filtration Certification	UL 900

Product Information

Part Number	Nominal Size Inches (W x H x D)	Actual Size Inches (W x H x D)	Std. Pkg. Qty.	Shipping Wt. Lbs. per Box (± 7%)	Cubic Ft.
1"					
220-319-051	12 x 24 x 1	11 ⁷ / ₈ x 23 ⁵ / ₈ x ³ / ₄	12	3.7	1.9
220-500-051	16 x 20 x 1	15 ⁷ / ₈ x 19 ⁵ / ₈ x ³ / ₄	12	3.9	2.1
220-600-051	16 x 25 x 1	15 ⁷ / ₈ x 24 ⁵ / ₈ x ³ / ₄	12	5.0	2.6
220-700-051	20 x 20 x 1	19 ⁵ / ₈ x 19 ⁵ / ₈ x ³ / ₄	12	4.8	2.6
220-782-051	20 x 24 x 1	19 ⁵ / ₈ x 23 ⁵ / ₈ x ³ / ₄	12	6.0	3.1
220-800-051	20 x 25 x 1	19 ⁵ / ₈ x 24 ⁵ / ₈ x ³ / ₄	12	5.3	3.2
220-863-051	24 x 24 x 1	23 ⁷ / ₁₆ x 23 ⁷ / ₁₆ x ³ / ₄	12	7.5	3.6
220-767-051	24 x 24 x 1 Full	23 ⁷ / ₈ x 23 ⁷ / ₈ x ³ / ₄	12	7.7	4.0
2"					
198-319-052	12 x 24 x 2	11 ⁷ / ₁₆ x 23 ⁷ / ₁₆ x 1 ³ / ₄	12	6.8	3.7
198-500-052	16 x 20 x 2	15 ⁷ / ₈ x 19 ⁵ / ₈ x 1 ³ / ₄	12	6.6	4.2
198-600-052	16 x 25 x 2	15 ⁷ / ₈ x 24 ⁵ / ₈ x 1 ³ / ₄	12	7.9	5.2
198-700-052	20 x 20 x 2	19 ⁵ / ₈ x 19 ⁵ / ₈ x 1 ³ / ₄	12	7.4	5.1
198-782-052	20 x 24 x 2	19 ⁵ / ₈ x 23 ⁵ / ₈ x 1 ³ / ₄	12	9.8	6.1
198-800-052	20 x 25 x 2	19 ⁵ / ₈ x 24 ⁵ / ₈ x 1 ³ / ₄	12	8.9	6.4
198-863-052	24 x 24 x 2	23 ⁷ / ₁₆ x 23 ⁷ / ₁₆ x 1 ³ / ₄	12	9.2	7.2

Additional sizes available upon request.

StrataDensity® is a registered trademark of AAF International in the U.S. and other countries.

AAF has a policy of continuous product research and improvement and reserves the right to change design and specifications without notice.

www.aafintl.com

