




SPECIFICATIONS

9175H

INDUSTRIAL FANS

30" Oscillating Assembled Fan Head

- **Motor**
3-speed, 1/3 HP, 120V, 1 phase, totally enclosed, ball bearing, permanently lubricated, permanent split capacitor
- **Controls**
Rear mounted pull cord switch
- **Power Cord**
Black, 10', 3-conductor, SJT type
- **Coating**
Blade, Guard, and Mounts are powder coated steel
- **Compliance**
ETL, OSHA
- **Oscillation**
90°
- **Shipping Information**
UPC: 0-46013-38730-1
Shipping Weight: 56.3 lbs.
- **Product Dimensions**
33.5"L x 17.5"W x 33.5"H
- **Available Mounts (sold separately)**
9100PB - Pedestal pole and base
9100WC - Wall mounting bracket
9100CM - Ceiling mounting bracket
9100i - I-beam mounting bracket
9100WB - Pedestal wheel kit



MODEL	CFM			RPM			AMPS			WATTS			DB A		
	HIGH	MED	LOW	HIGH	MED	LOW	HIGH	MED	LOW	HIGH	MED	LOW	HIGH	MED	LOW
9175H	8780	7480	5570	1075	925	800	2.8	2.0	1.7	308	205	170	72	70	64



U.S.: 820 Lincoln Drive
West Chester, Pennsylvania 19380-4466
Tel: (610) 692-7400 • 877-304-3785
Fax: (610) 696-8048