



GINIUS

**INNOVATIVE NEW INDIRECT
WATER HEATER**

**ALL STAINLESS STEEL
CONSTRUCTION**

**NEW PICANTO HEAT
EXCHANGER TECHNOLOGY**

**LIMITED RESIDENTIAL
LIFETIME WARRANTY**



**Available in 4 models
35, 45, 55 & 65 gallon**

Integral aquastat included

**80 PSI heat exchanger
pressure rating**


Drain port

**Low pressure drop
heat exchanger**

**Low standby loss (CFC/HCF
free foam insulation)**

**Ginius 65 features dual heat
exchangers for high output or
multi-energy applications**

- 1. AUX PORT FOR RELIEF VALVE**
- 2. INTEGRAL AQUASTAT**
- 3. COLD WATER INLET**
- 4. HOT WATER OUTLET**
- 5. INNOVATIVE STAINLESS
STEEL HEAT EXCHANGER**
- 6. BOILER WATER SUPPLY**
- 7. BOILER WATER RETURN**
- 8. DOMESTIC WATER DRAIN**
- 9. FULL STAINLESS STEEL
STORAGE TANK**



GINIUS


Available in 4 models 35, 45, 55 & 65 gallon




**GINIUS 35 - 45 - 55
SIZES FOR TYPICAL RESIDENTIAL APPLICATIONS**

**GINIUS 65 DUAL
FOR LARGE RESIDENTIAL OR LIGHT COMMERCIAL PROJECTS**


GINIUS 65 DUAL PIPING OPTIONS



**Piped in series for
general applications**



**Piped in parallel for
higher flow rates**



**Piped to multiple
heat sources**

SPECIFICATIONS AND FEATURES

MODEL	Ginius 35	Ginius 45	Ginius 55	Ginius 65	Ginius 65	Ginius 65
Heat Exchanger	Single	Single	Single	Single	Dual - series	Dual - parallel
Continuous Flow* (GPH)	205	205	205	205	365	380
1st Hour Rating* (GPH)	230	240	250	255	415	430
Peak Flow* (Gal/10 min)	60	70	80	85	110	115
Boiler Output (MBH)	155	155	155	155	270	280
Boiler Capacity (Gal)	1	1	1	1	2	2
Domestic Capacity (Gal)	34	44	54	64	64	64
Height (Inch)	44	54	64	72	72	72
Width (Inch)	22	22	22	22	22	22
Weight (Lbs)	96	110	124	164	164	164
* Performance based on 200°F boiler water and 90°F temperature rise						

ginius



contact

If you have any questions or comments regarding our products and services, we'd love to hear from you. Please contact us through one of the options below.

Corporate office

T 856-228-8881

E info.na@acv.com

W triangletube.com

