

**PFINHCJ**

# Import Standard No-Hub Couplings



## Product Features

- The PROFLO Import Standard No-Hub Coupling conforms to CISPI 310 and ASTM C1277
- Band and housing type 301 AISI stainless steel
- Screw type 305 AISI stainless steel 5/16" hex head
- Shield type 301 AISI stainless steel corrugated, thickness of 0.007"
- Gasket made from an elastomeric compound that meets ASTM C564



PFINHCJ

## Available Sizes

SIZE	SKU	INSTALL TORQUE INCH POUNDS	NO. OF CLAMPS PER COUPLING
1-1/2"	PFINHCJ	60	2
2"	PFINHCK	60	2
3"	PFINHCM	60	2
4"	PFINHCP	60	2
5"	PFINHCS	60	4
6"	PFINHCU	60	4
8"	PFINHCX	60	4
10"	PFINHC10	60	4

## Warranty and Codes

All parts for PROFLO products are warranted to the original consumer purchaser to be free from defects in material and workmanship for a period of one (1) year. This warranty is made to the original consumer purchaser and shall be effective from date of purchase as shown on purchaser's receipt.

PROFLO will replace, free of charge, during the warranty period, any part which proves defective in material and/or workmanship under normal installation, use and service. It is PROFLO's obligation under this warranty to the replacement of any part or parts which prove defective upon PROFLO's local PROFLO Dealer, transportation charges prepaid, with a copy of the purchase receipt. For the PROFLO Dealer nearest you, call 1-800-221-3379.

