




Z1201-N_3

EZCARRY® ADJUSTABLE HORIZONTAL HIGH PERFORMANCE SIPHON JET NO-HUB WATER CLOSET CARRIER SYSTEM

SPECIFICATION SHEET

TAG _____

Dimensional Data (inches and [mm]) are Subject to Manufacturing Tolerances and Change Without Notice



Product Number	Approx. Wt. lbs [kg]
Z1201-NL3	55 [25]
Z1201-NR3	

Note:

1. Z coupling, Min. 'P' Dim. Obtainable=2 [51].
ZQ coupling, Min. 'P' Dim. Obtainable=5 [127].
EZ-Set™ Coupling, Min. 'P' Dim. Obtainable=4-1/4 [108] or 2-1/16 [52] for 12 [305] NPT.
2. Feet bolted to floor using min. 1/2 [13] dia. anchors.
3. Rear anchor foot required for secure installation.

Z1201-NR3 Illustrated

ENGINEERING SPECIFICATION: ZURN Z1201-N_3

EZCarry® horizontal siphon jet water closet carrier system with high performance waterway and 3" [76mm] no-hub connections. System includes Dura-Coated cast iron main fitting with hydro-mechanically optimized sweep and extended 2" [51mm] vent, adjustable gasketed faceplate, floor mounted pre-fab slotted foot supports with top anchoring pre-fab support base, heavy-duty 1/2" [13mm] rear anchor tie down, fixture bolts, trim, stud protectors, bonded "Neo-Seal" gasket, and corrosion resistant, adjustable 3" [76mm] dia. X 6" [152mm] coupling with integral test cap designed to increase flow velocity and line carry. EZCarry® system complies with the requirements of ASME A112.6.1M up to a 500 lbs [227 kg] static load rating.

OPTIONS (Check/specify appropriate options)

- ____ Z1201-NL3 3 [76] No-Hub Left Hand Inlet with Flow to Right
____ Z1201-NR3 3 [76] No-Hub Right Hand Inlet with Flow to Left

PREFIXES

- ____ Z D.C.C.I. System with Zurn ZZ Adjustable Coupling*
____ ZQ D.C.C.I. System with NPT Faceplate, Non-Adjustable Coupling

SUFFIXES

- | | | | |
|----------|--|-------------|---|
| ____ -A | Auxiliary Support Assembly
(For 'P' Dim. Greater than 18 [457]) | ____ -F | Floor Mounted, Back Outlet Fixture Support |
| ____ -CC | Corrosion Resistant Cast Iron Coupling
(2-1/4 [57] to 12 [305]) | ____ -G | Galvanized Cast Iron |
| ____ -CE | EZ-Set™ Coupling (NPSM 6 [152], 12 [305] or custom)
(NPT 12 [305] or custom) | ____ -M | Auxiliary Foot Support
(for 'P' Dim. 7 thru 18 [178 thru 457]) |
| ____ -CL | Custom Length Standard Coupling with Integral Test Cap
(Specify Length 4, 8, 10, 12 [102, 203, 254, 305]) | ____ -RYK17 | One Piece Unistrut Pre-Fab Foot |
| ____ -CS | 2-1/4 [57] Polymer Coupling with Integral Test Cap | ____ -VP | Vandal-Proof Trim |
| | | ____ -45 | Finishing Frame for Siphon Jet System |
| | | ____ -50 | Flush Valve Supply Support for Water Closets |

* Regularly furnished unless otherwise specified.