
American Standard

Style That Works Better

## HAMPTON TWO-HANDLE BOTTOM-MOUNT KITCHEN FAUCET WITH BRASS GOOSENECK SPOUT



## **GENERAL DESCRIPTION:**

Durable brass construction. 1/4 turn washerless ceramic disc valve cartridges - reversible for use with either lever or cross handles. Brass 22mm (7/8") diameter swivel spout. One -half inch male inlet shanks with brass coupling nuts. 2.2 gpm/8.3 L/min. maximum flow rate. Color-matched hand spray. Cap provided for less spray applications.

### **PRODUCT FEATURES:**

**Ceramic Disc Valve Cartridges:** Assures a lifetime of drip-free performance.

**Brass Construction and Cast Brass Waterway:** Durable - Excellent in high use applications. Ideal for prolonged contact with water.

Larger Spout: Increased spout height, reach and diameter.

**Lead Free:** Faucet contains  $\leq$  0.25% total lead content by weighted average.

**Choice of Finishes:** Available in a wide range of durable finishes.

#### SUGGESTED SPECIFICATION:

Two handle bottom-mount kitchen faucet shall feature brass construction with all brass inlet shanks and coupling nuts. Brass swivel spout. Shall also feature 1/4 turn washerless ceramic disc valve cartridges that are reversible for use with cross or lever handles. Fitting shall be American Standard Model # 4751.\_\_\_\_\_.




Style That Works Better

## HAMPTON TWO-HANDLE BOTTOM-MOUNT KITCHEN FAUCET WITH BRASS GOOSENECK SPOUT

# **CODES AND STANDARDS**

These products meet or exceed the following codes and standards:

ASME A112.18.1 CSA B 125 NSF 61/Section 9 & Annex G



			Finish Options		
	Product		Polished Chrome	PVD Polished Brass	PVD Satin Nickel
	Number	Description	002	099	295
£	4751.712	Kitchen faucet. Color-matched Handspray. Porcelain lever handles.			
£	4751.732	Kitchen faucet. Color-matched Handspray. Metal lever handles.			

Meets the American Disabilities Act Guidelines and **ANSI A117.1** Requirements for the physically challenged.