

Joelson Collection

Joelson 1 Light LED Wall Sconce NI

45921NIL16 (Brushed Nickel)

Project Name: \_\_\_\_\_

Location: \_\_\_\_\_

Type: \_\_\_\_\_

Qty: \_\_\_\_\_

Comments: \_\_\_\_\_



Dimensions

Height	18.25"
Width	5.00"

Ordering Information

Product ID	45921NIL16
Finish	Brushed Nickel
Available Finishes	NI, NI, OZ, OZ
Collection	Joelson Collection

Dimensions

Extension	5.25"
Height from center of Wall opening	9.00"
Base Backplate	5.00 DIA
Weight	1.78 LBS

Photometrics

Kelvin Temperature	3000K
Color Rendering Index	80

Specifications

Material	Steel
Glass Description	Satin Etched Cased Opal

Electrical

Dimmable	Yes
Voltage	120V

Qualifications

Safety Rated	Damp
Energy Star	Yes
Warranty	<a href="http://www.kichler.com/warranty">www.kichler.com/warranty</a>

Installation

Install Glass Up or Down	Yes
--------------------------	-----

Primary Lamping

Light Source	LED
Lamp Included	Included
Light Source Equivalent	60(1) Incandescent
Number of Lights/LEDs	1
Initial Lumens	800
Socket Wire	150
Socket Type	Medium
Lamp Type	A19
Dimming	Yes

Joelson Collection  
Joelson 1 Light LED Wall Sconce NI  
45921NIL16 (Brushed Nickel)

Project Name: \_\_\_\_\_  
Location: \_\_\_\_\_  
Type: \_\_\_\_\_  
Qty: \_\_\_\_\_  
Comments: \_\_\_\_\_

Alternate Lamps

Lamp Included	Bulb Listing	Light Source	Max Wattage/Range	Bulb Product ID	Dimming
No	Alternate	INCA	100W		