



Aria Outdoor Mini Flush ARMF Series

Features

This product offers contemporary and clean styling in an outdoor wet location flush mount fixture that is fully gasketed. Fixture has a 7" diameter, meets ADA for wall mount applications, can be used under canopies or as a shower light. The aluminum die-cast housing has a threaded hand blown white glass diffuser screws in place for easy re-lamping. Fixture mounts to standard junction box (not included).

Construction

Housing is die-cast of .090" thick aluminum. Standard mounting holes and hardware are included. Power supply connections must be made inside a junction box (not included) or inside the housing.

Finish

All metal parts are plated satin nickel or applied oil-rubbed bronze. Both finishes include a clear topcoat.

Diffuser

Diffuser is .120" thick hand-blown frosted glass in two color options: white with the satin nickel finish and tea stained with the bronze finish. Diffuser is threaded and screws into gasketed housing.

Electrical

This unit is wired with UL listed electronic normal power factor instant start ballast for 120V/60 Hz AC operation. Minimum starting temperature is 0 F.

Lamping

For use with 1/13 watt flat spiral compact fluorescent 2700K 4 pin lamp included.

Certification

All fixtures are cULus listed for wet locations.

Specifications and dimensions
subject to change without notice.

Ordering Information:

Satin Nickel	Oil-Rubbed Bronze	Qty.	Lamp	DIA.	H
ARMF1F13SNECT	ARMF1F13RBECT	1	13W CFQ 4-Pin	7"	3-5/8"

LOCATION		DATE
PREPARED BY		QUANTITY
COMMENTS		FIXTURE TYPE
CATALOG NUMBER		

