


The SHF-Series style temperature controls have a bi-metal disc that senses the temperature and quickly separates the contacts. This results in long life characteristics at loads up to 25 amps at 240 VAC. SHF-Series switches are single pole single throw 60T12 style (3/4") with auto-reset. These switches are designed to close on temperature rise. The surface mounting configuration positions the disc against the mounting surface to sense the actual surface temperature. Each switch comes with an adapter flange plate. For air-stream installation, simply attach the SHF control with the bi-metal protruding through the mounting surface. For surface installation, insert the two spacers between the screw holes in the flange, and the heating surface. Install the original screws and tighten securely.



Contact Arrangement	FLA	LRA	Pilot Duty VA	Resistive Amps	Voltage AC
1 & 3 SPST	10	60	125	25	120
1 & 3 SPST	5	30	125	25	240

