

Dishwasher

FGID2479SF



Signature Features



A Complete Clean

Clean dishes in one cycle with OrbitClean® Wash System, which uses four times more water coverage¹ for a complete clean.



Best 30-Minute Clean

Don't wait when dishes can be cleaned with the best 30-Minute Quick Clean3.



Remarkable Dry

Dishes come out remarkably dry every time with EvenDry™2.



Easy Access

Serving utensils and tools are mealtime-ready with our Store-More™ removable third rack, which offers easy loading and unloading access.

24" Built-In

Product Dimensions

33-3/4"-35-3/4" Height (Adjustable) Width 24" Depth (Including Door) 24-1/4"

More Easy-To-Use Features

Automatically Adjusts Cycles

DishSense™ Technology automatically adjusts the cycle time based on the level of clean that your dishes need for an efficient clean.

Smudge-Proof™ Stainless Steel

Resists fingerprints and cleans easily.

Clean Dishes of All Sizes

Loading your dishwasher is no longer a puzzle with our SpaceWise® Adjustable Rack, which adjusts to fit oversized dishes and kitchen tools of all shapes and sizes.

Ready-to-Use Dish Alert

Know when your dishes are clean with LED Floor Beam Indicator, which beams a green light alerting you that your dishes are mealtime-ready.

Stay-In-Place Door

The door stays put at whatever angle you open it for easy loading and unloading.

24-Hour Delay Start

Set your dishwasher in advance to run on your schedule. It can be set to run 1-24 hours in advance.

Cleans 14 Place Settings

Clean up to 14 place settings in one cycle.

Efficient Water Usage

Cleans a full load of dishes using 15% less water4.

ENERGY STAR® NSF® International Certification





Available in:




Stainless

- ¹Than a traditional spray arm.
- ²When used with rinse aid.
- ³Tested against competing models with comparable quick cycle times according to ANSI/AHAM DW-1-2010 with only 6 place settings.
- ⁴Over a year when using normal cycle in our stainless tub compared to our plastic tub.

FRIGIDAIRE GALLERY.

Fully-Integrated Express-Select®
Yes
Yes/Yes
Stainless Steel/Tall Tuk
Direct Feed
OrbitClean®
5/5
Yes
Yes
SilentDesign™
S. Steel/Removable
40
49
EvenDry™
8
Yes
Yes
Yes
No/Yes
LED
Yes / Yes
Yes
Yes
1-24 Hour
Deluxe
Nylon TufRacks™
Nyion funtacks
Yes
Yes
2/2
-/-
Yes
3-Piece Split
2 Full Rows
2
Yes
V
Yes
Yes
Left Bottom Front
4.0 - 8.0
20 - 120
Yes
Yes
Right Bottom Front
Right Bottom Front 120V/60Hz/15A






NOTE: For planning purposes only. Always consult local and national electric and plumbing codes. Refer to Product Installation Guide for detailed installation instructions on the web at frigidaire.com.


Product Dimensions	
A - Height (Adjustable)	33-3/4" - 35-3/4"
B-Width	23-3/4"
C-Depth (Including Door)	24-1/4"
D-Depth (To Tub Flange)	22-1/2"
Depth with Door Open 90°	50-1/4"

¹For use on adequately wired 120V, dedicated circuit having 2-wire service with a separate ground wire. Appliance must be grounded for safe operation.

Cutout Dimensions	
Height (Min.)	34"
Height (Max.)	35-3/4"
Width (Min.)	24"
Depth (Min.)	24"

Accessories information available on the web at **frigidaire.com**





Dishwasher Specifications

- Product Shipping Weight (approx.) 91 Lbs.
- Voltage Rating 120V/60 Hz/15 Amps (maximum 20 Amps if connected with disposer)
- Connected Load (kW Rating) @ 120 Volts = 1.44 kW (For use on adequately wired 120V, dedicated circuit having 2-wire service with a separate ground wire. Appliance must be grounded for safe operation.)
- Amps @ 120V = 15 Amps
- Always consult local and national electric & plumbing codes.
 Meets requirements of ASSE 1006 integral air gap on supply.
- Water Pressure Hot water line to dishwasher must provide between 20 and 120 pounds per square inch (psi) with at least 120°F hot water temperature.
- Make sure location has correct drain, water and electrical outlets to make connections—MUST be confined to shaded areas.
- Electrical and water supplies should enter cabinet opening on floor, or through back or side walls, as shown in shaded areas.
- Keep back free of drain, water & electrical supply.
- Connections preferably located toward left side of dishwasher.
 Do not cross drain, water or electrical lines in front of motor, blower or frame.

- If connecting drain hose to sink trap, local code may require installation of Air Gap Kit (not included).
- Leveling legs supplied to adjust height. (Note: Height only adjustable to 35-3/4" max. when installed in 35-3/4" max. standard cabinetry cutout. 5/16" min. clearance required from top of unit to underside of countertop. Dimensions do NOT include insulation — insulation blanket may be compressed during installation.)
- When installing adjacent to wall, cabinet or other obstruction that extends beyond front edge of unit, allow 2" minimum clearance between opened door and obstruction.
- Floor should be flat and free of obstructions with carpet removed to provide motor clearance.
- When installing at end of cabinet line, sides and back must be fully enclosed.
- Do not install unit under a cooktop, damage will occur.
- Recommended to seal cabinets, enclosing all sides of dishwasher, including underside of countertop, with oil-based paint or moistureproof polyurethane to prevent possible steam/moisture damage.

Note: For planning purposes only. Refer to Product Installation Guide on the web at frigidaire.com for detailed instructions.

