
## **Press-On Collars**



# **Product Data Sheet**





### Description

Elgen's Press-On Collar is used for Low & Medium Pressure applications.

#### **Standard Construction**

Manufactured using 24 GA ASTM A-653 G60 material

1" Flange

1/8" x 1" Polyethylene "High Density" Gasket

A (in)	B (in)	C (in)	D (in)
4	6	6	3
5	7	6	3
6	8	6	3
7	9	6	3
8	10	6	3
9	11	6	3
10	12	6	3
12	14	6	3
14	16	6	3
16	18	6	3

#### **Features**

Meets SMACNA requirements - 2005 3rd Edition Section 4.8 Figure 4-6 Made from one piece of metal Welded Seam for added strength and low leakage Pressure rating +40" Water gauge Gasket - 1/8" x 1" Two Sided Neoprene Gasket Union Made Yellow Label

### **Optional Construction**

All Volume Dampers for air control Elgen Super Standoff Insulation Guard Scoop Remote Cable Operated Controls (internal mounted or external mounted)

30 GA Galvanized G90 Galvanized Stainless Steel 304 Stainless Steel 316 Aluminum PCD Galvanneal (Paint Grip) Agion (Antimicrobial Coating)

# Packaging

Size (in)	Tray Qty	Skid Qty	Weight per Skid (lbs)
4	MTO	MTO	N/A
5	MTO	MTO	N/A
6	9	300	310
7	MTO	MTO	N/A
8	9	200	280
9	MTO	MTO	N/A
10	9	120	210
12	9	90	200
14	9	90	220
16	9	90	180

#### Guarantee

All Elgen products are guaranteed by Elgen Manufacturing against defective material.

Elgen Manufacturing

10 Railroad Ave, Closter NJ 07624
Tel: 800.503.9805 :: Fax: 201.964.9030
info@elgenmfg.com :: www.elgenmfg.com