
FL FLEXIBLE INSULATED DUCT SUBMITTAL DATA

better AIRFLOW by DESIGNTM

FL FLEXIBLE INSULATED DUCT W/BLACK POLYETHYLENE COVER

UL-181 Class 1 Air Duct, wrapped with R4.2 insulation and black polyethylene cover. Suitable for use with various types of ventilation, heating and cooling systems.



FEATURES & BENEFITS

- Available in 4" to 12" diameter
- Flexible galvanized steel wire helix
- · Polyester film with bonding agent
- Maximum Flame Spread Index not over: 25
- Maximum Smoke Developed Index not over: 50

PERFORMANCE DATA

- Maximum air velocity 5000 fpm
- Maximum rated pressures:
 - Positive: 10 in. wg
 - Negative: 0.5 in. wg
- Operating temperature range: 0 to 265 F (-18 to 130 C) intermittent

PROJECT		ARCHITECT	ARCHITECT	
DATE		ENGINEER	ENGINEER	
SUBMITTED BY		CONTRACTOR	CONTRACTOR	
SPECIFICATION				
MODEL NO.	LENGTH (FT)	QTY	OPTIONAL EQUIPMENT	