
## Conical



# **Product Data Sheet**





## Description

Elgen's Conical is used for Low Pressure Applications.

#### **Standard Construction**

Collar- Formed using 24 GA ASTM A-653

G60 material

Body- Formed using 24 GA ASTM A-653

G60 material

1/8" x 1" Two Sided Neoprene Gasket

A (in)	B (in)	C (in)	D (in)
4	8	9.75	3
5	9	9.75	3
6	10	9.75	3
7	11	9.75	3
8	12	9.75	3
9	13	9.75	3
10	14	9.75	3
12	16	9.75	3
14	18	10.5	3
16	20	10.5	3

#### **Features**

Welded Seams For Added Strength
Welded Seams Provide Low Leakage
Many Damper Hardware Options
Pressure Rating – Designed Per SMACNA 3rd Edition
2005 Section 4.8 4-6 Brand Connections
Union Made Yellow Label

### **Optional Construction**

All Volume Dampers for air control
20 GA Heavy Duty Damper Blade for 10" and larger
22 GA Heavy Duty Damper Blade for 6"- 8"
Insulation Guard
Elgen Super Standoff
Scoop
Remote Cable Operated Controls (internal mounted or external mounted)

G90 Galvanized Stainless Steel 304 Stainless Steel 316 Aluminum PCD Galvanneal (Paint Grip) Agion (Antimicrobial Coating)

## Packaging

Size (in)	Tray Qty	Skid Qty	Weight per Skid (lbs)
4	MTO	MTO	N/A
5	MTO	MTO	N/A
6	9	210	350
7	MTO	MTO	N/A
8	9	112	250
9	MTO	MTO	N/A
10	9	84	240
12	9	63	200
14	9	42	160
16	9	35	155

#### Guarantee

All Elgen products are guaranteed by Elgen Manufacturing against defective material.

Elgen Manufacturing

10 Railroad Ave, Closter NJ 07624 Tel: 800.503.9805 :: Fax: 201.964.9030 info@elgenmfg.com :: www.elgenmfg.com