




OPTIONAL PARTS FOR SPLIT & MULTI SPLIT

Optional Parts List


Type			Wall Mounted						Duct						Cassette			Floor	Floor/Ceiling		Ceiling
			Compact				Large		Slim		Medium static	High static		Compact		Large					
			ASYG 09/12 LTCA	ASYG 07/09/12/14 LUCA	ASYG 07/09/12/14 LMCA	ASYG 09/12 LLCA	ASYG 07/09/12 LJCA	ASYG 18LFCAL/24LFCC	ASYG30 LFCA	ARYG 07/09 LLTA/12/14 LLTB	ARYG18 LLTB	ARYG22/24/36/45 LMLA30/36LMLE	ARYG 45/54 LHTA	ARYG60 LHTA	ARYC72 LHTA ARYC90 LHTA	AUYG 07/09 LVLA 12/14/18 LVLB	AUYG 22/24 LVLA		AUYG 30/36 LRLE 36/45/54 LRLA		
Controllers	Wired Remote Controller		● UTY-RVNYM			● UTY-RVNYM			● UTY-RVNYM						● UTY-RVNYM			● UTY-RVNYM	● UTY-RVNYM		● UTY-RVNYM
	Wired Remote Controller		● UTY-RNNYM			● UTY-RNNYM			● UTY-RNNYM						● UTY-RNNYM			● UTY-RNNYM	● UTY-RNNYM		● UTY-RNNYM
	Simple Remote Controller		● UTY-RSNYM			● UTY-RSNYM			● UTY-RSNYM						● UTY-RSNYM			● UTY-RSNYM	● UTY-RSNYM		● UTY-RSNYM
	Central Remote Controller	 For 8 Room	● UTY-DMMYM			● UTY-DMMYM			● UTY-DMMYM						● UTY-DMMYM			● UTY-DMMYM	● UTY-DMMYM		
Others	IR Receiver Kit with Wireless Remote Controller	 For Duct For Cassette						● UTY-LRHYM								● UTY-LRHYA2					
	Communication Kit	 For Compact Wall Mounted	● UTY-TWBXF		● UTY-XCBXZ2		● UTY-XCBXZ1														
	External Connect Kit	 For Indoor Unit *Duct type is excluded.	● UTY-XWZXZ5				● UTY-XWZX								● UTY-XWZX		● UTY-XWZX	● UTY-XWZX		● UTY-XWZX	
	External Control Set	 For indoor unit (Duct type only) (Use to connect with various peripheral devices and air conditioner PC board).							● UTD-ECS5A						● UTD-ECS5A					● UTD-ECS5A	
	Remote Sensor Unit	 New amenity space can be offered by installing the Remote sensor.							● UTY-XSZX												
	Auto Louver Grille Kit								● UTD-GXSA		● UTD-GXSB										
	Long Life Filter										● UTD-LF25NA		● UTD-LF60KA								
	Flange										● UTD-RF204 UTD-SF04ST								● UTD-RF204		
	Drain Pump Unit										● UTZ-PX1NBA								● UTR-DPB24T		
	Wide Panel																● UTG-AGYA-W				
	Panel Spacer																● UTG-BGYA-W				
	Fresh Air Intake Kit	 For Compact Cassette For Cassette													● UTZ-VXAA		● UTZ-VXGA				
	Air Outlet Shutter Plate	 For Compact Cassette For Cassette													● UTR-YDZB		● UTR-YDZC				
	Insulation for High Humidity	 For Compact Cassette													● UTZ-KXGC		● UTZ-KXGA				
	Half Concealed Kit	 This kit is used to half conceal floor type indoor unit into the wall.																● UTZ-STA			
	Remote controller holder				● UTZ-RXLA																

Type		Single-phase			3-phase		
		Single Split		8 Rooms Multi	Single Split		Simultaneous Multi
		AOYG09LLC AOYG12LLC	AOYG45LETL AOYG54LETL	AOYG45LB78	AOYG38LATT / AOYG45LATT AOYG54LATT / AOYG60LATT	AOYA72LALT AOYA90LALT	AOYG38LATT / AOYG45LATT / AOYG54LATT
Others	External Connect Kit	 For Outdoor unit		●		●	
	External Connect Kit (For Base heater)	 For Outdoor unit		●		●	
	Protective net	Net A  Net B 	●				
Refrigerant piping parts	Separation Tube	 For 3-phase simultaneous multi For 8 Rooms Multi		●			●
	Branch Box	 For 8 Rooms Multi		●			●

Wired Remote Controller : UTY-RVNYM

Hi-grade individual control using various functions.

- 3.7-inch LCD backlight screen.
- Supporting various Energy Saving functions with simple operation.
- Multiple Language Support.
(English, German, French, Spanish, Russian, Portuguese, Italian, Greek, and Turkish)



Max.
controllable
16
Indoor units

High performance and compact size

- In addition to the individual control, various energy saving controls can be realized using only one remote controller.



Various energy saving function

Auto OFF Timer

- The indoor unit automatically is turned off when it reaches the preset operating time frame.
- The time frame of the "Auto off timer" can be flexibly scheduled.
- Can be set off time 30 ~ 240 minutes


Weekly Timer function

- Can be set up to 8 times per day (On/Off, mode, Temp)
- 2 pattern settings (i.e. Summer/Winter setting) are available.




User friendly view and Easy operation

- Icon display of effectual functions.
- Main functions in large icons: "Mode", "Set Temp", and "Fan".
- Easy to operate by Control guide display.
- Simple operation with easy 4-way navigation pad.




Set Temperature Auto Return

- The setting temperature automatically returns to the previously set temperature.
- The time range in which the set temperature can be changed is 30 to 120 minutes.



Set Temperature Upper and Lower Limit Setting

- The set temperature range can be set for each operation mode.
(Cooling / Heating / Auto)



Specifications

Model name	UTY-RVNYM
Power supply	DC 12V
Dimension (H × W × D) (mm)	120 × 120 × 21.3
Weight (g)	220

* DC12V is supplied by indoor unit.

OPTIONAL PARTS FOR SPLIT & MULTI SPLIT

Auto Louver Grille Kit : UTD-GXSA-W / UTD-GXSB-W / UTD-GXSC-W

Simple flat Auto Louver will provide comfort airflow and harmonize with luxury interior.



Flexible Control

• Operation with indoor unit


Auto Louver can be operated by synchronizing remote controller of indoor unit.

• UP and Down auto swing


- Auto airflow direction and auto swing
- 4 steps selectable

• Auto-closing louver

When operation of indoor unit is stopped, the louver will automatically close.



Dimensions



Unit: mm

Model Name	W1	W2	H1	H2	D1	D2
UTD-GXSA-W	683	645	180	148	9	84
UTD-GXSB-W	883	845				
UTD-GXSC-W	1,083	1,045				

Specifications

Model name			UTD-GXSA-W	UTD-GXSB-W	UTD-GXSC-W
Applicable Indoor Unit			ARYG07/09LLTA ARYG12/14LLTB ARXD04/07/09/12/14GALH (For VRF)	ARYG18LLTB ARXD18GALH (For VRF)	ARXD24GALH (For VRF)
Power Supply			Connecting with Control box of indoor unit		
Fixing of Auto Louver Grille			Screw fixing to Flange or Square Duct		
Extension Square Duct Limit			1.0m (Max. duct length between indoor unit and Grille)		
Net Dimension (H x W x D)		mm (inch)	180x683x(84+9) [7-3/32x26-7/8x(3-5/16+11/32)]	180x883x(84+9) [7-3/32x34-3/4x(3-5/16+11/32)]	180x1083x(84+9) [7-3/32x42-5/8x(3-5/16+11/32)]
Weight	Net	kg (lb.)	2.0 (4.4)	2.5 (5.6)	3.0 (6.7)
	Gross	kg (lb.)	3.0 (6.7)	3.5 (7.8)	4.0 (8.9)
Color			White		
Louver Motor			Stepping Motor		
Accessories			Fitting Flame, etc.		
Operation range	Cooling	°C (°F)	18 to 32 (64 to 90)		
		% RH	80% or less		
	Heating	°C (°F)	16 to 30 (60 to 88)		

Refrigerant Piping Parts

Connection Units

Separation Tube

For 3-phase simultaneous multi




UTP-SX236A / UTP-SX254A

For 3-phase simultaneous multi



UTP-SX354A


For 8 Rooms Multi



UTP-SX248A

Branch Box

For 8 Rooms Multi



3 zones type

2 zones type

UTP-PY03A / UTP-PY02A

Controllers

For Individual & Centralized Control

Wired Remote Controller



UTY-RVNYM

Wired Remote Controller



UTY-RNNYM

Simple Remote Controller



UTY-RSNYM

Central Remote Controller

For 8 Rooms Multi



UTY-DMMYM

Panels

For Cassette type

Cassette Grille



UTG-UFYD-W



UTG-UGYA-W

OPTIONAL PARTS FOR SPLIT & MULTI SPLIT

Others

Communication System


External Connect Kit For Indoor Unit



UTY-XWZX


UTY-XWZXZ5

External Control Set For Indoor Unit



UTD-ECS5A

External Connect Kit For Outdoor unit



UTY-XWZXZ2

UTY-XWZXZ3

UTY-XWZXZ4

Function list

		For Indoor unit			For Outdoor unit		
		UTY-XWZX	UTY-XWZXZ5	UTD-ECS5A	UTY-XWZXZ2	UTY-XWZXZ3	UTY-XWZXZ4
Input	Control	●	●	●	—	—	—
	Peak cut	—	—	—	●	●	—
	Low noise	—	—	—	●	●	—
	Priority	—	—	—	—	●	—
	Emergency stop	—	—	—	—	●	—
Output	Operation status	●	●	●	●	●	—
	Error status	—	●	●*1	●	●	—
	Fresh air control	—	—	●	—	—	—
	Auxiliary heater	—	—	●*2	—	—	—
	Preparation	—	—	●*2	—	—	—
	Base heater	—	—	—	—	—	●

* 1 : Duct type does not have this function.

* 2 : Cassette and Ceiling type does not have this function.

For Duct type

Remote Sensor Unit

New amenity space can be offered by installing the Remote sensor.




UTY-XSZX

IR Receiver Kit For Duct type




UTY-LRHYM

Auto Louver Grille Kit



UTD-GXSA (For 07 / 09 / 12 / 14 type)
UTD-GXSB (For 18 type)

Long-Life Filter



UTD-LF60KA

UTD-LF25NA

Flange



(Round)
UTD-RF204

(Square)
UTD-SF045T

Drain Pump Unit



UTZ-PX1NBA

Feature summary

	Wall Mounted	Floor	Compact Cassette / Cassette	Floor/Ceiling	Ceiling	Slim Duct	Medium Static Pressure Duct	High Static Pressure Duct										
	ASYG07/09/12/14LTCA	ASYG07/09/12/14LCA	ASYG18/30LFCA, ASYG24LFCC	ASYG09/12LLCA	ASYG07/09/12LJCA	AUYG12/14/18VLB, AUYG24LVCA	AUYG30/36RLRLE, AUYG36/45/54RLA	ABYG18LVTB, ABYG24LVTA	ABYG30/36LRTE, ABYG36/45/54LRTA	ARYG24/36/45/MLA, ARYG30/36LMLE	ARYG12/14/18LLTB	ARYG45/54/60LHTA	ARYG72/90LHTA					
Comfortable function	Human sensor	●																
	Up / down swing flaps	●	●	●		●	●	●	●	●		○						
	Double swing automatic				●					●	●							
	Automatic air flow adjustment	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
	Auto restart	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
	Auto-changeover	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
	10°C heat operation	●	●	●	●		●	●	○	●	●	○	○	○	○	(60)		
	Connectable distributing duct							●				●						
	Connectable fresh air duct							○	●		●	○	●				○	
	Fresh air intake							○	○		○	○	○	○	○	○	○	○
Convenient function	Economy mode	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
	Powerful mode	●	●	●		●												
	Low Noise mode	●	●	●					○ (45/54) (36LRLA)		○ (45/54) (36LRTA)		○ (45) (36LMLA)	○	○			
	Sleep timer	●	●	●	●	●	●	●	○	●	●	○	○	○	○	(60)	○	
	Program timer	●	●	●	●	●	●	●	○	●	●	○	○	○	○	(60)	○	
Clean function	Weekly timer	●	●															
	Weekly + setback timer	○	○	○	○		○	○	○	●	○	○	●	●	●	●	●	●
	Filter sign	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
	Long-life ion deodorization filter	●	●	●	●		●	●										
	Apple-catechin filter	●	●	●	●		●	●										
	Washable panel			●	●	●	●	●										

○: Optional function