Spun Press-On Collar





Technical Data

- GSI Collars are designed and tested to surpass SMACNA Class 3 Leakage Standards.*
- Pre-sealed with gasket made of EPDM rubber and proprietary co-polymer
- Zero VOCs
- · Galvanized Steel (ASTM A653 and A924)
- Standard product is supplied in 26 GA, G-60 coating (ASTM A653 and ASTM A90)
- · Available in Specialty Metals**:
 - G-90 Galvanized Steel
 - Aluminum (ASTM B209 Alloy 3003 Temper H14)
 - 304 Stainless Steel (ASTM A480 2B Finish)
- Pressure Rating: Designed per SMACNA Third Edition 2005 Section 4.8 Figure 4-6 Branch Connections
- Dimensional Tolerance: ± 1/4"
- * Test performed on standard fittings without dampers
- ** 2 piece collar provided on Aluminum and Stainless Steel.











Low Leakage

Low Leakage w/Stand-Off


ossi w/Solid Windga 3/8'' Rod 3/8'

Windgate w/Solid

Product Availability

Size (Ød)*	Gauge Av	/ailability	Quantity			
Size (bu)	26 Ga.	24 Ga.	Carton	Skid		
4"	Yes	-	25	300 - 45x45		
5"	Yes	Yes	25	300 - 45x45		
6"	Yes	Yes	20	240 - 45x45		
7"	Yes	Yes	20	240 - 45x45		
8"	Yes	Yes	20	240 - 45x45		
9"	Yes	Yes	10	120 - 45x45		
10"	Yes	Yes	10	120 - 45x45		
12"	Yes	Yes	10	120 - 48x48		
14"	Yes	Yes	5	60 - 45x45		
16"	Yes	Yes	5	60 - 45x45		
18"	Yes	Yes	5	60 - 45x45		
20"	Yes	Yes	2	24 - 45x45		

Dampered fittings are available with 2" Stand-Off. See Damper Hardware options on pages 27-30.



- A. Collars now come standard with sealed joints! The riveted seam is sealed with the GreenSeam integral gasket. Unsealed fittings are available upon request.
- B. Non-dampered Collars are supplied with a 3/8" knock-out. Dampered Collars are supplied with 24GA. damper blades and GSI's proprietary low-leakage hardware. See Page 27.
- C. 7/8" flange for 4" and 5" collars. 1" flange for 6" and larger collars.

	Part Number Schematic									
	Example: 6POS15CR10GA26**D38 = Spun Press-on Collar for 10" Pipe in 26Ga. Galv. Steel, with a Solid Rod Damper and 1½" Stand-Off									
S Scoop (Opt.)	6 Collar Length	PO Press-On Start Collar	S2 Stand-Off S2 - 2" (Opt. on Dampers Only)	C End C - Crimped (Std.)	R Riveted	Collar Diameter (Ød)	GA Material GA-Galvanized (Std.) AL - Aluminum S4 - 304 S.S	26 Gauge GA - 28, 26, 24 AL - 32 S4 - 26	D Damper (Opt.)	C Windgate hardware 38 Rossi hardware (Opt. on Dampers Only) See Damper Hardware options on pages 27-30

^{**} Add 90 for G90 Galvanized Coating
Items in green denote other available features
Check with your sales representative for availability of any size, gauge, or specialty metal item not shown here.

Spun **Press-On Flex Collar**





Technical Data

- · GSI Collars are designed and tested to surpass SMACNA Class 3 Leakage Standards.*
- Pre-sealed with gasket made of EPDM rubber and proprietary co-polymer
- Zero VOCs
- · Galvanized Steel (ASTM A653 and A924)
- Standard product is supplied in 26 GA, G-60 coating (ASTM A653 and ASTM A90)
- Available in Specialty Metals**:
 - G-90 Galvanized Steel
 - Aluminum (ASTM B209 Alloy 3003 Temper H14)
 - 304 Stainless Steel (ASTM A480 2B Finish)
- Pressure Rating: Designed per SMACNA Third Edition 2005 Section 4.8 Figure 4-6 Branch Connections
- Dimensional Tolerance: ± 1/4"
- Test performed on standard fittings without dampers
- ** 2 piece collar provided on Aluminum and Stainless Steel.











Low Leakage

Low Leakage w/Stand-Off

3/8" Rod


Windgate w/Solid

Product Availability

Size	* Flex Collar	Gauge A	vailability	Quantity		
(Ød)	Size (Ød)	26 Ga.	24 Ga.	Carton	Skid	
4"	31/8"	Yes	-	25	300 - 45x45	
5"	47/8"	Yes	Yes	25	300 - 45x45	
6"	51/8"	Yes	Yes	20	240 - 45x45	
7"	67/8"	Yes	Yes 20		240 - 45x45	
8"	71/8"	Yes	Yes	20	240 - 45x45	
9"	87/8"	Yes	Yes	10	120 - 45x45	
10"	97/8"	Yes	Yes	10	120 - 45x45	
12"	111/8"	Yes	Yes	10	120 - 48x48	
14"	131/8"	Yes	Yes	5	60 - 45x45	
16"	15½"	Yes	Yes	5	60 - 45x45	
18"	171/8"	Yes	Yes	5	60 - 45x45	
20"	19¾"	Yes	Yes	2	24 - 45x45	

^{* -} Actual diameter is - 1/8" to allow for flex duct connection. Dampered fittings are available with 2" Stand-Off.

See Damper Hardware options on pages 27-30.



- A. Collars now come standard with sealed joints! The riveted seam is sealed with the GreenSeam integral gasket. Unsealed fittings are available upon request.
- B. Non-dampered Collars are supplied with a 3/8" knock-out. Dampered Collars are supplied with 24GA. damper blades and GSI's proprietary low-leakage hardware. See Page 27.
- C. 1/8" flange for 4" and 5" collars. 1" flange for 6" and larger collars.

	Part Number Schematic									
Example: 6POS15FC10GA26**D38 = Spun Press-on Flex Collar for 10" Pipe in 26Ga. Galv. Steel, with a Solid Rod Damper and 1½" Stand-Off										
S Scoop (Opt.)	6 Collar Length	PO Press-On Start Collar	S2 Stand-Off S2 - 2" (Opt. on Dampers Only)	F Flex (Smaller Diameter for Flex Duct)	C End C - Crimped (Std.)	Collar Diameter (Ød)	GA Material GA-Galvanized (Std.) AL - Aluminum S4 - 304 S.S	26 Gauge GA-28, 26, 24 AL - 32 S4 - 26	D Damper (Opt.)	C Windgate hardware 38 Rossi hardware (Opt. on Dampers Only) See Damper Hardware options on pages 27-30

Add 90 for G90 Galvanized Coating Items in green denote other available features Check with your sales representative for availability of any size, gauge, or specialty metal item not shown here.