Unico System®

Submittal Data

For: File Resubmit Approval Other

M2430R1 2.5-ton Return Air Plenum Module

Job Name:	Location:	
Date:	Tag #:	
Architect:	Engineer:	
Mechanical:	Distributor:	

Rep:

(Company)



Features

(Project Manager)

- Blank side and top allow for custom, multiple-return openings
- Centrally located filter
- Heavy-duty closed cell insulation (no exposed fiberglass insulation)
- · Filter access from both sides
- Standard Unico System 'latch' system

Matching Modules
M2430BL1-EC1/EC2
M2430CL1-B
M2430CL1-E
M2430CL1-C
M2430CL1-H

Indoor Unit Size

General Data:

17.5 x 25 x 14 in.	
(445 x 635 x 349 mm)	
154 in ² (0.10 m ²)	
14 in (356 mm)	
14 in x 25 in x 1 in	
(356 mm x 635 mm)	
850 CFM (400 L/s)	
350 FPM (1.78 m/s)	
0.04 in. wg (10 Pa)	

Optional Accessories

Hot water coil heating module (M2430CL1-H)

□ Modular Variable Speed Air Handler (*M2430BL1-EC**)

□ Secondary drain pan, 2 module (*UPC-20B*)

□ Secondary drain pan, 3 module (UPC-20C)

□ Return adapter (UPC-104-2430)

Notes:

1. Refer to installation manual for more information.

Model Number Key (available models):

2430	D	
2430	R	1
Nominal	Module	Revision
Capacity	Туре	
2430 =	R = Return	
24000 to 30000	Air Plenum	
Btu/hr		
	Capacity 2430 = 24000 to 30000	Capacity Type 2430 = R = Return 24000 to 30000 Air Plenum


M2430R1

Location:

Job Name: Date:


Tag #:

RETURN AIR PLENUM MODULE DIMENSIONS



* Contact Unico for dimensions of assembled modules.

Installation Clearances



Note – for continuous product improvement, Unico reserves the right to change specifications without notice.