


Jennifer

Classic sophistication in design, using elegant curves to contrast with the rectangular overall shape, contoured side walls, gently sloping backrest and molded armrests, the Jennifer will allow you to immerse yourself to a new comfort level.



Available Sizes:

72"L x 48"W x 261/2"D 90 Gallons

Acrylic Tub - construction features

Acrylic models finished in 1/8" thick layer of deep lustrous acrylic.

Extra thick reinforced fiberglass.

Pre-wired pump on pump platform (standard pump location only)

Integral E-Z Level platform facilitates installation.

Non-skid bottom.

PVC Systems – include:

8 Fully directional adjustable PVC jets

Anti-vortex safety suction.

Color matched system trim

HydrOzone ozone sanitation system

Rigid PVC piping

Self draining pump and system

Soft Touch electronic on/off control with 30-min. integral timer

2.25 HP Single Speed Pump

Cable waste & overflow

Hydro Systems - Options:

Available as Tub only, Thermal Air, Whirlpool or Combo

Microban Antibacterial Protection

Extra High Density Fiberglass

Waterfall Fill Spout (recirculating option available)

Custom jet and pump locations

Plated Metallic finish

Additional directional Jets

Swirling, Rotating, or Jumbo Jets

Micro Therapy Jet

Integral Waste & Overflow

1.5 HP Variable Speed Pump (digital temperature display optional)

Electronic low water protection

In-line Heater

Chromatherapy-LED Lighting System

Chromatherapy-LED Mini Spotlights

Mood Light

Grab Bars

Back Masseuse

Neck Masseuse Pillow

Hydro Fragrance

Hydro Fusion

Hydro Coat

Hydro Express quick ship

Approvals & Listings

Commonwealth of Massachusetts UPC & USPC - US & Canada













Jennifer



Must be set in Mortar Base



AS SHOWN: Whirlpool option w/ standard jets

ALSO AVAILABLE: Soaking Tub Only, Thermal Air, Combo




Pump motor




Jets

➡● Anti-vortex suction


Overflow location





Side View

Model	GC	AC	A	В	С	D	E	F	G	Н	-1	J	K	L	M	N	0	Jet	Pump	Wat.Cap.
7248	N/A		71¼"	47½"	26½"	42"	8"	22"	66"	31½"	25"	1"	3½"	4½"	19½"	13"	35½"	8	2.25	90 gal.
Amp	Volt	Bre	aker	Dedicated Service																
13.5	120	20	amp	GFCI Protected																



Island Drop-In										
Model	(L)ength	(W)idth	(H)eigth Finish							
7248	69¼"	45½"	23"							

Disclaimer: Certain options or altering the pump/blower location may cause the pump/blower to extend beyond the tub decking. For cutout dimensions wait for unit to arrive.

All specifications subject to change without notice.