KOHLER_®

Features


- ExoCrylicTM
- 8 color-matched Kohler hydro-massage jets
- Integral apron with removable access panel
- Pump with air switch and grounding-type plug-in cord
- Integral tile flange
- T-style heater
- Left or right drain
- Slotted overflow for maximum bathing depth
- Low threshold height
- Integral lumbar support
- 60" (1524 mm) x 30" (762 mm) x 19" (483 mm)

Codes/Standards Applicable

Specified model meets or exceeds the following:

- ADA
- ICC/ANSI A117.1
- CSA B45.5/IAPMO Z124
- CSA C22.2 No 218.2
- ASME A112.19.7/CSA B45.10
- UL 1795
- NMX-J-521





Colors/Finishes

- 0: White
- Other: Refer to Price Book for additional colors/finishes

Accessories

- CP: Polished Chrome
- Other: Refer to Price Book for additional colors/finishes

Specified Model

Model	Description	Co	Colors/Finishes			
K-1947-HLA	5' bath whirlpool with integral apron and heater, left drain	0	Other			
K-1947-HRA	5' bath whirlpool with integral apron and heater, right drain	0 🗆	□ Other			
		Required Accessories				
Required Acce	ssories					
Required Acce K-7271	ssories Clearflo slotted overflow brass bath drain OR	CP	□ Other			

Product Specification

The ExoCrylic bath whirlpool shall be 60" (1524 mm) in length, 30" (762 mm) in width, and 19" (483 mm) in height. Bath whirlpool shall feature 8 color-matched jets, and pump with air switch and grounding-type plug-in cord. Bath whirlpool shall have a T-style heater. Bath whirlpool shall have an integral apron with removable access panel and integral tile flange. Bath whirlpool shall have slotted overflow for maximum bathing depth, low threshold height, and integral lumbar support. Bath whirlpool shall be Kohler Model K-1947-_____-

Technical Information

Fixture*:				
Bathing well				
Basin area, bottom		1/8″ (1146 ı 11/16″ (500		
Basin area, top	52-1/8″ (1324 mm) x 22-1/16″ (560 mm)			
Weight	113 lbs (51.3 kg)			
To overflow				
Water depth	15-1/8" (384 mm)			
Capacity	57 gal (216.9 L)			
* Approximate measurements for comparison only.				
Pump:		V	Hz	А
1 append		100	60	7

1-speed		120	60	7
Heater:	kW	V	Hz	А
	1.5	120	60	12.5
	-			

Required Electrical Service

Two dedicated circuits required, each protected with Class A Ground-Fault Circuit-Interrupter (GFCI):

Pump/control	120 V, 15 A, 60 Hz
Heater	120 V, 15 A, 60 Hz

Installation Notes

Install this product according to the installation guide.


Pump is supplied with 24 $^{\prime\prime}$ (610 mm) grounding-type plug-in cord.

Floor support under this product must provide for a minimum of 49 lbs/square foot (240 kg/square meter) loading.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

Will comply with **ADA** when installed per Section 607 Bathtubs of the Act.

No change in measurements if connected with drain illustrated. (K-7272)



Product Diagram

