



PRODUCT DESCRIPTION

Match your mood with your lighting by switching between 3 color temperatures: 2700K, 3000K, and 4000K. All are 90+ CRI for accurate color rendering when compared to natural light. Set the mood when entertaining with a warmer light or brighten the area for a clearer task area. Also, the 3K has a patented gimbal designed to allow light to be directed as well as a patented LED strip for even light distribution to eliminate hot spots.

MEASUREMENTS

DIMENSION : 30." L x 3.5" W x 1." H
HANGING WEIGHT : 2.84 lb

LAMPING

INPUT VOLTAGE : 120V
LUMENS : 1,000 Rated (900 Del.)
BULB : 1 x 16W (INTEGRATED), 16W Total
DIMMABLE : Dimmable
CRI : 90+ CRI
COLOR_TEMP : 2700/3000/4000K

FINISHES OPTION

White WT



MATERIAL

Aluminum

RATINGS

Dry Location
Energy Star
CA Title 24
Dimmable



ADDITIONAL

INSTALL UP/DOWN:
RATED LIFE 40000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
4200 SHIRLEY DR. | ATLANTA, GA 30336

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com