

Irvine[™] Comfort Height[®]

elongated toilet bowl with skirted trapway K-20485

Features

- Elongated bowl offers added room and comfort.
- Skirted trapway simplifies cleaning.
- Revolution 360[®] swirl flushing technology generates a forceful swirling motion to keep the bowl cleaner, longer.
- Comfort Height[®] feature offers chair-height seating that makes sitting down and standing up easier for most adults.
- 2-1/8" fully glazed trapway.
- CleanCoat[™] technology inhibits the growth of water scale and mineral stains for improved ease of cleaning.
- Combines with the K-20205/-RA or K-90098 tank to create a complete K-20450/-RA Irvine[™] or K-90097 Irvine[™] ContinuousClean toilet.

Installation

- Standard 12" rough-in.
- 10" and 14" rough-in kits are also available.
- Seat not included.
- Patented ReadyLock[™] installation system is a simple solution for skirted toilets that saves time, hassle and eliminates the need to drill into the floor for a standard 12" rough-in.

Recommended Products/Accessories

K-20203 toilet tank K-20203-RA toilet tank K-90098

Included Components

Additional Components: ReadyLock™ installation system



Codes/Standards

ASME A112.19.2/CSA B45.1

KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description

- 0 White 96 Biscuit 47 Almond NY Dune
 - 95 Ice™ Grey
 - G9 Sandbar
 - 7 Black Black™





Irvine[™] Comfort Height[®]

elongated toilet bowl with skirted trapway K-20485

No image available. This product is a component and not intended to be a standalone installation.

Technical Information

All product dimensions are nominal.	
Toilet type:	Two-piece, Floor-mount
Waste Outlet:	Floor
Bowl shape:	Elongated
Water Consumption	
Full:	1.28 gpf (4.8 lpf)
Water surface size:	9-3/8" x 7-3/16" (238 mm x 183 mm)
Rough-in:	12" (305 mm)

Fixture Supply Requirements

Min static pressure:15 psi (103.4 kPa)Max static pressure:80 psi (551.6 kPa)

Notes

Install this product according to the installation instructions.

