

Type

Project


Catalog No.

Lamp/Wattage

## NL-3310

### Adjustable Stepped Baffle with Metal Ring

#### TRIM DIMENSIONS



Trim OD: 3-5/8"  
Aperture: 2-1/2"  
Height: 1-5/8"

#### FEATURES

##### Trim

Precision spun 0.040 aluminum baffle with deep grooves to reduce aperture glare. Non-reflective painted finishes. Gimbal ring allows lamp to be mounted on top of the trim and adjustable up to 35°. Separate trim ring available in metal, may also be used with custom combination of ring finishes.

##### Mounting

Trim includes three trim clips that securely mount trim in housing.

##### Compatible Housings

Compatible with Line Voltage and Low Voltage housings.  
See individual specification sheets for more information.

##### Lamp

###### Line Voltage

50W 120V MR16 GU10 Max. (NH-350AT; NHIC-350AT; NHR-354AT)

###### Low Voltage

**IMPORTANT: DO NOT USE GLASS LENS (PROVIDED) WHEN ALREADY USING LAMP WITH GLASS COVER**  
20W-50W 12V MR16 (NL-301 Series; NLIC-301 Series; NLR-304 Series)

##### Labels and Listings

cULus Listed for Damp Location when used with compatible housing.

#### Compatible Housings

##### LINE VOLTAGE

Item Number	Installation Type	Lamp	Dimensions
<b>NH-350AT</b>	Non-IC Air-Tight New Const.	50W MR16	W: 6-3/8" L: 16" H: 5-5/8"
<b>NHIC-350AT</b>	IC Air-Tight New Construction	50W MR16	W: 6-3/8" L: 16" H: 8-1/8"
<b>NHR-354AT</b>	Non-IC Air-Tight Remodel	50W MR16	W: 4-1/4" L: 11-1/4" H: 5-5/8"

##### LOW VOLTAGE

<b>NL-301QAT/20</b>	Non-IC AT New Const., Mag.	20W MR16	W: 6-3/8" L: 16" H: 5-5/8"
<b>NL-301QAT/37</b>	Non-IC AT New Const., Mag.	37W MR16	W: 6-3/8" L: 16" H: 5-5/8"
<b>NL-301QAT</b>	Non-IC AT New Const., Mag.	50W MR16	W: 6-3/8" L: 16" H: 5-5/8"
<b>NL-301AT/1EL</b>	Non-IC AT New Const., Elec.	50W MR16	W: 6-3/8" L: 16" H: 5-5/8"
<b>NLIC-301QAT/20</b>	IC Air-Tight New Const., Mag.	20W MR16	W: 6-3/8" L: 16" H: 8-1/8"
<b>NLIC-301QAT/37</b>	IC Air-Tight New Const., Mag.	37W MR16	W: 6-3/8" L: 16" H: 8-1/8"
<b>NLIC-301QAT</b>	IC Air-Tight New Const., Mag.	50W MR16	W: 6-3/8" L: 16" H: 8-1/8"
<b>NLIC-301AT/1EL</b>	IC Air-Tight New Const., Elec.	50W MR16	W: 6-3/8" L: 16" H: 8-1/8"
<b>NLR-304QAT/20</b>	Non-IC Air-Tight Remodel, Mag.	20W MR16	W: 4-1/4" L: 11-1/4" H: 5-5/8"
<b>NLR-304QAT/37</b>	Non-IC Air-Tight Remodel, Mag.	37W MR16	W: 4-1/4" L: 11-1/4" H: 5-5/8"
<b>NLR-304QAT</b>	Non-IC Air-Tight Remodel, Mag.	50W MR16	W: 4-1/4" L: 11-1/4" H: 5-5/8"
<b>NLR-304AT/1EL</b>	Non-IC Air-Tight Remodel, Elec.	50W MR16	W: 4-1/4" L: 11-1/4" H: 5-5/8"

#### Adjustable Stepped Baffle with Metal Ring

- NL-3310BB:** Black Adjustable Stepped Baffle with Black Metal Ring
- NL-3310BC:** Black Adjustable Stepped Baffle with Chrome Metal Ring
- NL-3310BG:** Black Adjustable Stepped Baffle with Gold Metal Ring
- NL-3310BW:** Black Adjustable Stepped Baffle with White Metal Ring
- NL-3310BZBZ:** Bronze Adjustable Stepped Baffle with Bronze Metal Ring
- NL-3310COCO:** Copper Adjustable Stepped Baffle with Copper Metal Ring
- NL-3310NN:** Natural Metal Adjustable Stepped Baffle with Natural Metal Ring
- NL-3310WB:** White Adjustable Stepped Baffle with Black Metal Ring
- NL-3310WBZ:** White Adjustable Stepped Baffle with Bronze Metal Ring
- NL-3310WC:** White Adjustable Stepped Baffle with Chrome Metal Ring
- NL-3310WG:** White Adjustable Stepped Baffle with Gold Metal Ring
- NL-3310WW:** White Adjustable Stepped Baffle with White Metal Ring