T24IW800SP
24-INCH FLUSH CUSTOM WINE PRESERVATION COLUMN
FREEDOM® COLLECTION

Thermador
REAL INNOVATIONS FOR REAL COOKS®



FEATURES & BENEFITS

- Freedom® Hinge enables true flush design
- Full-height door–true cabinet integration without exposed venting grille
- All-LED theater lighting
- Accepts custom or stainless steel panels
- Reversible door swing

TEMPERATURE RANGES	
Upper Zone	41°F (5°C) to 64°F (18°C)
Lower Zone	41°F (5°C) to 64°F (18°C)

ACCESSORIES (OPTIONAL)

Stainless Steel Panel Options:
TFL24IW800 - 24-Inch Flat Stainless Steel Panel
TCH24IW800 - 24-Inch Chiseled Stainless Steel Panel

Handle Options:
PR36HNDL10 - 36-Inch Professional Handle
MS36HNDL10 - 36-Inch Masterpiece® Handle

FRAMEKIT10 - Freedom® Frame Kit


HEATRKIT10 - Freedom® Heater Kit

GENERAL PROPERTIES	
Panel Ready	Yes
Reversible Door Swing	Yes
Carbon Air Filter	Yes
Lighting	All-LED Theater Lighting
Number of Shelves	11
Shelf Material	Dark Exotic Hardwood
Full Extension Shelves at 90° Door Opening Angle	Yes
Presenter Shelf	Yes
Bottles Per Shelf	7
Portable Aluminum Wine Presenter	Yes
Type Of Glass Door	Tempered and UV-protective
Number Of Temperature Zones	2
Door Open Alarm	Yes
Special Modes	Sabbath, Economy, Vacation
CAPACITY	
Bottle Capacity (750 ml)	80
TECHNICAL DETAILS	
Watts (W)	102 W
Current (A)	15 A
Volts (V)	120 V
Frequency (Hz)	60 Hz
Power Cord Length (in.)	78 3/4"
Plug Type	120V-3 Prong
DIMENSIONS & WEIGHT	
Appliance Dimensions (H x W x D) (in.)	84" x 23 3/4" x 24"
Required Cutout Size (H x W x D) (in.)	84" x 24" x 24 3/4"
Net Weight (lbs)	317 lbs
EFFICIENCY	
Annual Energy Consumption	421 kWh
WARRANTY	
Limited, Entire Appliance, Parts and Labor on Any Part of the Refrigerator that Fails Because of a Manufacturing Defect	2 Year
Limited Warranty for Sealed Refrigeration System*; Parts And Labor	3rd to 6th Year
Limited Warranty for Sealed Refrigeration System*; Parts Only	7th to 12th Year

* Sealed refrigeration system includes compressor, evaporator, condenser, dryer / strainer and connection tubing


T24IW800SP
24-INCH FLUSH CUSTOM WINE PRESERVATION COLUMN
FREEDOM® COLLECTION

CUTOUT DIMENSIONS




A: Area for installation of power connection.
B: Niche depth depends on kitchen design. For a flush installation, the depth needs to be at least 24 inches plus the thickness of the door panel. Panel dimensions based on a standard 1/8 inch reveal and 4 inch toe kick. Custom panel dimensions may vary depending on kitchen reveals and toe kick. Stainless steel models contain a panel-ready base unit, ready-to-install Stainless steel door(s) with a right or left door swing and handle(s).

TOP VIEW CLEARANCE




** Door handle must be added to this dimension

* Depends on the thickness of the furniture door. 3/4" (19 mm) is relevant for the stainless steel door. (special Accessory).



T24IW800SP
24-INCH FLUSH CUSTOM WINE PRESERVATION COLUMN
FREEDOM® COLLECTION

PANEL DIMENSIONS



†Excludes thickness of door panel. If standard panel with 3/4" thickness is mounted, total depth is 24 3/4".

These warranties give you specific legal rights and you may have other rights that vary from state to state. Full warranty and limited warranty from date of installation. For complete warranty details, refer to your Use & Care manual, or ask your dealer.

Specifications are for planning purposes only. Refer to installation instructions and consult your countertop supplier prior to making counter opening. Consult with a heating and ventilation engineer for your specific ventilation requirements. For the most detailed information, refer to installation instructions accompanying product or write to Thermador indicating the model number. Specifications are correct at time of printing. Thermador reserves the right to change product specifications or design without notice. Some models are certified for use in Canada. Thermador is not responsible for products that are transported from the U.S. for use in Canada.

1 800 735 4328 | USA THERMADOR.COM | CANADA THERMADOR.CA | ©2015 BSH HOME APPLIANCES CORPORATION. ALL RIGHTS RESERVED.