

CG152TF/S



FEATURES

Integrated design, slim 15" width pairs well with other Wolf modules

Dual-stacked burners go from 12,000 Btu down to a mere breath of flame

Lower tier of dual-stacked burner lets you simmer and melt

Spark ignition system re-ignites if flame goes out

Easy-clean seamless burner pan

Stylish stainless control knobs capped in black

Continuous cast-iron grate for easy movement of pots and pans

Rigorously tested in our U.S. manufacturing facilities for decades of use

Exceptional 24/7 support from our Customer Care team in Madison

ACCESSORIES

Filler Strip

Filler Strip for Downdraft

Filler strip for installation with another module

Filler strip for installation with another cooktop or module and downdraft

Accessories available through an authorized Sub-Zero dealer.
For local dealer information, visit subzero-wolf.com/locator.



COOKTOP SPECIFICATIONS


- 1 - 9,200 Btu Burner
- 1 - 12,000 Btu Burner




PRODUCT SPECIFICATIONS

Model	CG152TF/S
Dimensions	15"W x 4"H x 21"D
Weight	30 lbs
Electrical Supply	120 VAC, 60 Hz
Electrical Service	15 amp dedicated circuit
Gas Supply	3/4" ID line
Gas Inlet	1/2" NPT female

ELECTRICAL




GAS




NOTE: Dimensions in parenthesis are in millimeters unless otherwise specified


DIMENSIONS




STANDARD INSTALLATION



COUNTERTOP CUT-OUT



SIDE VIEW



FRONT VIEW

NOTE: Shaded area above countertop indicates minimum clearance to combustible surfaces, combustible materials cannot be located within this area.