wolfappliance.com

### **FEATURES**

- Heavy-duty, stainless steel seamless construction with black glass front.
- Internal, in-line or remote blower required (sold separately).
- Telescopic chimney.
- Black glass touch control panel with display.
- Three-speed blower with boost to temporarily increase airflow.
- · LED lighting with high and low settings.
- Delay-off feature to automatically turn unit off.
- Filter clean indicator.
- Dishwasher-safe filters.
- Transition with backdraft damper.





Model VW30B

## **BLOWER OPTIONS**

MODEL VW30B	CFM
Internal	300*, 600
In-line	600
Remote	600

\*For make-up air restricted applications.

Cooktop hoods are recommended for use with Wolf induction, electric and gas cooktops and integrated modules. For Wolf ranges and rangetops, a pro ventilation hood is recommended.

# **ACCESSORIES**

- Internal, in-line and remote blowers (refer to chart).
- Remote control.
- Chimney extension.
- 30" high stainless steel wall shield.
- Recirculating kit and filter for nonducted applications.
- Make-up air damper.

Accessories available through an authorized Wolf dealer. For local dealer information, visit the find a showroom section of our website, wolfappliance.com.


wolfappliance.com

SPECIFICATIONS	
PRODUCT Dimensions Overall Height Weight	30"W x 2 <sup>1</sup> / <sub>4</sub> "H x 19 <sup>1</sup> / <sub>4</sub> "D 31 <sup>3</sup> / <sub>8</sub> " - 41 <sup>1</sup> / <sub>2</sub> " 53 lb
<b>DISCHARGE</b> Vertical	6" Round
ELECTRICAL Supply Service	110/120 VAC, 60 Hz 15 amp circuit
INSTALLATION Bottom of Hood	to Countertop 30" – 36"


Specifications are subject to change without notice. Visit wolfappliance.com/specs for the most up-to-date information.

Dimensions may vary  $\pm 1/8$ " (3). Dimensions in parentheses are millimeters unless otherwise specified.

### **DIMENSIONS**



### **ELECTRICAL LOCATION**



 $30\ensuremath{\text{"}}\xspace$  (762) to  $36\ensuremath{\text{"}}\xspace$  (914) bottom edge to countertop