




Elect SPECIFICATION SHEET

LOSONE SELECT® IN-LINE VENTILATORS MODELS L200L, L250L & L300L



Incredibly reliable. Unbelievably quiet. Offering the CFM choices you need at the lowest sound levels in the industry.

FEATURES

BLOWER:

- Low RPM for quiet operation
- Resilient anti-vibration mounts
- Dynamically-balanced, polymeric, centrifugal blower wheel for quiet, efficient performance
- Permanently lubricated, thermally protected motor
- Plug-in motor rated at 120 VAC
- Designed for continuous operation

HOUSING:

- Rugged galvanized steel
- 8" round duct connectors
- May be installed in ceiling or wall (size permitting)
- 8-position mounting brackets for easy installation and greater adaptability to various mounting requirements
- Automatic backdraft damper located within duct connector
- Factory-shipped in horizontal discharge position easily converted to vertical discharge
- Removable panel allows for easy motor access without disturbing ductwork
- Suitable for kitchen installations

CONTROLS:

- Model 57V (Ivory) / 57W (White) 3 amp Electronic Variable Speed Control
- Model 59V (Ivory) / 59W (White) 60-Minute Time Control
- Model 61V (Ivory) / 61W (White) 15-Minute Time Control
- Model 71V (Ivory) / 71W (White) 12-Hour Time Control
- Model 72V (Ivory) / 72W (White) 6-Amp Electronic Variable Speed Control

TYPICAL SPECIFICATION

Ventilator shall be Broan Model L200L, (L250L), (L300L).

Ventilator shall have galvanized steel housing. Housing to have adjustable mounting brackets and removable panel to allow motor access without disturbing ductwork.

Automatic backdraft damper to be located within duct connector. Duct connector, blower assembly and wiring plate shall be adjustable for either horizontal or vertical installation.

Blower unit shall be removable from housing and will have a polymeric, dynamically balanced centrifugal-type blower wheel. Motor to be permanently lubricated and mounted with resilient anti-vibration mounts. RPM not to exceed number listed for each model.

Air delivery shall be no less and sound levels no greater than listed for each model. All air and sound ratings shall be certified by AMCA. Units to be UL and cUL listed.



"Broan-NuTone LLC certifies that the models shown herein are licensed to bear the AMCA Seal. The ratings shown are based on tests and procedures performed in accordance with AMCA Publication 211 (and AMCA Publication 311 if sound is also certified) and comply with the requirements of the AMCA Certified Ratings Program"





Broan-NuTone LLC, A Nortek Company, Hartford, Wisconsin 53027 (1-800-548-0790) **Broan-NuTone Canada**, A Nortek Company, Mississauga, Ontario, L5T 1H9 (905-670-2500)

REFERENCE	QTY.	REMARKS	Project	
			Location	
			Architect	
			Engineer	
			Contractor	
			Submitted by	Date

PERFORMANCE RATINGS - LOSONE SELECT® IN-LINE VENTILATORS MODELS L200L, L250L & L300L


AMCA LICENSED PERFORMANCE


		CFM / SONES - AT STATIC PRESSURES (Ps - inches of H₂O)													
MODEL NO.	NOMINAL VOLTAGE		0.0" Ps	.10" Ps	.125" Ps	.250" Ps	.375" Ps	.50" Ps	.625" Ps	.750" Ps	.875" Ps	1.0" Ps	NOMINAL RPM	AMPS @60 Hz	_
L200L	120 VAC	CFM St. Thr. SONES St. Thr.	205 1.7	196 1.9	195 1.9	190 2.1	185 2.3	175 2.4	158 3.0	135 3.3	96 3.4	47 3.4	865	1.8	127
		CFM Rt. Ang. SONES Rt. Ang.	183 1.6	177 1.6	176 1.6	170 1.9	163 2.3	152 2.7	137 2.9	121 3.1	96 3.4	51 3.6	930	1.8	127
L250L	120 VAC	CFM St. Thr. SONES St. Thr.	248 2.0	245 2.3	245 2.3	241 2.6	235 2.8	224 3.2	208 3.4	183 3.6	141 3.9	84 3.8	1005	2.1	166
		CFM Rt. Ang. SONES Rt. Ang.	229 2.4	224 2.5	222 2.6	214 2.8	204 3.0	193 3.2	177 3.4	157 3.7	132 3.8	95 3.8	1115	2.1	166
L300L	120 VAC	CFM St. Thr. SONES St. Thr.	300 2.9	294 3.0	293 3.1	285 3.3	274 3.4	259 3.5	243 3.6	214 3.7	168 4.0	113 3.9	1145	2.6	212
		CFM Rt. Ang. SONES Rt. Ang.	270 3.7	261 3.7	259 3.7	248 3.7	234 3.9	220 3.9	200 4.0	174 4.2	146 4.4	104 4.0	1285	2.6	212

Performance ratings include the effects of backdraft damper in the airstream. Speed (RPM) shown is nominal. Performance is based on actual speed of test. The sound ratings shown are loudness values in fan sones at 5' (1.5m) in a hemispherical free field calculated per AMCA Std. 301. Values shown are for Installation Type D: Ducted inlet, Ducted outlet. Ratings do not include the effect of duct end correction. Performance ratings include the effects of 18 feet of round inlet duct and, if needed, a rectangular to round duct transition in the airstream. Performance shown is for Installation Type D: Ducted inlet, Ducted outlet.



"Broan-NuTone LLC certifies that the models shown herein are licensed to bear the AMCA Seal. The ratings shown are based on tests and procedures performed in accordance with AMCA Publication 211 (and AMCA Publication 311 if sound is also certified) and comply with the requirements of the AMCA Certified Ratings Program."





WEIGHT -

MODEL NO.	SHIPPING WT.					
L200L	23.1 lbs.					
L250L	23.2 lbs.					
L300L	23.2 lbs.					

