Shaded area indicates change Rev. 9-16



#### Mueller® 300™ Ball Angle **Meter Valve**

Mueller 110® Conductive Compression Connection for CTS O.D.\* tubing x meter swivel nut\*\* Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number.

Example: B-24258-3



#### Mueller 300 Ball Angle **Meter Valve**

Mueller Pack Joint Connection for CTS O.D.\* tubing x meter swivel nut\*\* Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number.

Example: P-24258-3

## B-24258N

Catalog size	5/8"x3/4" R †	5/8"x3/4"	5/8"x3/4"x3/4"	R <i>†</i>
Meter size	5/8"	5/8"	5/8"x3/4", 3/4"	
Tubing size	3/4"	3/4"	3/4"	
Catalog size	5/8"x3/4"x3/4"	5/8"x3/4"x1"	1" R <i>†</i>	1"
Meter size	5/8"x3/4", 3/4"	5/8"x3/4", 3/4	1"	1"
Tubing size	3/4"	1"	1"	1"

#### P-24258N

Catalog size	5/8"x3/4" R †	5/8"x3/4"	5/8"x3/4"x3/4"	R †
Meter size	5/8"	5/8"	5/8"x3/4", 3/4"	
Tubing size	3/4"	3/4"	3/4"	
Catalog size	5/8"x3/4"x3/4"	5/8"x3/4"x1"	1" R †	1"
Meter size	5/8"x3/4", 3/4"	5/8"x3/4", 3/4	1"	1"
Tubing size	3/4"	1"	1"	1"



#### Mueller 300 Ball Angle **Meter Valve**

Mueller 110 Conductive Compression Connection for IPS PE\* pipe x meter swivel nut\*\* Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number.

Example: B-24259-3



#### Mueller 300 Ball Angle **Meter Valve**

Mueller Pack Joint Connection for IPS PE\* pipe x meter swivel nut\*\* Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number.

Example: B-24259-3

## B-24259N

Catalog size	5/8"x3/4"x3/4"	5/8"x3/4"x1"	1"
Meter size	5/8"x3/4", 3/4"	5/8"x3/4", 3/4	1"
Tubing size	3/4"	1"	1"

#### E-24259N

Catalog size	5/8"x3/4"x3/4"	5/8"x3/4"x1"	1"
Meter size	5/8"x3/4", 3/4"	5/8"x3/4", 3/4	1"
Tubing size	3/4"	1"	1"



B-24266N

## Mueller 300 Ball Angle **Meter Valve**

Mueller INSTA-TITE Connection for IPS PE\* pipe x meter swivel nut\*\* Quarter turn check - lock wing. 360° turn option available byadding -3 suffix to catalog number.

Example: B-24266-3



## B-24267N

#### Mueller 300 Ball Angle **Meter Valve**

Mueller INSTA-TITE Connection for CTS O.D.\* tubing x meter swivel nut\*\*Quarter turn check - lock wing. 360° turn option available byadding -3 suffix to catalog number.

Example: B-24267-3

Note: Two-piece factory assembly

Catalog size	5/8"x3/4"x3/4"	1"
Meter size	5/8"x3/4", 3/4"	1"
Tubing size	3/4"	1"

Catalog size	5/8"x3/4"x3/4"	1"	Catalog size	5/8"x3/4"x3/4"	1"
Meter size	5/8"x3/4", 3/4"	1"	Meter size	5/8"x3/4", 3/4"	1"
Tubing size	3/4"	1"	Tubing size	3/4"	1"

<sup>\*</sup> See charts on pages 8D.17 and 8D.18 for tubing and pipe that can be used with this connection.

<sup>\*\*</sup> Meter swivel nuts are regularly furnished with a saddle feature to aid in meter installation and removal. A plain swivel nut is available as an option by adding a suffix of -1 to the catalog number.

<sup>†</sup> The "R" indicates this valve has a reduced port. Port size is one nominal size smaller than the valve inlet/outlet

Catalog size

Meter size

Tubing size

Catalog size

Meter size

Tubing size

Catalog size

Meter size

Tubing size



Rev. 9-16 Shaded area indicates changes

#### B-24255N

5/8"

3/4'

5/8"x3/4" R †

5/8"x3/4"x3/4"

5/8"x3/4", 3/4"

## Mueller® 300™ Ball Angle Meter

Copper flare nut x meter swivel nut\*\*

Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number.

5/8"x3/4"x3/4"

5/8"x3/4", 3/4"

1"

1" 1"

Example: B-24255-3

3/4'

1"

1" R +

5/8"x3/4"

5/8"x3/4"x1"

5/8"x3/4", 3/4

5/8"

3/4"

1-1/2"

1-1/2"

1-1/2"



#### Mueller 300 Ball Angle **Meter Valve**

F.I.P. x meter swivel nut\*\* Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number.

Example: B-24265-3

B	-2	42	6	5	N
			. •	•	

Catalog size	5/8"x3/4" R †	5/8"x3/4"	5/8"x3/4"x3/4"	R †
Meter size	5/8"	5/8"	5/8"x3/4", 3/4"	
Tubing size	3/4"	3/4"	3/4"	
Catalog size	5/8"x3/4"x3/4"	5/8"x3/4"x1"	1" R †	1"
Meter size	5/8"x3/4", 3/4"	5/8"x3/4", 3/4	1"	1"
Tubing size	3/4"	1"	1"	1"



B-24276N

#### Mueller 300 Ball Angle **Meter Valve**

Mueller 110® Conductive Compression Connection for CTS O.D.\* tubing x meter flange Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number.

2" † †

2"

1-1/2", 2"

Example: B-24276-3

Walter (

#### Mueller 300 Ball Angle **Meter Valve**

Mueller® Pack Joint Connection for CTS O.D.\* tubing x meter

Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number.

Example: P-24276-3

P	-2	42	27	6	N	
---	----	----	----	---	---	--

Catalog size	1-1/2"	2" † †
Meter size	1-1/2"	1-1/2", 2"
Tubing size	1-1/2"	2"

1-1/2"

1-1/2"



Two piece factory assembled
Copper flare nut x meter flang

**Meter Valve** 

Mueller 300 Ball Angle

er flange Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number.

Example: B-24277-3



**B-24286N** 

Catalog size

Meter size

Tubing size

#### Mueller 300 Ball Angle **Meter Valve**

F.I.P. x meter flange Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number.

Example: B-24286-3

#### B-24277N

Catalog size	1-1/2"	2" † †
Meter size	1-1/2"	1-1/2", 2"
Tubing size	1-1/2"	2"



B-24371N

#### Mueller 300 Ball Angle **Meter Valve**

F.I.P. x meter swivel nut\*\* Extended length.

Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number.

Example: B-24265-3



V-24288N

## 1-1/2'

Mueller 300 Ball Angle

**Meter Valve** 

Mueller® Pack Joint Connection for PVC tubing\* x meter flange Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog

2" † †

1-1/2", 2"

Note: Two-piece factory assembly

Example: V-24288-3

Catalog size	3/4" R †
Meter size	3/4"
Tubing size	3/4"

Catalog size	1-1/2"	2" † †
Meter size	1-1/2"	2"
Tubing size	1-1/2"	2"

<sup>\*</sup> See charts on pages 8D.17 and 8D.18 for tubingand pipe that can be used with this connection.

<sup>†</sup> The "R" indicates this valve has a reduced port. Port size is one nominal size smaller than the valve inlet/outlet

<sup>††</sup>These valves have meter flanges double drilled to fit either 1-1/2" or 2" meters.

Shaded area indicates change Rev. 4-14



Mueller® 300 ™ Ball Angle Service Valve
MUELLER 110® Compression

Connection for CTS O.D.\* tubing x F.I.P.

Quarter turn check - lock wing.

360° turn option available by adding -3 suffix to catalog number. Example: B-24274-3



B-24275N

#### Mueller 300 Ball Angle Service Valve

Copper flare nut x F.I.P. Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number.

Example: B-24275-3

#### B-24274N

Catalog size	3/4"	1"
Tubing size	3/4"	1"

Catalog size	3/4"	1"
Tuhing size	3/4"	1"



#### Mueller 300 Ball Angle Service Valve

F.I.P x F.I.P.

Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number.

Example: B-24285-3



#### Mueller 300 Ball Angle Service Valve

F.I.P x M.I.P.

Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number.

Example: B-24287-3

\* See charts on pages 8D.17 and 8D.18 for tubing and pipe that can be used with

## B-24285N

Catalog size	3/4"	3/4" R †	1" R †	1"
Tubing size	3/4"	3/4"	1"	1"

#### B-24287N

Catalog size	3/4"	1"
Tubing size	3/4"	1"

this connection.

† The "R" indicates this valve has a reduced port. Port size is one nominal size smaller than the valve inlet/outlet.

Rev. 2-17 Shaded area indicates changes



B-24350N

#### Mueller® 300™ Ball Straight Meter Valve Mueller 110<sup>®</sup> Conductive Compression

Connection for CTS O.D.\* tubing x meter swivel nut\*\*

Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number. Example: B-24350-3

Catalog size	3/4"x5/8" R †	3/4" R†	3/4"	5/8"x3/4"x1"	1"R†	1"
Meter size	5/8"	5/8"x3/4", 3/4"	5/8"x3/4", 3/4"	5/8"x3/4", 3/4"	1"	1"
Tubing size	3/4"	3/4"	3/4"	1"	1"	1"



P-24350N

Mueller 300 Ball Straight Meter Valve

Mueller Pack Joint Connection for CTS O.D.\* tubing x meter swivel nut\*\*.

Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number. Example: P-24350-3

Catalog size	3/4"x5/8" R †	3/4" R†	3/4"	5/8"x3/4"x1"	1"R†	1"
Meter size	5/8"	5/8"x3/4", 3/4"	5/8"x3/4", 3/4"	5/8"x3/4", 3/4"	1"	1"
Tubing size	3/4"	3/4"	3/4"	1"	1"	1"



B-24353N

Mueller 300 Ball Straight Meter Valve

Mueller 110 Conductive Compression Connection for PE plastic pipe (IPS) \* tubing x meter swivel nut\*\*

Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number. Example: B-24353-3

Catalog size	3/4"	5/8"x3/4"x1"	1"R†	1"
Meter size	5/8"x3/4", 3/4"	5/8"x3/4", 3/4"	1"	1"
Tubing size	3/4"	1"	1"	1"

5/8"x3/4", 3/4"



E-24353N

Mueller 300 Ball Straight Meter Valve

Mueller Pack Joint for plastic pipe (IPS) \* tubing x meter swivel nut\*\*.

Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number. Example: B-24353-3

Catalog size	3/4"	5/8"x3/4"x1"	1"R†	1"
Meter size	5/8"x3/4", 3/4"	5/8"x3/4", 3/4"	1"	1"
Tubing size	3/4"	1"	1"	1"



B-24352N

3/4" R †

5/8"x3/4", 3/4"

Catalog size

Meter size

Tubing size

#### Mueller 300 Ball Straight Meter Valve

Copper flare nut x meter swivel nut\*\*.

• •
Quarter turn check - lockwing. 360° turn option
available by adding -3 suffix to catalog number.
Example: B-24352-3

5/8"x3/4"x1"

5/8"x3/4", 3/4"

1"R†

1"

1"



Mueller 300 Ball Straight Meter Valve

F.I.P. x meter swivel nut\*\*

Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number. Example: B-24351-3

B-24351N

Catalog size	3/4" R †	3/4"	5/8"x3/4"x1"	1"R†	1"
Meter size	5/8"x3/4", 3/4"	5/8"x3/4", 3/4"	5/8"x3/4", 3/4"	1"	1"
Tubing size	3/4"	3/4"	1"	1"	1"



### Mueller 300 Ball Straight Meter Valve

M.I.P. x meter swivel nut\*\*.

Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number. Example: B-24394-3

B-24394N

Catalog size	3/4"R†	3/4"	1"R†	1"
Meter size	5/8"x3/4", 3/4"	5/8"x3/4", 3/4"	1"	1"
Tubing size	3/4"	3/4"	1"	1"



B-24363N

Mueller 300 Ball Straight Meter Valve Mueller INSTA-TITE® Connection for CTS O.D.\* tubing x meter swivel nut\*\*.

Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number.

Example: B-24363-3

Catalog size	3/4"R†	3/4"	5/8"x3/4"x1"	1"
Meter size	5/8"x3/4", 3/4"	5/8"x3/4", 3/4"	5/8"x3/4", 3/4"	1"
Tubing size	3/4"	3/4"	1"	1"



V-25237N

#### Mueller 300 Ball Straight Meter Valve

Mueller Pack Joint for PVC x meter swivel nut\*\*.

Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number.

Example: V-25237-3

Catalog size	5/8"x3/4"x1"	1"
Meter size	5/8"x3/4", 3/4"	1"
Tubing size	1"	1"



B-24371RN

## Mueller® 300™ Ball Straight Meter Valve

F.I.P meter swivel nut

Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number. 4" length.

Example: B-24351-3

Catalog size	5/8"x3/4"x3/4"R
Meter size	5/8"x3/4", 3/4"
Pipe size	3/4"

<sup>\*</sup> See charts on pages 8D.17 and 8D.18 for tubing and pipe that can be used with this connection.

<sup>\*</sup>Meter swivel nuts are regularly furnished with a saddle feature to aid in meter installation and removal. A plain swivel nut is available as an option by adding a suffix of -1 to the catalog number.

<sup>†</sup>The "R" indicates this valve has a reduced port. The port size is one nominal size smaller than the valve inlet/outlet.

# BALL STRAIGHT METER VALVES 3/4" - 2" SIZES



8D.5

Shaded area indicates change Rev. 1-16



B-24331N

Catalog size

Meter size

Pipe size

#### Mueller 300 Ball Straight Meter Valve

Mueller 110 Conductive Compression Connection for PE plastic pipe (IPS) \* tubing x meter swivel nut\*\*.

Quarter turn check. Non- lock wing body. 360° turn option available by adding -3 suffix to catalog number.

5/8"x3/4"x1"

5/8"x3/4", 3/4"

Example: B-24331-3

5/8"x3/4"x1" R †

5/8" 1"

		)
	330000	

P-24335N

## Mueller 300 Ball Straight Meter Valve

Mueller Pack Joint Connection for CTS O.D.\* tubing x meter flange

Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog

Example: P-24335-3

Catalog size	1-1/2"	2" † †
Meter size	1-1/2"	2" † †
Pipe size	1-1/2"	2" † †



## Mueller 300 Ball Straight Meter Valve

1"

Mueller 110® Conductive Compression Connection for CTS O.D.\* tubing x meter flange.

Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number. Example: B-24335-3

B-24	3	35	Ν
------	---	----	---

Catalog size	1-1/2"	2" ††
Meter size	1-1/2"	2" ††
Pipe size	1-1/2"	2" ††



### Mueller 300 Ball Straight Meter Valve

F.I.P. x meter flange.

Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number.

Example: B-24337-3

#### B-24337N

Catalog size	1-1/2"	2" † †
Meter size	1-1/2"	2" † †
Pipe size	1-1/2"	2" † †



#### Mueller 300 Ball Straight Meter Valve

Copper flare nut x meter flange Quarter turn check - lock wing. 360° turn option by adding -3 suffix to catalog number. Example: B-24334-3

B-24334N

Catalog size	1-1/2"	2"††
Meter size	1-1/2"	2"††
Pipe size	1-1/2"	2" † †



## E-24333N

**Mueller 300 Ball Straight Meter Valve**IPS PEP Pack Joint x outlet 2 bolt meter flange w lock wing

Quarter turn check. Non- lock wing body. 360° turn option available by adding -3 suffix to catalog number.

Example: B-24331-3



#### Mueller 300 Ball Straight Meter Valve

PVC Pack Joint x outlet 2 bolt meter flange w lock wing

Quarter turn check - lock wing. 360° turn option by adding -3 suffix to catalog number. Example: B-24334-3

#### V-25240N

Catalog size	1-1/2"	2" † †
Meter size	1-1/2"	2" † †
Pipe size	1-1/2"	2" † †

Catalog size
 1-1/2"
 2" † †

 Meter size
 1-1/2"
 2" † †

 Pipe size
 1-1/2"
 2" † †

<sup>\*</sup> See charts on pages 8D.17 and 8D.18 for tubing and pipe that can be used with this connection. ††These valves have meter flanges double drilled to fit either 1-1/2" or 2" meters.

1"R†

3/4"

1"

Catalog size

Meter size

Tubing size

3/4'

3/4'



## B-25146N

3/4" R †

5/8'

3/4'

#### Mueller® 300™ Ball Straight **Service Valve**

Mueller 110<sup>®</sup> Conductive Compression Connection for CTS O D \* tubing - both ends

OTO O.B. tabing <b>both chas</b>
Quarter turn check - lock wing.
360° turn option available by adding -3
suffix to catalog number (B-25146-3)

1"

1"

1-1/2" 2"

1-1/2" 2"

1-1/2" 2"

MD

#### Mueller 300 Ball Straight Service Valve

Mueller® Pack Joint Connection for CTS O.D.\* tubing - both ends Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number (P-25146-3)

## P-25146N

Catalog size	3/4" R †	3/4"	1"R†	1"	1-1/2"	2"
Meter size	5/8"	3/4"	3/4"	1"	1-1/2"	2"
Tubing size	3/4"	3/4"	1"	1"	1-1/2"	2"



## **B-25170N**

#### Mueller 300 Ball Straight **Service Valve**

Mueller 110 Conductive Compression Connection for CTS O.D.\* tubing x F.I.P. Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number (B-25170-3)

Catalog size	3/4" R †	3/4"	3/4"x1"	1"R†	1"x3/4" R †	1-1/2"	2"
Meter size	5/8"	3/4"	3/4"	3/4"	3/4"	1-1/2"	2"
Tubing size	3/4"	3/4"	3/4"	1"	1"	1-1/2"	2"



## P-25170N

## Mueller 300 Ball Straight Service Valve

Mueller Pack Joint Connection for CTS O.D.\*

tubing x F.I.P.

Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number (P-25170-3)

Catalog size	3/4" R †	3/4"	3/4"x1"	1"R†	1"x3/4" R†	1-1/2"	2"
Meter size	5/8"	3/4"	3/4"	3/4"	3/4"	1-1/2"	2"
Tubing size	3/4"	3/4"	3/4"	1"	1"	1-1/2"	2"



**B-25196N** 

8D-VALVES/CHECKS

#### Mueller 300 Ball Straight Service

Mueller 110 Compression Connection for IPS\* PE pipe x

Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number (B-25196-3)

,		
Catalog size	3/4	1
Valve size	3/4	1
Pipe size	3/4	1



## **B-25143N**

#### MUELLER 300 Ball Straight Service Valve

Copper flare nut - both ends Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number (B-25143-3)

Catalog size	3/4R	3/4	1R†	1-1/2	2
Valve size	3/4	3/4	3/4	1-1/2	2
Pipe size	3/4	3/4	1	1-1/2	2



## **B-25166N**

#### Mueller 300 Ball Straight **Service Valve**

Copper flare nut x F.I.P. Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number (B-25166-3)

Catalog size	3/4" R †	3/4"	1"R†	1"	1-1/2"	2"
Meter size	5/8"	3/4"	3/4"	1"	1-1/2"	2"
Tubing size	3/4"	3/4"	1"	1"	1-1/2"	2"



## **B-25168N**

#### Mueller 300 Ball Straight Service Valve

F.I.P. x Copper flare nut Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number--4-3/8" laying length for retrofit applications

Catalog size	3/4" R †	1"
Meter size	5/8"	1"
Tubing size	3/4"	1"



B-20200N

#### Mueller 300 Ball Straight **Service Valve**

F.I.P. x F.I.P.

Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number (B-20200-3)

Catalog size	3/4" R †	3/4"	1"x3/4"	1"R <i>†</i>
Catalog size	1"	1-1/2"	2"	



### B-20245N

#### Mueller 300 Ball Straight Service Valve

F.I.P. x F.I.P.

Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number -- 3-13/16" end-toend dimension for retrofit applications \* See charts on pages 8D.17 and 8D.18 for

3/4" R † Catalog size

tubing and pipe that can be used with this connection.

†The "R" indicates this valve has a reduced port. The port size is one nominal size smaller than the valve inlet/outlet.

## **BALL STRAIGHT SERVICE VALVES** 3/4"-2" SIZES





Shaded area indicates change Rev. 9-17



V-25236N

Catalog size Valve size Pipe size

#### Mueller 300 Ball Straight Service Valve

Mueller® Pack Joint Connection for for IPS\* PVC pipe- both ends Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number (V-25236-3)



B-25130N

#### Mueller 300 Ball Straight **Meter Valve**

Mueller 110 Compression Connection for CTS O.D.\* tubing

Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number (B-25130-3) 3/4" = 3.95" length, 1" = 5" length, and 3.4"R = 4-1/16" length

Catalog size	3/4" R	3/4"	1"
Valve size	3/4"	3/4"	1"
Pipe size	3/4"	3/4"	1"



1"

#### Mueller 300 Ball Straight Service Valve

Mueller Pack Joint Connection for IPS\* PVC pipe x F.I.P.

Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number (V-25108-3)



#### Mueller 300 Ball Straight Service Valve

Mueller Pack Joint Connection for IPS PE\* pipe x F.I.P. Quarter turn check - lock wing.

360° turn option available by adding -3 suffix to catalog number (B-25196-3) NOTE: 3/4" size may also be used on PVC

### V-25108N

Catalog size	1"	1-1/2"	2"
Valve size	1"	1-1/2"	2"
Pipe size	1"	1-1/2"	2"

## E-25196N

Catalog size	3/4"	1"	1-1/2"	2"
Valve size	3/4"	1"	1-1/2"	2"
Pipe size	3/4"	1"	1-1/2"	2"



B-20211N

#### Mueller 300 Ball Straight **Meter Valve**

Mueller INSTA-TITE® Connection for CTS O.D.

tubina x F.I.P.

Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number (V-25108-3)

Example: B-20211-3



#### Mueller 300 Ball Curb Valve F.I.P. x M.I.P

Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number (B-20285-3)

Catalog size	3/4"	3/4"R	1"	1"R
Valve size	3/4"	5/8"x3/4", 3/4"	1"	1"
Pipe size	3/4"	3/4"	1"	1"

## **B-20242N**

Catalog size	3/4"	1"	1-1/2"	2"
Valve size	3/4"	1"	1-1/2"	2"
Pipe size	3/4"	1"	1-1/2"	2"



#### Mueller 300 Ball Straight **Curb Valve**

F.I.P x Kitec Compression Quarter turn check - lock wing. 360° turn option available by adding -3 suffix to catalog number (K-25170-3)

## K-25170N

Catalog size	3/4"	3/4"R	1"	1"R
Valve size	3/4"	5/8"	1"	3/4"
Pipe size	3/4"	3/4"	1"	1"

<sup>\*</sup> See charts on pages 8D.17 and 8D.18 for tubing that may be used with these connections.



STRAIGHT SERVICE VALVES
3/4"& 1" SIZES

Rev. 4-14 Shaded area indicates changes



Mueller MARK II ORISEAL® Straight Service Valve
Mueller 110® Conductive
Compression Connection for
CTS O.D.\* tubing x F.I.P.
Quarter turn check - lock wing



Mueller MARK II ORISEAL Straight Service Valve Mueller® Pack Joint Connection for CTS O.D.\* tubing x F.I.P. Quarter turn check - lock wing

H-15170N

P-1	<b> 51</b>	7	N	N
			u	

Catalog size	3/4	1	Catalog size	3/4	1



Mueller MARK II ORISEAL Straight Service Valve Mueller INSTA-TITE® Connection for IPS\* PE pipe x F.I.P. Quarter turn check - lock wing



Mueller MARK II ORISEAL Straight Service Valve Mueller INSTA-TITE® Connection for CTS O.D.\* tubing x F.I.P. Quarter turn check - lock wing

H-15195N

H-15197N

Catalog size	3/4	Catalog size	3/4



H-15166N

3/4

Catalog size

Mueller MARK II ORISEAL Straight Service Valve Copper flare nut x F.I.P. Quarter turn check - lock wing



H-10200N

Mueller MARK II ORISEAL Straight Service Valve F.I.P. x F.I.P. Quarter turn check - lock wing

Catalog size 3/4 1	
--------------------	--

<sup>\*</sup> See charts on pages 8D.17 and 8D.18 for tubing that may be used with these connections.

Shaded area indicates change Rev. 3-18



#### Mueller MARK II ORISEAL Straight Meter Valve

Mueller 110 Conductive
Compression Connection for CTS
O.D.\* tubing x meter swivel nut\*\*
Quarter turn check - lock wing



### Mueller MARK II ORISEAL Straight Meter Valve

Mueller Pack Joint Connection for CTS O.D.\* tubing x meter swivel nut\*\*

Quarter turn check - lock wing

## H-14350N

Catalog size	3/4	1
Meter size	5/8x3/4, 3/4	1
Tubing size	3/4	1

P-1	435	50N
-----	-----	-----

Catalog size	3/4	1
Meter size	5/8x3/4, 3/4	1
Tubing size	3/4	1



## Mueller MARK II ORISEAL Straight Meter Valve

Copper flare nut x meter swivel nut\*\*

Quarter turn check - lock wing



## Mueller MARK II ORISEAL Straight Meter Valve

F.I.P. x meter flange Quarter turn check - lock wing

## H-14352N

Catalog size	3/4
Meter size	5/8x3/4, 3/4
Tubing size	3/4

## H-14337N

Catalog size	2" R††
Meter size	1-1/2" or 2"
Tubing size	2"



#### Mueller MARK II ORISEAL Straight Meter Valve F.I.P. x meter swivel nut\*\* Quarter turn check



## Mueller MARK II ORISEAL Straight Meter Valve

F.I.P. x meter swivel nut\*\*
Quarter turn check - lock wing 360° turn option available by
adding -3 suffix to catalog number.
Example: H-24351-3

Example. H-24

#### H-14345N

Catalog size	1"
Valve size	1"
Pipe size	1"

## H-14351N

Catalog size	3/4	1
Meter size	5/8x3/4, 3/4	1
Tubing size	3/4	1

<sup>\*</sup> See charts on pages 8D.17 and 8D.18 for tubing that may be used with these connections.

<sup>\*\*</sup> Meter swivel nuts are regularly furnished with a saddle feature to aid in meter installation and removal. A plain swivel nut is available as an option by adding a suffix of -1 to the catalog number.

<sup>††</sup> These valves have meter flanges double drilled to fit either 1-1/2" or 2" meters.

Rev. 3-18 Shaded area indicates changes



## 

www.muellercompany.com • moreinfo@muellercompany.com

## GROUND KEY ANGLE METER VALVES 3/4" & 1" SIZES



8D.11

Shaded area indicates change Rev. 5-18



Ground key angle meter stop Mueller 110® Conductive Compression Connection for CTS O.D.\* tubing x meter swivel nut\*\* 180° turn check - lock wing



Ground key angle meter stop

Mueller® Pack Joint Connection for

CTS O.D.\* tubing x meter swivel nut\*\*

180° turn check - lock wing

#### H-14258N

Catalog size	5/8"x3/4"	5/8"x3/4"x3/4"	5/8"x3/4"x1"	1"
Meter size	5/8"	5/8"x3/4", 3/4"	5/8"x3/4", 3/4"	1"
Pipe size	3/4"	3/4"	1"	1"

#### P-14258N

Catalog size	5/8"x3/4"x3/4"	5/8"x3/4"x1"	1"
Meter size	5/8"x3/4", 3/4"	5/8"x3/4", 3/4"	1"
Pipe size	3/4"	1"	1"



#### Ground key angle meter stop

Mueller 110 Compression Connection for IPS PE\* plastic pipe x meter swivel nut\*\* 180° turn check - lock wing



#### Ground key angle meter stop

Mueller INSTA-TITE® Connection for IPS PE\* plastic pipe x meter swivel nut\*\*

180° turn check - lock wing
Ground key angle meter stop

H-14259N

Catalog size	5/8"x3/4"x3/4"	5/8"x3/4"x1"	1"
Meter size	5/8"x3/4", 3/4"	5/8"x3/4", 3/4"	1"
Pipe size	3/4"	1"	1"

## H-14266N

Catalog size	5/8"x3/4"x3/4"	5/8"x3/4"x1"	1"
Meter size	5/8"x3/4", 3/4"	5/8"x3/4", 3/4"	1"
Pipe size	3/4"	1"	1"



#### Ground key angle meter stop

Mueller INSTA-TITE® Connection for CTS O.D.\* PE plastic tubing x meter swivel nut\*\*

180° turn check - lock wing



Copper flare nut x meter swivel nut\*\*
180° turn check - lock wing

#### H-14267N

Catalog size	5/8"x3/4"x3/4"	5/8"x3/4"x1"	1"
Meter size	5/8"x3/4", 3/4"	5/8"x3/4", 3/4"	1"
Pipe size	3/4"	1"	1"

#### H-14255N

Catalog size	5/8"x3/4"	5/8"x3/4"x3/4"	5/8"x3/4"x1"	1"
Meter size	5/8"	5/8"x3/4", 3/4"	5/8"x3/4", 3/4"	1"
Pipe size	3/4"	3/4"	1"	1"



#### Ground key angle meter stop

F.I.P. x meter swivel nut\*\*
180° turn check - lock wing



#### Ground key angle meter stop

Mueller Pack Joint for IPS PE\* plastic pipe x meter swivel nut\*\* 180° turn check - lock wing

#### H-14265N

Catalog size	5/8"x3/4"	5/8"x3/4"x3/4"	5/8"x3/4"x1"	1"
Meter size	5/8"	5/8"x3/4", 3/4"	5/8"x3/4", 3/4"	1"
Pipe size	3/4"	3/4"	1"	1"

## E-14259N

Catalog size	5/8"x3/4"x3/4"	5/8"x3/4"x1"	1"
Meter size	5/8"x3/4", 3/4"	5/8"x3/4", 3/4"	1"
Pipe size	3/4"	1"	1"

<sup>\*</sup> See charts on pages 8D.17 and 8D.18 for tubing and pipe that can be used with this connection.

<sup>\*\*</sup> Meter swivel nuts are regularly furnished with a saddle feature to aid in meter installation and removal. A plain swivel nut is available as an option by adding a suffix of

<sup>-1</sup> to the catalog number.



## **GROUND KEY ANGLE METER VALVES** & SERVICE VALVES - 3/4"-2" SIZES

Rev. 4-14 Shaded area indicates changes



**Ground Key Angle Meter Valve** Mueller 110<sup>®</sup> Conductive **Compression Connection** for CTS O.D.\* tubing x meter flange 180° turn check - lock wing

#### H-14277N

	••	
Catalog size	1-1/2"	2"††
Meter size	1-1/2"	1-1/2", 2"
Tuhing size	1_1/2"	2"



**Ground Key Angle Meter Valve** Mueller® Pack Joint Connection for CTS O.D.\* tubing x meter flange 180° turn check - lock wing

#### P-14277N

Catalog size	1-1/2"	2"††
Meter size	1-1/2"	1-1/2", 2"
Tubing size	1-1/2"	2"



**Ground Key Angle Meter Valve** Copper flare nut x meter flange 180° turn check - lock wing

## H-14276N

Catalog size	1-1/2"	2"††
Meter size	1-1/2"	1-1/2", 2"
Tubing size	1-1/2"	2"



#### **Ground Key Angle Meter Valve** F.I.P. x meter flange 180° turn check - lock wing

#### H-14286N

Catalog size	1-1/2"	2"††
Meter size	1-1/2"	1-1/2", 2"
Tubing size	1-1/2"	2"



H-14285N

Groun	d Ke	у А	ngl	e l	Vlete	r Va	alve
F.I.P. x	F.I.P.						

180° turn check - lock wing



**Mueller Solid Tee Head Roundway Meter Stop** F.I.P. x F.I.P. 360° turn - lock wing

#### H-10281N

	Catalog size	3/4"		Catalog size	1-1/2"
--	--------------	------	--	--------------	--------

<sup>\*</sup> See charts on pages 8D.17 and 8D.18 for tubing that may be used with these connections. ††These valves have meter flanges double drilled to fit either 1-1/2" or 2" meters.



8D.13

Shaded area indicates change Rev. 6-17



Straight dual check valve

Inlet: M.I.P. Outlet: F.I.P.

To order ASSE approved†† model add suffix -A to catalog number



Straight dual check valve

Inlet: F.I.P. Outlet: F.I.P.

To order ASSE approved†† model add

suffix -A to catalog number

#### H-14241N

Catalog size	3/4"	3/4"x1"††	1"
Pipe size	3/4"	3/4" in, 1" out	1"

H-14243N	
----------	--

Catalog size	3/4"	3/4"x1"††	1"	1-1/2"††	2"††
Pipe size	3/4"	3/4" in, 1" out	1"	1-1/2"	2"



Straight dual check valve Inlet: Meter swivel nut\*

Outlet: F.I.P.

To order ASSE approved model add suffix

-A to catalog number



H-14283N

Straight dual check valve Inlet: M.I.P.

**Outlet:** Mueller 110 Conductive Compression Connection for

CTS O.S. \*\* tubing.

To order ASSE approved†† model add

suffix -A to catalog number

## H-14242N

Catalog size	5/8"x3/4"x3/4"	5/8"x3/4"x1" † †	1"	1-1/2"††,†††	2"†,††
Pipe size	5/8"x3/4", 3/4"	5/8"x3/4", 3/4"	1"	1-1/2"	1-1/2", 2"
Tubing size	3/4"	1"	1"	1-1/2"	2"

Catalog size	3/4
Pipe size	3/4



Straight dual check valve

Inlet: M.I.P. Outlet: M.I.P.

To order ASSE approved†† model add

suffix -A to catalog number



Straight dual check valve

Inlet: Meter swivel nut\*

Outlet: M.I.P.

To order ASSE approved†† model add suffix -A to catalog number

#### H-14282N

Catalog size	3/4
Pipe size	3/4

## H-14272N

Catalog size	5/8"x3/4"x3/4"	1"
Meter size	5/8"x3/4", 3/4"	1"
Tubing size	3/4"	1"

<sup>\*</sup> Meter swivel nuts are regularly furnished with a saddle feature to aid in meter installation and removal. A plain swivel nut is available as an option by adding a suffix of -1 to the catalog number.

†These valves have meter flanges double drilled to fit either 1-1/2" or 2" meters.

††These 3/4"x1", 1-1/2" and 2" sizes are not available as ASSE approved.

†††These have meter flanges for 1-1/2" meters

<sup>\*\*</sup> See charts on page 8D.17 and 8D.18 for tubing and pipe that can be used with this connection.

## ANGLE METER & TOP ENTRY VERTICAL DUAL CHECK VALVES

Rev. 4-14 Shaded area indicates changes



#### **Angle Meter Dual Check Valve**

Inlet: Meter swivel nut\* Outlet: Mueller 110 Conductive Compression Connection for CTS O.D.\*\* tubing. To order ASSE approved model add suffix

## H-14269N

Catalog size	5/8"x3/4"x3/4"	1"	1-1/2"	2"
Pipe size	5/8"x3/4", 3/4"	1"	1-1/2"	2"
Tubing size	3/4"	1"	1-1/2"	2"

-A to catalog number



#### **Angle Meter Dual Check Valve**

Inlet: Meter swivel nut\* Outlet: Mueller 110 Pack Joint Connection for CTS O.D.\*\*

To order ASSE approved model add suffix -A to catalog number

## P-14269N

Catalog size	5/8"x3/4"x3/4"*	1"
Pipe size	5/8"x3/4", 3/4"	1"
Tubing size	3/4"	1"



#### Top entry vertical dual check valve **ASSE** approved

Inlet: Meter swivel nut\* Outlet: MUELLER 110® Conductive Compression

Connection for CTS O.D.\*\* tubing To order test valve feature add suffix (-05)

to catalog number



#### Angle dual check valve

Inlet: Meter swivel nut\*

Outlet: F.I.P

To order ASSE approved model add suffix

-A to catalog number

#### H-14462-AN

Catalog size	5/8"x3/4"x3/4"*	1"	2"
Pipe size	5/8"x3/4", 3/4"	1"	2"
Tubing size	3/4"	1"	2"***



Catalog size	5/8"x3/4"	5/8"x3/4"x1"***	1"	1-1/2"***	2"***
Pipe size	5/8"	5/8"x3/4", 3/4"	1"	1-1/2"	1-1/2", 2"
Tubing size	3/4"	3/4"	1"	1-1/2"	2"



#### Top entry vertical dual check valve **ASSE** approved

Inlet: Meter swivel nut\* Outlet: Copper flare nut

To order test valve feature add suffix (-05)

to catalog number



#### Top entry vertical dual check valve ASSE approved

Inlet: Meter swivel nut\*

Outlet: F.I.P

To order test valve feature add suffix (-05) to catalog number

To order test valve feature add suffix (-05) to

catalog number.

Example: H-14462-A-05

#### H-14461-AN

Catalog size	5/8"x3/4"x3/4"*	1"
Pipe size	5/8"x3/4", 3/4"	1"
Tubing size	3/4"	1"

#### H-14460-AN

Catalog size	5/8"x3/4"	5/8"x3/4"x3/4"*	1"*	2***
Pipe size	5/8"	5/8"x3/4", 3/4"	1"	1-1/2" or 2"
Tubing size	3/4"	3/4"	1"	2"



#### Top entry vertical dual check valve

ASSE approved Inlet: Meter swivel nut\* Outlet: M.I.P

To order test valve feature add suffix (-05)

to catalog number



#### Top entry vertical dual check valve **ASSE** approved

Inlet: Meter swivel nut\* Outlet: Mueller® Pack Joint Connection for CTS O.D.\*\* tubing To order test valve feature add suffix

(-05) to catalog number

#### H-14463-AN

Catalog size	5/8"x3/4"x3/4"*	1"
Pipe size	5/8"x3/4", 3/4"	1"
Tubing size	3/4"	1"

### P-14462-AN

Catalog size	5/8"x3/4"x3/4"*	1"	2"***
Pipe size	5/8"x3/4", 3/4"	1"	1-1/2", 2"
Tubing size	3/4"	1"	2"

<sup>\*</sup> Meter swivel nuts are regularly furnished with a saddle feature to aid in meter installation and removal. A plain swivel nut is available as an option by adding a suffix of

<sup>-1</sup> to the catalog number.

<sup>\*\*</sup>See charts on pagse 8D.17 and 8D.18 for tubing that may be used with these connections.

<sup>\*\*\*</sup>Valves with meter flanges double drilled to fit either 1-1/2" or 2" meters

# DUAL CHECK REPAIR KITS AND OPTIONAL PARTS & ACCESSORIES



8D.15

Shaded area indicates change Rev. 4-14



Repair kit for REGULAR dual check valves Not for use on top entry vertical style.



Repair kit for ASSE APPROVED regular dual check valves
Not for use on top entry vertical style.

Catalog number	681434	681435	681436
Valve size	5/8" or 5/8"x3/4" or 3/4"	1"	1-1/2" or 2"

Catalog number	681437	681438
Valve size	5/8" or 5/8"x3/4" or 3/4"	1"



Repair kit for M-98™ top entry vertical style checks



and ground key valves - one size fits both 3/4" and 1" valves.

2" Brass square wrench nut adapter

For use on Mueller® 300™ Ball Valves

Catalog number	682231	682232	682611
Valve size	3/4"	1"	1-1/2" or 2"



Brass straight lever handle

For use on Mueller® MARK II ORISEAL® Curb Valves and Mueller ORISEAL III Curb Valves.



Brass angle lever handle For use on Mueller® MARK II

For use on Mueller® MARK II ORISEAL® Curb Valves and Mueller ORISEAL III Curb Valves.

H-10298

3/4"	1"

H-14339

3/4" 1"



Brass straight lever handle

For use on Mueller 300 Ball Curb Valves - one size fits both 3/4" and 1" valves. 4.25" overall handle length.



B-24339

Brass angle lever handle

For use on Mueller 300 Ball Curb Valves - one size fits both 3/4" and 1" valves.





Brass straight lever handle
For use on Mueller 300 Ball Curb
Valves - one size fits both 3/4" and 1"
valves. 3.21" overall handle length for
use in confined areas where longer
handle will not work.



B-20298-99001

"RECLAIMED WATER" straight lever handle with marking and standard color for positive identification

For use on Mueller 300 Ball Valves one size fits both 3/4" and 1" valves. 3.21" overall handle length for use in confined areas.

\*Fits 1-1/2" and 2" Ball Valves




To order test valve features add suffix (-05) to catalog number. Example: H-14462-A-05

#### **RECLAIMED WATER STYLE:**

Valves area available marked for "reclaimed water" by adding "-20" to the catalog number.

Example: B-24274-20.



<sup>\*</sup> Meter swivel nuts are regularly furnished with a saddle feature to aid in meter installation and removal. A plain swivel nut is available as an option by adding a suffix of

<sup>-1</sup> to the catalog number.

<sup>\*\*</sup>See charts on pagse 8D.17 and 8D.18 for tubing that may be used with these connections.

<sup>\*\*\*</sup>Valves with meter flanges double drilled to fit either 1-1/2" or 2" meters

# COPPER FLARE TOOLS AND MISCELLANEOUS EQUIPMENT

Rev. 4-14 Shaded area indicates changes

### Copper flare connection optional equipment

## Copper flare nut



#### CATALOG NUMBER:

1/2" 3/	/4" 1"	1-1/4"	1-1/2"	2"
---------	--------	--------	--------	----


#### Solid copper disc

Used with regular copper flare nut to shut off line.

CATALOG NUMBER: H-15535

1/2" 3/4" 1"	1-1/4"	1-1/2"	2"
--------------	--------	--------	----

#### Brass cap



CATALOG NUMBER: H-15540N

ń		
ı	3/4"	1"
ı	J/ <del>+</del>	1

#### Flaring tool



Used to make 45° flare on type "K" copper tubing.

CATALOG NUMBER: H-18000

		1/2"	3/4"	1"	1-1/4"	1-1/2"	2"
--	--	------	------	----	--------	--------	----

#### **Drilled flaring tool**



Used to make 45° flare on type "K" copper tubing without shutting off water--drilled to exhaust water at right angle to tubing.

CATALOG NUMBER: H-18005

3/4"	1"

#### Reamer



Used to ream the inside of type "K" copper tubing to remove burrs prior to flaring.

CATALOG NUMBER: H-18010

3/4"

#### **Brass Hammer**

Solid brass head with 10" wooden handle. Weight 2-3/4lb.

CATALOG NUMBER: H-18025



Note: When using any striking tool, safety eye protection must be worn. Inspect hammer and tools for any damage after each use and repair or replace if mushrooming or chipping is evident.

# MUELLER 110<sup>®</sup> COMPRESSION CONNECTION INFORMATION & KITS



8D.17

Shaded area indicates change Rev. 9-17

#### Tubing, Pipe and Liners Used with Mueller 110 Compression Connection

Nominal size of connection	Material	Tubing or pipe wall O.D. range (in.)	Tubing or pipe wall thickness range (in.)	Tubing or pipe I.D. range (in.)	Liner Part Number
3/4" CTS	Type "K" copper	0.872 - 0.878	0.061 - 0.069	-	-
3/4 013	Polyethylene PE	0.871 - 0.879	0.097 - 0.107	0.657 - 0.685	504281
1" CTS	Type "K" copper	1.127 - 1.129	0.061 - 0.069	-	-
1 013	Polyethylene PE	1.120 - 1.130	0.125 - 0.137	0.846 - 0.880	504835
1-1/2" CTS	Type "K" copper	1.620 - 1.630	0.067 - 0.077	-	-
-1/2 015	Polyethylene PE	1.619 - 1.631	0.181 - 0.199	1.227 - 1.275	506139
2" CTS	Type "K" copper	2.120 - 2.130	0.076 - 0.090	-	-
2 013	Polyethylene PE	2.119 - 2.131	0.236 - 0.260	1.605 - 1.665	506141
3/4" IPS	Polyethylene PE	1.045 - 1.110	0.113 - 0.134	0.780 - 0.828	505141
1" IPS	Polyethylene PE	1.329 - 1.399	0.150 - 0.170	1.029 - 1.059	505142

Type "K" copper tubing per ASTM B888. CTS polyethylene (PE) per ASTM D-2737 SDR-9 IPS polyethylene (PE) per ASTM D-2239 PE SIDR-7 Polyvinylchloride (PVC) per ASTM D1785



#### **Mueller 110 Compression Connection Replacement Parts**

Size	Gasket part number †	Connection nut
3/4" CTS	581949	507831
1" CTS	581951	507835
3/4" IPS	89599	508826
1" IPS	89788	508827
1-1/2" CTS	581955	507847
2" CTS	581957	507851





**Gasket Assembly** 

Nut

#### Adapter Nut for pre-1976 style Mueller 110 Compression Connection for CTS tubing


Kit includes one standard Gasket (same used with current style 110 connections) and a special Nut that adapts to the older style connection threads on the fittings. It is installed in the same way as the current style connection (Gasket conductor spring should be toward fitting body).

Size	Connection kit
3/4" CTS	682552
1" CTS	682551



## Mueller KITEC® Compression Connection

Size	Kit part number
3/4" CTS	682605N
1" CTS	682606N



<sup>†</sup> Gasket and gripper band assembly.

## MUELLER® PACK JOINT & INSTA-TITE® **CONNECTION INFORMATION & KITS**

Rev. 4-14 Shaded area indicates changes

#### Pack Joint Connection Kits (including gasket and washer)

Nominal size of connection	Tubing or pipe O.D. range (in.)	Tubing or pipe wall thickness (in.)	Tubing or pipe I.D. range (in.)	Part number
3/4" CTS	0.871 - 0.879	0.097 - 0.107	0.657 - 0.685	681921
1" CTS	1.120 - 1.130	0.125 - 0.137	0.846 - 0.880	681922
1-1/2" CTS	1.619 - 1.631	0.181 - 0.199	1.221 - 1.269	681923
2" CTS	2.119 - 2.131	0.236 - 0.260	1.599 - 1.659	681924



† 3/4" & 1" size kits (CTS only) will interchange with valves or fittings using Mueller 110° Compression Connections (CTS). 1-1/2" & 2" size kits are not interchangeable with valves or fittings presently using Mueller 110 Compression Connections (CTS). The 1-1/2" & 2" sizes should only be used as replacements for products currently using Mueller Pack Joint Connections (CTS).

#### Tubing Pipe and Liners for Mueller Pack Joint Connection (not required for Type "K" copper pipe)

Nominal size of connection	Tubing or pipe O.D. range (in.)	Tubing or pipe wall thickness (in.)	Tubing or pipe I.D. range (in.)	Length of line	Part number
3/4" CTS PE	0.871 - 0.879	0.097 - 0.107	0.657 - 0.685	1.625	528704
1" CTS PE	1.120 - 1.130	0.125 - 0.137	0.846 - 0.880	2.125	528705
1-1/2" CTS PE	1.619 - 1.631	0.181 - 0.199	1.221 - 1.269	2.562	528706
2" CTS PE	2.119 - 2.131	0.236 - 0.260	1.599 - 1.659	2.562	528707

#### Polyethylene PE Tubing and Pipe Used with Mueller INSTA-TITE Connections

Nominal size of connection	Material	Tubing or pipe wall O.D. range (in.)	Tubing or pipe wall thickness range (in.)	Tubing or pipe I.D. range (in.)
3/4" CTS	Polyethylene PE	0.871 - 0.879	0.097 - 0.107	0.657 - 0.685
1" CTS	Polyethylene PE	1.120 - 1.130	0.125 - 0.137	0.846 - 0.880
3/4" IPS	Polyethylene PE	1.045 - 1.110	0.118 - 0.138	0.809 - 0.834
1" IPS	Polyethylene PE	1.329 - 1.399	0.150 - 0.170	1.029 - 1.059

CTS Polyethylene (PE) per ASTM D-2737 SDR-9 IPS polyethylene (PE) per ASTM D-2239 PE SIDR-7

#### Polyethylene PE Tubing and Pipe Used with Mueller INSTA-TITE Connections

Nominal size of connection	Gripper ring part number	O-ring part number
3/4" CTS (red gripper)	506325	506324
1" CTS (red gripper)	506327	506326
3/4" IPS (white gripper)	505885	505883
1" IPS (white gripper)	505886	505884



O-ring

#### Optional tools for use with Mueller INSTA-TITE Connections

#### Pipe beveling tool

To assure proper installation, the end of the pipe or tubing must be properly beveled before it is installed into the Mueller INSTA-TITE Connection. Mueller Co. offers a special beveling tool for both CTS PE tubing and IPS PE pipe.

PART NUMBER: H-18015 for 3/4" and 1" CTS tubing. PART NUMBER: H-18017 for 3/4" and 1" IPS pipe



#### Pipe removal tool

Pipe or tubing may be removed from the Mueller INSTA-TITE Connection using special removal tools. Use one tool for 3/4" size connection and two tools for 1" size.



PART NUMBER: 506336