


6. Exploded Views and Parts List


6-1 Indoor unit



° Parts List

No	CODE NO	Description	Specification	Q'TY	Remark
1	DB92-70002F	Ass'y panel (F)	ABS SC-93438R	1	
2	DB63-30020A	Guard-air filter	PP	2	
3	DB94-10023G	Ass'y-tray drain	ABS SC-93438R	1	
	DB66-30014C	Blade (H.LW)	ABS	1	
	DB66-30015C	Blade (H.UP)	ABS	1	
	DB66-30017A	Blade (V)	PP	9	
	DB66-30019A	Blade	PP	3	
	DB66-30041A	Blade connector	ABS	3	
3-1	DB31-10085B	Motor-louver	mitsubishi MP35EA	1	
4	DB96-40162A	Ass'y-evaporator	ASS'Y	1	
	DB96-10069B	Ass'y tube evap in		1	
	DB96-31298A	Ass'y tube evap out		1	
6	DB61-40227A	Holder motor	PP	1	
7	DB39-20283A	Connector wire outdoor	6P	1	
	DB39-20284A	Connector wire com	3P	1	
8	DB93-10476A	Ass'y-main PCB	ASM240UE	1	
9	DB63-10024B	Cover-PCB	PP	1	
10	DB63-10079A	Terminal cover	ABS	1	
11	DB93-10427A	Ass'y-display PCB	ASM240UE	1	
12	DB64-50021A	KNOB		1	
13	DB31-10078A	Motor-fan in	AMPAS-040WTVA	1	
14	DB67-50021A	Fan	D95	1	
15	DB61-40040B	Ass'y holder bearing		1	
15-1	DB94-40007A	Bearing	POLY SLIDER PG5	1	
15-2	DB94-40003A	Bearing-mold	CR	1	
15-3	DB61-40008B	Holder-bearing	HIPS	1	
16	DB94-20010B	Ass'y-back body	AS-966	1	
17	DB61-40029A	Holder-pipe	PP	1	
18	DB70-10214A	Plate-hanger	SGCC-M	1	

6-2 Outdoor Unit




° Parts List

No	CODE NO	Description	Specification	Q'TY	Remark
1	DB90-10163D	ASS'Y-WELD FRONT	SC-90073T	1	
1-1	DB72-60049A	INSUL FRONT OUT	FOAM PU + FOAM PE	1	
2	DB67-50067A	FAN-PROPELLER	AS+G/F20%	1	
3	DB31-10141A	MOTOR-FAN OUT	OSME-606SRC	1	
4	DB61-20094A	BASE-MOTOR	SGCC-M	1	
5	DB64-60134A	CABINET-SIDE	SECC-P	1	
5-1	DB72-60053A	INSUL SIDE CABI	FOAM PU + FOAM PE	1	
6	DB90-40120A	ASS'Y COVER VALVE	ASS'Y	1	
6-1	DB63-10433A	COVER-CONTROL	P.P	1	
6-2	DB63-10434A	COVER-VALVE	P.P	1	
7	DB90-20176A	ASS'Y-BASE OUT	ASM240UE	1	
8	DB99-10082A	ASS'Y-VALVE	ASM240UE	1	
8-1	DB62-40100A	VALVE-PACKED 1/2"	1/2 °	2	
8-2	DB62-40099A	VALVE-PACKED 1/4"	1/4 °	2	
8-3	DB62-31576A	TUBE CAPI (C)	ID 1.7 ° 1000	1	
9	DB63-30027C	GUARD-COND	SC-90073T	1	
10	DB93-40604A	ASS'Y CONTROL OUT	ASM240UE	1	
10-1	DB61-10139A	CASE CONTROL OUT	SGCC-M	1	
10-2	DB65-10015A	CLIP-CAPACITOR	SGCC-M	2	
10-3	2501-001062	C-OIL	30 B 420V	2	
10-4	DB65-40041B	TERMINAL BLOCK	10P	1	
10-5	2501-000398	C-OIL	4 B 450V	1	
11	DB94-50029A	PARTITION	SGCC-P	1	
11-1	DB72-60052A	INSUL PARTITION	FOAM PU + FOAM PE	1	
11-2	DB70-10541A	PARTITION	SGCC-M	1	
12	DB63-10214B	COVER-TOP	SECC-P	1	
13	DB95-10062Y	ASS'Y-COMP	48A124JV1E5	2	
13-1	DB73-10004A	GROMMET-ISOLATOR	EPDM	6	
13-2	DB60-30029A	NUT-HEXAGON	M8	6	
13-3	DB60-30018A	NUT-FLANGE	P10.8	2	
13-4	DB63-10165B	COVER-TERMINAL	NORYL	2	
13-5	DB47-20005A	OLP	MRA12030-12008	2	
14	DB96-30080A	CONDENSER	ASS'Y	1	
15	DB63-30110J	SCREEN-GUARD	P.E.H 100%	1	

6-3 Remote Control & PCB Box


6-3-1 Remote Control



° Parts List

No	CODE NO	Description	Specification	Q'TY	Remark
	DB93-30010F	Ass'y-remocon		1	
1	DB61-10011A	Case-remocon(LW)	ABS	1	
2	DB73-20025A	Rubber-button(B)	NBR	1	
3	DB09-10083A	IC-MCU	SMC621A	1	
	DB07-20034A	LCD	AT-025ZAR	1	
4	DB73-20009C	Rubber-button(A)	NBR	1	
5-1	DB61-10020A	Case remocon(UPP)	ABS	1	
5-2	DB64-20035A	Door-remocon	ABS	1	
5-3	DB64-40068C	Window-remocon	PC	1	
5-4	DB74-10008A	Filter-remocon	PC	1	
6	DB64-40068C	Inlay-remocon	ABS	1	
	DB61-40009A	Holder remocon	ABS	1	
7	DB63-10081A	Cover battery	ABS	1	

6-3-2 PCB Box



° Parts List

No	CODE NO	Description	Specification	Q'TY	Remark
1	DB63-10024B	COVER-PCB		1	
2	DB93-10476A	ASS'Y MAIN PCB	ASM-240UE	1	
2-1	DB09-10128A	MICOM	MB89635R-314	1	
2-2	DB32-10008B	THERMISTOR-ASS'Y	103AT	1	
2-3	DE26-20114A	TRANS-POWER	EF33 X 41	1	
2-4	2306-000294	C-FILM	1.5 B /400VAC	1	
2-5	3501-000261	POWER-RELAY	G4A-1A 250V	1	
2-6	DE32-10037A	FUSE	250V 3.15A	1	
2-7	3711-000643	CONNECTOR-WAFER	SMAW 250-12	1	
3	DB93-10427A	ASS'Y-DISPLAY PCB	ASM-240UE	1	
3-1	A3018-0077	SW TACT, H	KDT-1105.S	1	
3-2	DB59-10012A	MODULE-REMOCON	GP1U271R		

MEMO