KOHLER®


Features

- Vitreous china
- 12" (30.5 cm) rough-in
- 1.6 gpf (6 lpf)
- 2" (5.1 cm) glazed trapway
- Combination toilet
- Ingenium_® flushing system
- Includes polished chrome trip lever
- Less seat and supply
- Elongated bowl
- 9" (22.9 cm) x 8" (20.3 cm) water area
- 30-7/8" (78.4 cm) x 18-1/4" (46.4 cm) x 31-1/2" (80 cm)

Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.2
- Energy Policy Act of 1992
- IAPMO/UPC
- CSA B45.0
- CSA B45.1
- CSA International



DEVONSHIRE_®

TWO-PIECE TOILET

Colors/Finishes

- 0: White
- Other: Refer to Price Book for additional colors/finishes

Accessories

- 0: White
- CP: Polished Chrome
- PB: Vibrant_® Polished Brass
- Other: Refer to Price Book for additional colors/finishes

Specified Model

Model	Description		Colo	Colors/Finishes		
K-3457	Elongated bowl toilet		0 🗆	Other		
Recommended Accessories						
K-4636	Cachet™ Quiet-Close™ elongated toilet seat		0 🗆	Other		
K-7637	Angle supply with stop – 3/8" NPT	D CP	D PB	Other		
Optional Accessories						
K-9439	Trip lever - non-CP] PB	Other		

Product Specification

The elongated bowl toilet combination shall be made of vitreous china. The toilet shall be 30-7/8'' (78.4 cm) in length, 18-1/4'' (46.4 cm) in width, and 31-1/2'' (80 cm) in height with 9'' (22.9 cm) x 8'' (20.3 cm) water area. The toilet shall be 12'' (30.5 cm) rough-in. The toilet shall have 2'' (5.1 cm) glazed trapway. The toilet shall be 1.6 gpf (6 lpf) with Ingenium_® flushing system. The toilet shall include polished chrome trip lever. The toilet shall be less seat and supply. The toilet shall be Kohler Model K-3457-_____.


DEVONSHIRE®

Technical Information

Fixture:				
Configuration	Two-piece, elongated			
Water per flush	1.6 gal (6 L)			
Passageway	2" (5.1 cm)			
Water area	9″ (22.9 cm) x 8″ (20.3 cm)			
Water depth from rim	6″ (15.2 cm)			
Seat post hole centers	5-1/2" (14 cm)			
Included components:				
Bowl	K-4269			
Tank	K-4619			
Tank cover	84652			
Trip lever	85132-CP			
Bolt cap accessory pack	1013092			

Installation Notes

Install this product according to the installation guide.



Product Diagram

