

Carrollton® Close Coupled Toilet, 1.6GPF

FEATURES

- G-Max® flushing system, low consumption (1.6GPF/6.0LPF)
- Traditional close coupled skirted design
- Elongated front bowl and tank set
- Color matched and chrome trip lever
- 12" Unifit rough-in, less supply (included)

MODELS

- CST774S

COMPONENTS

- CT774S - Elongated Front Bowl
- ST774S - Tank and Cover only
- SS154 SoftClose® seat (sold separately)
- SS114 SoftClose® seat (sold separately)
- TSU01W.10 - 10" Unifit rough-in (sold separately)
- TSU01W.14 - 14" Unifit rough-in (sold separately)

COLORS/FINISHES

- Standard
 - #01 Cotton
 - #03 Bone
 - #11 Colonial White
 - #12 Sedona Beige
 - #51 Ebony

PRODUCT SPECIFICATION

The two-piece G-Max flushing system toilet shall be 1.6GPF/6.0LPF. Toilet shall have high-profile tank, elongated front bowl and color matched/chrome trip lever. Toilet shall be TOTO Model CST774S_____.



CODES/STANDARDS

- Meets and exceeds ASME A112.19.2/CSA B45.1
- Certifications: IAPMO(cUPC), State of Massachusetts, City of Los Angeles, and others
- Code compliance: UPC, IPC, NSPC, NPC Canada, and others



CST774S

Carrollton® Close Coupled Toilet, 1.6GPF

SPECIFICATIONS




- Water Use 1.6 GPF/6.0LPF
- Flush System G-Max®
- Min. Water Pressure 8 psi (static)
- Water Surface 10-3/8" x 8-3/8"
- Trap Diameter 2-1/8"
- Rough-in 12" (10" & 14" available)
- Trap Seal 2-1/16"
- Warranty One Year Limited Warranty
- Material Vitreous china
- Shipping Weight CT774S - 84lbs
ST774S - 40lbs
- Shipping Dimensions CT774S
31-1/8" L x 17-1/8" W
x 22-5/8" H

ST774S
23-5/8" L x 8-7/8" W
x 16-7/8" H

INSTALLATION NOTES

Back-to-Back Toilet Installations:

TOTO recommends the use of a nationally listed, double sanitary tee-wye only, in vertical waste stacks, in accordance with the stipulations noted in the majority of nationally recognized plumbing codes.



TOTO

These dimensions and specifications are subject to change without notice