

# TOTO®

# TL960DD12

## Soirée® Widespread Lavatory High-Efficiency Faucet, 1.2 gpm

### FEATURES

- WaterSense certified low-flow 1.2 gpm (4.5 lpm) faucet
- Lever handles
- Solid brass construction
- Ceramic disk valve cartridge
- Accommodates 8"-16" spread
- Metal pop-up drain assembly included



### COLORS/FINISHES

- #CP Polished Chrome
- #BN Brushed Nickel

### CODES/STANDARDS

- Complies with federal and state lead-free legislation
- Meets or exceeds ASME A112.18.1/CSA B125.1, NSF 61-9, NSF 372
- Certifications: IAPMO(cUPC), EPA WaterSense, California Energy Commission (CEC), State of Massachusetts and others
- Code Compliance: UPC, IPC, NSPC, NPC Canada, California Green Building Code, City of Los Angeles Water Efficiency Ordinance, City of New York and others
- ADA compliant
- Complies with CA Prop 65 warning requirements



### PRODUCT SPECIFICATION



The widespread lavatory faucet shall have a maximum flow rate of 1.2 gpm (4.5 lpm). Product shall have lever handles. Product shall have a solid brass construction. Product shall have a ceramic disk valve cartridge. Product shall accommodate 8"-16" spread. Product shall include metal pop-up drain assembly. Product shall be TOTO Model TL960DD12#\_\_\_\_\_.

# TL960DD12

## Soirée® Widespread Lavatory High-Efficiency Faucet, 1.2 gpm

### SPECIFICATIONS

<b>Warranty</b>	Lifetime Limited Warranty (Residential Use) One Year (Commercial Use)
<b>Material</b>	Brass
<b>Maximum Flow Rate</b>	1.2 GPM (4.5 LPM)
<b>Shipping Weight</b>	11.5 lbs.
<b>Shipping Dimensions</b>	20-1/2" L x 9-3/4" W x 3-1/2" H



**TOTO®**

These dimensions and specifications are subject to change without notice