

## MOOD

## STEEL

STEEL







<sup>\*</sup> May require pre-drilling; consult joist manufacturer.

## SAMMYS SWIVEL HEAD<sup>™</sup> FOR WOOD - Swivel Application

鑫	Applicatior	1				Product Features					
	HANGER HANGER MAX ANGLE 89"					<ul> <li>Eliminates distortion of threaded ro.</li> <li>Accommodates up to 3 ½" x 12 pite.</li> <li>Allows 17° deflection from vertical.</li> <li>Saves time from traditional method.</li> <li>Reduces installation costs.</li> <li>Manufactured in the U.S.A.</li> </ul>					ch roof.
	Approvals	Rod Size	Part Number	Model	Screw Descriptions	Ultimate Pullout (lbs)	UL Test Load (Ibs)	FM Test Load (Ibs)	Min Thickness	Box Qty	Case Qty
#14 Black	SWIVEL MOUNT										
Nut Driver – Part # 8113910	<b>D</b> .	3/8"	8139957	SH-GST 20	1/4 x 2"	1257 (Fir)	1050	1475		25	125
	<u>Q</u> .	3/8"*	8269957	SH-GST/CST 20	5/16 x 1-3/4"	1903 Dim. Lumber 1406 @ 45°off vertical Dim. Lumber	1500 850 @ 45°			25	125
	* May require pre-dr	1/2"	8303957 ult joist manuf	SH-GST/CST 2.0	5/16 x 1-3/4"	903 Dim. Lumber 1406 @ 45°off vertical Dim. Lumber				25	125
#14 SH Orange Nut Driver Part # 8273910		ig, oorio	an joint mailuit								