

*American
Standard*

americanstandard.com

CHAMPION[®] PRO[™]



SUPERIOR HET PERFORMANCE. ENGINEERED NOT TO CLOG

- Trade exclusive toilet styles and features
- Champion PRO has robust metal parts not found on products at the big box stores
- Save time with EZ-Install installation kits included at no extra cost
- Full portfolio of 3 bowls and 1 tank

Compare the Champion PRO differences versus other brands:

	CHAMPION PRO	OTHER BRANDS
A FLUSH VALVE	4" Diameter (Largest available)	2" to 3" Diameter
B SIPHON OUTLET	2-3/8" (Largest available)	2" to 2-1/8"
C WATER SPOT	9" x 8"	8" to 10" x 7" to 9"
D BOWL RINSE	PowerWash®	Standard†
SURFACE	Standard with EverClean	Ordinary surface
MAP* SCORE	BEST 1,000 g	400 - 1,000 g
WARRANTY	10 Years (Covers chinaware and trim)	1 Year



TRIP LEVER FINISHES (CHROME COMES STANDARD)



Left Hand Trip Lever: 7381232-200.XXX0A
Right Hand Trip Lever: 7381232-201.0020A

BOWL SHAPE	BOWL MODEL	BOWL HEIGHT	ROUGH-IN	COMBO MODEL	TANK MODEL
RIGHT HEIGHT® ELONGATED	3195A	16-1/2"	12"	211AA	4225A
RIGHT HEIGHT ROUND FRONT	3195B	16-1/2"	12"	211BA	4225A
ELONGATED	3195C	15"	12"	211CA	4225A

CHINAWARE COLORS



1.28 gpf/4.8 Lpf Water Usage Tanks‡

TANK SKU	TANK DESCRIPTION	CHINAWARE COLORS
4225A.104	12" Tank	020, 021, 222, 178
4225A.105	Tank with RHTL	020
4225A.154	Tank with liner	020, 021, 222, 178
4225A.164	Tank with TCLD	020
4225A.174	Tank with TCLD and liner	020

RHTL = Right Hand Trip Lever

TCLD = Tank Cover Lock Device

* Maximum Performance (MaP) testing performed by IAPMO R&T Lab.
MaP Report conducted by Veritec Consulting, Inc. and Koeller and Company.
† Gravity flow through rim punchings.

‡ High Efficiency, ultra-low consumption 1.28 gpf (4.8 Lpf) models utilize 20% less water and meet EPA WaterSense® criteria.

Champion® PRO™



Pictured: 211BA Right Height Round Front Toilet
Cover: 211AA Right Height Elongated Toilet

SCAN FROM YOUR
MOBILE DEVICE TO
LEARN MORE ABOUT
THESE PRODUCTS

