

"Hand Krafted" Construction Tools
Made in the USA Since 1981

GONGRETE MASONRY ASPHALT LEVELS FLOOR COVERING DRYWALL

TABLE OF CONTENTS



CONCRETE	Trowels, Floats, Fresnos, Edgers, Groovers, Screeds	4-60
HI-CRAFT™	Value Priced Trade Tools - Concrete, Masonry, Drywall	61-63
ASPHALT	Lutes, Rakes, Squeegees, Pour Pots, Brooms, Brushes	64-66
SHOVELS	Shovels, Scoops	67
GENERAL CONTRACTOR	Squeegees, Scrapers, Boots, Safety Equipment, Tool Belts	68-72
SANDS LEVEL & TOOL CO.®	Levels, Squares, Rulers, T-Squares	73-83
W.ROSE™	World's Finest Bricklayer's Tools Since 1798	84-90
MASONRY	Trowels, Jointers, Line, Mortar Boxes, Brushes, Archaeology	91-107
PLASTER	Rubber Floats, Hawks, Trowels, Slickers, Darbies	108-112
EIFS	Notch Trowels, Sanding Rasps, Corner Tools	113
DRYWALL	Texture Guns, Taping Knives, Mud Pans, Tapers, Sanders	114-124
TILE & FLOOR COVERING	Tile, Wood, Vinyl, Carpet	125-138
HI-CRAFT™	Value Priced Trade Tools - Floor Covering	135
KITS & DISPLAYS	Apprentice Kits, Displays, Kraft Apparel	139-143
INDEX		144-146



KRAFT TOOL CO.®

8325 Hedge Lane Terrace · Shawnee, Kansas 66227 USA
Phone 800-422-2448 · 913-422-4848
Fax: 800-985-7238 · 913-422-1018
Visit us online: www.KraftTool.com

FOLLOW US











For over 30 years Kraft Tool Co.® has been a leader in manufacturing trowel trade tools. Our goal is to provide the very best professional tools and customer service. Each of our brands represents the very best of concrete, masonry, asphalt, drywall, plaster, tile and floor covering tools.



We proudly manufacture Kraft Tools in the United States of America



NEW PRODUCTS



Elite Series Five Star[™] Plaster Trowels Page 5



Flexible Radius Cement Trowel Page 10



Mag Check Rod Page 27



Coated Steel Threaded Broom Handle Page 33, 68



Double V-Notch Rake Page 56



Long Shaft Junior Mud Mixer Page 57, 66, 117



Clipped Angle Joint Knife Page 63



Diamond-Shaped Joint Knife Page 63



All-Steel Tamper Page 66



Long Handle Round End Drain Spade Page 67



Fiberglass Handle Sledge Hammer Page 68



3 Knot Roof Coating Brush Page 68



Snow Puller Page 68



Floor Squeegees Page 69



W. Rose[™] Limber Blade Masonry Trowels Page 87



Coating/Cleaning Brush Page 98



Green Texture Floats Page 108



Plasterer's Scarifier Page 111



Outside Corner Tool Page 112



10" Steel Joint Knife Page 119



Tile Nipper Page 127



Kraft Tool's Revolutionary Line of Trowels

The Elite Series Five Star Trowel™ is designed and engineered for the professional finisher. These professional trowels are manufactured with state of the art machinery that precisely finish grinds the working surface of each individual trowel. This innovative procedure enables these trowels to possess a truly "broken-in" blade ready for immediate use. The Elite Series Five Star Trowel™ is available in three handle styles that make these tools a finisher's favorite trowel: soft ProForm®, Hardwood and Leather.



Five Star "Broken-In" Blade Ready for Use The Best Blade in the Business

- ★ Stainless Steel Power Pin Rivets for Exceptional Strength
- ★ Greater Flexibility and Durability to Reduce Fatigue
- ★ Unique, Lightweight
- ★ No-Turn Handle
- ★ Precision Ground Edge Ready for Immediate Use

Each Elite Series Five Star
Trowel™ comes with a special
trowel holder to protect the trowel
blade. Protector can also be used
to hang trowels in storage.

Elite Series CONCRETE FINISHING TROWELS



Carbon Steel

Five Star Concrete Trowels

ProForm[®] Handle No. Size CFE211PF 12"x3" CFE212PF 12"x4" CFE216PF 14"x3" 14"x4" CFE217PF 14"x5" CFE534PF CFE222PF 16"x4" 16"x5" CFE535PF 18"x4" CFE227PF 18"x5" CFE546PF CFE231PF 20"x4" CFE232PF 20"x5"

Carbon Steel

Five Star Concrete Trowels

, VIII GIG I
Size
12"x3"
12"x4"
14"x3"
14"x4"
14"x5"
16"x4"
16"x5"
18"x4"
18"x5"
20"x4"
20"x5"

Carbon Steel


Five Star Concrete Trowels

i ive otai	
Leather Han	<u>dle</u>
No.	Size
CFE211L	12"x3'
CFE212L	12"x4'
CFE216L	14"x3'
CFE217L	14"x4'
CFE534L	14"x5'
CFE222L	16"x4'
CFE535L	16"x5'
CFE227L	18"x4'
CFE546L	18"x5'
CFE231L	20"x4'
CFE232L	20"x5'

Flite Series CONCRETE FINISHING TROWELS

Flite Series POOL TROWELS

Flite Series *** PLASTER TROWELS



Golden Stainless Steel

Five Star Concrete Trowels

ProForm [®] Handle		
No.	Size	
CFE536PF	12"x4"	
CFE541PF	14"x4"	
CFE543PF	14"x5"	
CFE545PF	16"x5"	
Wood Handle	<u>e</u>	
No.	Size	
CFE536	12"x4"	
CFE541	14"x4"	
CFE543	14"x5"	
CFE545	16"x5"	
Leather Han	dle	
No.	Size	
CFE536L	12"x4"	
CFE541L	14"x4"	
CFF543I	14"x5"	



Blue Steel Five Star Pool Trowels

ProForm® Handle Shank 6" CFE277BPF 14"x4" short CFE279BPF 16"x4" 7-5/8" short CFE738BPF 18"x4" 15-5/8" long CFE292BPF 18"x5" 9-5/8" short 11-5/8" CFE295BPF 20"x5" short Wood Handle

No. Size Shank 14"x4" 6" CFE277B short CFE279B 16"x4" 7-5/8" short 18"x4" CFE738B 15-5/8" long 9-5/8" CFE292B 18"x5" short 20"x5" 11-5/8" CFE295B short Leather Handle

6" 14"x4" CFE277BL short 16"x4" 7-5/8" CFE279BL short 18"x4" 15-5/8" CFE738BL long CFE292BL 18"x5" 9-5/8" short 11-5/8" CFE295BL 20"x5" short



Golden Stainless Steel Five Star Plaster Trowels

 ProForm®
 Handle

 No.
 Size

 PLE454PF
 11"x4-1/2"

 PLE457PF
 11-1/2"x4-3/4"

 PLE459PF
 12"x5"

 PLE460PF
 13"x5"

 Wood Handle

No. Size
PLE454 11"x4-1/2"
PLE457 11-1/2"x4-3/4"
PLE459 12"x5"
PLE460 13"x5"

Leather Handle
No. Size

PLE454L 11"x4-1/2" PLE457L 11-1/2"x4-3/4" PLE459L 12"x5" PLE460L 13"x5"

Carbon Steel

Five Star Plaster Trowels ProForm® Handle

No. Size
PLE425PF 10-1/2"x4-1/2" NEW
PLE451PF 11"x4-1/2"
PLE468PF 12"x5" NEW
PLE470PF 13"x5" NEW
Wood Handle
No. Size
PLE425 10-1/2"x4-1/2" NEW

PLE425 10-1/2"X4-1/2" NE PLE451 11"x4-1/2" PLE468 12"x5" NE

PLE468 12"x5" **NEW**PLE470 13"x5" **NEW**<u>Leather Handle</u>

No. Size PLE425L 10-1

PLE425L 10-1/2"x4-1/2" **NEW**PLE451L 11"x4-1/2"
PLE468L 12"x5" **NEW**PLE470L 13"x5" **NEW**

3 Handle Styles SOFT GRIP PROFORM®

16"x5"

Handle reduces muscle fatigue after a long day on the job.

LEATHER

CFE545L

Wicks away sweat from hand for a comfortable grip. The only leather handle finishing trowel on the market.

LAMINATED HARDWOOD

Handle comes in a variety of vibrant patterns.



CONCRETE FINISHING TROWELS


Professional Quality Precision Balanced Ready to Use

- Guaranteed NO-TURN handle design locks handle to mounting.
- Each blade is cross ground to just the right dimension for that perfect feel.
- Features a high-strength, lightweight aluminum mounting.
- · Compression fit stainless steel rivets.
- Oversized toe rivet for extra strength.
- Comfortable ProForm® handle with contoured shape and an enhanced textured ribbing for a "GREAT GRIP."









Carbon Steel

	ck Wood Handle		
No.	Size		
CF201C	10"x3"		
CF202C	10"x4"		
CF207C	11"x4"		
CF211C	12"x3"		
CF212C	12"x4"		
CF216C	14"x3"		
CF215C	14"x3-1/2"		
CF217C	14"x4"		
CF218C	14"x4-1/2"		
CF219C	14"x4-3/4"		
CF534C	14"x5"		
CF221C	16"x3"		
CF220C	16"x3-1/2"		
CF222C	16"x4"		
CF223C	16"x4-1/2"		
CF224C	16"x4-3/4"		
CF535C	16"x5"		
CF226C	18"x3"		
CF225C	18"x3-1/2"		
CF227C	18"x4"		
CF228C	18"x4-1/2"		
CF229C	18"x4-3/4"		
CF546C	18"x5"		
CF231C	20"x4"		
CF232C	20"x5"		
CF550C	22"x5"		
CF233C	24"x4"		
CF234C	24"x5"		

Carbon Steel

Straight	Wood Handle
No.	Size
CF201	10"x3"
CF202	10"x4"
CF207	11"x4"
CF211	12"x3"
CF212	12"x4"
CF216	14"x3"
CF215	14"x3-1/2"
CF217	14"x4"
CF218	14"x4-1/2"
CF219	14"x4-3/4"
CF221	16"x3"
CF220	16"x3-1/2"
CF222	16"x4"
CF223	16"x4-1/2"
CF224	16"x4-3/4"
CF226	18"x3"
CF225	18"x3-1/2"
CF227	18"x4"
CF228	18"x4-1/2"
CF229	18"x4-3/4"
CF231	20"x4"
CF232	20"x5"





Golden Stainless Steel

- Heat treated golden stainless steel
- · Special alloy will not rust, pit, or stain
- Forged aluminum shank

Camel Back Wood Handle

Carrier Dack	VVOOU Hallu
No.	Size
CF536	12"x4"
CF541	14"x4"
CF540	14"x4-3/4"
CF543	14"x5"
CF533	16"x4"
CF542	16"x4-1/2"
CF545	16"x5"
CF547	18"x4"
CF548	18"x5"
CF549	20"x5"

ProForm® Soft Grip Handle

No.	Size
CF536PF	12"x4"
CF541PF	14"x4"
CF540PF	14"x4-3/4"
CF543PF	14"x5"
CF533PF	16"x4"
CF542PF	16"x4-1/2"
CF545PF	16"x5"
CF547PF	18"x4"
CF548PF	18"x5"
CF549PF	20"x5"



Blue Steel

Round End Burn Trowel

High quality blue steel. 3" rounded narrow blade with long shank. Allows finishers to apply pressure for smooth, hard finish.

Camel Back Wood Handle

No. Size CF470 12"x3" CF471 14"x3"

ProForm® Soft Grip Handle

No.	Size
CF470PF	12"x3"
CF471PF	14"x3"

Blue Steel

- High quality blue steel blade with additional flexibility
- · Forged aluminum shank

Camel Back Wood Handle

No.	Size
CF725B	10"x4"
CF726B	12"x3"
CF730B	12"x4"
CF727B	14"x3"
CF731B	14"x4"
CF732B	16"x4"
CF535B	16"x5"
CF729B	18"x4"
CF733B	18"x5"
CF728B	20"x4"
CF734B	20"x5"
CF743B	24"x4"
CF735B	24"x5"

ProForm® Soft Grip Handle

No.	Size
CF725BPF	10"x4"
CF726BPF	12"x3"
CF730BPF	12"x4"
CF727BPF	14"x3"
CF731BPF	14"x4"
CF732BPF	16"x4"
CF535BPF	16"x5"
CF729BPF	18"x4"
CF733BPF	18"x5"
CF728BPF	20"x4"
CF734BPF	20"x5"
CF743BPF	24"x4"
CF735BPF	24"x5"

Replacement Handles

ProForm® Soft Grip Handle

No. Description

CF053 ProForm® Camel Back Handle

Wood Handles

No. Description
CF052 Straight Handle
CF051 Camel Back Handle



Swedish Stainless Steel

- High quality heat treated Swedish stainless steel
- Special alloy will not rust, pit, or stain
- Forged aluminum shank

Camel Back Wood Handle

No.	Size	
CF742	12"x4	
CF744	14"x4	
CF747	16"x4	

ProForm® Soft Grip Handle

NO.	Size
CF742PF	12"x4"
CF744PF	14"x4"
CF747PF	16"x4"

Carbon Steel Midget Trowel

Great for window sills, closets and small areas. Carry one in your tool bag

for those tough-to-reach jobs.

Camel Back Wood Handle

 No.
 Size

 PL407
 8"x3"

 PL408
 8"x5"

 ProForm®
 Soft Grip Handle

 PL407PF
 8"x3"

 PL408PF
 8"x5"

Carbon Steel Mini Pool Trowel

Finish hard to get places, wall forms, window sills and small areas.

Camel Back Wood Handle

No. Size
CF724 7-1/2"x4"

ProForm® Soft Grip Handle
CF724PF 7-1/2"x4"

POOL TROWELS



Carbon Steel

Short Shanks, Flexible Blade

Forged aluminum shanks

Camel Back Wood Hand	
Carrier Dack Wood Harid	le

No.	Size	Shank
CF435	10"x3"	3"
CF436	12"x3-1/2"	4-3/8"
CF437	14"x4"	6"
CF438	16"x4"	7-5/8"
CF439	18"x5"	9-5/8"
CF440	20"x5"	11-5/8"
CF441	22"x4"	13-5/8"
CF442	24"x4"	13-5/8"
CF445	24"x5"	13-5/8"
<u>ProForm</u> ®	Soft Grip Har	<u>ndle</u>
ProForm® CF435PF	Soft Grip Har 10"x3"	<u>ndle</u> 3"
	-	
CF435PF	10"x3"	3"
CF435PF CF436PF	10"x3" 12"x3-1/2"	3" 4-3/8"
CF435PF CF436PF CF437PF	10"x3" 12"x3-1/2" 14"x4"	3" 4-3/8" 6"
CF435PF CF436PF CF437PF CF438PF	10"x3" 12"x3-1/2" 14"x4" 16"x4"	3" 4-3/8" 6" 7-5/8"
CF435PF CF436PF CF437PF CF438PF CF439PF	10"x3" 12"x3-1/2" 14"x4" 16"x4" 18"x5"	3" 4-3/8" 6" 7-5/8" 9-5/8"
CF435PF CF436PF CF437PF CF438PF CF439PF CF440PF	10"x3" 12"x3-1/2" 14"x4" 16"x4" 18"x5" 20"x5"	3" 4-3/8" 6" 7-5/8" 9-5/8" 11-5/8"

Blue Steel

Long Shanks

- Longer shank creates a less flexible blade
- Rounded edges prevent surface gouging Camel Back Wood Handle

No.	Size	Shank	
CF721B	12"x4"	9-5/8"	
CF736B	14"x4"	11-5/8"	
CF737B	16"x4"	13-5/8"	
CF742B	16"x5"	14-5/8"	
CF738B	18"x4"	15-5/8"	
CF739B	20"x4"	15-5/8"	
CF740B	20"x5"	15-5/8"	
CF741B	22"x4"	15-5/8"	
CF745B	24"x4"	15-5/8"	
CF746B	24"x5"	15-5/8"	
017.100	24 XU	10 0/0	
	Soft Grip H		
ProForm® 3	Soft Grip H	andle	
ProForm® CF721BPF	Soft Grip H 12"x4"	9-5/8"	
ProForm® CF721BPF CF736BPF	Soft Grip H 12"x4" 14"x4"	9-5/8" 11-5/8"	
ProForm® CF721BPF CF736BPF CF737BPF	Soft Grip H 12"x4" 14"x4" 16"x4"	9-5/8" 11-5/8" 13-5/8"	
ProForm® CF721BPF CF736BPF CF737BPF CF742BPF	Soft Grip H 12"x4" 14"x4" 16"x4" 16"x5"	9-5/8" 11-5/8" 13-5/8" 14-5/8"	
ProForm® S CF721BPF CF736BPF CF737BPF CF742BPF CF738BPF	Soft Grip H 12"x4" 14"x4" 16"x4" 16"x5" 18"x4"	9-5/8" 11-5/8" 13-5/8" 14-5/8" 15-5/8"	

24"x4"

24"x5"

15-5/8"

15-5/8"



Blue Steel

Short Shanks, Flexible Blade Camel Back Wood Handle

No.	Size	Shank
CF274B	10"x3"	3"
CF271B	12"x3"	4-3/8"
CF276B	12"x3-1/2"	4-3/8"
CF275B	12"x4"	4-3/8"
CF272B	14"x3"	6"
CF277B	14"x4"	6"
CF273B	16"x3"	7-5/8"
CF279B	16"x4"	7-5/8"
CF280B	16"x5"	9-5/8"
CF292B	18"x5"	9-5/8"
CF293B	20"x4"	11-5/8"
CF295B	20"x5"	11-5/8"
CF296B	22"x5"	13-5/8"
CF297B	24"x5"	13-5/8"
ProForm® .	Soft Grip Har	<u>idle</u>
CF274BPF	10"x3"	3"
0		
CF271BPF	12"x3"	4-3/8"
	12"x3-1/2"	4-3/8" 4-3/8"
CF271BPF		4-3/8" 4-3/8"
CF271BPF CF276BPF CF275BPF CF272BPF	12"x3-1/2" 12"x4" 14"x3"	4-3/8" 4-3/8" 6"
CF271BPF CF276BPF CF275BPF	12"x3-1/2" 12"x4" 14"x3" 14"x4"	4-3/8" 4-3/8"
CF271BPF CF276BPF CF275BPF CF272BPF	12"x3-1/2" 12"x4" 14"x3" 14"x4" 16"x3"	4-3/8" 4-3/8" 6"
CF271BPF CF276BPF CF275BPF CF272BPF CF277BPF CF273BPF CF279BPF	12"x3-1/2" 12"x4" 14"x3" 14"x4" 16"x3" 16"x4"	4-3/8" 4-3/8" 6" 6" 7-5/8" 7-5/8"
CF271BPF CF276BPF CF275BPF CF272BPF CF277BPF CF273BPF CF279BPF CF280BPF	12"x3-1/2" 12"x4" 14"x3" 14"x4" 16"x3" 16"x4" 16"x5"	4-3/8" 4-3/8" 6" 6" 7-5/8" 7-5/8" 9-5/8"
CF271BPF CF276BPF CF275BPF CF272BPF CF277BPF CF273BPF CF279BPF	12"x3-1/2" 12"x4" 14"x3" 14"x4" 16"x3" 16"x4" 16"x5" 18"x5"	4-3/8" 4-3/8" 6" 6" 7-5/8" 7-5/8" 9-5/8" 9-5/8"
CF271BPF CF276BPF CF275BPF CF272BPF CF277BPF CF273BPF CF279BPF CF280BPF CF292BPF CF293BPF	12"x3-1/2" 12"x4" 14"x3" 14"x4" 16"x3" 16"x4" 16"x5" 18"x5" 20"x4"	4-3/8" 4-3/8" 6" 6" 7-5/8" 7-5/8" 9-5/8" 9-5/8" 11-5/8"
CF271BPF CF276BPF CF275BPF CF272BPF CF277BPF CF273BPF CF279BPF CF280BPF CF292BPF CF293BPF CF295BPF	12"x3-1/2" 12"x4" 14"x3" 14"x4" 16"x3" 16"x4" 16"x5" 18"x5" 20"x4"	4-3/8" 4-3/8" 6" 6" 7-5/8" 7-5/8" 9-5/8" 9-5/8" 11-5/8"
CF271BPF CF276BPF CF275BPF CF272BPF CF277BPF CF273BPF CF279BPF CF280BPF CF292BPF CF293BPF CF295BPF CF296BPF	12"x3-1/2" 12"x4" 14"x3" 14"x4" 16"x3" 16"x4" 16"x5" 18"x5" 20"x4" 20"x5"	4-3/8" 4-3/8" 6" 6" 7-5/8" 7-5/8" 9-5/8" 9-5/8" 11-5/8" 13-5/8"
CF271BPF CF276BPF CF275BPF CF272BPF CF277BPF CF273BPF CF279BPF CF280BPF CF292BPF CF293BPF CF295BPF	12"x3-1/2" 12"x4" 14"x3" 14"x4" 16"x3" 16"x4" 16"x5" 18"x5" 20"x4"	4-3/8" 4-3/8" 6" 6" 7-5/8" 7-5/8" 9-5/8" 9-5/8" 11-5/8"



Carbon Steel

Long Shanks

- Longer shank creates a less flexible blade
- Rounded edges prevent surface gouging

Camel Back Wood Handle

No.	Size	Shank
CF429	12"x4"	9-5/8"
CF446	14"x4"	11-5/8"
CF447	16"x4"	13-5/8"
CF448	18"x4"	15-5/8"
CF450	18"x5"	15-5/8"
CF449	20"x4"	15-5/8"
CF451	20"x5"	15-5/8"
<u>ProForm</u> ®	Soft Grip H	andle_
ProForm® CF429PF	Soft Grip H	<u>andle</u> 9-5/8"
		-
CF429PF	12"x4"	9-5/8"
CF429PF CF446PF	12"x4" 14"x4"	9-5/8" 11-5/8"
CF429PF CF446PF CF447PF	12"x4" 14"x4" 16"x4"	9-5/8" 11-5/8" 13-5/8"
CF429PF CF446PF CF447PF CF448PF	12"x4" 14"x4" 16"x4" 18"x4"	9-5/8" 11-5/8" 13-5/8" 15-5/8"
CF429PF CF446PF CF447PF CF448PF CF450PF	12"x4" 14"x4" 16"x4" 18"x4" 18"x5"	9-5/8" 11-5/8" 13-5/8" 15-5/8" 15-5/8"



Swedish Stainless Steel

Short Shanks, Flexible Blade

• Forged aluminum shanks

CF745BPF

CF746BPF

Camel Back Wood Handle

Carrier Da	CK WOOD Hall	110
No.	Size	Shank
CF325	10"x3"	3"
CF326	12"x3-1/2"	4-3/8"
CF329	14"x3"	6"
CF327	14"x4"	6"
CF330	16"x3"	7-5/8"
CF328	16"x4"	7-5/8"
ProForm ®	Soft Grip Har	ndle
CF325PF	10"x3"	3"
CF326PF	12"x3-1/2"	4-3/8"
CF329PF	14"x3"	6"
CF327PF	14"x4"	6"
CF330PF	16"x3"	7-5/8"

16"x4"

7-5/8"

CF328PF



Golden Stainless Steel

Short Shanks, Flexible Blade Camel Back Wood Handle

No. Size Shank CF274 10"x3" 3" CF276 12"x3-1/2" 4-3/8" CF277 14"x4" 6" 16"x4" CF279 7-5/8" ProForm® Soft Grip Handle 10"x3" 3"

CF274PF 12"x3-1/2" CF276PF 4-3/8" 6" CF277PF 14"x4" 16"x4" 7-5/8" CF279PF



Chrome (No Burn)

Exposed Rivets for Extra Strength

- Extra hard troweling blade for long wear
- Forged aluminum shanks
- The hardened chrome surface is great for pool work
- Eliminates burn marks

Camel Back Wood Handle

No.	Size	Shank
CF490	10"x3"	3-1/2"
CF491	12"x3-1/2"	5-1/2"
CF492	14"x3"	6"
CF493	14"x4"	6"
CF494	16"x3"	7-5/8"
ProForm ®	Soft Grip Har	ndle
ProForm® CF490PF		<u>ndle</u> 3-1/2"
	Soft Grip Har	
CF490PF	Soft Grip Har 10"x3"	3-1/2"
CF490PF CF491PF	Soft Grip Har 10"x3" 12"x3-1/2"	3-1/2" 5-1/2"

Blue Steel

CF343BPF

Round Front Square Back

- Round front minimizes trowel marks
- Square back allows trowel to get close to forms

Camel Back Wood Handle

No.	Size
CF213B	10"x4"
CF214B	12"x4"
CF284B	14"x4"
CF285B	16"x4"
CF230B	16"x5"
CF343B	18"x5"
	Soft Grip Handle
ProForm®	Soft Grip Handle
ProForm® CF213BPF	Soft Grip Handle 10"x4"
ProForm® CF213BPF CF214BPF	Soft Grip Handle 10"x4" 12"x4"

18"x5"

Carbon Steel

Round Front Square Back

- Round front minimizes trowel marks
- Square back allows trowel to get close to forms

Camel Back Wood Handle

No.	Size
CF428	10"x4"
CF284	14"x4"
CF285	16"x4"
CF286	18"x4"
CF343	18"x5"
CF287	20"x4"
CF288	20"x5"
CF340	22"x4"
CF341	22"x5"
CF342	24"x5"

ProForm® Soft Grip Handle

CF428PF	10"x4"
CF284PF	14"x4"
CF285PF	16"x4"
CF286PF	18"x4"
CF343PF	18"x5"
CF287PF	20"x4"
CF288PF	20"x5"
CF340PF	22"x4"
CF341PF	22"x5"
CF342PF	24"x5"

PLASTER TROWELS



Carbon Steel

Camel Back Wood Handle

No.	Size
PL425	10-1/2"x4-1/2"
PL451	11"x4-1/2"
PL447	11"x4-3/4"
PL456	11-1/2"x4-1/2"
PL448	11-1/2"x4-3/4"
PL468	12"x5"
PL470	13"x5"
ProForm ®	Soft Grip Handle
PL425PF	10-1/2"x4-1/2"
DI 454 DE	4411 4 4 (011

PL451PF 11"x4-1/2" PL447PF 11"x4-3/4" PL456PF 11-1/2"x4-1/2" PL448PF 11-1/2"x4-3/4" PI 468PF 12"x5" PL470PF 13"x5"

View more Plaster products on pages 108-112



Swedish Stainless Steel

- Made of heat treated Swedish stainless
- Special alloy will not rust, pit, or stain
- Forged aluminum shanks

Camel Back Wood Handle

Camer bac	k wood mandie
No.	Size
PL525	10-1/2"x4-1/2"
PL551	11"x4-1/2"
PL547	11"x4-3/4"
PL556	11-1/2"x4-1/2"
PL548	11-1/2"x4-3/4"
PL568	12"x5"
PL570	13"x5"
ProForm ®	Soft Grip Handle
PL525PF	10-1/2"x4-1/2"
PL551PF	11"x4-1/2"
PL547PF	11"x4-3/4"





Golden Stainless Steel

- Made of heat treated golden stainless steel
- Special alloy will not rust, pit, or stain
- Forged aluminum shanks

Camel Back Wood Handle

Carrier Back	Wood Hallaic
No.	Size
PL452	10-1/2"x4-1/2"
PL454	11"x4-1/2"
PL455	11"x4-3/4"
PL453	11-1/2"x4-1/2"
PL457	11-1/2"x4-3/4"
PL459	12"x5"
PL460	13"x5"

ProForm® Soft Grip Handle

PIOFOIII	Soft Grip Harius
PL452PF	10-1/2"x4-1/2"
PL454PF	11"x4-1/2"
PL455PF	11"x4-3/4"
PL453PF	11-1/2"x4-1/2"
PL457PF	11-1/2"x4-3/4"
PL459PF	12"x5"
PL460PF	13"x5"



Silo Trowel

Carbon Steel Rounded Corner

Finish hard to reach places. Four special rounded corners (1/2" radius) prevents digging on slab.

Camel Back Wood Handle

No. Size 14"x4" CF332 16"x4" CF333

ProForm® Soft Grip Handle

Size CF332PF 14"x4" CF333PF 16"x4"



Carbon Steel Pipe Trowel

Finish hard to get places in half the time, with half the effort. The offset handle lets you slip the trowel between pipes: the long nose makes it easy to get behind fixtures.

Straight Wood Handle

No. Size PL501 10-1/2"x3" ProForm® Soft Grip Handle

No. Size PL501PF 10-1/2"x3"


Trowel Bracket

When used with a standard fresno handle this device turns a normal concrete steel finishing trowel into a small fresno. Just remove handle and add bracket to trowel. Fits on all Kraft finishing trowels.

No. Description

Single Action Bracket CC657 CC658 Swivel Action Bracket

Order Finishing Trowels Separately Professional Pool Trowels See Page 8



Plexi-Plastic Trowels

Plexi-plastic trowel has an aluminum mounting and is made from a special plastic for better wear. It is used on white portland, interior stucco, swimming pools and on special projects requiring trowels that will not blacken material.

ROUND END

Camel Back Wood Handle

No. Size PI 610 10"x3" PL612 12"x3-1/2" 14"x4" PL614 PL616 16"x4"

ProForm® Soft Grip Handle

No. Size PL610PF 10"x3" PL612PF 12"x3-1/2" PL614PF 14"x4" PL616PF 16"x4"

SQUARE END

Camel Back Wood Handle

No. Size 11"x4-1/2" PL658 ProForm® Soft Grip Handle

No. Size PL658PF 11"x4-1/2"



Flexible Radius Trowels

High grade steel blade flexes to various radii. Fewer rivets create a wider range of motion for the blade. High-strength, short shank aluminum mountings provide additional flexibility to work surface while maintaining control. Camel back wood handle.

Pool Trowels

No.	Material	Size	Rivets
CF277B-5R	Blue Steel	14"x4"	5
CF279B-5R	Blue Steel	16"x4"	5
CF738B-6R	Blue Steel	18"x4"	6
CF437-5R	Carbon Steel	14"x4"	5
CF438-5R	Carbon Steel	16"x4"	5
CF448-6R	Carbon Steel	18"x4"	6



Finishing Trowels

Material No. Size Rivets CF731B-5R 14"x4" Blue Steel CF729B-10R 18"x4" Blue Steel 10

Trowel Sharpener

Keeps edges sharp. Ideal tool for eliminating small nicks and dull edges of finishing trowels.

No. CF200



Order Handles and Adapters seperately

Funny Trowel Replacement **Bracket** CC661

Funny Trowel

Blue steel blade with handle bracket (CC661). Ideal for extra reach or finishing under overhangs or obstructions.

No. Size 24"x5" CC624F



Trapezoid shape stainless steel finish trowels. Designed for finishing and polishing decorative plaster and stucco. Machined edge with smooth bright finish.

ProForm® Soft Grip Handle

Size No. PL627PF 8"x3"

203mmx76mm (small) PL628PF 9-1/2"x3-1/2"

241mmx89mm (med.)

Camel Back Wood Handle

Size No. PL627 8"x3"

203mmx76mm (small)

9-1/2"x3-1/2" PL628

241mmx89mm (med.)





MAG HAND FLOATS



Professional Quality Mag Floats

Tough durable Extru-Lite Magnesium™ blade offers superb floating action Float ends are beveled and the blade is "broken-in" with rounded corners Precise handle position gives perfect balance



Square End Mag Float ProForm® Handle

No.	Size
CF012PF	12"x3-1/4"
CF014PF	14"x3-1/4"
CF016PF	16"x3-1/4"
CF018PF	18"x3-1/4"
CF020PF	20"x3-1/4"
CF024PF	24"x3-1/4"

Standard Wood Handle		
Size		
12"x3-1/4"		
14"x3-1/4"		
16"x3-1/4"		
16"x3-1/4" (no paint)		
18"x3-1/4"		
20"x3-1/4"		
24"x3-1/4"		
ood Handle		
Size		
12"x3-1/4"		
14"x3-1/4"		
16"x3-1/4"		
18"x3-1/4"		
20"x3-1/4"		

24"x3-1/4"

Round End Mag Float

ProForm® Handle

No.	Size
CF076PF	16"x3-1/4"
CF074PF	18"x3-1/4"
CF075PF	20"x3-1/4"
High Lift	Wood Handle

No. Size CF076 16"x3-1/4" 18"x3-1/4" CF074 CF075 20"x3-1/4"

Round Front Square Back Mag Float

ProForm® Handle No. Size CF078PF 16"x3-1/4" Standard Wood Handle Size CF078 16"x3-1/4"

Replacement Wood Float Handles

A) 10" Wood Float Handle

No. CF261

B) 10" Wood Drilled Countersunk Handle

C) 10" Wood High Lift Float Handle

No. CF050

D) Fits only rubber floats, your choice of wood or plastic handle

No. CF263 7-1/4" Wood Float Handle No. CF263P 7-1/4" Plastic Float Handle (not shown)

E) 10" Wood Replacement Handle with

Larger Diameter No. CF265



Float Hook

Float hook clips to belt. Holds hand floats and other tools.

No. CF011



Replacement ProForm® Float Handles Soft textured ProForm® Handle with special ribbing for that

"Great Grip"

A) 10" ProForm® Soft Grip Float Handle

No. CF266

B) 10" Large Diameter ProForm® Soft Grip Handle for Mag-150™ and ThinLine Floats

No. CF266CB





Mini Mag Float

Extra lightweight magnesium wall float. Great tool for floating in small areas, stairs or top of wall between forms. Fitted with ProForm® handle. Blade measures 7-1/2"x3-1/4".

No. CF663PF

CF024M



Professional Quality Mag Floats

Durable Magnesium blade offers superb floating action Float ends are beveled and the blade is "broken-in" with rounded corners Precise handle position gives perfect balance


ThinLine Pro Mag Float

Cast Magnesium

- Tough, durable cast magnesium blade
- Thin edges and smooth rounded corners gives this float that perfect "broken-in" feel
- Precise handle position provides a perfect balance
- Float design allows for greater knuckle clearance in large diameter wood handle. Also available with ProForm® soft grip handle.

Large Diameter Wood Handle

No. Size CF064 16"x3-1/8" ProForm® Handle Size CF064PF 16"x3-1/8"




MAG-150™ Float

Cast Magnesium

- Tough, durable cast magnesium blade
- · Great "broken-in" feel with beveled ends
- · Larger diameter wood handle allows for improved user control. Also available with ProForm® soft grip handle.

Large Diameter Wood Handle

No. Size 16"x3-1/2" CF150 ProForm® Handle No. Size CF150PF 16"x3-1/2



Wide Mag Float

Extruded Magnesium

- Tough, durable 3-1/2" Extru-Lite Magnesium™ blade
- Precise handle position gives the float perfect balance and superb floating action
- Beveled edges and smooth rounded corners gives this float that perfect "broken-in" feel

Standard Wood Handle

No. Size CF015 16"x3-1/2" High Lift Wood Handle No. Size

CF015M 16"x3-1/2" ProForm® Handle No. Size

XTRU-LITE™

CF015PF





16"x3-1/2"

Sand Cast Mag Float

"The Original"

- Tough, durable long-wearing sand cast magnesium blade
- Made the same as it was fifty years ago
- Precise handle position gives the float perfect balance and superb floating action
- Comfortable large diameter wood handle
- · Corners rounded and both ends beveled

Large Diameter Wood Handle

No. Size CF066 16"x3-1/4"



Redwood Float

Top quality clear heart redwood float with comfortable handle. This lightweight float is easy to work with on outdoor projects. You'll have many uses for these two popular sizes.

No. Size CF251 12"x5" CF252 15"x5"



Laminated Canvas-Resin Float

Wears like magnesium for extremely long life. Laminated canvas-resin is 3/8" thick with broken-in face. Ready to use.

A) Round Ends

Wood Handle		ProForm [®] Handle	
No.	Size	No.	Size
CF501	16"x3-1/2"	CF501PF	16"x3-1/2"
CF502	18"x3-1/2"	CF502PF	18"x3-1/2"
CF524	20"x3-1/2"	CF524PF	20"x3-1/2"


B) Square Ends


Wood I	Handle	ProForm [®] Handle	
No.	Size	No.	Size
CF503	12"x3-1/2"	CF503PF	12"x3-1/2"
CF504	14"x3-1/2"	CF504PF	14"x3-1/2"
CF505	16"x3-1/2"	CF505PF	16"x3-1/2"
CF506	18"x3-1/2"	CF506PF	18"x3-1/2"
CF507	20"x3-1/2"	CF507PF	20"x3-1/2"

C) Wide Sizes

Wood Handle		ProForm [®] Handle	
No.	Size	No.	Size
CF529	12"x5"	CF529PF	12"x5"
CF530	14"x5"	CF530PF	14"x5"
CF531	16"x5"	CF531PF	16"x5"







Laminated Canvas-Resin Darby

Quickly covers more area than a regular float. Long-wearing canvas-resin 3/8" thick; has rounded corners and "broken-in" shape. Ready to use. Perfect tool for curb and gutter forming.

No. Size

CF037 40"x3-1/2" Straight Darby


d gutter forming.

Cast Magnesium Beveler Float

Large Diameter Wood Handle

Float designed to provide an 8" or 12" bevel in front of overhead doors for water drainage. Blade measures 16"x3-1/4".

No. Size CF066H-8 8" Bevel CF066H-12 12" Bevel



US Patent # 6,183,237



7/8" Deep Lip

12" Bevel

5/8" Wide Lip 7/8" Deep Lip

HAND FLOATS

Beveled Redwood Float

Made of the best top quality clear heart redwood. The float face is beveled to make it possible to work in the tightest quarters.

No. Size CF256 15"x3-1/2" CF257 18"x3-1/2"



Bodark Wood Float

Bodark floats outlast ordinary floats. Handle is bonded to the blade. Popular float with many finishers.

 Wood Handle
 ProForm® Handle


 No.
 Size

 CF642
 16"x2-1/4"

 CF643
 16"x3"

 CF644
 20"x3"

 CF644PF
 20"x3"



Very hard, long wearing 5/8" thick float. Comes with 10" float handle.

CF269 18"x3-1/4"

Cast Magnesium
Drain Float

Large Diameter Handle

Beveled to allow finisher to use around floor drains and other areas where water drainage or run off is essential. "Broken-in" blade is hand ground.

US Patent # 6,183,237

No. Size CF066H-D 16"x3-1/4"



WITH SINGLE FLOAT AND FRESNO BRACKETS

Threaded Fresno or Broom Bracket

Attach to fresno or broom to lock the handle at the best angle. Use with 1-1/4" and 1-3/4" threaded handles.

No. CC665

Button Fresno or Broom Bracket

Attach to single action fresno or broom to lock the handle at the best angle. Use with 1-3/8" and 1-3/4" button handles.


No. CC666

Button Handle Float Brackets

Quick and easy coupling of 1-3/8" or 1-3/4" button handles. Handle sockets adjust to desired anale.

Description No.

CC696 A) Complete 4-Hole Bracket CC697 B) Complete 2-Hole Bracket Button Handle Socket (only) CC698



Threaded Handle Float Brackets

Handle socket fits all 1-1/4", 1-1/2" or 1-3/4" threaded extension handles. Handle sockets adjust to desired angle.

A) 2-Hole Bracket

No. Description

CC676 Complete 2-Hole Bracket CC678 Threaded Handle Socket (only)


CC681 Bracket Base (only)

B) 4-Hole Bracket

Description No.

CC800 Complete 4-Hole Bracket CC678 Threaded Handle Socket (only)

CC679 Bracket Base (only)



MULTI-TWIST™ BRACKETS



Multi-Twist™

Concrete Tool Brackets

These small brackets rotate 360° to work from all angles. Attach brackets to brooms, bull floats, edgers, fresnos or groovers. Twist the handle to tighten and set any angle. Adapters connect to push button or threaded handles.

A) Clevis Handle Bracket

Use with walking groovers, edgers, brooms and tools with clevis brackets.

No. CC686*

B) 6-Hole Handle Bracket

Fits all 2 or 4 hole floats.

No. CC687*

C) 2-Hole Handle Bracket

Attach to fresnos, bull floats or brooms.

No. CC688*

D) Push Button Handle Adapter


Connects to 1-3/8" and 1-3/4" button extension handles.

No. CC689*

E) Threaded Handle Adapter

Connects to all threaded bull float handles. No. CC685*

> **Multi-Twist Tool Brackets MUST** be used with adapter















WITH DOUBLE BUTTON HANDLE FLOAT BRACKETS

EZY-Tilt® II

• Made of rugged lightweight aluminum

• One to one turning ratio of handle and pitch of blade

Eliminates bending and lifting

• Designed to fit all 2 or 4 hole metal bull floats No. CC294



EZY-Tilt®

• Made of rugged lightweight aluminum

• Pitch of blade controlled by turning handle

· Eliminates bending and lifting

• Fits only 2 hole metal bull floats • Converter plate (CC287) required

when mounting to 4 hole metal bull float

No. CC290





ALL Double Action Tilt Brackets accept handles inside or outside of the bracket!

Use them with any 1-3/8" or 1-3/4" button handles!

Knucklehead® II Bull Float Bracket

"The Original"

Lighter design helps to eliminate concrete build up! Fits all 2 or 4 hole metal bull floats. No adapter needed.


• Made of rugged lightweight aluminum

• One to one turning ratio of handle and pitch of blade

• Protected grease reservoir for longer wear

• Turning handle eliminates bending and lifting No. CC296

US Patent #4.335.485



Knucklehead® II Rebuild Kit

Includes plastic bushing and snap rings.

No. CC296K

Bronco[™] Tilt

• Made of rugged lightweight aluminum • Pitch of the blade is controlled by

turning the handle

• Eliminates bending and lifting

• Designed to fit all 2 or 4 hole metal bull floats

 No adapter needed No. CC280





- Quick & easy turning action
- Pitch of float blade controlled by turning handle
- Floats flush against the wall
- Fits ALL 2 or 4 hole floats No. CC270*

Converter Plate

Use to convert a 4-hole mount to a 2-hole mount for more versatility.

No. CC287



THREADED EXTENSION HANDLES

MAGNESIUM IS 30% LIGHTER THAN ALUMINUM

Aluminum Threaded

1-3/4" or 1-1/4" Diameter

- Molded thread plugs in each end join handles together
- Fits bull float/fresno threaded brackets and can be combined with 1-1/4" or 1-3/4" float handles made by other manufacturers

1-3/4" Diameter

Size No. CC234 6' CC236 CC238 8' CC239** 10'

1-1/4" Diameter No. Size

CC668 4' CC670

**Must ship via truck

Magnesium Threaded

1-3/4" Diameter

- Lightest handle available in 6 sizes
- Magnesium prevents hands from turning black caused by oxidation
- · Threaded handles are lightweight and extra strong
- Fits bull float and fresno threaded brackets and can be combined with 1-3/4" float handles made by other manufacturers
- Molded thread plugs in each end join handles together

1-3/4" Diameter

. o, . = .a	
No.	Siz
CC224	4'
CC225	5'
CC226	6'
CC227	8'
CC228**	10'
CC229**	12'

**Must ship via truck



ADAPTERS

1-3/4" Diameter **Aluminum Adapters** Threaded to Button Handle Adapters

- Adapters allow finisher to use lightweight button handles with threaded-type bracket assemblies
- · Also can be used to adapt other bracket and handle connections

No. Description CC286 Male CC285 Female



Clevis to Button Handle Adapter

• Adapts clevis style tools to 1-3/4" snap style handles



1-3/8" Button Handle Style **Adapters**

Clevis to Button Handle Bracket

This adapter is for use with western-style longhandled tools. It is used with walking edgers, walking groovers, long-handled trowels, fresnos and other tools with post-type or angle connectors.

No. Description CC332 8" Long Clevis CC332L 12" Long Clevis

Threaded to Button Handle Bracket

This adapter can be used with 1-3/8" button handles and other similar handles. It is used to convert threaded float brackets for use with button handles.

Description No. CC333 Female CC334 Male

Clevis to Threaded Handle Bracket

This adapter converts western style handle trowels, fresnos, walking edgers, walking groovers and brooms for use with threaded handles.

No. Description CC335 Clevis to Female CC337 Clevis to Male



Threaded Handle

Button Handle

Fiberglass Threaded And Button

1-1/2" Diameter

 Fiberalass threaded handle for use with bull floats and brackets Threaded Handle

No. Size CC672 6' Handle

Button Handle (use with Adapter) CC674 6' Handle

Button Handle Adapter

 Versatile adapter enables the fiberglass handle's 1-3/8" connector to attach to tilting brackets that accept 1-3/4" and 1-3/8" push button handles without additional adapters

No.

CC675 Adapter

CAUTION: Metal extension handles/adapters should not be used near electrical wiring

17



Anodized Aluminum Button

1-3/8" Diameter Swaged

- Swaged handles are anodized aluminum which prevents hands from turning black caused by oxidation
- Popular western style
- Handles can be adapted for use on bull floats, fresnos, and all long handle type construction tools
- Swaged ends nest and snap together with spring lock buttons

1-3/8" Diameter Silver Anodized

No. Size CC336 6' Handle CC331 8' Handle

1-3/8" Diameter Blue Anodized

No. Size CC336B 6' Handle CC331B 8' Handle CC336-01 Single Button Clip



High-Visibility Orange Powder Coated Aluminum

1-3/4" or 1-3/8" Diameter

Swaged Handle 1-3/4" Diameter

1-3/8" Diameter No. Size No. Size CC289SO CC336SO 6' 6' CC293SO אי

CC289-01 **Double Button Clip** CC336-01 Single Button Clip

BUTTON EXTENSION HANDLES

Anodized Aluminum Button

1-3/4" Diameter Swaged

- Swaged handles are anodized aluminum which prevents hands from turning black caused by oxidation
- Lightweight aluminum button handles for use with Kraft double tilt action float brackets

1-3/4" Diameter Silver Anodized

Size No. CC289S 6' Handle CC293S 8' Handle 10' Handle CC291S**

1-3/4" Diameter Blue Anodized

No. Size 6' Handle CC289SB CC293SB 8' Handle CC291SB** 10' Handle

1-3/4" Diameter Red Anodized

No. Size CC289SR 6' Handle CC293SR 8' Handle CC291SR** 10' Handle CC289-01 Double Button Clip

**Must ship via truck

Aluminum Button Handles With Insert

1-3/4" Diameter

• Use with insert to connect handles together

No. Size CC289 6' Handle with Insert CC293 8' Handle with Insert CC291** 10' Handle with Insert CC292** 12' Handle with Insert CC289-01 Double Button Clip

CC289-02 Insert with Button Clip

**Must ship via truck



Gold Anodized Aluminum Button

1-3/4" Diameter Swaged

- Swaged handles are anodized aluminum which prevents hands from turning black caused by oxidation
- Lightweight aluminum button handles for use with Kraft double tilt action float brackets

1-3/4" Diameter Gold Anodized

No. Size CC289SG 6' Handle CC293SG 8' Handle CC291SG** 10' Handle CC289-01 **Double Button Clip**

**Must ship via truck



Handle Cleaning Brush

Ideal brush for cleaning out concrete that collects inside threaded and button handles. Stiff, rigid plastic bristles clean without damaging handles.

Length No. BI 434



BULL FLOATS

MAGNESIUM IS 30% LIGHTER THAN ALUMINUM MULTI-RIBBED FOR EXTRA STRENGTH **BROKEN-IN BLADE**

Magnesium Bull Float 4-Hole Bracket

- · Lightweight and longer lasting than aluminum alloy
- Float blade is "broken-in", curved and balanced to prevent digging
- Use with threaded handles
- Floats will accept any 4-hole adjustable tilting handle bracket. Comes complete with 4 hole bracket assembly (CC800)

Square End

No.	Size 🥨
CC735	36"x8"
CC801	42"x8"
CC745	45"x8"
CC802	48"x8"
CC754	54"x8"
CC760	60"x8"
CC761	72"x8"

Add "01" after part number for float without bracket

EXTRU-LITE™

CC802NP 48"x8" (NO PAINT)

Round End	
No.	Size
CC736	36"x8"
CC742	42"x8"
CC743	45"x8"
CC803	48"x8"
CC744	54"x8"
CC804	60"x8"
CC808	72"x8"
CC803NP	48"x8"








Magnesium Bull Float

2-Hole Bracket

- Multi-ribbed top provides extra strength
- · Provides a smooth finish on all concrete jobs
- Complete with 2-hole bracket assembly
- Use with threaded handles.

Size No. 42"x8" CC805 CC806 48"x8" CC807 60"x8"





Aluminum Bull Float 4-Hole Bracket

- Multi-ribbed for extra strength
- · Lightweight but strong; engineered for proper balance and long wear
- Complete with 4-hole bracket assembly
- Use with threaded handles

No. Size CC771 42"x7-1/4" CC773 48"x7-1/4"

Add "01" after part number for float without bracket



Laminated Wood Bull Float 4-Hole Bracket

- · Long lasting, laminated float with bracket
- 1-3/4" thick; with stiffener embedded in ends of float
- Available with 4-hole bracket, EZY-Tilt® II Bracket or "H" bracket

II DIACKEL OI	II DIAGNOL
No.	Size
CC781	36"x7-1/4"
CC782	48"x7-1/4"
CC783	60"x7-1/4"
00-01	40" 7 4 / 4 !! /

CC784 48"x7-1/4" (EZY-Tilt® II Bracket) 48"x7-1/4" (With "H" Bracket) CC782H



Brass threaded inserts for superior strength

Add "01" after part number for float without bracket



Cali Mahogany Bull Float

2-Hole Bracket Bar

"H" Bracket

Made of Asian Mahogany wood

• Smooth 7-1/4" wide by 3/4" thick wood face

"H" Bracket

- Handle bracket will accept (CC295) Fresno/Broom adapter for 1-3/4" diameter button handles, (CC332) adapter for 1-3/8" diameter button handles Fresno Trowel adapter (CC662) for threaded handles
- Float can also be fitted with a 5' or 6' clevis wood handle (order handles separately)

No.	Size
CC982	24"x7-1/4"
CC983	36"x7-1/4"
CC984	48"x7-1/4"

2-Hole Bracket Bar

- Steel "H" Style bracket supports float working surface
- Bracket Bar accepts any 2-hole fixed or tilt bracket float brackets (order brackets separately)

No.	Size
CC981	24"x7-1/4"
CC985	36"x7-1/4"
CC986	48"x7-1/4"


Bronze Bull Float Groover Bit

Use bull float as groover. Attaches with two thumbscrews. Mount as many groovers as needed. Works on 8" wide bull floats.

No.	Bit Depth	Radius	Widt
CC940	3/4"	1/4"	1/2"
CC941	1"	1/4"	1/2"
CC942	1-1/2"	1/4"	1/2"
CC943	2"	1/4"	1/2"



CAUTION: Metal extension handles/adapters should not be used near electrical wiring



• Broken-in rounded edges with EZY-Tilt® II bracket (CC294)

• 8' and 10' include support braces and bearing collar for easy float adjustment. All with 2" high sides.

Size No. CC044 48"x6" CC045 60"x6" CC046 72"x6" 96"x6" CC048

Add "01" after part number for float without bracket

Includes (1) 8' Button Handle and 4' Braces 120"x6" Includes (1) 10' Button Handle and 4' Braces CC050**

**Must ship via truck

Magnesium Dual Edge Channel Float with Knucklehead® II Bracket

- Rounded front edge for floating
- Square 90 degree back edge for finishing
- Great tool for finishing floors requiring high "F" numbers
- Fitted with Knucklehead II[®] bracket (CC296)

Size
48"x6"
60"x6"
72"x6"

CC048SR 96"x6" Includes (1) 8' Button Handle and 4' Adjustable Braces CC050SR** 120"x6" Includes (1) 10' Button Handle and 4' Adjustable Braces

**Must ship via truck



after part number

for float without bracket



Rounded Front Edge 90° Squared Back Edge

Cast Magnesium Bull Float

- · Cast magnesium bull float with broken-in flat face and raised edges
- Complete with 4-hole bracket assembly
- Use with threaded handles

No. Size Add "01" CC352 42"x8" after part number CC358 48"x8" for float without bracket

Laminated Canvas-Resin Bull Float

- Long wearing 3/8" thick canvas-resin float
- Rounded ends and "broken-in" shape • Heavy-duty (.125 gauge)
- 4" C-Channel for extra rigidity Fitted with our exclusive EZY-Tilt® II

(CC294) handle bracket

No. Size CC785 48"x7"

Add "01" after part number for float without bracket

IDEAL FOR DECORATIVE CONCRETE APPLICATIONS

CAUTION: Metal extension handles/adapters should not be used near electrical wiring



FRESNO TROWELS





All-Angle Steel Fresno Trowels

Carbon Steel or Blue Steel

- Made of high quality tempered steel for a perfect finish
- 360 degree all-angle bracket lets you work at any angle
- · Available in round or square end
- Use fresno adapters for handle attachment
- Attach bronze fresno groover attachment for grooving

Round E	nd Ö	Square E	nd
No.	Size	No.	Size
CC849	24"x5"	CC906	24"x5"
CC850	30"x5"	CC907	30"x5"
CC851	36"x5"	CC908	36"x5"
CC852	42"x5"	CC909	42"x5"
CC853	48"x5"	CC910	48"x5"

Fresno Trowel With Swivel Bracket

Carbon Steel or Blue Steel

- · Made of high-quality tempered steel with square steel mounting
- 360 degree swivel bracket lets you work at any angle
- Round end fresno eliminates marking or gouging slabs
- Bracket to be used with clevis handles
- Fresno handle adapters and fresno groover attachments also available

Add "B" after part no. for Blue Steel

Size

24"x5"

30"x5"

36"x5"

42"x5"

48"x5"

Square End

No.

CC825

CC826

CC827

CC828

CC829

Round En	nd	Square End		
No.	Size	No.	Size	
CC618	18"x5"	CC518	18"x5"	
CC624	24"x5"	CC524	24"x5"	
CC630	30"x5"	CC530	30"x5"	
CC636	36"x5"	CC536	36"x5"	
CC642	42"x5"	CC542	42"x5"	
CC648	48"x5"	CC548	48"x5"	
CC551	Replacement Swivel Bracket			

Fresno Trowel with **Adjustable Tooth Bracket**

Carbon Steel or Blue Steel

- Made of high quality tempered steel for a perfect finish
- Uniquely designed bracket has teeth to keep handle at set angle without slippage
- Use with threaded handles or add "BT" for use with snap handle

Round End No. Size

CC820 24"x5" 30"x5" CC821 CC822 36"x5" CC823 42"x5" CC824 48"x5"

> Add "B" after part no. for Blue Steel



Center Line Groover

Groover is adjustable on any 5" wide fresno. Leaves a clear, fine line in concrete, Slide groover to proper position and tighten. Fresno not included. Great for decorative concrete applications.



Fresno Trowel With EZY-Tilt® Bracket

Carbon Steel or Blue Steel

- · Quality tempered steel blade with square steel mounting
- EZY-Tilt® bracket eliminates bending and lifting. Controls blade pitch with turn
- Bracket features quick and easy coupling for either 1-3/4" button handle or 1-3/8" button handle

No. Size CC830 24"x5" 30"x5" CC831 CC832 36"x5" CC833 42"x5" CC834 48"x5"

Add "01" after part no. for fresno without bracket

Add "B" after part no. for Blue Steel

Only EZY-Tilt® bracket (CC290) fits this fresno

Bronze Fresno Trowel Groover Bits

Change your fresno into a long-handled groover by simply turning the two thumbscrews. Use more than one to make parallel grooves. 1/4" radius. Fits 5" wide

11651105.	
No.	Bit Depth
CC622	1/4"
CC623	1/2"
CC625	3/4"
CC626	1"

CAUTION: Metal extension handles should not be used near electrical wiring

Multi-Trac Bull Float Groover with Knucklehead® II Bracket

Cuts clean sharp grooves every time

- Made in the USA
- Ideal for: Streets, Highways, Off Ramps, Safety Ramps and Bridges
- Produces a uniform sharp groove in various concrete applications where water drainage and traction are critical.

• All floats: groove depth and width 1/4"x1/4"

· All Hoats.	groove depui	and width
No.	Float Size	Spacing
CC789	24"x8"	1/2"
CC788	36"x8"	1/2"
CC787	48"x8"	1/2"
CC792	24"x8"	3/4"
CC791	36"x8"	3/4"
CC790	48"x8"	3/4"
CC798	24"x8"	1"
CC797	36"x8"	1"
CC796	48"x8"	1"
CC795	24"x8"	2-1/4"
CC794	36"x8"	2-1/4"
CC793	48"x8"	2-1/4"

Add "01" after part no. for float without bracket

Use with any Kraft Tool Double Tilt Action float bracket





Stainless Steel Multi-Trac Fresno

Cuts clean sharp grooves every time

- Cuts clean sharp safety grooves
- Grooves are 1/4" wide by 1/4" deep
- Fitted with a threaded tilting handle bracket (CC665)

SIze 24"x5"		Size 36"x5"		Size 48"x5"	
No.	Groove Spacing	No.	Groove Spacing	No.	Groove Spacing
CC875	3/4"	CC878	3/4"	CC889	3/4"
CC876	1"	CC880	1"	CC890	1"
CC874	1-1/2"	CC877	1-1/2"	CC888	1-1/2"



7" Wide No bracket interference

7" Wide Blue Steel Fresno

40% More Finishing Area


- Made of high quality tempered flexible blue steel blade
- Round ends and wider working surface prevent marking and gouging while creating a smooth finish
- Includes Knucklehead® II bracket (CC296), but can be used with any tilting bracket
- 7" wide blade allows user to finish close to walls and obstruction without bracket interference

No. Size CC840B 36"x7" CC841B 48"x7" Add "01" after part no. for fresno without bracket

Round End Fresno with Edger

- Finish and edge in one pass
- Carbon steel blade with 1/2" radius edger on one end
- Great tool for sidewalks and decorative concrete
- Fresno groover bits can also be added

Bottom view



EZY-Tilt® Fresno/Broom Adapter Accepts 1-3/8" and 1-3/4" diameter button

Accepts 1-3/8" and 1-3/4" diameter butto handles to fit fresnos, brooms, walking edgers and groovers.

No. CC295

Fresno Trowel Adapter

Adapts 1-3/4" molded threaded handles to fit fresnos, brooms, walking edgers and groovers.

No. CC662



Fresno Bracket

360° all-angle bracket **No.**

NO.


CC298 Bracket (Complete)
CC288 Top Half (Only)
CC300 Bottom Half (Only)



Hardware not included

Fresno Float Weight

Fits over the 1/2" fresno bar. 5 lb. iron weight. Using 2 for balance is recommended. **No.** CC755 (Each)



CAUTION: Metal extension handles should not be used near electrical wiring

Concrete Tools

www.KraftTool.com

DARBIES



Extruded Magnesium Mini Bull Float and DarbyUnique T-slotted reinforcing rib (no threads to strip) adds strength and allows threaded

bracket to be quickly set off center to work float around obstructions. Two wood float handles can easily slide for adjusting to hand and curb work. This float is also ideal for floating lightweight concrete on roof decks. Use with threaded handles.

NO.	Size	
CC816	36"x3-1/4"	
CC816RE	36"x3-1/4"	Round End
00017	401120 4 /411	

CC817 42"x3-1/4 CC818 48"x3-1/4" 60"x3-1/4" CC819

Tapered Magnesium Darby

The most popular lightweight 30" darby for precision finish work. Extruded Magnesium blade is 3-1/8" wide at the heel, tapered to 1-7/8" at the toe.

Wood Handle

No. CF030 30" ProForm® Handle No. CF030PF 30"



Extruded Magnesium Darby with Knob Handle

This lightweight magnesium darby has a float-type handle and a round knob handle. The unique T-Channel design gives the finisher the option of sliding the handle position to their preference.

Wood Handles No. CF032 30"x3-1/4"

CF033

ProForm® Handles No. CF032PF 30"x3-1/4" CF033PF 36"x3-1/4"



36"x3-1/4"



Extruded Magnesium Hand & Curb Darby

Specially designed for curb work, this lightweight tool comes with one or two float- type handles. T-Channel design gives the finisher the option of adjusting handle position to their preference.



EXTRU-LITE™

With 2 handles

Handle
Size
36"x3-1/4"
42"x3-1/4"
48"x3-1/4"

With 1 Handle

Wood Handle		ProForm® I	Handle
No.	Size	No.	Size
CF031	30"x3-1/4"	CF031PF	30"x3-1/4"
CF036	36"x3-1/4"	CF036PF	36"x3-1/4"



Tapered Laminated Canvas-Resin Darbies

Same as our other floats. 3/8" thick; has rounded corners and "broken-in" shape. Ready to use.

No.

45" Tapered Darby (3) Hole Handle 30" Tapered Darby (1) Hole Handle CF510 CF509

Tapered Mahogany Darby

Tapers from about 3-1/2" at the heel to 2-1/2" at the front

Three sizes designed and made of clear seasoned mahogany wood. Finished smooth and comes with either a one, two or three hole grip. Very popular with many concrete finishers.

A) No.	Sizes	B)
CF236	36" (1) Hole Grip	
CF258	28" (1) Hole Grip	
CF254	Replacement Handle 21" (1) Hole	

) No. Sizes

CF259 45" (3) Hole Grip 48" (2) Hole Grip (Not Tapered) CF255 CF253 Replacement Handle 32" (3) Hole

Sizes CF237 36" (2) Hole Grip CF237-01 Replacement Handle (2) Hole

Redwood Striker™ Straightedge/Screed

Liahtweight. Rounded Edges

Made of the finest redwood, this tool is great for striking off concrete and leveling other material. 3 popular lengths with convenient hand hole spacing. 2 widths with rounded edges will not dig into material.



	· · · · · · · ·	
No.	Size	W
CC439	6'x4-1/2"x1-1/4"	5/4
CC440	8'x4-1/2"x1-1/4"	5/4
CC441	10'x4-1/2"x1-1/4"	5/4
CC442	6'x4-1/2"x2"	8/4
CC443	8'x4-1/2"x2"	8/4
CC444	10'x4-1/2"x2"	8/4
With Adjust	able Level Vial	
CC442L	6'x4-1/2"x2"	8/4
CC443L	8'x4-1/2"x2"	8/4
CC444L**	10'x4-1/2"x2"	8/4


**Must ship via truck

Without Level Vial

Tapered Darby with Level Vial

Tapered, laminated canvas-resin darby is 3/8" thick. Has rounded corners, and broken-in shape. Ready to use. Top reading spring-loaded vial for easy on the job adjustments. 45" long with 3-hole handle. No. CF510L





Aussi Combo Darby/Screed 🝕 With Adiustable Handles

This innovative tool can be used as a float, screed, or check rod when you want for the perfect finish. Base of tool comes with a round edge for floating and a square edge for cutting and filling. Lightweight magnesium with handles that adjust for comfort.


No.	Size	Handles	No.	Size	Handles
CC421	4'x1-3/8"	x2" 1	CC423**	10'x1-3/8	"x2" 2
CC422	6'x1-3/8"	x2" 1		**M	lust ship via truck

Whiskey Stick

5' Magnesium blade levels and places concrete fast. Rounded edge for floating and square edge for cutting and filling. Handle tilts to the

right floating angle. Fitted with heavy-duty braces and 72" snap button 1-3/8"

extension handle. No. Size CC425



Extruded Magnesium Walking Float Square End or Round End

This lightweight magnesium float is perfect for floating small areas of concrete. Fitted with our 360° all-angle bracket, which lets you work at any angle. Unique T-Channel design gives the finisher the option of adjusting handle bracket position to their preference. Bracket fits clevis handles and with adapters will accept button or threaded handles.

Square Ends

No.

Round Ends CC814 24"x3-1/4" CC813 30"x3-1/4"

Extruded Magnesium Walking Float

With Multi-Twist™ Bracket Work at any angle. Bracket rotates 360° Round Ends with 2-Hole

No. Size CC814MT 24" CC813MT 30" CC812MT



Round



CONCRETE SPREADERS AND PLACERS





Packed 5

per carton or 5 per bundle

assembled

Right Angle Placer[™]
• Blade is welded to a 60" anodized

- Blade is welded to a 60" anodized aluminum handle with textured foam grip
- Heavy-duty aluminum blade and braces for added strength
- 1-3/8" diameter handle
- 60 degree blade keeps tool at just the "right angle" to spread and level concrete
- Blade measures 19-1/2"x4"

No. Size

CC964** 19-1/2" without Hook CC965** 19-1/2" with Hook

**Assembled spreaders ship via oversized rate or truck



Packed 5 per bundle

60° Angle

Cardinal[™] Aluminum Placer

.125" Aluminum

- Heavy gauge aluminum with reinforced rib construction formed for easy pulling, leveling and placing of concrete
- Sturdy, oversize, large diameter 60" wood handle with 2 bolt attachment
- Blade measures 19-1/2"x4-1/2"

No.
CC936
CC936-01
CC936-02
CC9364**

Description 19-1/2"x4-1/2" Blade ONLY Handle ONLY Placer

Assembled nbled spreaders ship

**Assembled spreaders ship via oversized rate or truck

Packed 5 per carton or 4 per bundle assembled

Mega Mover[™] Concrete Placer

- Blade bent to proper angle to move maximum amount of material
- Available in aluminum or steel
- Comes with 60" heavy-duty shovel-type wood handle with bracket
- Bracket allows for secure connection for easy assembly
- Blade measures 20"x5"
- Add"01" to part no. for head only

No.	Description	Blade Edge
CC977	Aluminum	Teeth
CC978	#14 Gauge Steel	Smooth
CC979	Aluminum	Smooth
CC977A**	Aluminum (Assembled)	Teeth
CC978A**	#14 Gauge Steel (Assembled)	Smooth
CC979A**	Aluminum (Assembled)	Smooth

CC977-02 60" Wood Handle with Adapter and Hardware

**Assembled spreaders ship via oversized rate or truck



• Made of strong, lightweight aluminum

 Blade is welded to a 60" anodized aluminum handle with textured foam grip
 Heavy-duty aluminum

 Heavy-duty aluminum blade and braces for added strength

• Blade measures 19-1/2"x4"

No. Size

CC944** 19-1/2"x4" without Hook (Assembled) CC945** 19-1/2"x4" with Hook (Assembled)

CC944-30** 30"x4" without Hook Wide Blade (Assembled)

**Assembled spreaders ship via oversized rate or truck



Packed 5 per carton or 5 per bundle assembled

Packed 5

per bundle

Lightweight Aluminum Concrete Spreader

Made of strong lightweight aluminum

• Two heavy-duty aluminum braces for added strength

• 54" wood jam handle

Blade measures 19-1/2"x4"

No. Size

CC904 19-1/2"x4" without Hook CC905 19-1/2"x4" with Hook CC107 54" Replacement Handle CC904A** Spreader Assembled CC905A** Spreader Assembled

Concrete Placer with Fiberglass Handle

• Made of strong lightweight aluminum

• Blade measures 19-1/2"x4" with heavy-duty bracing

• Fitted with 54" reinforced Fiberglass® handle

Size

CC904AF** 19-1/2"x4" without Hook

(Assembled)

CC905AF** 19-1/2"x4" with Hook

(Assembled)

**Assembled spreaders ship via oversized rate or truck



Packed 5 per bundle



^{**}Assembled spreaders ship via oversized rate or truck

CONCRETE KUMALONG®AND RAKES

Packed 3 per bundle

Cali Kumalong® Concrete Spreader #14 Gauge Steel Blade

- Made of strong and heavy-duty, yet lightweight steel
- Blade measures 19-1/2"x4"
- Comes with 60" heavy-duty pinned wood handle to prevent spinning
- Double-edged blade doubles the blade life

lo. Size

CC917** 19-1/2"x4" (Assembled)

 $\ensuremath{^{**}}\mbox{\sc Assembled}$ spreaders ship via oversized rate or truck

Concrete Displacer (Steel)#14 Gauge Steel Blade

Smooths, spreads and grades concrete. Strong reinforced rib construction. 14 gauge steel; 19-1/2"x4"; weighs 3-1/2 lbs. Comes with 54" wood jam handle.

No. Size

CC019 19-1/2"x4" with Hook CC009 19-1/2"x4" without Hook CC107 54" Replacement Handle



The "Original" Concrete Spreader

- Sturdy, lightweight tool spreads and grades concrete
- Made of #14 gauge, cold rolled steel
- Comes with 54" wood jam handle

No. Size

CC105 19"x4" with Hook CC106 19"x4" without Hook CC107 Replacement Handle

Heavy-Duty (Steel) Concrete Spreader

- Made of 12 gauge, cold rolled steel
- Blade measures 20"x5"
- Comes with 60" or 48" heavy-duty shovel-type wood handle

60" Heavy-Duty Wood Handle

No. Size

CC901 20"x5" without Hook CC902 20"x5" with Hook

CC901-02 Repl. Handle/Ferrule w/o Hook CC902-02 Repl. Handle/Ferrule w/ Hook

CC901A** Spreader Assembled CC902A** Spreader Assembled Packed 5 per carton or Packed 3 per bundle assembled

Packed 5

per carton

48" Wood Handle

No. Size

CC901-48 20"x5" without Hook CC902-48 20"x5" with Hook

CC901-04 Repl. Handle/Ferrule w/o Hook CC902-04 Repl. Handle/Ferrule w/ Hook

CC901A-48** Spreader Assembled CC902A-48** Spreader Assembled

**Assembled spreaders ship via oversized rate or truck



Concrete Rake

Magnesium or Steel

This well-constructed rake is favored by many concrete tradesmen over straight spreaders for its ease in moving concrete. Comes with 54" wood iam handle.

o i wood ja	iii iiaiiaio.	
No.	Size	Material
CC010	22-1/2"x5"	Steel
CC113	19-1/2"x4"	Magnesium
CC114	24"x4"	Magnesium
CC107	Replacement	Handle

Packed 5 per carton

Concrete Spreader (Steel) #14 Gauge Steel Blade

- Made of 14 gauge, cold rolled steel
- Blade measures 19-1/2"x5"
- Two metal braces for added strength
- Comes with 54" heavy-duty shovel-type wood handle

No. Size

CC903 19-1/2"x5" Head CC903A** Spreader Assembled

**Assembled spreaders ship via oversized rate or truck

e or truck

Packed 5 per carton or 4 per bundle assembled

Magnesium Tri Level Placer

- Float, screed and level concrete with this versatile placer
- Adjust height of handle to engage surface of tool or to engage point of triangle for checking flatness
- Fitted with 60" wood handle

Handle

No. Size

CC932 24" Blade Length

CC933 30" Blade Length

CC934 36" Blade Length

CC935 42" Blade Length

CC933-02 60" Replacement Wood



Packed 5 per bundle

Add "01" after part no. for placer without handle

SCREEDS



Magnesium Screed 30% Lighter than other aluminum screeds

Kraft screeds are made of Genuine Extru-Lite Magnesium™. These screeds are built for strength and rigidity but lightweight enough for those big jobs. Ends are capped to prevent concrete from building up inside. Extra end caps are available.

CC621

Made of 100% Aluminum Alloy

STRIKER Screed

CC514

CC516





CC612 12' CC412 12' 14' CC614 14' CC414 14' 16' CC616 16' CC416 16' (1"x4" shipped CC619 18' CC417 20' 2 per carton) CC620 20' CC418 26'

24'

Screeds 10' or longer must ship via truck

A) Magnesium Keyhole **Paver's Straightedge**

Special keyhole design for strength. Sturdy highway straightedge and checking tool. Complete with braces, 10' button handle (CC291). Knucklehead® II bracket (CC296) and roller bearing collar for easy adjustment.

No.	Size
CC721	10'
CC722	12'
CC723	16'
CC724	20'

Add "01" after part no. for screed without bracket

B) Magnesium Keyhole Hand Screed (Only)


Unique shape makes it easy to grip and the perfect tool for hand screeding.

No.	Size
CC726	10'
CC727	12'
CC728	16'
CC729	20'

EXTRU-LITE TM

Tools 10' or longer must ship via truck

End View



CC417AL

20'

Aluminum Curb Forming Tool

CC619AL

CC620AL

Use to shape curbs. Features two comfortable wooden knob handles.

18'

20'

End caps prevent build up of material

(1"x4" shipped

2 per carton)



Screed Handles

Lightweight aluminum handles adapt to any screed size. Drill holes and attach with hardware.

No. CC503 (Pair)





BuckEye™ Straightedge With Level Vial Handle

One-man straightedge for striking off. leveling and bringing concrete to surface grade. Top reading spring-loaded level vial for easy on-the-job adjustments. Made of lightweight high grade aluminum alloy. Wood handle tapered for smooth comfortable grip.

No. Size CC891 4'x1-1/2"x1-1/2" CC892 5'x1-1/2"x1-1/2" 6'x1-1/2"x1-1/2" CC893 CC894 8'x1-1/2"x1-1/2" CC895** 10'x1-1/2"x1-1/2" CC896** 12'x1-1/2"x1-1/2"



EXTRU-LITE™

EXTRU-LITE™

ותעינבדות


Buckaroo™ Straightedge With Level Vial Handle

One-man straightedge for floating or striking off concrete. Smooth tapered handle includes top reading adjustable level vial for easy positioning. Base of tool comes with round edge for floating and square edge for cutting. Made from magnesium, very lightweight. Ideal for concrete and landscape construction.

Size No. 40"x1-3/8"x2" CC897 CC421L 4'x1-3/8"x2" 6'x1-3/8"x2" CC422L CC428L 8'x1-3/8"x2" 10'x1-3/8"x2" CC423L** **Must ship via truck








Magnesium Super Flat Paver's Straightedge

"Bump Cutter"

Durable, accurate straightedge and checking tool lets user produce a flat, even surface. Knucklehead® II bracket (CC296) adjusts blade to fill and level uneven areas. Comes complete with braces. 10' button handle (CC291), and roller bearing collar for easy adjustments.

No. Size CC708 8' CC714** 10' CC716** 12' CC720** 16 **Must ship via truck



Aluminum Paver's Straightedge

A lightweight durable, accurate straightedge and checking tool. Easy to handle, which makes inspection easy. Comes with 10' threaded handle (CC228) and braces.

No. Size CC710** 10' CC712** 12 **Must ship via truck



Magnesium Paver's Straightedge

An excellent checking tool. It is a lightweight, durable, and accurate straightedge. Easy to handle, which makes inspection of slabs easy. Comes with 12' threaded handle (CC229) and braces.

No. Size EXTRU-LITE™ CC561** 10 CC562** 12

**Must ship via truck

Fnd View

Round End Mag Check Rod Cut down high spots and ridges, or move

materials to low areas with this adjustable square edge tool. Round ends prevent marking. Comes complete with braces, 10' button handle (CC291), Knucklehead® II bracket (CC296) and roller bearing collar for easy tool adjustment.

No. Size CC709** 2"x5"x12 **Must ship via truck



PROFORM® POWER TROWELER REPLACEMENT BLADES









Machine Size

MFG No.



Size

Kraft No.

Blade

Machine Siz	е	MFG No.	Blade	Size	Kraft No.
Allen/Raze	orba	ck			
30"	1000	41696	Finish	6"x10-1/2"	SK237
			Comb.	6"x10-1/2"	SK236
36"	and the same	015890	Finish	6"x14"	SK100
		016095	Comb.	8"x14"	SK101
	100	0282314	Float	10"x14"	SK102
46"	1	015695	Finish	6"x18"	SK214
	4	016094	Comb.	8"x18"	SK215
		02822318	Float	10"x18"	SK105
Bartell					
24"	A STATE OF THE PARTY OF THE PAR	20455	Finish	4-3/4"x9"	SK238
30"		20407	Finish	4-3/4"x10"	SK239
4	No. of Contract of	10400	Finish	6"x10-1/2"	SK237
36"	No. of London	20414	Finish	6"x14"	SK100
	1	20479	Comb.	8"x14"	SK101
	1	20415	Float	10"x14"	SK102
46"	B. San Park	20410	Finish	6"x18"	SK214
		20480	Comb.	8"x18"	SK215
		20411	Float	10"x18"	SK105
Edco (V-N	otch	Channel)			
34" & 36"	4500	F-1	Finish	6"x14"	SK300
		C-1	Comb.	8"x14"	SK301
		M-1	Float	10"x14"	SK302
42"			Finish	6"x16"	SK304
			Comb.	8"x16"	SK305
	1		Float	10"x16"	SK306
44"- 48"	N. Salar	F-3	Finish	6"x18"	SK307
	1	C-3	Comb.	8"x18"	SK308
	1	M-3	Float	10"x18"	SK309
Goldblatt					_
28"		19177	Comb.	6"x10"	SK177
36"		19172	Finish	6"x14"	SK172
		19179	Comb.	8"x14"	SK179
		19102	Float	10"x14"	SK102

Re	tro	A	dap	ter	Bar

Mount adapter bar to power troweler and quickly change blades with snap pins. Bar fits 7/8" channel. Each bar comes with 2 snap clips for mounting.

No. Size SK148 10" Long 36" (Only fits SK232 & SK233) SK150 14" 46"/48 (Only fits SK234 & SK235) SK147 Snap Clip for Bar

A	
3"	

Master	Arrow				
36"	A STATE OF THE PARTY OF THE PAR	FT36	Finish◊	6"x14"	SK151
	1	FC3	Comb.◊	8"x14"	SK152
	100	RT36	Channel Finish	6"x14"	SK232
	300	RC36	Channel Comb.	8"x14"	SK233
	4500		Finish	6"x14"	SK100
	8		Comb.	8"x14"	SK101
	10	Float		10"x14"	SK102
46"		BFT46	Finish◊	6"x18"	SK153
		3FC46	Comb.◊	8"x18"	SK154
	1	3RT46	Channel Finish	6"x18"	SK234
			Comb.	8"x18"	SK215
		3FF46	Float	10"x18"	SK105
		3RC46	Channel Comb.	8"x18"	SK235
		RC46	Offset Channel Com	b. 8"x18"	SK231
◊ Include	s: nuts, l	oolts and wa	shers		
MBW					
30"			Comb.	6"x10"	SK242
36"	A. C.	5347	Finish	6"x14"	SK100
		5402	Comb.	8"x14"	SK101
	10	5403	Float	10"x14"	SK102
46"		5383	Finish	6"x18"	SK214
		5412	Comb.	8"x18"	SK215
		5413	Float	10"x18"	SK105
Stone					
36"	-	34578	Finish	6"x14"	SK100
	100	34583	Comb.	8"x14"	SK101
		34586	Float	10"x14"	SK102
46"		34580	Finish	6"x18"	SK214
		34585	Comb.	8"x18"	SK215
	47	34589	Float	10"x18"	SK105
Stow					
Old Style	-	7394-401	Finish	6"x14"	SK186
34"		11686-503	-	8"x14"	SK187
36"	B. Contract	22027	Finish	6"x14"	SK100
		22029	Comb.	8"x14"	SK101
		22028	Float	10"x14"	SK102
42"		10937-50		6"x14"	SK186
46"		21637	Finish	6"x18"	SK214
		21988	Comb.	8"x18"	SK215
		21989	Float	10"x18"	SK105
		- BI I	ac ara mada		

Blades are made of heavy-duty steel to exacting specifications. Each blade is designed for longer life and greater performance.

ProForm® Long Life Replacement Blades

Designed with a hard thick steel to cut down on blade changes on the job

Each blade is designed for longer life and greater performance

Long life blades are ideal for the tough demands of riding power trowelers



Combo Rounded Corners (RC)

		(masto	i/Aiiow)	Corner		
Machine	Size	MFG No.	Blade	Size	Kraft No.	
Superio	or / H	usqvarna				
36"		2836FL	Comb.	8"x14"	SK220	
44"		2844C	Comb.	8"x16"	SK226	
			Float	10-1/2"x17-1	/2" SK108	
		2844FL	Flat Finish RC	8"x16"	SK227	
48"	1	2848FL	Comb.	8"x18"	SK228	
Wacker						
36"	4500	79638	Finish	6"x14"	SK100	
		75061	Float	10"x14"	SK102	
		79637	Comb.	8"x14"	SK101	
48"		79642	Finish	6"x18"	SK214	
		79641	Comb.	8"x18"	SK215	
		112000	Float	10"x18"	SK105	
Wagma	n					
24"	1000	WB47590	Finish	4-3/4"x9"	SK238	
	-	WB6105F	Finish	6"x10-1/2"	SK237	
30"		WX5925M6	6 Comb. Metric	5"x9"	SK241	
36"	N. Salar	WX614F	Finish	6"x14"	SK100	
	1	WX8140	Comb.	8"x14"	SK101	
		WX1014FC	Float	10"x14"	SK102	
44"		WF816F	Flat Finish RC	8"x16"	SK227	
46-48"	400	WX618F	Finish	6"x18"	SK214	
		WX8180	Comb.	8"x18"	SK215	
		WX1018FC	Float	10"x18"	SK105	
60"		WX-818F	Flat Finish RC	8"x18"	SK217	
		WX-623F	GOLD Finish	6"x23"	SK216G	
		WX8230	GOLD Comb.	8"x23"	SK218G	
Whitem	an /	MultiQuip				
24"		C244	Comb. Metric	5"x9"	SK241	
36"	A STATE OF THE PARTY OF THE PAR	F-90	Finish	6"x14"	SK100	
		C-844	Comb.	8"x14"	SK101	
		CL-954F	Float	10"x14"	SK102	
46-48"		F-400	Finish	6"x18"	SK214	
		C-464	Comb.	8"x18"	SK215	
		CL444F	Float	10"x18"	SK105	
		RC818	Flat Finish RC	8"x18"	SK217	
Daniel	-10-	0 1	in alien Diada			

Rounded Corner Combination Blades

Flat combination blade with 2" radius corners. Offers more blade surface

0110101110	io biado odi io	200.		
	Fits most	Comb. RC	8"x14"	SK101R
	popular	GOLD Comb. RC	8"x18"	SK215GR
	models	Comb. RC	8"x18"	SK215R
	Fits	Comb. RC	8"x14"	SK220R
	Superior	Comb. RC	8"x16"	SK226R
		Comb. RC	8"x18"	SK228R



Quality and Value are the trademarks of every ProForm® Blade

ProForm® Ultra Blue 15-25% Longer Life

Machine		9			
Size		Blade	Size	Part No.	Mfg. Compatibility
36"	No. of Lot	Finish	6"x14"	SK100B	Fits Allen, Bartell,
		Comb.	8"x14"	SK101B	Stone, Stow, Whiteman, Wacker
46"-48"	No. of Concession, Name of Street, or other Persons, Name of Street, or ot	Finish	6"x18"	SK214B	& other popular
		Comb.	8"x18"	SK215B	styles of Trowelers
	1	Comb.	8"x16"	SK226B	Fits Superior Trowelers
	1	Comb.	8"x18"	SK228B	Tita duperior froweiera
Offset Channel		Comb.	8"x18"	SK231B	Fits Master Trowelers

ProForm® Heavy-Duty Gold Thick and Rugged

25-50% Longer Life

Machine		_			
Size		Blade	Size	Part No.	Mfg. Compatibility
36"	N. S.	Finish	6"x14"	SK100G	Fits Allen, Bartell,
		Comb.	8"x14"	SK101G	Stone, Stow, - Whiteman, Wacker
46"-48"	-	Finish	6"x18"	SK214G	& other popular
	1	Comb.	8"x18"	SK215G	styles of Trowelers
	1000	Comb.	8"x16"	SK226G	Fito Cumoviou Trouvalou
	1	Comb.	8"x18"	SK228G	Fits Superior Trowelers
Offset Chan	nel 🧼	Comb.	8"x18"	SK231G	Fits Master Trowelers
60"	4500	Finish	6"x23"	SK216G	Fits Allen, Wagman, Whiteman/Multi Quip
		Comb.	8"x23"	SK218G	_ Trowelers
Bent Bla	de Cori	ners			
36"	27000	Finish	6"x14"	SK100GB	Ε
46"-48"	-	Finish	6"x18"	SK214GB	E

Grinding Stone Holder (Only)

Please specify troweler and make. (Up to 36" Machine Size) (Over 36" Machine Size) SK312 SK318

Grinding Stone Holder (With Stone)

SK313 (Up to 36" Machine Size) (Over 36" Machine Size) SK319

Grinding Stone (Only) SK320 (6 Grit, 2"x2"x8")



Concrete Tools www.KraftTool.com

PROFORM® FLOAT PANS

Achieve flatter floors with less time on the job! Made to fit non-overlapping, "Walk Behind" and "Ride-On" power trowelers

Pan fits right over power troweler blades

STORAGE:

Always store pans securely and vertically. Pans can be bent or damaged if not stored properly.

The best way to achieve flatter floors

- Made to fit non-overlapping "Walk-Behind" or "Ride-On" power trowelers
- Rotate pans for optimal life

30

- Beveled slightly to keep pan from digging into concrete
- Finish area is slightly smaller than the float pan due to beveling
- Blade slots on the float pan fit to blades on troweler
- Blade slots can be used on trowelers that run either direction






Slide rod in for secure attachment

Add "F" after part number for flat Z-Clip or Safety Rod Style float pans

Safety Rod StylePlease specify troweler make and size



(Slight bevel keeps pan from digging into the concrete)





Pan Diameter (12-Gauge Pan) Steel SK400SR 35-3/4" (34-3/4" Inside Diam.) 4 Blade **SK401SR** 36-1/2" (35-1/2" Inside Diam.) 4 Blade (37-1/4" Inside Diam.) SK402SR 38-1/4" 4 Blade (44-3/4" Inside Diam.) SK403SR 45-3/4" 4 Blade 45-3/4" (44-3/4" Inside Diam.) + SK407SR 5 Blade 47-3/4" (46-3/4" Inside Diam.) SK404SR 4 Blade

Heavy-Duty	Pan Dia	Steel		
SK410SR	45-3/4"	(44-3/4" Inside Diam.)	4 Blade	
SK411SR	45-3/4"	(44-3/4" Inside Diam.)	5 Blade	
SK406SR	47-3/4"	(46-3/4" Inside Diam.)	4 Blade	
SK409SB	47-3/4"	(46-3/4" Inside Diam.)	5 Blade	

Heavy-Duty Pan Diameter (10 Gauge Pan) Steel SK408SR (58-1/4" Inside Diam.) 6 Blade (90° lip)

+ Fits Whiteman B-Series and BAN Series "Ride-On" trowelers

Add "F" after part number for flat Z-Clip or Safety Rod Style float pans

Z-Clip Style

Please specify troweler make and size

No.	Pan Dia	meter (12-Gauge Pan)	Steel
SK400	35-3/4"	(34-3/4" Inside Diam.)	4 Blade
SK401	36-1/2"	(35-1/2" Inside Diam.)	4 Blade
SK402	38-1/4"	(37-1/4" Inside Diam.)	4 Blade
SK403	45-3/4"	(44-3/4" Inside Diam.)	4 Blade
+ SK407	45-3/4"	(44-3/4" Inside Diam.)	5 Blade
SK404	47-3/4"	(46-3/4" Inside Diam.)	4 Blade


Heavy-Duty	Pan Dia	meter (10 Gauge Pan)	Steel
SK410	45-3/4"	(44-3/4" Inside Diam.)	4 Blade
SK411	45-3/4"	(44-3/4" Inside Diam.)	5 Blade
SK406	47-3/4"	(46-3/4" Inside Diam.)	4 Blade
SK409	47-3/4"	(46-3/4" Inside Diam.)	5 Blade

+ Fits Whiteman B-Series and BAN Series "Ride-On" trowelers

Edger Pan #14 Gauge Steel

Edger pans with 90° lip allow machine troweling and floating close to walls and obstructions.

No. SK420	24" (90° lip)	Bartell and Whiteman
SK421	30" (90° lip)	Wacker and Whiteman / MultiQuip



Cuts and bends up to #5 rebar Top-Loading Rebar Cutter/Bender Cuts and bends rebar up to 5/8" diameter. Top loading of rebar makes for fast and easy cutting. Tool is made of heavy-duty castings and shipped mounted on wood board (66"x7-1/2"). Weight 55 lbs. No. Description GG729 Top-Loading Rebar Cutter/Bender

Rebar Lifter Hook

Hook provides leverage to lift rebar and wire mesh. Fitted with heavy-duty 60" wood handle. **No.** GG635

Tie Wire Reel

GG729-01

GG727-01

Lightweight but strong. Will not chip, crack or break. Highly visable safety yellow plastic. Fits any standard belt. **No.** GG309



Replacement Cutter Blades, Steel (1 pair)

48" Metal Replacement Handle

Metal Tie Wire Reel

Made of strong lightweight aluminum. Will not chip, crack or break. Easy turn handle. Fits any standard belt.



Professional Tie Wire Twister

Special loop hook designed to twist wire bar ties with a minimum of effort. Lets you do the job right, quickly and safely. Fitted with 4-1/4" wood handle.

No. GG310

dle.

Economy Tie Wire Twister

Designed to twist wire bar ties with a minimum of effort. Fitted with 4" plastic handle.

No. GG312*

"Big John" and "Little John" Pry Bars All Steel Heavy-Duty Pry Bars

Strong Tubular Handles

All purpose tool ideal for prying forms and other construction jobs. Specially designed 3" wide blade angle and hardened steel claw make for easy prying.

"Big John" Heavy-Duty Pry Bar

No. Description
GG630 56" Length
14 lbs.
"Little John" Pry Bar

GG631 46" Length 7 lbs.

Rocker Head Pry Bar

Extra heavy-duty. Unique rocker head for more power without blocking. Unique push/pull action makes even the toughest job simple. Open claw design works in tight places. Double claw for hard-to-reach areas.

No. Size GG632 30" GG634 48"

Rebar Bender

Strong, light, easy and simple to use. Completely portable. Can be used anywhere on the job. 36" length provides enough leverage to bend 5/8" reinforcing bar.

No. GG629

Channellock® Ironworker's Pliers

Wire cutting plier for tying concrete reinforcing bars. Bevel nose design plus long curved handles. Hand honed cutting edge. Plastic-dipped grips.

No. Length



Tie Wire Twister

Two or three pulls of the handle turns the hook within its socket, twisting the wire. Designed for rough treatment. Rubber coated 12" ribbed handle for firm grip.

No. GG325*



Concrete Tools

www.KraftTool.com

CONCRETE FINISH BROOMS



Concrete Finishing Broom (Aluminum)

Brush down new concrete after floating with these lightweight aluminum brooms. Three style bristles to choose from: medium/ general purpose black poly (shown), extra soft white poly, or natural horsehair and poly blend. All bristles are epoxy set for long wear and durability. Use with threaded or snap handle adapters.

No.	Size	Bristle Material
CC175	24	Medium/General Purpose (Black Poly)
CC177	36"	Medium/General Purpose (Black Poly)
CC178	48"	Medium/General Purpose (Black Poly)
CC189	60"	Medium/General Purpose (Black Poly)
CC203	72"	Medium/General Purpose (Black Poly)
CC179	36"	Extra Soft (White Poly)
CC180	36"	Natural Horsehair and Poly Blend
CC176	48"	Natural Horsehair and Poly Blend



Weigh-Lite® Concrete Finishing Broom

Made for brushing down newly laid concrete surface. No waiting for surface to dry. Soft, plastic fibers on solid stock brush. CC160 clevis bracket included. Use with threaded or snap handle adapters.

No.	Size	Replac	ement	Bris	tle Strip
CC154	24"	CC155		24"	
CC156	36"	CC157		36"	
CC158	48"	CC159		48"	
.022 Bristle,	Medium	Coarse	White	Poly	(not shown)
CC247	36"	CC247-	-01	36"	
CC248	48"	CC249		48"	

CC251 CC250 .030 Bristle, Coarse Black Poly (not shown)

Bracket Only CC160 CC246 36" CC246-01



Concrete Finishing Broom for broom without handle

Add "01" after part no.

Soft plastic bristles designed to give a fine finish on newly poured concrete. Long-wearing bristles are set solidly in wood. All brooms come with 5' wood handle (CC163).

Plastic Bristles

No.	Size	Bristles	No.	Size	Bristles
CC164	18"	2-3/8"	CC166	36"	3-1/4"
CC165	24"	2-3/8"	CC188	48"	3-1/4"
Horsehair Bristles (for a softer finish)					
CC193	24"	2-1/2"	CC194	36"	2-1/2"
CC163	5' Metal Threaded Replacement Wood Handle				



Concrete Finishing Broom (Wood)

Brush down new concrete after floating, with these poly fiber brooms. Medium-general purpose black poly bristles. All bristles are epoxy set for long wear and durability. All brooms are made from solid hardwood lacquered blocks for just the right feel and finish. Use with threaded or snap handle adapters.

No.	Size	Bristle Material	
CC170	24"	Medium-General Purpose (Black Poly)	Soft Finish
CC172	36"	Medium-General Purpose (Black Poly)	
CC173	48"	Medium-General Purpose (Black Poly)	



"The Performer" Concrete Finishing Broom

Concrete finishing broom has three rows of black 3" nylon bristles. Fits any standard threaded handle. Adapter included. Accepts standard broom threaded handles.

No.	Size	No.	Size
CC254	24"	CC256	36"
CC255	30"	CC259	Replacement Handle Adapter



Soft Nylon Concrete Finishing Broom

Lightweight broom with two rows of extra soft 4" nylon bristles. Made for a fine finish on newly laid concrete. Use with threaded or snap handle adapters.

No.	Size
CC457	36"
CC458	48"

Concrete Floor Broom

All-purpose floor broom for concrete and wood floors. 3" black tampico fiber on wooden block, 60" threaded wood handle. Accepts broom threaded extension handles.

Size No. CC183 18" CC184 24" CC186 36"

Add "01" after part no. for broom without handle

All-Purpose Horsehair Floor & Finish Broom

All-purpose floor broom for concrete and wood floors. 2-7/8" pure 100% black horsehair on wood block with 60" threaded wood handle. Accepts broom threaded extension handles.

Size No. CC187 24" 36" CC192

Add "01" after part no. for broom without handle



D

Float and Broom Combo

Foat and broom in one pass Helps eliminate reaching and lifting Perfect tool for wide slabs

Great tool to finish wide slabs without reaching or lifting. Adjustable broom adapter bar allows user to determine the working angle of the broom. For best results, broom should extend past end of float.

PARTS MUST BE ORDERED SEPARATELY.

No. Description

CC802-01 A) 48"x8" Heavy-Duty Magnesium Bull Float

CC294 B) EZY-Tilt® II 6-Hole Bracket (use 1-3/8" or 1-3/4" Snap Button Bull Float Handle)
CC181 C) Combo Broom Adapter Bar (Fits Bull Floats, Big "D" Floats & Fresnos with

tilting brackets or adapters to use with texture brooms)

CC182 D) 54" Weigh-Lite® Broom with two brackets (CC191) for adapter bar CC190 E) 54" Replacement Broom Strip for (CC182); Medium Bristles

CC191 F) Replacement Bracket for Adapter Bar (2 required)

Green Nylex® Soft Finish Broom

Soft concrete finish broom with memory resistant soft green Nylex® bristles. Comes with 5' wood handle (CC163).

No. Size CC454 24" CC456 36"



Hand Concrete Finish Brush

Curb brush with built in handle for finishing newly laid concrete. 12" long with soft poly horsehair blend bristles. Great for finishing small areas

No. CC269



These handles fit all brooms that take a broom thread. Swivel twist lock loosens and tightens handles when extended to desired length.

No. Size

CC446 A) Fiberglass® with Aluminum Extensions 6'3" to 12' CC429 B) Fiberglass® with Aluminum Extensions 6'6" to 18'

CC448 C) All Fiberglass® 6'3" to 12'

Wood Handle

No. Size

CC163 D) 5' Metal Thread Wood Broom Handle CC163L E) 6' Metal Thread Wood Broom Handle

Steel Handle

60" heavy-duty coated steel handle with broom threaded tip.

No. F) GG232 **NEW**

All-Angle Broom Adapter

Cut out section of adapter fits over broom bracket. Adjustable angle.

Accepts broom thread handle. (Hardware not included.)

No. Size

CC493 Broom Adapter CC494 Broom Bracket Base

Extension Handle Broom Adapter


Attach paint rollers, brooms, etc., to molded thread extension handles. **No.** CC297



Base

Add "01" after part no.

for broom without handle





Curb brush for hand brushing newly laid finished concrete surfaces. 12" long with soft plastic fiber bristles. Perfect for those small jobs.



Broom Cover/Protector

Designed to fit aluminum finish brooms up to 48". Open ends allow broom to dry and keep original shape. Velcro closures secure broom in place.



3-Piece Aluminum Handle

3-piece snap-style 5' aluminum handle with broom thread tip.

No. CC263

Flipper Tilt Bracket™

Pre-set your broom to automatically tilt at desired angle to finish during both extension and retrieval. Adjustable stops limit broom to pivot to a pre-set angle *or* maintain a fixed handle position. Allows for a full 105° range of motion. Use with thread or button

handle adapters. Attach bracket to CC494 broom bracket base (included with most Kraft finishing brooms).

finishing brooms **No.** CC496





Aluminum Concrete Chutes

Extruded aluminum one-piece concrete chutes. Lightweight and welded for extra strength. Welded flat bar braces across the top of each chute. Includes chain for attaching to truck. Available with or without flare. (Add "F" to the number for flare).

Νo.	Size	Weight
CC988**	8'	42 lbs.
CC992**	12'	75 lbs.
CC996**	16'	98 lbs.
CC999**	20'	120 lbs.

^{**} Must ship via truck

Concrete Chute Tool

Sturdy, lightweight and made of 1/8" aircraft aluminum. Blade size is 10"x7-1/2" and the radius will fit most chutes. Comes with 54" wood handle.

No.	Description
CC987**	Not Assembled
CC987ASM**	Assembled

^{**}Must ship via oversized rate or truck




Telescoping Extension Handle

Aluminum telescoping extension handle. 1-3/8' button style attachment. Use with brackets and No. adapters to fit 1-3/8" diameter. Ideal for extra CC430 long reach with lighter tools like brooms. Twistlock holds handle at desired length.

Size 8'-16'

Telescoping Handle 12'-24' Telescoping Handle CC436 CC430-01 Replacement Lock Assembly

Packed 6 per carton



Easy Mixer Concrete Hoe Great tool for mixing concrete fast in

wheelbarrows, backhoe buckets and other mixing containers. Patented forged head easily mixes 60 to 90 lb. bags of concrete in less than a minute. Special design creates minimum splash with 50% less drag. Great in corners. Open bag with point of hoe. 7-1/2"x6" blade.

No.	Description	
A) CC211	Easy Mixer Con	

ncrete Hoe with 60" Handle Easy Mixer Concrete Hoe B) CC212 with 21" Handle

Flat Wire Texture Broom

Broom produces a uniform rough groove surface on roads and bridges for maximum traction. Bracket accepts all clevis handles. Flat wires are 5" in length by .125 width, with 3/4" standard spacing on center; 1/2", 5/8" and 1" also available. Order adapters extra to use with bull float handles (page 16).

When Ordering Please Specify:

1/2", 5/8", 3/4" or 1" spacing on center (3/4" is the most popular size).

(6, 1 16 111 111 111 111 111 111 111 111				
No.	Size	Spacing		
CC196-1/2	36"	1/2"		
CC196-5/8	36"	5/8"		
CC196-3/4	36"	3/4"		
CC196-1	36"	1"		
CC198-1/2	48"	1/2"		
CC198-5/8	48"	5/8"		
CC198-3/4	48"	3/4"		
CC198-1	48"	1"		
CC199-1/2	60"	1/2"		
CC199-5/8	60"	5/8"		
CC199-3/4	60"	3/4"		
CC199-1	60"	1"		
CC200	Replacer	ment Tines		

Kraft also offers wire texture brooms that vary according to State or Federal specifications in relation to tine spacing and length.





SPECIAL ORDERING AVAILABLE: Special length and spacing needed? **CALL TODAY!**

Special lengths are also available for large paving machines.

Barrier Trowel

Great for making safety grooves. Carbon steel blade with rounded corners. Comes with 5' wood handle (CC386). Use with fresno groover attachments to adjust for bit size, depth and spacing. Order groover bits separately (page 20).



Round Rub Brick

Lightweight round rub brick with handle. Makes grinding easy. Use one in each hand. Stone is 1" thick and 6" diameter.

Grit Size CF270 6"x1' 20

Broken-In Rub Brick

Already broken-in and ready for smoothing and dressing down concrete. A good value for the price.

No. Size Grit CF281 8"x3-1/2"x3/4" 20



Rub Bricks A) Fluted

Fluted silicon carbide rub bricks with a contoured handle to minimize fatigue. Preferred by finishers for fast and easy concrete smoothing and dressing down.

Size	Grit
8"x3-1/2"x1-1/2"	20
6"x3"x1"	20
6"x3"x1"	60
	8"x3-1/2"x1-1/2" 6"x3"x1"

B) Fluted Less Handle

Made of silicon carbide, fluted on two sides.

No.	Size	Gri
CF462	6"x2"x2"	20
CF482	8"x2"x2"	20



Rub Brick Mop

Used for concrete smoothing, dressing down and removing form marks. Aluminum bracket with 5' wood clevis handle.

No.	Size	Grit
CC497	8"x7"	20
CC497-01	8"x7" w/o Handle	20
CF268-01	Replacement	20
	Rub Brick (2 req)	

Curved Shotcrete Fresno

This fresno is specially curved for shotcrete work. The rivets are left unground for extra strength. High quality round end carbon blade with steel mounting. Single action bracket.

No. Size CC914 24"x5" CC915 30"x5"



GUNITE AND SHOTCRETE

Gunite Trowel

Same craftsmanship as regular all Kraft concrete trowels Rivets have not been ground off, making the trowel stronger for use on qunite.

Straight V	Vood Handle	ProForm®	Handle
No.	Size	No.	Size
CF208	12"x4"	CF208PF	12"x4"
CF209	14"x4"	CF209PF	14"x4"



Radius Bender

Radius bender is used for rounding and finishing corners of pools and other shotcrete or gunite corners that need freehand finishing. Blue steel blade measures 24"x2-1/2".

No. CC980

Heavy-Duty Gunite Step Trowel

Strongest trowel around. Long-wearing thicker blade adds rigidity to this extra heavy-duty trowel. ProForm® handle is attached to a 1/2" square steel bar which provides the strength needed to work with gunite material.

18" Trowel is ideal for pool steps

ProForm® Handle No. Size CF204PF 14"x4" CF206PF 18"x4"



Flexible Gunite Shoes

Gray flexible plastic lets you work on gunite, epoxy or sealers with ease of movement. Protect your work and bring air bubbles out of the application. (13) firmly attached 3/4" (overall length) steel spikes cover the bottom of the shoe. Two adjustable nylon straps securely hold gunite shoe to work boot. No. Description

HC177* HC177-01*

Flexible Gunite Shoes (pair) 3/4" Replacement Spikes (26) HC178-02* Replacement Straps (set)





Gunite Shoes With Spikes

Adjustable lightweight aluminum shoes. One size fits all. Fitted with (12) 1" steel spikes. Adjustable sole plate and heel support. Two nylon adjustable straps securely hold qunite shoe to work boot.

No. CC970 (pair)



Gunite Shoes

Used for Epoxy and Gunite installation. One size fits all. Fitted with (13) 1-1/2" (overall length) steel spikes. Two nylon adjustable straps securely hold gunite shoe to work boot.

Description No.

HC178* Gunite Shoes (pair) HC178-01* 1-1/2" Replacement Spikes HC178-02* Replacement Straps



Horizontal **Control Joints**

Ideal for Parking Curbs, Step Faces, Step Corners, Control Joints,

Curb & Gutter, Stadium Risers, Exposed Aggregate

Concrete Tools

- Easy to use, saves time and increases the quality of your work
- Must-have tools for every concrete finisher

Step-Saver® Groovers

- Used to groove vertical and horizontal control joints into the face of slabs, curbs and steps
- Simply work the groover between the form and concrete for a perfect joint every time

No.	Size
05007	4011

CF007	12"L x 3/8"W x 3/4"D
CF008	12"L x 1/2"W x 1"D
CF009	12"L x 7/8"W x 3/4"D
CF010	6"L x 1/2"W x 1"D



U.S. Patent #D-333,600


Step-Saver® Edgers

≤Vértical

Control Joints

- · Make finishing step corners a breeze
- Insert and work between forms and concrete at step corners
- Once risers are stripped perfect rounded corners remain

No.	Size
CF001	10"L x 3/8"R
CF002	10"L x 1/2"R
CEUU3	10"I v 2//1"D





Vertical Corners

ALL-STEEL GROOVERS

- · Available in hand and walking styles
- Extra weight of tools allows sharp clean grooves
- Target sites on walking groovers for straight lines

All-Steel Walking Groovers

A) For Bull Float Brackets

Groover made with sight guide and two studs. Order bull float brackets or handle adapters separately (see pages 14-15)

adapters	eparatery (see	pages 14	·- 1 <i>0)</i> .
No.	Size	Depth	Radius
CC700	12"x14"	1"	1/2"
CC701	12"x14"	1"	3/4"
CC702A	8"x10"	1"	1/2"
CC703A	8"x10"	1"	3/4"

B) For Fresno Adapters

Groover made with sight guide and prong style mounting bracket. Use with fresno adapters (see page 21).

No.	Size	Depth	Radius
CC702	8"x10"	1"	1/2"
CC703	8"x10"	1"	3/4"

All-Steel Hand Groovers

Comfortable soft grip handle


No.	Size	Depth	Radius
CF483	6"x6"	1"	1/2"
CF484	6"x6"	1"	3/4"



Walking Angle Groovers Cuts groove diagonally away from corners

and enclosed areas.

No.	Size	Depth	Radius
CC704	8"x10"	1"	3/4"
CC705	8"x10"	1"	1/2"
CC706	8"x10"	7/8"	3/4"



Silver Bit Airplane Groover

Solid aluminum milled for perfect balance. Bits cut smooth and are bolted to blade for easy replacements. Special handle adapters adjust handle to comfortable height, order

separatel	y. Measures	24"x8".	
No.	Depth	Radiu	IS
CC868	3/4"	3/8"	
CC869	1"	3/8"	
CC870	1-1/4"	3/8"	ı
	adapter with		Ю
Airplane Gr	oover		



Add "01" after part no. for replacement bit

Handle Adapter Plates

Handle adapters for all-steel groovers and hand tools. Three styles: swivel action, 2-hole single action, or 4-hole single action.

Description No.

CC653 4-Hole Single Action Plate Adapter

CC659 2-Hole Single Action Adapter CC660 2-Hole Swivel Action Adapter

2-Hole 2-Hole Single Action Swivel Action

Handle Adapters

For Silver Bit Airplane Groover

Handle adapter adjusts handle height. Twist and lock to tighten in place.

No.	Description
CC490	A) 1-3/8" Snap Handle Adapter
CC491	B) 1-3/4" Snap Handle Adapter
CC492	C) 1-3/4" Threaded Handle Adapter



4-Hole

Single Action






BRONZE GROOVERS











MEDIUM BIT 5-1/2"x3"






Wood CF408 **ProForm®** CF408PF

BIG TEX BIT 6"x4-1/2"

Radius 1/4" 5/8" Deep Bit 5/8" Wide Bit



Wood CF314 **ProForm®** CF314PF

DEEP BIT 6"x4-1/2"


1" Deep Bit 1/2" Wide Bit Radius 1/4"



Wood CF380 **ProForm®** CF380PF

COLORADO BIT 6-1/2"x3"

3/4" Deep Bit 3/8" Wide Bit Radius 1/8"





CF301



SMALL BIT 6"x2"

3/16" Deep Bit 3/16" Wide Bit Radius 1/4"



Wood CF305

ProForm® CF305PF

NARROW BIT 6"x4-1/2"





Wood CF316

ProForm® CF316PF

ProForm®

CF317PF

DENVER JUMBO BIT 6"x4-1/2"





Wood CF317

EXTRA DEEP BIT 7-1/2"x4-1/2"


1-1/2" Deep Bit 1/2" Wide Bit Radius 1/4" Choice of Handle



Wood **ProForm®** CF303 CF303PF

> LARGE BIT 6"x4-1/2"

1/2" Deep Bit 3/8" Wide Bit Radius 1/4"



6

Wood CF304

ProForm® CF304PF

BIG BIT 6"x4-1/2"

3/4" Deep Bit 7/8" Wide Bit Radius 3/8"



Wood

ProForm® CF315PF CF315

CANADIAN **DEEP BIT** 6"x4-1/2"

1-1/2" Deep Bit 1/2" Wide Bit Radius 1/4"



Wood CF374

ProForm® CF374PF

DEEP BIT 8"x4-1/2"

1/2" Wide Bit 1" Deep Bit

Radius 1/4"

www.KraftTool.com **Concrete Tools**

BRONZE EDGERS & GROOVERS

- Unique long-wearing one-piece casting
- Hand polished for the professional concrete finisher
- Available in either wood or soft grip ProForm® handles
- Made in the USA



Bronze Groover and Edger

Groover bit (depth and radius) matches edger lip. Perfect for matching edge and groove finishes on sidewalks and driveways.

Choice of Handle



38



Wood	<u>ProForm</u> ®	
No.	No.	Size
CF318	CF318PF	Edger, 6"x3", 3/8" Radius, 3/4" Lip
CF319	CF319PF	Groover, 6"x6", 3/4" Bit Depth, 5/8" Width, 3/8" Radius
CF324	CF324PF	Edger/Groover (Set)

Bronze Chamfer Tube Edger

- · Belt polished surface for cutting clean, smooth edges
- Used for creating chamfered edges on round support piers
- Made of long wearing one-piece bronze with 1" lip and 1/2" radius and turned
- Slope on the pier edge can be varied depending upon wetness of the concrete and the angle and pressure of the Chamfer Tube Edger

Wood	<u>ProForm</u> ®	Diamete
No.	No.	Diamete
CF382	CF382PF	12"
CF383	CF383PF	16"
CF384	CF384PF	18"



Quick Change Converter Bracket for Hand-Held Tools

- Converts any wood handled tool into a walking tool in seconds
- Thumb screws hold aluminum bracket securely fixed in place
- Fits all wooden handled bronze, stainless steel and blue steel hand tools





Iron Groover Dallas Bit Groover

Made of long-wearing heavy-duty malleable iron. Features approximately 1/8" radius.

non roataroa	approxima		i aaiao.
No.	Size	Depth	Width
CF299	6"x4-1/2"	5/8"	5/8"



Special turned up ends to eliminate gouging of concrete

Wood	ProForm®			
No.	No.	Size	Radius	Lip
CF311	CF311PF	6"x2-3/4"	1/4"	5/8"
CF313	CF313PF	6"x4"	1/4"	5/8"



Jumbo Bronze Edger

Special turned up ends to eliminate gouging of concrete

Wood				
No.	No.	Size	Radius	Lip
	CF312PF		1/4"	3/4"



Bronze Rocker Groover

Curved blade and tilt handle give plenty of knuckle room.

No.	Size	Bit	Depth
CF306	5"x1-3/4"	1/4"x1/4"	1/8"
CF307	5"x1-3/4"	3/8"x3/8"	1/4"
CF308	5"x1-3/4"	1/2"x1/2"	1/4"



Ultra Hard Groover Heavy-Duty Iron

This west coast favorite is made of a special formula chrome-nickel-iron metal that is long lasting. 6" wood handle with steel clevis tightens to various angles.

No.	Size	Depth	Width
CF404	3-1/2"x4"	1/4"	3/8"



Bronze Concrete Name Stamp

The perfect way to mark concrete for permanent identification. Made from high grade bronze. Stamp is 5"x9" oval with flat ends. 16 spaces on three lines plus the year. Replacement year stamp is 5/8" high. Stamp can be furnished without date on request. Allow approximately 2-3 weeks for shipment.

No. Description
CF400 Stamp with 2014 Insert
CF400PF Stamp with 2014 Insert
with ProForm® Handle
CF400-01 Stamp without Date
CF401-14 2014 Date (Insert Only)

CF401-15

Stamp without Date 2014 Date (Insert Only) 2015 Date (Insert Only)

PUT YOUR NAME HERE

Order forms available online or ask your Customer Service Representative

KRAFT TOOL CO

8325 HEDGE LANE

2014

Walking Bronze Groover Single End Bit Groover

- Belt polished surface for cutting clean smooth sharp grooves
- Long wearing one-piece bronze with turned up ends
- Easy to clean and comfortable to use
- Comes with 5' wood clevis handle (CC386)
 6"x4-1/2"

• / · · / -			
No.	Depth	Width	Radius
CC303	1/2"	3/8"	1/4"
CC308	5/8"	5/8"	1/4"
CC304	3/4"	7/8"	3/8"
CC305	3/4"	3/8"	1/4"
CC314	1"	1/2"	1/4"
CC316	1-1/4"	1"	1/2"
7-1/2"x4-1/2	2"		
CC317	1-1/2"	1/2"	1/4"
8"x4-1/2"			
CC374	1"	1/2"	1/4"

Add "01" after part no. for groover without handle

Double End Bit Groover

- Grooves in both directions
- Comes with 5' wood clevis handle (CC386)

8"x4-1/2"

 No.
 Depth
 Width
 Radius

 CC275
 1"
 1/2"
 1/4"

Add "01" after part no. for groover without handle

Single End Bit Groover 8"x8"

- Largest bronze walking groover available
- Belt polished surface for cutting clean smooth sharp grooves
- Long wearing one-piece bronze with turned up ends
- Easy to clean and comfortable to use
- Comes with 5' wood clevis handle (CC386)

Add "01" after part no. for groover without handle

No.	Depth	Width	Radius
CC276	3/4"	3/8"	1/4"
CC277	3/4"	1/4"	1/8"
CC278	1"	3/8"	1/4"
CC279	1-1/2"	5/8"	1/4"

Bronze Groover With 360° Swivel Bracket

- Belt polished surface for cutting clean, smooth and sharp grooves
- Fitted with 360 degree swivel handle bracket
- Easy to clean and comfortable to use
- Includes 54" heavy-duty wood clevis handle (CC656)

Add "01" after part no. for groover without handle

6"x4-1/2"

No.	Depth	Width	Radius
CC303CA	1/2"	3/8"	1/4"
CC304CA	3/4"	7/8"	3/8"
CC305CA	3/4"	3/8"	1/4"
CC314CA	1"	1/2"	1/4"

"Side Railer" Bronze Groover

- Unique design with raised sides allows this popular bronze groover to more accurately follow forms and straightedges when grooving
- Comes with 5' wood clevis handle (CC386)
 No. Size Depth Width Radius

NO.	SIZE	Depui	WIGHT	nauiu
CC314SR	6"x4-1/2"	1"	1/2"	1/4"
CC304SR	6"x4-1/2"	3/4"	7/8"	3/8"



Add "01" after part no. for edger without handle

 Belt polished surface for cutting clean smooth edges

Bronze Edgers


 Long-wearing one-piece bronze with turned up ends

Easy to clean and comfortable to use
Comes with 5' wood clevis handle (CC386)

 No.
 Size
 Radius
 Lip

 CC302
 9"x4"
 1/4"
 3/4"

 CC313
 6"x4"
 1/4"
 5/8"



40

Walking Airplane Groovers With EZY-Tilt® II Bracket

Groovers are made of high quality cast aluminum with broken-in face. Bit size matches hand groovers (CF304 and CF314; page 37) in depth. Adjustable EZY-Tilt® II bracket (CC294) allows finisher to use tool at the perfect angle.

Single Bit Groovers A) 24"x8" Groover

	Bit	Bit
No.	Depth	Width
Big Bit CC304AS	3/4"	7/8"
Deep Bit CC314AS	1"	1/2"

Double Bit Groovers B) 24"x8" Groover


	Bit	Bit
No.	Depth	Width
Big Bit		
CC304A	3/4"	7/8"
Deep Bit		
CC314A	1"	1/2"
C) 24"x81	Round En	d Groove
	Rit	Rit

No.	Depth	Widtl
Big Bit		
CC304ARE	3/4"	7/8"
Deep Bit		
CC314ARE	1"	1/2"
D) 12"x8" 6	Proover	

	Bit	Bit
No.	Depth	Width
Big Bit		
CC304B	3/4"	7/8"
Deep Bit		
CC314B	1"	1/2"
E) 8"x8"	Groover (no	t shown)

	Bit	Bit
No.	Depth	Widtl
Big Bit CC304C	3/4"	7/8"
Deep Bit CC314C	1"	1/2"

WALKING **GROOVERS**



West Coast Style Airplane Groover

Made of high quality cast aluminum. Groover cuts clean sharp grooves. Tool measures 24"x8" with broken-in face. Fits all bull float handle adapters and clevis handles (sold separately).

A) Square Ends Double End Groover Bit

No.	Depth	Radius	
CC320	3/4"	3/8"	
CC322	1"	1/4"	
CC324	1-1/2"	1/4"	
Single End Groover Bit			

No.	Depth	Radius
CC321	3/4"	3/8"
CC323	1"	1/4"
CC325	1-1/2"	1/4"

B) Round Ends Double End Groover Bit


No.	Depth	Width	Radius
CC322RE	1"	1"	1/4"



Magnesium Jumbo Paver's Groover

This popular groover is available with either a 1" or 1-1/2" bronze bit. It comes with 4-hole adjustable bracket for use with 1-1/4" or 1-3/4" threaded handle. Groove bits are replaceable (page18).

No.	Size	Depth	Radius
CC858	8"x8"	1"	1/4"
CC859	8"x8"	1-1/2"	1/4"
CC861	8"x10"	1"	1/4"
CC863	8"x10"	1-1/2"	1/4"
CC865	8"x24"	1"	1/4"
CC867	8"x24"	1-1/2"	1/4"



Wood Handles

A) For Long Handle Bronze and Stainless Steel Tools

No. Description

5' Wood Handle w/Steel Clevis CC386 CC266 6' Wood Handle w/Steel Clevis

B) Short Clevis Wood Handle

Short handle attaches to long-handled tools so they can be used as hand tools and in tight spaces.

No. Description



8"x8" Stainless Steel **Walking Groover**

Made of heavy gauge stainless steel. Includes EZY-Tilt® II bracket. Closed end bit for clean grooves.

No.	Depth	Radiu
CC021	3/4"	1/2"
CC022	7/8"	1/2"

Power Groover

- Cuts sharp, clean grooves
- Aluminum bits are replaceable
- Broken-in front and back
- Bits are curved in front and back
- Use clevis handle (sold separately, page 40)
 No. Size Depth Width Radius
 CC380 9"x12" 3/4" 5/8" 1/4"

CC381 9"x12" 1" 5/8" 1/4" CC382 9"x12" 1-1/2" 5/8" 1/4" CC383 Set of (3) Different Size Replacement Bits (3/4", 1", 1-1/2") Walking Groover
With Handle
Socket Bracket

 Same as all-angle walking groover except with adjustable threaded handle socket

 Accepts threaded bull float extension handles (sold separately, see page 16)

No.	Size	Depth	Radius
CC357	8"x5"	1"	3/8"
CC356	8"x6"	3/4"	1/4"
CC355	10"x3-1/2"	1/2"	3/8"

Add "01" after part no. for groover without handle



All-Angle Walking Groover

- Made of heavy gauge stainless steel
- Reinforced with an electrically welded back plate to which the all-angle attachment is fastened
- No rivets to break up completely smooth face
- Comes with 5' wood clevis handle (CC386)
 No. Size Depth Radius

No.	Size	Depth	Radius	
CC347	8"x6"	1"	1/4"	
CC373	10"x3-1/2"	1/2"	3/8"	

Add "01" after part no. for edger without handle

Add "01" after part no. for groover without handle

Heavy-Duty Walking Groover

- Full top-plate for extra strength
- Narrow top plate available in some sizes for a lighter tool
- Includes 54" hardwood clevis handle (CC656)

Full Top Plate

No.	Size	Bit Width	Depth
CC756	8"x12"	1/4"	1/4"
No.	Size	Radius	Depth
CC757	8"x12"	3/8"	3/4"
CC758	8"x18"	3/8"	3/4"
CC759	8"x12"	3/4"	7/8"

Narrow Top Plate (not shown)

No.	Size	Radius	Depth
CC757N	8"x12"	3/8"	3/4"
CC759N	8"x12"	3/4"	7/8"

Single-Action Two-Way Walking Edger

Made of heavy gauge stainless steel, this tool is reinforced with electrically welded back plate to which the handle attachment is fastened. Handle can be tightened so it can be flipped from one side to the other. Comes with 5' wood clevis handle (CC386).

No.	Size	Radius	Lip
CC244	8"x4"	1/2"	5/8"
CC241	10"x6"	3/8"	1/2"
CC242	10"x6"	1/2"	5/8"
CC245	10"x10"	1/8"	1/2"
CC243	10"x10"	1/2"	5/8"

Add "01" after part no. for edger without handle

Heavy-Duty Hand Groover

- Polished stainless steel creates smooth working surface
- Top plate increases strength for cutting grooves in concrete

No.	Size	Width	Depth
CF756	6"x6"	1/4"	1/4"
No.	Size	Radius	Depth

Stainless Steel Hand Groover

- Special polished stainless steel for extra smooth working surface
- Turned up ends prevents gouging



 Wood
 ProForm®

 No.
 Size
 Depth
 Radius

 CF599
 CF599PF
 6"x6"
 3/8"
 1/4"

Stainless Steel Walking Groover (not shown)

- 360° swivel bracket
- 5' wood clevis handle (CC386)
- Turned up ends prevents gouging

No.	Size	Depth	Radius
CC599	6"x6"	3/8"	1/4"

Walking Edger with Handle Socket Bracket

Made of heavy gauge stainless steel. This tool is reinforced with electrically welded back plate to which the handle attachment is fastened. Handle socket can be tightened so you can move it from one side to the other. Handle socket accepts threaded bull float extension handles (sold separately, page 16).

No.	Size	Radius	Lip
CC351	8"x5"	3/8"	1/2"
CC350	10"x6"	3/8"	1/2"



Made of heavy gauge stainless steel, this tool is reinforced with an electrically welded back plate to which the all-angle attachment is fastened. No rivets, completely smooth face. Comes with 5' wood handle (CC386).

No.	Size	Radius	Lip
CC122	6"x2-3/4"	3/8"	1/2"
CC168	8"x4"	1/4"	3/8"
CC167	8"x4"	3/8"	1/2"
CC120	8"x4"	1/2"	5/8"
CC121	8"x4"	3/4"	7/8"
CC101	8"x6"	1/4"	3/8"
CC102	8"x6"	3/8"	1/2"
CC103	8"x6"	1/2"	5/8"
CC104	8"x6"	3/4"	7/8"
CC123	8"x8"	1/4"	3/8"
CC124	8"x8"	3/8"	1/2"
CC108	8"x8"	1/2"	5/8"
CC109	8"x8"	3/4"	7/8"
CC125	10"x6"	1/2"	5/8"
CC126	10"x6"	3/4"	7/8"
CC127	10"x10"	3/8"	1/2"
CC128	10"x10"	1/2"	5/8"
CC129	10"x10"	3/4"	7/8"
CC371	10"x3"	3/8"	3/4"
CC370	10"x6"	3/8"	1/2"
CC365	10"x6"	3/8"	3/4"
CC366	10"x10"	1/8"	3/4"

Hand Seamer/Groover Stainless Steel

Seamer makes smooth control joints. No rivet design and hand polished stainless steel for an extra smooth working surface. Closed end bit eliminates build up in tool.



Wood	ProForm®			
No.	No.	Size	Depth	Radius
CF019	CF019PF	8"x5"	5/8"	3/8"
CF023	CF023PF	8"x5"	3/4"	1/2"
CF027	CF027PF	8"x5"	7/8"	3/4"
CF025	CF025PF	8"x8"	1/2"	3/8"
CF040	CF040PF	8"x8"	5/8"	3/8"
CF026	CF026PF	8"x8"	3/4"	1/2"
CF021	CF021PF	8"x8"	7/8"	3/4"
CF029	CF029PF	10"x10"	7/8"	3/4"




Walking Seamer/Groover Stainless Steel with Threaded Handle Bracket

Seamer makes smooth control joints. No rivet design and hand polished stainless steel for an extra smooth working surface. Closed end bit eliminates build up in tool. Use with threaded float handles (pages 16-17).

No.	Size	Depth	Radius
CC025	8"x8"	1/2"	3/8"
CC040	8"x8"	5/8"	3/8"
CC026	8"x8"	3/4"	1/2"
CC027	8"x8"	7/8"	3/4"
CC024	9"x7"	7/8"	3/4"
CC028	10"x10"	1/2"	1/4"
CC030	10"x10"	3/4"	1/2"
CC029	10"x10"	7/8"	3/4"





Single Edger with Groover Stainless Steel

Heavy-duty stainless steel groover makes smooth clean joints while edging. Closed end bit. Use with threaded float handles (pages 16-17).

No.	Size	Shiner	Bit	Radius
CC663	8"x6"	2"	3/4"	1/2"
CC664	8"x6"	2"	7/8"	3/4"



Hand Edger

Special *hand polished stainless steel* for an extra smooth working surface.

Wood	<u>ProForm</u> °			
No.	No.	Size	Radius	Llp
CF039	CF039PF	8"x8"	1/4"	1/2"
CF035	CF035PF	8"x8"	1/2"	3/4"
CF038	CF038PF	8"x8"	3/4"	7/8"
	No. CF039 CF035	No. No. CF039 CF035 CF03	No. No. Size CF039 CF039PF 8"x8" CF035 CF035PF 8"x8"	No. No. Size Radius CF039 CF039PF 8"x8" 1/4" CF035 CF035PF 8"x8" 1/2"



Western Groover

Stainless Steel

www.KraftTool.com

Popular on commercial jobs. Cuts grooves 3/16"x3/16". Blade is 2" wide, 3" long.

No. CF402



12"x5" Walking Edger with Adjustable Groover Stainless Steel

Heavy gauge stainless steel. Adjustable bronze groover locks in place. Accepts one or more fresno groover bits (page 20) for making parallel grooves. Fitted with 360 degree all-angle bracket. Includes 5' wood clevis handle (CC386).

No.	Radius	Bit Depth
CC609	3/8"	1/4"
CC607	3/8"	1/2"
CC600	3/8"	3/4"
CC601	3/8"	1"
CC613	1/2"	1/4"
CC611	1/2"	1/2"
CC602	1/2"	3/4"
CC603	1/2"	1"
CC617	3/4"	1/4"
CC615	3/4"	1/2"
CC604	3/4"	3/4"
CC605	3/4"	1"

12"x5" Hand Edger with Adjustable Groover Stainless Steel


Heavy gauge stainless steel. Adjustable bronze groover is adjustable and locks in place. Accepts one or more fresno groover bits (page 20) for making parallel grooves. Fitted with wood handle.

No.	Radius	Bit Depth
CF609	3/8"	1/4"
CF607	3/8"	1/2"
CF600	3/8"	3/4"
	-, -	3/4 1"
CF601	3/8"	
CF613	1/2"	1/4"
CF611	1/2"	1/2"
CF602	1/2"	3/4"
CF603	1/2"	1"
CF617	3/4"	1/4"
CF615	3/4"	1/2"
CF604	3/4"	3/4"
CF605	3/4"	1"
	A)	

Walking Seamer/Edger With Threaded Handle Bracket

Walking edger with threaded handle socket bracket. Special hand polished stainless steel for an extra smooth working surface.

Size	Radius	Lip
8"x8"	1/4"	1/2"
8"x8"	3/8"	1/2"
8"x8"	3/8"	5/8"
8"x8"	1/2"	3/4"
8"x8"	3/4"	7/8"
9"x7"	3/8"	1/2"
9"x7"	1/2"	3/4"
9"x7"	3/4"	7/8"
10"x10"	1/2"	3/4"
	8"x8" 8"x8" 8"x8" 8"x8" 8"x8" 9"x7" 9"x7" 9"x7"	8"x8" 1/4" 8"x8" 3/8" 8"x8" 3/8" 8"x8" 1/2" 8"x8" 3/4" 9"x7" 3/8" 9"x7" 1/2" 9"x7" 3/4"



6" Long Sidewalk Edgers Width

Plastic Handle Stainless Steel

Stainless Steel

Wood Handle Stainless Steel

ProForm®			
		H	landle
011	0:4	Stainles	
No.	Width	alk Edge Radius	rs Lip
CF161PF	1-1/2"	1/4"	3/8"
CF160PF	2"	3/8"	1/2"
CF162PF CF170PF	2-1/2" 3"	1/4" 1/8"	3/8" 1/4"
CF163PF	3"	1/4"	3/8"
CF092PF	3"	3/8"	1/2"
CF164PF CF171PF	3-1/2" 4"	3/8" 1/8"	1/2" 1/4"
CF171FF	4"	1/4"	3/8"
CF173PF	4"	3/8"	1/2"
CF165PF	4" 4"	1/2"	5/8"
CF907PF CF174PF	4"	5/8" 3/4"	3/4" 1"
CF136PF	6"	1/8"	1/4"
CF137PF	6"	1/4"	3/8"
CF138PF CF175PF	6" 6"	3/8" 1/2"	1/2" 5/8"
CF139PF	6"	3/4"	1"
CF912PF	6"	5/8"	3/4"
CF908PF 8" Long	6"	1" alk Edge	1-1/4"
CF169PF	4"	1/8"	1/4"
CF168PF	4"	1/4"	3/8"
CF167PF	4"	3/8"	1/2"
CF166PF CF185PF	4" 4"	1/2" 3/4"	5/8" 1"
CF127PF	5"	1/4"	3/8"
CF128PF	5"	3/8"	1/2"
CF129PF CF130PF	5" 5"	1/2" 3/4"	5/8" 1"
CF100PF	6"	1/8"	1/4"
CF101PF	6"	1/4"	3/8"
CF102PF CF103PF	6" 6"	3/8" 1/2"	1/2" 5/8"
CF103FF	6"	3/4"	1"
CF105PF	8"	1/8"	1/4"
CF106PF	8"	1/4"	3/8"
CF107PF CF108PF	8" 8"	3/8" 1/2"	1/2" 5/8"
CF109PF	8"	3/4"	1"
9" Long	Highw	ay Edge	rs
CF155PF CF176PF	2-1/2" 3"	1/2" 1/2"	5/8" 5/8"
CF188PF	4"	1/2"	5/8"
CF189PF	4"	3/4"	1"
CF190PF CF191PF	5" 5"	3/8" 1/2"	1/2" 5/8"
CF241PF	6"	1-1/2"	2"
10" Lon	g Highv	vay Edge	ers
CF158PF CF159PF	3-1/2" 4"	1/4" 3/8"	3/8" 1/2"
CF159PF CF154PF	4 4"	3/8 1"	1-1/4"
CF140PF	4"	1-1/2"	2"
CF143PF	5-3/4" 6"	2"	2-5/8"
CF909PF CF320PF	6"	1/4" 3/8"	3/8" 1/2"
CF321PF	6"	1/2"	5/8"
CF906PF	6"	5/8"	3/4"
CF322PF CF323PF	6" 6"	3/4" 1"	1" 1-1/4"
CF240PF	6"	1-1/2"	2"
CF144PF	6-1/4"	3	3-1/4"

www.KraftTool.com

		Stainl	Handle ess Steel
GII I o	na Cido		
No.	ng Side Width	<i>Naik Ed</i> Radius	
CF161	1-1/2"	1/4"	3/8"
CF160	2"	3/8"	1/2"
CF162	2-1/2"	1/4"	3/8"
CF170	3"	1/8"	1/4"
CF163	3"	1/4"	3/8"
CF092	3"	3/8"	1/2"
CF164	3-1/2"	3/8"	1/2"
CF171	4"	1/8"	1/4"
CF172	4"	1/4"	3/8"
CF173	4"	3/8"	1/2"
CF165	4"	1/2"	5/8"
CF907	4"	5/8"	3/4"
CF174	4" 6"	3/4"	1"
CF136 CF137	6"	1/8" 1/4"	1/4" 3/8"
CF137	6"	3/8"	1/2"
CF175	6"	1/2"	5/8"
CF139	6"	3/4"	1"
CF912	6"	5/8"	3/4"
CF908	6"	1"	1-1/4"
8" Lo		walk Ed	gers
CF169	4"	1/8"	1/4"
CF168	4"	1/4"	3/8"
CF167	4"	3/8"	1/2"
CF166	4"	1/2"	5/8"
CF185	4"	3/4"	1"
CF127	5"	1/4"	3/8"
CF128	5"	3/8"	1/2"
CF129	5" 5"	1/2"	5/8"
CF130	6"	3/4"	1" 1/4"
CF100 CF101	6"	1/8" 1/4"	3/8"
CF101	6"	3/8"	1/2"
CF103	6"	1/2"	5/8"
CF104	6"	3/4"	1"
CF105	8"	1/8"	1/4"
CF106	8"	1/4"	3/8"
CF107	8"	3/8"	1/2"
CF108	8"	1/2"	5/8"
CF109	8"	3/4"	1"
9" Lo	ng High		
CF155	2-1/2"	1/2"	5/8"
CF176	3"	1/2"	5/8"
CF188 CF189	4" 4"	1/2" 3/4"	5/8" 1"
CF189 CF190	5"	3/4	1/2"
CF190	5"	3/6 1/2"	5/8"
CF241	6"	1-1/2"	2"
	ng High	way Ec	lgers
CF158	3-1/2"	1/4"	3/8"
CF159	4"	3/8"	1/2"
CF154	4"	1"	1-1/4"
CF140	4"	1-1/2"	2"
CF143	5-3/4"	2"	2-5/8"
CF909	6"	1/4"	3/8"
CF320	6"	3/8"	1/2"
CF321	6"	1/2"	5/8"
CF906	6"	5/8"	3/4"
CF322	6"	3/4"	1"
CF323	6"	1"	1-1/4"
CF240	6"	1-1/2" 3"	2"
CF144	6-1/4"	3	3-1/4"

6" Loi		valk Ed	
No.	Width	Radius	
CF161P	1-1/2"	1/4"	3/8"
CF160P	2"	3/8"	1/2"
CF162P	2-1/2"	1/4"	3/8"
CF170P	3"	1/8"	1/4"
CF163P	3"	1/4"	3/8"
CF092P	3"	3/8"	1/2"
CF164P	3-1/2"	3/8"	1/2"
CF171P	4"	1/8"	1/4"
CF171P	4"	1/4"	3/8"
			3/0
CF173P	4"	3/8"	1/2"
CF165P	4"	1/2"	5/8"
CF907P	4"	5/8"	3/4"
CF174P	4"	3/4"	1"
CF136P	6"	1/8"	1/4"
CF137P	6"	1/4"	3/8"
CF138P	6"	3/8"	1/2"
CF175P	6"	1/2"	5/8"
CF139P	6"	3/4"	1"
CF912P	6"	5/8"	3/4"
CF908P	6"	1"	1-1/4"
8" Lon CF169P	g Sidew 4"	ralk Edg	
		1/8"	1/4"
CF168P	4"	1/4"	3/8"
CF167P	4"	3/8"	1/2"
CF166P	4"	1/2"	5/8"
CF185P	4"	3/4"	1"
CF127P	5"	1/4"	3/8"
CF128P	5"	3/8"	1/2"
CF129P	5"	1/2"	5/8"
CF130P	5"	3/4"	1"
CF100P	6"	1/8"	1/4"
	6"	1/0	
CF101P		1/4"	3/8"
CF102P	6"	3/8"	1/2"
CF103P	6"	1/2"	5/8"
CF104P	6"	3/4"	1"
CF105P	8"	1/8"	1/4"
CF106P	8"	1/4"	3/8"
CF107P	8"	3/8"	1/2"
CF108P	8"	1/2"	5/8"
CF109P	8"	3/4"	1"
	ng High	way Ede	
CF155P	2-1/2"	1/2"	5/8"
CF176P		1/2"	5/8"
	4"		5/8"
CF188P		1/2"	
CF189P	4"	3/4"	1"
CF190P	5"	3/8"	1/2"
CF191P	5"	1/2"	5/8"
CF241P	6"	1-1/2"	2"
10" Lo		way Ed	gers
CF158P	3-1/2"	1/4"	3/8"
CF159P	4"	3/8"	1/2"
CF154P	4"	1"	1-1/4"
CF140P	4"	1-1/2"	2"
CF143P	5-3/4"	2"	2-5/8"
CF909P	6"	1/4"	3/8"
CF320P	6"	3/8"	1/2"
	6"		1/Z E/0
CF321P		1/2"	5/8"
CF906P	6"	5/8"	3/4"
CF322P	6"	3/4"	1"
CF323P	6"	1"	1-1/4"
CF240P	6"	1-1/2"	2"
CF144P	6-1/4"	3"	3-1/4"
	Proud	V Made	In The L

www.KraftTool.com **Concrete Tools**



Wheelchair Hand and Walking Groovers

Stainless Steel

- · Cuts safety grooves for wheelchair ramps and non-skid areas
- Popular for most commercial and government jobs
- Bit is 1/4" deep and 1/4" wide
- Walking groovers include threaded handle

2-1/4" On Center

Wood	ProForm [®]	
No.	No.	Size
CF093	CF093PF	8"x10-1/2"
Walking	g Groover (n	ot shown)
No.		Size
CC093		8"x10-1/2"

2" On Center

Wood	ProForm ®		No. of
No.	No.	Size	Grooves
CF918	CF918PF	7-1/2"x6"	4
CF919	CF919PF	10"x6"	5
Walking	Groover (no	t shown)	No. of
Walking No.	g Groover (no	t shown) Size	No. of Grooves
	g Groover (no		
No.	g Groover (no	Size	Grooves

Universal Groover

- Popular among concrete finishers
- Turned up edges for clean groove
- Rivet-free

Universal Hand Groover

vvooa	ProForm	,	
No.	No.	Size	Bit
CF118	CF118PF	6"x3"	1/2" wide
			1/2" deep

Jumbo Hand Groover (not shown)

Wood	ProForm [®]	9	
No.	No.	Size	Bit
CF119	CF119PF	6"x4-3/4"	3/8" wide
			1/2" deep

Universal Walking Groover

(not shown)

 Comes with all-angle bracket and 5' wood clevis handle (CC386)

Size No. CC089 6"x3" 1/2" wide/deep





Stainless Steel Driveway Safety Groover• Heavy-duty stainless steel

- Guide lip on each side
- Grooves 3/4" on center

Wood	ProForm ®		
No.	No.	Size	Bit Depth
CF131	CF131PF	6"x6"	1/4"



Stainless Steel **Safety Step Edger/Groover**

- Popular on commercial jobs
- Cuts four grooves while edging the step
- Grooves 3/4" on center
- 6"x4-1/2"

Wood	ProForm [®]	,	
No.	No.	Bit Depth	Radius
CF112	CF112PF	1/4"	1/2"



- gouging of concrete
- Edger radius 1/4"
- Your choice of wood, plastic or soft grip ProForm® handle



CF142





CF141P CF142P

ProForm® No. Size CF141PF 6"x3" CF142PF 6"x2-1/2"



- Stainless steel
- Cuts safety grooves in non-skid areas
- 2" wide groove spacing
- Bit is 1/4" deep and 3/4" wide

Hand Groover

Wood	ProForm®		No. of
No.	No.	Size	Grooves
CF094	CF094PF	7-5/8"x6"	3
CF095	CF095PF	10-3/8"x8"	4

Walking Groover (not shown)

Comes with threaded handle bracket

Na	C:	No. of
No.	Size	Grooves
CC094	7-5/8"x6"	3
CC095	10-3/8"x8"	3



Stainless Steel

- Handy tool for most commercial jobs
- Forms top of curb and cuts grooves all in

Wood	ProForm®				
No.	No.	Size	Radius	Groove	
CF034	CF034PF	6"x8"	3/8"	1/4"	
CF046	CF046PF	6"x8"	1/2"	1/4"	
CF149	CF149PF	6"x8"	3/4"	1/4"	
CF044	CF044PF	6"x10"	3/4"	1/4"	
CF045	CF045PF	6"x12"	3/4"	1/4"	

Walking Edger-Groover (not shown)

• Comes with all-angle bracket and 5' wood clevis handle (CC386)

No.	Size	Radius	Groove
CC034	6"x8"	3/8"	1/4"
CC149	6"x8"	3/4"	1/4"



Deep Bit Hand Groover

Stainless Steel

 Edger has turned up ends to prevent gouging of concrete

Wood	ProForm ®			
No.	No.	Size	Depth	Radius
CF110	CF110PF	10"x3-1/2"	1/2"	3/8"
CF622	CF622PF	6"x5"	1/2"	3/8"
CF117	CF117PF	6"x6"	2"	1/4"
CF116	CF116PF	6"x6"	1-1/2"	1/4"
CF115	CF115PF	6"x6"	1"	1/4"

Walking Chamfer Tool

- Made of the finest stainless steel
- · Designed especially for tilt up and concrete slab work
- Comes with 5' wood handle (CC386)

OUTTIES WILL	i o wood ne	
No.	Size	Lip
CC342	9"x6"	1/2"
CC345	9"x6"	3/4"
CC349	9"x6"	1"
	A	705
	di	
	10	

Stainless Steel Edger With Float Handle

- Made of high quality rivet-free stainless
- Designed to fit exact contour of edge

Wood	ProForm [®]		
No.	No.	Size	Radius
CF900	CF900PF	10"x6"	1/4"
CF901	CF901PF	10"x6"	3/8"
CF902	CF902PF	10"x6"	1/2"
CF903	CF903PF	10"x6"	5/8"
CF904	CF904PF	10"x6"	3/4"
CF905	CF905PF	10"x6"	1"



Chamfer Edger

Stainless Steel Narrow Edger

Narrow Edger

- Made of stainless steel
- Perfect for narrow or hard-to-get-at finishing jobs

Wood	ProForm®		
No.	No.	Size	Radius
CF111	CF111PF	6"x1"	1/4"
CF113	CF113PF	6"x1"	3/8"
CF114	CF114PF	6"x1"	1/2"
CF120	CF120PF	6"x1"	3/4"


Stainless Steel Chamfer Edger

Wood	ProForm®		
	No.	Size	Lip
CF199	CF199PF	6"x1"	3/4

STAINLESS STEEL CHAMFER TOOLS

Single Lip Chamfer Tool





- Wall Capping Tool
 Made of high quality heavy-gauge rivet-free stainless steel
- · Ideal for rounding concrete on top of walls

I ProForm [®]		
No.	Size	
CF520PF	6-9/16"x9"	(6" Wall)
CF521PF		(8" Wall)
	No. CF520PF CF521PF	ProForm No. Size CF520PF 6-9/16"x9" CF521PF 8-7/8"x9"



Carpet Edger

- Made of high quality rivet-free stainless
- Designed to fit exact contour of edge
- Lip angle is 45 degrees

Wood			
No.	No.	Size	Lip
CF089	CF089PF	6"x3"	3/16"
CF090	CF090PF	6"x4"	3/16"
CF091	CF091PF	6"x6"	3/16"



Tapered Hand Edger

Made of heavy gauge stainless steel to work in all-angle corners. 4" edger available in wood or comfortable ProForm® soft grip handles.

Wood	<u>ProForm</u> [®]	,		
No.	No.	Size	Radius	Lip
CF151	CF151PF	Tapered 8" to 3"	3/8"	1/2"
CF156	CF156PF	Tapered 8" to 3"	1/2"	5/8"

Stainless Steel Wall Edger

Wall edger fits between wall forms and smooths the surface. Turned up end. Made of stainless steel and fitted with ProForm® handle. Blade measures 8"x7-1/2".

No. CF661PF



90° Carpet Edger

- Made of high quality rivet-free stainless
- Designed to fit exact contour of edge
- Lip angle is 90 degrees

Wood | ProForm® Size No. No. Lip CF528 CF528PF 6"x3" 1/4"



Heavy-Duty Steel Edger #7• Made of long lasting 12-gauge steel

- Designed to fit exact contour of edge
- A favorite of the professional edger <u>ProForm®</u> Wood

Radius Size No. No. CF527 CF527PF 8"x2" 3/8"






BLE BLUE STEEL EDGERS

• Tempered blue crucible spring steel • Flexible lightweight blade • "Gives" for just the right feel when working • 3 solid rivets







Blue Steel Edgers With ProForm® Uandle

with Pro	orme Ha	andie
No.	Size	Radius
CF566PF	6"x3"	1/8"
CF568PF	6"x3"	1/4"
CF569PF	6"x3"	3/8"
CF570PF	6"x3"	1/2"
CF565PF	6"x3"	3/4"
CF567PF	6"x4"	1/8"
CF572PF	6"x4"	1/4"
CF573PF	6"x4"	3/8"
CF574PF	6"x4"	1/2"
CF562PF	6"x4"	5/8"
CF571PF	6"x4"	3/4"
CF675PF	6"x4"	1"
CF579PF	6"x6"	1/8"
CF575PF	6"x6"	1/4"
CF576PF	6"x6"	3/8"
CF577PF	6"x6"	1/2"
CF563PF	6"x6"	5/8"
CF578PF	6"x6"	3/4"
CF564PF	6"x6	1"
CF670PF	6"x5-1/2"	1/8"
CF671PF	6"x5-1/2"	1/4"
CF672PF	6"x5-1/2"	3/8"
CF673PF	6"x5-1/2"	1/2"
CF674PF	6"x5-1/2"	3/4"
CF595PF	9"x6"	1/4"
CF596PF	9"x6"	3/8"
CF597PF	9"x6"	1/2"
OFFOORF		- / - !!

Blue Steel Edgers With Wood Handle

No.	Size	Radiu
CF566	6"x3"	1/8"
CF568	6"x3"	1/4"
CF569	6"x3"	3/8"
CF570	6"x3"	1/2"
CF565	6"x3"	3/4"
CF567	6"x4"	1/8"
CF572	6"x4"	1/4"
CF573	6"x4"	3/8"
CF574	6"x4"	1/2"
CF562	6"x4"	5/8"
CF571	6"x4"	3/4"
CF675	6"x4"	1"
CF579	6"x6"	1/8"
CF575	6"x6"	1/4"
CF576	6"x6"	3/8"
CF577	6"x6"	1/2"
CF563	6"x6"	5/8"
CF578	6"x6"	3/4"
CF564	6"x6"	1"
CF670	6"x5-1/2"	1/8"
CF671	6"x5-1/2"	1/4"
CF672	6"x5-1/2"	3/8"
CF673	6"x5-1/2"	1/2"
CF674	6"x5-1/2"	3/4"
CF595	9"x6"	1/4"
CF596	9"x6"	3/8"
CF597	9"x6"	1/2"
CF598	9"x6"	3/4"

Blue Steel Edgers With Plastic Handle

<i>DDILII</i> 1	Iuotio Iiuiit	110
No.	Size	Radiu
CF566P	6"x3"	1/8"
CF568P	6"x3"	1/4"
CF569P	6"x3"	3/8"
CF570P	6"x3"	1/2"
CF565P	6"x3"	3/4"
CF567P	6"x4"	1/8"
CF572P	6"x4"	1/4"
CF573P	6"x4"	3/8"
CF574P	6"x4"	1/2"
CF562P	6"x4"	5/8"
CF571P	6"x4"	3/4"
CF675P	6"x4"	1"
CF579P	6"x6"	1/8"
CF575P	6"x6"	1/4"
CF576P	6"x6"	3/8"
CF577P	6"x6"	1/2"
CF563P	6"x6"	5/8"
CF578P	6"x6"	3/4"
CF564P	6"x6"	1"
CF670P	6"x5-1/2"	1/8"
CF671P	6"x5-1/2"	1/4"
CF672P	6"x5-1/2"	3/8"
CF673P	6"x5-1/2"	1/2"
CF674P	6"x5-1/2"	3/4"
CF595P	9"x6"	1/4"
CF596P	9"x6"	3/8"
CF597P	9"x6"	1/2"
CF598P	9"x6"	3/4"
		1000

Blue Crucible Steel Curb and Step Tools• Made of blue crucible spring steel

9"x6"

- Provides just the right feel and flex for a professional finish

A) Curb Tool - Outside


Measures 9"x5"

CF598PF

Wood | ProForm® Radius Batter No. No. Lip Outside CF580PF CF580 1/2" 1-1/2" at 6" 3/4" CF581 | CF581PF 5" 1-1/2" at 6"



No.	No.	Size	Lip
CF515	CF515PF	6"x4"	3"
CF516	CF516PF	6"x6"	3"



Blue Crucible Steel Junior Step Tools • Made of blue crucible spring steel

- Provides just the right feel and flex for a professional finish
- · Purchase together or separately

A) Junior Step Tool - Outside


<u>ProForm®</u> Wood | **Radius** No. No. Size CF517 | CF517PF 6" x5" 2"

B) Junior Step Tool - Inside

Wood ∣ **ProForm®** No. **Radius** CF518 | CF518PF 6"x5" 2" 1/2"

Inside and Outside Pair

Wood | **ProForm®** Size **Radius** No. No. CF519 CF519PF 6"x5" 2" 1/2"



Outside





- Bracket has special angle for increased tilt action
- Comes with 54" wood clevis handle (CC656)

No.	Size	Radius
CC390	9"x4 "	1/4"
CC391	9"x4"	3/8"
CC392	9"x4"	1/2"
CC393	9"x6"	1/4"
CC394	9"x6"	3/8"
CC395	9"x6"	1/2"
CC396	9"x6"	3/4"
CC384	9"x8"	1/4"
CC385	9"x8"	3/8"
CC387	9"x8"	1/2"
CC388	9"x8"	3/4"

Size	Radius
9"x10"	1/4"
9"x10"	3/8"
9"x10"	1/2"
9"x10"	3/4"
9"x14"	1/4"
9"x14"	3/8"
9"x14"	1/2"
9"x14"	3/4"
	9"x10" 9"x10" 9"x10" 9"x10" 9"x14" 9"x14" 9"x14"

All-Angle Blue Steel Walking Edger

With Swivel Bracket

- The edger blade "gives" a little for just the right feelBracket rotates 360 degrees
- Comes with 54" wood clevis handle (CC656)

None

No.	Size	Radius
CC390A	9"x4 "	1/4"
CC391A	9"x4"	3/8"
CC392A	9"x4"	1/2"
CC393A	9"x6"	1/4"
CC394A	9"x6"	3/8"
CC395A	9"x6"	1/2"
CC396A	9"x6"	3/4"
CC384A	9"x8"	1/4"
CC385A	9"x8"	3/8"
CC387A	9"x8"	1/2"
CC388A	9"x8"	3/4"

No.	Size	Radius
CC397A	9"x10"	1/4"
CC398A	9"x10"	3/8"
CC399A	9"x10"	1/2"
CC400A	9"x10"	3/4"
CC401A	9"x14"	1/4"
CC402A	9"x14"	3/8"
CC403A	9"x14"	1/2"
CC404A	9"x14"	3/4"

Blue Crucible Steel Step Tools


- Tempered blue crucible spring steel
- Blade is very flexible and lightweight
- Available with or without batter


A) Inside Step Tool


No.	No.	Size	Lip	Radius
CF584	CF584PF	7"x6"	6"	1/4"
CF760	CF760PF	7"x6"	6"	1/4"
CF585	CF585PF	7"x6"	6"	3/8"
CF761	CF761PF	7"x6"	6"	3/8"
CF586	CF586PF	7"x6"	6"	1/2"
CF762	CF762PF	7"x6"	6"	1/2"
CF587	CF587PF	7"x6"	6"	3/4"
CF763	CF763PF	7"x6"	6"	3/4"
CF588	CF588PF	7"x6"	6"	1"
CF764	CF764PF	7"x6"	6"	1"
		_	_	


ĺood	ProForm®)			1/2 Da
0.	No.	Size	Lip	Radius	Batter
F584	CF584PF	7"x6"	6"	1/4"	1/2" at 6"
F760	CF760PF	7"x6"	6"	1/4"	None
F585	CF585PF	7"x6"	6"	3/8"	1/2" at 6"
F761	CF761PF	7"x6"	6"	3/8"	None
F586	CF586PF	7"x6"	6"	1/2"	1/2" at 6"
F762	CF762PF	7"x6"	6"	1/2"	None
F587	CF587PF	7"x6"	6"	3/4"	1/2" at 6"
F763	CF763PF	7"v6"	6"	3///"	None












Blue Steel Chamfer Tool

- Professional quality tool
- Formed to fit exact contour
- Lip is at a 45 degree angle

vvooa	ProForm [®]		
No.	No.	Size	Lip
CF523	CF523PF	6"x8"	3/4"
CF594	CF594PF	9"x6"	3/4"



54" Hardwood Replacement Handle

- Narrow steel clevis
- Made to fit blue steel walking tools No. CC656




Two-Way Blue Steel Walking Step Tools


- Tempered blue crucible spring steel
- Blade is very flexible and lightweight
- Comes with heavy-duty 54" clevis handle (CC656)

A) Inside	Step	Tool	
Nó.	Size	Lip	Radius
CC586	7"x6"	3"	1/2"

B) Outside Step Tool Nó. Size Lip

Radius CC590 6"x6" 3-1/2" 3/8" 1/2" CC591 6"x6" 3-1/2"





Curb and Gutter Tools

- Stainless steel and rivet free
- · Formed to fit the exact contour

A) 6" Length (2" Batter at 6")

ProForm® Wood No. No.

Size CF514 | CF514PF

CF513PF

4" Top, 6" Face, 2" Radius Curb

B) 6" Length (2" Batter at 6")

Wood **ProForm®** No. No.

CF513

Size 4" Top, 6" Face,

3" Bottom

2" Radius Curb, 90 Degree Gutter

C) 6" Length (1-1/2" Batter at 6")

Wood **ProForm®** No. No. CF650 CF650PF

4-1/4" Top, 6" Face,

4" Bottom

Size


1-1/2" Radius Curb/Gutter

D) 6" Length (8" Batter at 6-1/2")

Wood **ProForm®** No. No.

CF651 CF651PF 4" Top, 8" Face, 2-3/4" Bottom

3/4" Radius Curb/Gutter






Stainless steel

A) Curb Tool

Wood	ProForm [®])		
No.	No. CF193PF	Length	Width	Radius
CF193	CF193PF	6"	5"	2"
CF195	CF195PF	6"	5"	3"
CF197	CF197PF	6"	5"	1-1/2"

B) Gutter Tool

Wood	ProForm [®]			
No.	No.	Length	Width	Radius
CF198	CF198PF	6"	4-1/2"	1-1/2"
CF196	CF196PF	6"	4-1/2"	2"
CE104	CE10/DE	6"	1_1/2"	3"



- Stailness steel and rivet free
- Formed to fitt the exact contour of edge
- · Matching walking tool available

6" Length (2" Batter at 6")

o Length (2 Datter at o)				
Wood	ProForm®			
No.	No.	Size		
CF511	CF511PF	6" Top, 6" Face,		
		6" Bottom		
		2" Radius Curb,		
		3" Radius Gutter		
CF512	CF512PF	6" Top, 6" Face,		
		6" Bottom		
		3" Radius Curb,		
		2" Radius Gutter		



Approach Tool

• Stainless steel, 6" length Wood Handle

	Тор	Bottom		
No.	Width	Width	Radius	Drop
CF097	5"	4"	3/4"	1"
CF098	5"	4"	1/2"	1"
CF099	5"	4"	1"	1"
ProForm	® <u>Handl</u>	е		

Bottom Top Width Width Radius Drop No. CF097PF 5" 4" 3/4" 1" 1" CF098PF 5" 4" 1/2" 1" CF099PF 5" 4" 1"

Curb and Gutter Walking Tool

• Comes with 5' wood clevis handle (CC386) 6" Length (1-1/2" Batter at 6")

No. Size

CC961 4-1/4" Top, 6" Face, 4" Bottom, 1-1/2" Radius Curb / Gutter

6" Length (2" Batter at 6")

В

No. Size

CC962 6" Top, 6" Face, 6" Bottom,


2" Radius Curb, 3" Radius Gutter

6" Length (2" Batter at 6") NEW

No.

CC553 6" Top, 6" Face, 6" Bottom 3" Radius Curb, 2" Radius Gutter





Bottom

Sidewalk and Curb Tools

Stainless Steel


A) Outside Nose Tool

• With 1-1/2" lip

Wood	ProForm®			
No.	No.	Length	Width	Radius
CF146	CF146PF	6"	4"	1/2"
CF147	CF147PF	6"	4"	3/4"
CF148	CF148PF	6"	4"	1"
CF243	CF243PF	6"	4"	1-1/2"
				with 2" lip
CF244	CF244PF	6"	6"	1/2"
CF245	CF245PF	6"	6"	3/4"
CF247	CF247PF	6"	6"	1"
CF242	CF242PF	6"	6"	1-1/2"
				with 2" lip

B) Inside Cove Tool

• With 1-1/2" lip Wood **ProForm®** Length Width Radius No. No. CF157 CF157PF 6" 1/2" 3/4" 4" CF152 CF152PF 4" CF153PF CF153 6" 6" 1/2" CF248 CF248PF 6" 6" CF249 CF249PF 6" 3/4" CF250 | CF250PF 6"



Step and Corner Tools

Stainless Steel

A) Outside Nose Tool


ProForm [®]	9		
No.		Width	Radius
CF123PF	6"	2-1/2"	1/2"
CF125PF	6"	2-1/2"	1/4"
CF121PF	6"	2-1/2"	Square
	No. CF123PF CF125PF	ProForm No. Length CF123PF 6" CF125PF 6" CF121PF 6"	No. Length Width CF123PF 6" 2-1/2" CF125PF 6" 2-1/2"

B) Inside Cove Tool

Outside

Inside

<u>Wood</u>	<u>ProForm</u> ®)		
No.	No.	Lenath	Width	Radius
CF124	CF124PF	6"	2-1/2"	1/2"
CF126	CF126PF	6"	2-1/2"	
CF122	CF122PF	6"	2-1/2"	Square



Step Tools

Stainless Steel

• Inside and outside step tools, available individually or as a matched pair

• 8"x4" with 1/2" radius and 4" lip

Wood	ProForm ®	·	
No.	No.	Description	Batter
CF177	CF177PF	Inside Tool	1/2" at 6"
CF178	CF178PF	Outside Tool	1/2" at 6"
CF179	CF179PF	Matched Pair	1/2" at 6"
CF180	CF180PF	Inside Tool	None
CF181	CF181PF	Outside Tool	None
CF182	CF182PF	Matched Pair	None

Two Radius Edger • Stainless Steel 6"x6" edger with two

radiuses (1-1/2" and 3/8" Radius)

• Fitted with our ProForm® handle



Safety Ramp Groovers

- Ideal for cutting grooves in sidewalk safety ramps where water drainage and traction are critical
- Use as a set of 3 (Left, Straight and Right)
- Order a line of part numbers for a complete set
- All safety ramp groover's groove depth and width is 1/4"x1/4"


Hand G	Groove		
Left (45°)	Straight	Right (45°)	Spacing
CF080	CF081	CF082	1-1/2"
CF083	CF084	CF085	3/4"
CF086	CF087	CF088	1"

Walking(Swivel) Groovers

- Comes with 360 degree all-angle bracket
- Uses wood clevis handle (sold separately)
- Use adapters (page16) for use with bull float handles

Groove

Left (45°)	Straight	Right (45°)	Spacing
CC080	CC081	CC082	1-1/2"
CC083	CC084	CC085	3/4"
CC086	CC087	CC088	1"





Left and Right Groover Dimensions: 13-1/2"x5-1/2"

Straight Groover

Dimensions: 13"x 5-1/2"

DECORATIVE CONCRETE TOOLS

Deco **Hand Edger** Made of quality stainless steel. Fitted with smooth

comfortable wood handle.

Rivet free for smooth clean edges.

No. Size **Radius** Lip CF659 2-1/2" 6"x6"

Deco Hand Groover

Made of quality stainless steel. Fitted with smooth comfortable wood handle. Rivet free for smooth clean grooves.

Radius **Bit Depth** No. Size CF660 6"x6' 1-1/2" 1-3/4



Made of quality stainless steel. Fitted with 360° all-angle bracket. Rivet free for smooth clean grooves.

Comes with 5' wood clevis handle (CC376)

No. Size Radius **Bit Depth** CC375 6"x12" 1-1/2" 1-3/4'

Adjustable Winged Groover

- Professional quality tool designed to fit exact contours of edges
- · Wings adjust up to fit contour of job
- Made of high quality stainless steel
- Use with clevis handle (CC386) or adapter for bull float handles (pages 16-17) Handles and adapters ordered separately

Depth Radius Size Width No. CC734 20"x9" 1-1/4" 1/2'



Broadcast Gun

Easily broadcasts decorative vinyl color chips and fine materials. Use gun with compressor at approximately 15 P.S.I. Vinyl chips are distributed evenly on epoxy floor projects. Adjust compressor for desired spraying distance and vinyl chip density on floor. No. PC801



Decorative Concrete Border Tools

Made of high quality stainless steel and rivet free for clean grooves and edge. Fitted with smooth comfortable wood handle.

5/8"

A) Single Edger with Double Groover

No. Spacing Shiner Radius Bit CF652 3/4" 5/8" 1/2" 9" 3" 5/8" CF653

1/2"

B) Double Edger with Groover No. Spacing Radius Bit


C) Double Edger

CF654

Radius No. Size CF655 9"x6" 1/2" CF657 9"x6 3/4"

D) Single Edger with Groover

Spacing Shiner Radius Bit No. CF656 5/8"




Plastic Step Tools

Special design for pools will not darken white coat. Heavy nose tool Plexiglas.

A) Outside Nose Tool

No.	Size	Lip	Radius
PL652	6"x5"	2-1/2"	3/4"
PL653	6"x5"	2-1/2"	1/2"
PL654	6"x5"	2-1/2"	1-1/2"
B) Inside (Cove Tool		
D) IIISIAC (_
No.	Size	Lip	Radius
		Lip 5"	Radius 3/4"
No.	Size	•	
No. PL655	Size 6"x5"	5"	3/4"



KRAFT




Single Dome Hand Tool

Touch up tool for truncated domes on CC144 (Style)
No. CC144A



A.D.A. Texture Mat

This safety orange texture mat meets all of the American Disability Act specifications for handicap curbing and walks. Mat forms



CHECK WITH LOCAL, STATE OR FEDERAL GUIDELINES FOR CORRECT SPECIFICATIONS.

No. Description

CC144-300 (Color Yellow) Specifications 2.35" diagonally Domes 1.63" (center to center) horizontal and vertical pattern

CC144-400 (Color Orange- not shown) Domes 2.35" (center to

center) on diagonal pattern

Utility Stamps

Stamp concrete with locations of water and sewer lines. 3" letters made of long-wearing cast aluminum.

No. Description
CF405 Water Utility Stamp
CF403 Sewer Utility Stamp





Salt Roller

30" long decorative salt roller. Make small decorative impressions in concrete using rock salt. Use with 1-3/8" diameter snap button handles. **No.** CC957

Concrete Sealer

Solvent-based sealer to protect and enhance concrete surfaces. Apply with sprayer. 5 Gallons.

No. Finish
RR176** High Gloss
RR178** Satin

**Must ship via truck



Liquid Release Easy to apply with sprayer. Forms lubricating barrier between concrete and

on colored or uncolored concrete. Alternative to powdered release agents. Ships via truck only. 5 Gallons. **No.** RR175**

**Must ship via truck

mats. Use



Curing Compound Sprayer

Chemical resistant. Epoxy-coated galvanized steel. Teflon® coated with VITON® seals. Heavy-duty control valve with long wand on solvent resistant Goodyear® hose. 3.5 Gallon capacity.

No. RR164

Color Release Agents & Color Hardener *For Kraft Texture Mats*

Dry Powder Release Agent is recommended for use with texture mats. The release agents keep material from sticking to mat. The rate of coverage will vary depending upon the depth of the texture mat impressions desired and the degree to which the concrete has set.

• 3.5 lbs. per 100 sq. ft. or more may be required.

Covers approximately 800 - 1,000 Sq. Ft. Available in five (5) gallon containers. (shipping weight 30 lbs.)

Color Hardener is used for coloring flatwork and is often used with antique release agents in the texturing of concrete. Wood float color hardener into the material before troweling.

• 60 lb. pail covers approximately 100 square feet.

CAUTION: Always use safety goggles and dust mask, when using color release agents and color hardener.

Color Release & Hardener

Release	Release Hardener Description				
No.	No.	Description			
RA100	CH100	Dark Gray			
RA200	CH200	Medium Gray			
RA300	CH300	Nutmeg Tan			
RA310	CH310	Cream Beige			
RA320	CH320	Golden Sandstone			
RA325	CH325	Sandstone			
RA350	CH350	Desert Tan			
RA375	CH375	Buff Tan			
RA400	CH400	Buff Tan Chestnut Brown			
RA425	CH425	Autumn Brown Tile Red			
RA500	CH500	Tile Red			
RA525	CH525	Dusty Rose			
RA550	CH550	Brick Red			
RA575	CH575	Victorian Red			
RA600	CH600	Light Gray			
RA625	CH625	Dover Blue			
RA700	CH700	Terra-cotta			
RA735	CH735	Cappuccino			
RA810	CH810	Walnut			
RA825	CH825	Slate Green			
RA900	CH900	Jet Black			
RA1080	CH1080	Adobe Buff			
RA1090	CH1090	Sun Buff			


Note: Colors shown above approximate the appearance of Color Hardener and Release Agent. Variations are to be expected due to jobsite conditions and finishing techniques. Prices vary with product and color. Contact your distributor for more information. Additional color charts available upon request.

DECORATIVE TEXTURE MATS

Decorative texture mats create a three dimensional impression on the concrete with all details of the shape, texture and feel of natural stone or brick. An excellent alternative to brick or tile for patios, driveways, walkways, poolside decking and many other applications. Mats are made of 3/4" thick polyurethane.




















EZY Deck Pro Gun & Hopper

Built-in downward hopper angle is *ideal for decorative overlays and decorative concrete applications*. Control hopper with built in finger tip handle and flexible neck. Full grip trigger for ease and comfort. Remove nozzle and tip for quick and easy cleaning.

Gun and Hopper (Only) No. PC401

Complete Unit

Includes EZY Deck Pro Gun and Hopper and compressor. No. PC400

Red, Yellow and Blue Mats: Some texture mats are offered in Red, Yellow or Blue. These mats are the same texture but have different configurations to avoid seeing repeat patterns. Recommend alternating Red, Yellow and Blue mats when available.

Floppy Texture Mats: All of the texture mats above are available in Floppy Texture Mats. Half the weight and half the thickness of regular texture mats. Very flexible, great for touch-ups, detail work and hard-to-reach areas such as walls and stairs. ADD "F" to Texture Mat part numbers for floppy mat.

See page 51 for 23 different shades of Color Hardeners and Release Agents available, plus Concrete Sealer and Liquid Release.

Texture Mats How-To Instructional DVD **No.** CC119DVD

Double End Deco "V" Jointer Double End Deco "V" Jointer is made of

Double End Deco "V" Jointer is made of high quality aluminum. Use in conjunction with texture mats for touch up or cutting of small grooves. Groover designed to cut 5/8" or 3/4" joints. A must tool for every finisher.

No. Size Description

CC112 12" "V" Jointer (5/8" x 3/4")

Hand Groover

Made of high grade aluminum.
Hand groover is designed to
cut straight control joints 1-3/4"
deep. Use in conjunction with walking
groovers. Fitted with comfortable wood float
handle. Groover length 12", width 2".

No. Size Bit Width Bit Depth CC012 12" 1/4" 1-3/4"



Kraft Texture Skins Super Flexible

Kraft Texture Skins are used by overlapping and gives the concrete a stone or slate texture. Skins can also be used for touchups and in conjunction with other texture mats.

No.	Description	Approx. Size
A) CC001	Stone Texture	24" x 36"
B) CC002	Slate Texture	24" x 36"



Kraft Rough Stone Texture Skins

Super Flexible

Texture Skins are used by overlapping and gives the concrete a rough stone texture. Skins can also be used for touch-ups etc. Back side of texture skin fitted with two handles. Feathered edges.

No. Approx. Size CC007 36" x 36" CC008 56" x 56"




Straight Arrow Groover for Control Joints

Ideal tool for cutting long straight control joints

High grade aluminum walking groover is designed to cut long straight 1-3/4" deep control joints. Special red groove cut in the top of groover along with sight marker, helps in cutting perfectly long straight control joints. Serrated bit groover helps in moving aggregate in the groove more easily. Use with wood clevis handle (CC386) or adapter for bull float handles (pages 16-17). Handles and adapters must be ordered separately.

A) Straight Bit				B) Serrated Bit			
No.	Size	Bit Width	Bit Depth	No.	Size	Bit Width	Bit Depth
CC003	36"	1/4"	1-3/4"	CC003S	36"	1/4"	1-3/4"
CC004	48"	1/4"	1-3/4"	CC004S	48"	1/4"	1-3/4"
CC005	60"	1/4"	1-3/4"	CC005S	60"	1/4"	1-3/4"



Joint Touch-Up Rollers

Super Flexible

Joint roller used for touching up joints when using texture mats. Match texture and width of existing joints.

or oxioting jointo.				
No.	Face Size	Face Typ		
CC565*	1/4"	Round		
CC567*	3/8"	Flat		
CC568*	3/8"	Sanded		
CC566*	3/16"	Flat		
CC569*	1/2"	Wedge		
CC570*	1/2"	Flat		
CC571*	1/2"	Sanded		



Concrete Tools

www.KraftTool.com

Concrete Roller Tamps

- 5" roller diameter
- Depresses the aggregate and brings the fat to the surface in a uniform manner
- Levels the slab in half the time and does a better job then other conventional tampers
- Prepares the surface for a smoother finish
- Rollers fit either threaded or button extension handles (sold separately - see pages 16-17)





Special Roller Tamp Screen



Double Roller Tamps - 2 rollers per tamp head

Uses 1-3/4" Threaded End Handles				
No.	Size	1010		
CC948	18"			
CC952	36"			
CC958	/8 "			

Uses 1-3/8" Button End Handles				
No.	Size	11/4		
CC948A	18"			
CC952A	36"	114		
CC958A	48"	4		
0000=/:	• •			

Uses 1-3/4	" Button End	d Handles
No.	Size	
CC948B	18"	
CC952B	36"	
CC958B	48"	1

Replacement Roller with Shaft Size No. CC949 18" CC954 36" CC959 48"

Single Roller Tamps - 1 roller per tamp head NEW

Uses 1-3/4" Thread	ed End Handles
No.	Size
CC952SINGLE	36"

Uses 1-3/8" Button End Handles CC952ASINGLE 36"

Uses 1-3/4" Button End Handles CC952BSINGLE 36"

Extension Handles See Pages 16-17

Concrete Tampers





Round Hole Grill Pattern

No.	Size	
CC887	36"x8"	Unassembled
CC887ASM**	36"x8"	Assembled
CC885	48"x8"	Unassembled
CC885ASM**	48"x8"	Assembled

Big Diamond Grill Pattern

Many concrete finishers prefer this style because it diverts the concrete splash away from the legs of the finisher.

No. Size CC879 36"x8" Unassembled CC879ASM** 36"x8" Assembled 48"x8" Unassembled CC881 CC881ASM** 48"x8" Assembled

**Must ship via truck

Replacement Handle No. CC883

Economy Concrete Tamper NEW

Available unassembled only.				
No.	Size	Grill Pattern		
CC887E*	36"x8"	Round Hole		
CC885E*	48"x8"	Round Hole		
CC879E*	36"x8"	Diamond		
CC881E*	48"x8"	Diamond		

Safety RollerDiamond Patterned Safety Roller gives a rough, skid resistant finish to concrete ramps. Perfect for wheelchair or loading walkways where a non-skid surface is a must. Roller is 5" in diameter. Roller is made of tough expanded steel diamond mesh. Handle bracket accepts threaded 1-3/4" threaded bull float extension handles.



8" Roller Tamp

Prepares the slab the same way as other roller tamps. Works great in small areas, steps, or close to buildings and walls. Special handle angle keeps the finisher from scraping against buildings, forms or walls. Use with 1-3/8" swaged button handle (CC336) or can be used with adapter (CC675) for 1-3/4" diameter handle.

Description No. CC946

8"x5" Diameter Roller with 1-3/8" Button Handle Adapter





of texture mats. Heavy-duty cast iron tampers fitted with 48" hardwood handle. A) Cast Iron/Poly-Coated Base Texture Mat Tamper with Heavy-Duty Handle

Special rubber coated base prevents tearing or marring of texture mats

No. Description

CC928 11"x11" Heavy-Duty / 22 lbs. CC928-01 Heavy-Duty Repl. Handle


B) Cast Iron Base Dirt Tamper with Heavy-Duty Handle

Description No. CC929 10"x10" Heavy-Duty / 21 lbs. CC928-01 Heavy-Duty Repl. Handle

C) Cast Iron Base Dirt Tamper

Excellent way to tamp dirt surfaces. Cast iron tamper fitted with a 44" hardwood handle.

No. Description CC925 8"x8" / 11 lbs. CC926 10"x10" / 14 lbs. Replacment Handle CC927







Complete kit with all the items required to mix and install self-leveling products. Includes mixing barrel, measuring pitcher, oval mixer, spiked shoes, gauge rake head, wood-framed stainless steel smoother and 5' 3-piece aluminum handle to fit gauge rake and smoother.



Oval Mixer



Wood Frame Stainless Steel Smoother

24" stainless steel blade in laminated wood mounting. Aluminum handle bracket accepts threaded handles (sold separately, see page 33). Used to apply and smooth coatings, especially self-leveling material. Can be used by hand or with standard broom threaded handle.

No. Description

A) GG603 24" Smoother with Bracket B) GG604 24" Smoother with Bracket

and Built-in Handle

Squeegee TrowelWith Soft Grip Handle for Comfort

G) DC717*

A contractor's favorite, used to smooth a variety of coatings in construction, drywall and concrete restoration. Can be used by hand or with threaded broom style handle (sold separately, see page 33).


Squeegee Tool Handle US Patent #D614,471S

No.	Description
GG242	12"
GG243	14"
GG244	18"
GG246	22"
GG247	26"
GG244-01	Replacement Handle

Squeegees and Aluminum Frame

Sturdy, lightweight 24" wide aluminum squeegee frame used with a 24" wide, 2" high, EPDM squeegee blade, available in straight, V-notched or U-notched. Used to ensure consistent depth when spreading thin materials. Can be used with threaded broom style handle. Shown with 3-piece aluminum handle (CC263). All items sold separately.

No. GG235-01	Description 24" Aluminum Frame ONLY (Order blades separately)
GG235-04	24" wide Straight Blade Squeegee Replacement Blade
GG235-02	24" wide 1/8" V-notched Squeegee Replacement Blade
GG235-03	24" wide 1/4" V-notched Squeegee Replacement Blade
GG235-05	24" wide 1/4" U-notched Squeegee Replacement Blade
CC263	3-piece Aluminum Handle






CONCRETE RESTORATION

Spiked Rollers

Roll out air bubbles in epoxy coatings and self-leveling material with two styles of spikes rollers



Super Spike Roller

Each spike measures 1/2" long. Super sharp

spikes.		
No.	Size	Description
GG476	9"	Roller with Frame
GG478	18"	Roller with Frame
GG477	9"	Super Spike Roller Only
GG479	18"	Super Spike Roller Only
DW179M*	9"	Roller Frame
DW178	18"	Roller Frame




Standard Spike Roller

Each spike measures 1-1/4" long				
No.	Size	Description		
GG609	9"	Roller with Frame		
GG618	18"	Roller with Frame		
GG610	9"	Standard Spike Roller Only		
GG619	18"	Standard Spike Roller Only		
DW179M*	9"	Roller Frame		
DW178	18"	Roller Frame		



Nap Roller Covers
Shed resistant. Used for applying adhesives and coatings,



18" Roller Frame

With Threaded Handle Adapter

18" aluminum frame securely holds standard 18" paint roller and adhesive rollers for rolling larger areas. Full, two-sided frame applies even pressure across length of roller. Handle accepts standard broom threaded handle for extended reach.

No. DW178 9" Roller Frame 9" roller frame with soft style handle,

No. DW189

Roller End Caps

Prevent material from building up inside rollers. Comes in a pack of 6 caps.

No. DW178-02

Double Notch Rake

Hardened steel blade with V-Notch for spreading floor coatings. Notched on 2 sides of rake. Comes with three-piece 60" threaded handle (CC263).

18" Double Notch Rake

No.	V-Notc	h Size
GG591	3/16"	NEW
GG605	1/4"	
GG592	3/8"	NEW
GG593	1/2"	NEW

24" Double Notch Rake No. V-Notch Size

NEW GG594 3/16" GG606 1/4" GG595 3/8" NEW **GG596** 1/2' Add "01" after part no. for rake without handle threaded end for broom threaded handle. Order roller covers separately. No. DW179*



Gauge Rake

Made of lightweight aluminum. Adjusts up to 2" for uniform coating of surface. Comes with 3-piece snap style aluminum threaded handle (CC263).

Description No.

24" Rake with Handle CC975 CC975-01 24" Rake without Handle CC976 36" Rake with Handle 36" Rake without Handle CC976-01 CC975-04 Replacement Sleds & Hardware



Flexible Gunite Shoes

Gray flexible plastic lets you work on gunite, epoxy or sealers with ease of movement. Protect your work and bring air bubbles out of the application. (13) firmly attached 3/4" (overall length) steel spikes cover the bottom of the shoe. Two adjustable nylon straps securely hold gunite shoe to work boot.

Description No.

HC177* Flexible Gunite Shoes (Pair) HC177-01* 3/4" Replacement Spikes (26) HC178-02* Replacement Straps (Set)





Gunite Shoes With Spikes Adjustable



aluminum shoes. One size fits all. Fitted with (12) 1" steel spikes. Adjustable sole plate and heel support. Two nylon adjustable straps securely hold gunite shoe to work boot.

No. CC970 (Pair)

Gunite Shoes Used for

epoxy and gunite installation. One size fits



all. Fitted with (13) 1-1/2" (overall length) steel spikes. Two nylon adjustable straps securely hold gunite shoe to work boot.

Description No. HC178* Gunite Shoes (Pair) HC178-01* 1-1/2" Replacement Spikes HC178-02* Replacement Straps

Oval Mixer

High viscosity mixer. Oval shape effectively removes air from mixtures. For use in a 1/2" drill. 26" Shaft.

No. DC717*

Unomixer

Ideal for fast mixing of all kinds of materials, from paint to cement. For use in a 1/2" drill chuck. 16" shaft, 3-3/4" diameter.

No. DC363*

Triangle Blade Mixer

Multi-purpose triangle blade mixer. Measures 24" long. Use with all concretebased products. For use in a 1/2" drill. No. DC721

Stainless Steel Jiffy Mud and Paint Mixers

Fits containers 3 gallons or larger. 21" long, 1/2" shaft, top diameter 4-1/2", bottom diameter 5", depth 5". For use in a 1/2" drill. No. DC409



For small containers, 2 gallons or less. 10-1/2" long, 1/4" shaft, top diameter 2-3/8", bottom diameter 2-5/8", head depth 2-1/2". For use in a 3/8" drill.

No. DC408

Junior Mud Mixer

Mud mixer has a cast aluminum paddle 8-1/2"x5" deep. 7/16" steel shaft works in slow speed 1/2" drill. Rounded end design for better balance when mixing. Ideal for mixing drywall mud and texture materials.

No. Size

DC713 7/16" diam. x 30" shaft DC714 7/16" diam. x 36" shaft

7/16" diam. x 46" shaft **NEW** DC714L

Epoxy Mixing Paddle

Flat steel blade with slots so material flows through and around mixer. Ideal for mixing epoxies, mortars, resins and other construction materials. Plated to resist wear and corrosion. Fits most 1/2" drill motors. 7/16" hex shaft. Overall length 18".

No. DC719

Double Bent Mixer

Bent mixing blades provide a bottom-to-top mixing action. Mix urethane and other materials smoothly. Plated to reduce wear and corrosion. Fits most 1/2" drill motors. 18" hex shaft. 4"x3" blades.

No. DC720



Hex Shaft

Hex Shaft

Tip

Plastic Bucket and Pail

Durable 90 mil 5 gal. translucent bucket and 10 qt. pail for general uses such as mixing or moving various materials. Lid for 5 gallon bucket sold separately.

5 Gal. Plastic Bucket

Liters, Quarts, Gallons measurements

No. Description

GG468 5 Gal. Plastic Bucket

GG468-01 Plastic Lid

(For GG468 5 Gal. Bucket)


GG468-02 Plastic Lid w/ Spout

(For GG468 5 Gal. Bucket)

10 Qt. Plastic Pail

Ounces, Liters, Quarts measurements

No. Description
GG470 Description
10 Qt. Plastic Pail



28" Countertop Darby

Smooth and level concrete countertops with this lightweight magnesium countertop darby. The base of the tool is rounded for floating and square edge for cutting or finishing. Knob and rib handle give perfect control.

No. Size

CC898 28"x1-3/8"x2"



40" Buckaroo™ Straightedge


Ideal tool for finishing concrete island countertops. Made of lightweight magnesium with a smooth wooden handle. Includes top reading adjustable level vial and square edge for cutting or finishing.

for cutting or finishing.

No. Size

Perfect size for countertops

CC897



Square

Round

Dual Cartridge Epoxy Gun

Easy to pull and release trigger for dispensing two component materials through static mixers. Dispensing rods are hardened for long wear and strength. Match material ratio to the size of gun listed.

No. Size

GG469* 300 mLx300 mL GG467* 300 mLx150 mL

MAY TOOL CO. MITTER BILL

Pool Finish Brush

Soft Nylex® brush for finishing concrete and specialty materials and exposing aggregate in pool finishes.



Blue Steel Smoother

Smoother's 24" blue steel flexible blade with aluminum mounting spreads material evenly. Use to smooth overlays, epoxies and coating materials when you need a thin consistent finish. Includes a 5' wood handle (CC163), and can be used with other extension handles.



Orange Latex Gloves

Sturdy latex gloves are resistant to most caustic chemicals, paints and sealers. Provides protection for hands from liquids and other materials.

 No.
 Size
 Length

 GG426-L*
 Large
 12"

 GG426-XL*
 X-Large
 12"



Professional Work Gloves

Lightweight yet durable professional work gloves. Comfortable neoprene cuff with Velcro® closure for a secure fit. Breathable spandex back provides ultimate comfort and fit.



Denver Sliders

Made with top quality #16 gauge stainless steel for an extra smooth sliding surface. Round edges and corners with special nesting design. Built-in toe brackets for easy back-and-forth motion. Weight 11 lbs.

No. Size

CC152 28"x8-1/2" (Pair)



Concrete Sliders (Knee Boards)

Made of lightweight, tough heavy-duty polystyrene plastic. Easy to use, easy to clean. One size fits all. Knee pads are replaceable.

No. Description CC153 30"x10" (Pair)

WL080 Replacement Pads (Pair)



Lightweight Stainless Steel Knee Boards

Knee boards are made of #18 gauge stainless steel. They are durable and easy to use. Knee pads are replaceable.

No. Size

CC162 28"x8" (Pair)

WL080 Replacement Pads (Pair) WL082 Replacement Straps (Pair)

#18 Gauge

Deluxe Heavy-Duty Stainless Steel Knee Boards

Made with #16 gauge polished stainless steel to reduce corrosive problems. Reinforced and contoured on the bottom to prevent digging into the concrete. Adjustable knee pads are replaceable and allow a "comfort fit."

No. Size

CC150 31"x8" (Pair) CC151 28"x8" (Pair)

WL080 Replacement Pads (Pair) WL082 Replacement Straps (Pair)



EZ-Kneeler™ Kneeboard

Comfortable Multi-Purpose Kneeboard

- Washable and chemical resistant
- Weighs only 2 lbs.
- 1-1/2" thick foam cushion

Provides the knees comfortable support and protection - *no more sore knees!* A 1-1/2" thick foam cushion (working surface measures 19-1/4"x13-1/2") securely fastened to 14"x24" polypropylene tray for maximum comfort and long life. It is a favorite of concrete finishers and tile installers.

Made in the USA.

No. WL069 (10) Per carton



Foam Rubber Knee Pads

Professional foam rubber hard shell knee pads. Contoured cap provides extra support and comfort for heavy use. Velcro® closures are easy to use and adjust.

No. WL135 (Pair)

Non-Skid Knee Pads

(not shown)

Same as above. Rubber cap prevents sliding and marring of surfaces.

No. WL136 (Pair)



Rubber Cushion Knee Pads A rubber cushion knee pad

on the inside with a solid rubber surface for rugged long wear. Adjustable web straps with Velcro® closures are embedded within the pad. (Judsen Knee Pads) No. WL070 (Pair)



Leather Knee Pads

Tough leather makes for long wear. Lined with felt and shaped to fit your knee. Rivet construction holds soft felt in place. One adjustable strap holds pad securely in place.

No. Description WI 087 1/2" Thick Felt (Pair) 1" Thick Double Felt (Pair) WL088

Flat Leather Knee Pads

Hard but pliable, comfortable leather knee pads, lined with soft felt that bends with the knee. One adjustable strap holds pad in place while you

No. WL071 (Pair)



Knee Pad

Super Soft / Front Closure

- Protect knees with soft neoprene pad
- Unique, easy to use front Velcro® strap
- Wide binding straps will not gouge
- Coated with non-marring polyurethane for added protection and durability

No. WL139* (Pair)



Hinge Style Knee Pads

- Hinge style
- Extra cushion back with hard shell cap
- Wide nylon Velcro® straps for extra comfort No. WL137 (Pair)



Polyurethane Knee Pads • Made of shock-absorbing and durable

- polyurethane
- One strap holds the pad in place
- Pads are molded in one piece
- Very popular with the concrete finishers No. WL083 (Pair)



Ultra Rubber Knee Pad

- Durable rubber with comfortable foam pad insert
- Adjustable replaceable straps
- Accordion style cap

Description No. WL084* Knee Pads (Pair) WL084-01 Replacement Straps



Economy Soft Cap Knee Pad

- Long, contoured flexible cap provides a protective base
- Foam rubber cushion offers a soft protection for knees
- Velcro® closures are easy to adjust



Polyurethane Knee Pads

- Made of durable lightweight polyurethane
- Used for all types of construction projects
- Two web straps hold pads to knees
- Pads are molded in one piece

Description No. WL080 Knee Pads (Pair) WL082 Replacement Straps (Pair)

Order in cartons of (12) each.




HI-CRAFT CONCRETE TOOLS

Concrete Trowels

Carbon steel blade ground for smooth finishing. Strong aluminum mounting fitted with camel back wood handle or soft grip handle.

Wood	Soft Grip	
No.	No.	Size
HC145*	HC145PF*	11"x4-1/2"
HC146*	HC146PF*	14"x4"
HC144*	HC144PF*	16"x4"
HC142*	HC142PF*	18"x4"

Order in cartons of (6) each.



Economy Concrete Trowel

9"x4" steel blade mounted to contoured plastic handle. No. Size



Cali Mahogany Wood Float Made of Asian Mahogany. Float is 3-1/2" wide and

1/2" thick. Fitted with a smooth wood handle.

No.	Size
HC160	12"x3-1/2"
HC161	14"x3-1/2"
HC162	16"x3-1/2"
HC164	18"x3-1/2"
HC165	20"x3-1/2"



Pointed Sword Trowels

High carbon steel blade. Trowels are used in tight corners and spaces. Soft handle and strong mounting for comfort and strength.

No.	Size
HC120*	14"x4"
HC121*	14-1/4"x4-11/16"
HC122*	15-3/4"x4-1/2"
HC123*	17-3/4"x4-1/2"
HC126*	26"x4-11/16"





Fresno Trowels with Swivel Bracket

Round end fresno eliminates marking or gouging slabs. 360 degree all-angle bracket lets you work at any angle. Handle bracket accepts clevis wood handles (CC386) or button threaded handles with specific adapters (pages 16-17).

No. Size HC189* 24"x5" HC190* 36"x5" HC191* 48"x5"

Fresno Weight

No. HC755 5 lb. Using in pairs is recommended.

Universal Groover

Popular among concrete finishers from coast to coast. This

No.

groover lasts longer because

rivet-free. Has 6"x3" blade and cuts a clean Order in cartons groove.

Size Bit

HC148* 6"x3" 1/2" wide,1/2" deep - Wood Handle HC148PF* 6"x3" 1/2" wide,1/2" deep - Soft Grip Handle

Aluminum Concrete Edger



Order in cartons of (6) each.

A) Front end turned up and back end straight

Lip Depth Radius No. Size HC155 5-7/8"x2-7/8" 3/4" 3/8" B) Both ends turned up

No. Size Lip Depth Radius HC154 5-7/8"x2-5/8" 1/2" 3/8"

Aluminum Concrete Groover



Order in cartons of (6) each.

A) Front end turned up and back end straight

No. Size Width Depth Radius HC152 6"x2-3/4" 3/8" 3/8" 7/32" B) Both ends turned up

No. Size HC153 5-3/4"x2-1/2" 1/2"

Bit Width Depth Radius

13/64"

1/2 "

Concrete Edger



6"x3" edger has 1/4" radius. Ends are turned up so it will not gouge concrete. Fitted with either wood or soft grip handle.

Handle No. HC147* Wood HC147PF* Soft Grip

Order in cartons of (6) each.



Texture Gun and Hopper

The Hi-Craft™ texture gun and hopper is lightweight and easy to use. Made from molded high impact plastic. Sprays variety of drywall textures including stucco and decking material. Gun comes complete with 2 air nozzles, adjustable orifice plate for texture adjustment, locking trigger system for less fatigue and large 2 gallon hopper. Hopper has built in angle for maximum fill and operates on 6.25 C.F.M free air at 25 P.S.I. No. HC501

Econo Mag Float Float blade made of tough durable Extru-Lite Magnesium™ blade. The precise handle position creates perfect balance and superb floating action. Wood Handle

No. Size HC065 16"x3-1/8" Soft Grip Handle

Soft Grin Handle

"x1-1/2"

No. Size HC065PF 16"x3-1/8"





HI-CRAFT™ MASONRY TOOLS

Pointing and Margin Trowel

Blade is made of tempered steel, taper ground and fitted with wood

handle or soft grip handle.

WOOU Hallule		Soft Grip Harrule	
No.	Blade Size	No.	Blade Size
HC150*	Pointing 5"	HC150PF*	Pointing 5"
HC422*	Pointing 5-1/2"	HC422PF*	Pointing 5-1/2"
HC423*	Pointing 7"	HC423PF*	Pointing 7"
HC431*	Margin 5"x1-1/2"	HC431PF*	Margin 5"x1-1/2
HC151*	Margin 5"x2"	HC151PF*	Margin 5"x2"
HC433*	Margin 8"x2"	HC433PF*	Margin 8"x2"







Trowels are made of carbon steel and ground for flexibility. Fitted with wood handle.

No.	Blade Siz
HC762*	7"x1/4"
HC763*	7"x3/8"
HC764*	7"x1/2"
HC765*	7"x5/8"
HC766*	7"x3/4"
HC768*	7"x1"











Line Blocks with Twigs 2 pairs of hard plastic yellow line blocks

(3-1/2"x1") with 4 line twigs (4"x1/2"). Blocks grip brick wall and twigs keep line from sagging. Sold as set only. No. HC349*

Metal Pole Sander

Lightweight aluminum pole sander with 48" wood handle. Use with broom threaded handle.

No. Size

HC517* Pole Sander with

48" Wood Handle Pole Sander

HC517-01* (Head Only)

48" Wood HC517-02 Handle

Order in cartons of (6) each.

More Drywall Tools On Pages 114-124

HI-CRAFT DRYWALL TOOLS

Hand Sander Hard plastic fitted with a soft comfortable

textured handle for improved grip. Padded sanding face provides a more uniform surface for

sanding. Use with pre-cut drywall sandpaper or half of 8"x11" sheet.

No. HC341

Pole Sander Hard plastic sander makes for easier sanding of walls and ceilings. Padded sanding face provides a more uniform surface for sanding. Use with pre-cut drywall sandpaper or half of 8"x11" sheet. Swivel handle bracket accepts standard broom threaded handle.

(Handle not included.) Order in cartons of (6) each.

No. HC217

Stainless Steel Threaded Handle Scrapers

Stainless steel bent scrapers with single bevel. Molded, threaded end can be used with standard threaded handle. Soft handle for comfortable grip and less fatigue.



Hammer End Putty and Joint Knives

Joint knives designed for many applications, including drywall and putty. Carbon blades ground for flexibility with nylon handle.



5 in 1 **Combination Tool**



5 tools in 1; scraper, seam opener, spreader, putty remover and a cutout to remove paint from rollers.

No. HC524*

Order in cartons of (5) each.

Vinyl Knife



Order in cartons of (5) each.

Diamond-Shaped Joint Knife



Work in corners and around doors and windows without changing the position of the tool. 3-1/4" polished steel work surface. Hammer end. No. HC522*

Order in cartons of (5) each.

MI HAW

Clipped Angle Joint Knife



Angle gives the proper amount of pressure in hard-to-reach places and awkward corners and angles. 6" polished steel work surface. Hammer end. No. HC523*

Order in cartons of (5) each.



Hi-Craft™ Texture Float

Special green formula foam plastic. Does an excellent job on any sand surface. Comes with comfortable plastic handle

Coarse Texture

No.	Size
HC132	10"x4"x3/4"
HC134	12"x4"x3/4"
HC136	12"x5"x1"
HC138	12"x5"x3/4"

Fine Texture

No.	Size
HC132F	10"x4"x3/4"
HC134F	12"x4"x3/4"
HC136F	12"x5"x1"
HC138F	12"x5"x3/4"





Lift 'n' Carry **Panel Mover**

One person can carry up to 150 lbs. of drywall, panel board, plywood, or wallboard with this lightweight molded plastic tool. Handle is angled away from hands. Rubber pads to prevent shifting. No. HC545*



www.KraftTool.com **Asphalt Tools**

LUTES & RAKES



Magnesium Asphalt Lute With T-Lute Bracket

Must ship via oversize rate or truck

Heavy-duty asphalt lute is available with standard teeth, flat teeth or no teeth. Made of genuine Extru-Lite™ Magnesium for longevity and strength. Used to ensure asphalt is applied evenly. Use smooth side for finishing.

Standard Tooth Lute

otanuaru	ICCIII LUIC		
No.	Teeth Style	Head Size	Handle Length
GG824-6	Standard	24"	6'
GG824	Standard	24"	7'
GG824-9	Standard	24"	9'
GG830-6	Standard	30"	6'
GG830	Standard	30"	7'
GG830-9	Standard	30"	9'
GG836-6	Standard	36"	6'
GG836	Standard	36"	7'
GG836-9	Standard	36"	9'
GG842-6	Standard	42"	6'
GG842	Standard	42"	7'
GG842-9	Standard	42"	9'

Flat Teeth I ute

I Ial IGGIII LUIG			
No.	Teeth Style	Head Size	Handle Length
GG824F-6	Flat	24"	6'
GG824F	Flat	24"	7'
GG824F-9	Flat	24"	9'
GG830F-6	Flat	30"	6'
GG830F	Flat	30"	7'
GG830F-9	Flat	30"	9'
GG836F-6	Flat	36"	6'
GG836F	Flat	36"	7'
GG836F-9	Flat	36"	9'
GG842F-6	Flat	42"	6'
GG842F	Flat	42"	7'
GG842F-9	Flat	42"	9'

No Teeth Lute

no noom Eato			
No.	Teeth Style	Head Size	Handle Length
GG830N	No Teeth	30"	7'
GG836N	No Teeth	36"	7'



Magnesium Asphalt Placer Lute With Round to Square Wood Handle

A must-have in this industry. Heavy-duty blade is made from 100% genuine Extru-Lite™ Magnesium. The round to square 66" wood handle not only adds comfort but gives the end user a great grip.

Description No. GG875 Asphalt Placer Lute GG875-01 Replacement Blade GG875-02 Replacement Bracket GG875-03 66" Replacement Handle

Right Angle Blade



Landscape and Asphalt RakeThe 36" aluminum head is made for rugged use on asphalt. The 2-1/2" teeth have ball tips to insure longer life. Comes with 7' magnesium handle that is attached with a lightweight bracket (GĞ824-03).

Size No. CC960 36"

GG824-02 7' Replacement Handle



Magnesium Asphalt Rake

Lightweight magnesium head. Standard teeth on one side and smooth edge on the other. Comes with 7' blue anodized aluminum handle which prevents hands from turning black caused by oxidation. Fitted with braces for extra support.

No. Size 24" Rake Head GG624 30" Rake Head GG625 36" Rake Head GG626 GG627 42" Rake Head GG626-03 7' Blue Aluminum Handle



Asphalt Crack Hoe

V-shaped 2"x4" steel head. Cleans cracks before sealing. Comes with 5' handle attached to head.

No. GG812



Reversible head allows a push or pull action to funnel material into cracks. Choose between V or U-shaped black Neoprene blade that withstands temperatures up to 220°F. V-shaped red silicone blade withstands temperatures up to 450°F. Each includes a 54" heavy-duty wood handle. Blades are reversible.

A) V-Shaped Black Neoprene **Description** No.

GG813 V-Shaped black Neoprene blade w/ 54" Clevis Handle

GG813-01 V-shape head and

black Neoprene blade ONLY

GG813-02 V-shape black Neoprene repl.

blade

CC656 54" Handle ONLY

B) V-Shaped Red Silicone

GG814 V-shape Reversible red Silicone blade w/ 54" Handle GG814-01

V-shape Reversible Head

and red Silicone blade ONLY

GG814-02 V-shape red Silicone repl. blade GG814-03 54" Handle without pin ONLY

C) U-Shaped Black Neoprene

GG815 U-shape black Neoprene blade w/ 54" handle

GG815-01 U-shape Reversible Head and

black Neoprene blade ONLY U-shape black Neoprene repl.

GG815-02 blade

GG814-03 54" Handle without Pin ONLY

Asphalt Trowel

Use the right angle edge to scoop and apply filler material into cracks. Steel blade tamps down the material and edge helps smooth out edges.



Asphalt Seal Coating Squeegees

Rounded end blade allows a thin layer of material to be placed on the surface. Square end blade cleans working surface and can apply sealant. Both styles feature a Neoprene blade that withstands temperatures up to 220°F and is clamped to aluminum head for an easy change or reversal of blade. Blade angle designed for easy working angle and quick break-in

Asphalt Seal Coating Squeegee With Rounded End Blade

Size No. 24" Round Edge Asphalt Sealcoat Squeegee (7' Handle) GG844RE GG844RE-6 24" Round Edge Asphalt Sealcoat Squeegee (6' Handle) GG844RE-01 24" Round Edge Rubber Refill Blade (Neoprene 60 G) GG845RE 36" Round Edge Asphalt Sealcoat Squeegee (7' Handle) 36" Round Edge Asphalt Sealcoat Squeegee (6' Handle) GG845RE-6 GG845RE-01 36" Round Edge Rubber Refill Blade (Neoprene 60 G) GG846RE 48" Round Edge Asphalt Sealcoat Squeegee (7' Handle) 48" Round Edge Asphalt Sealcoat Squeegee (6' Handle) GG846RE-6 GG846RE-01 48" Round Edge Rubber Refill Blade (Neoprene 60 G)

Asphalt Seal Coating Squeegee with Square End Blade

No.	Size
GG844	24" Asphalt Seal Coating Squeegee (7' Handle)
GG844-01	24" Rubber Refill Blade (Neoprene 60 G)
GG845	36" Asphalt Seal Coating Squeegee (7' Handle)
GG845-01	36" Rubber Refill Blade (Neoprene 60 G)
GG846	48" Asphalt Seal Coating Squeegee (7' Handle)
GG846-01	48" Rubber Refill Blade (Neoprene 60 G)





Squeegee Coater Brush

18" hardwood block includes squeegee, brush and handle hole. Two rows of 2" palmyra bristles permits even distribution of coatings and asphalt sealers. Squeegee creates a smooth professional finish. Comes with 60" metal threaded wood handle (CC163).





Line Box

No. GG876

Heavy-duty 150' chalk line. Holds 1-1/2 lbs of chalk. Moisture-resistant easy refill lid. Great for paving contractors and highway departments.

No. Description Ammo Chalk Line Box GG302 GG302-01 150' Replacement Line

SQUEEGEES

Permanent Head Crack Squeegees



V-shaped head is welded into a fixed position for your choice of either pull or push action. V-shape funnels hot or cold crack filler. Red silicone blade withstands temperatures up to 450°F. Attached to a 54" heavy-duty wood handle (GG814-03).

No. Description

Push Style V-Shaped Squeegee **GG816** Pull Style V-Shaped Squeegee **GG817**

ASPHALT TOOLS


ilverback

PROFESSIONAL SERIES

Construction • Landscaping • General Construction

Aluminum Scoop

Multipurpose aluminum scoop that is lightweight and rust proof. Double riveted hardwood handle with "D" grip. Size #12. No. GG869



Steel Asphalt Rake

Heavy-duty construction, designed for tough use in asphalt paving. 12" long shank provides extra reach to burn asphalt build up. Sturdy wood handle is 66" long. Entire length of tool is 78".

No. GG870

46" Junior Mud Mixer

Mud mixer has a cast aluminum paddle 8-1/2"x5" deep. 7/16" steel hex shaft works in slow speed 1/2" drill. Rounded end design for better balance when mixing. Extra long shaft for mixing in large containers.

No. Size

DC714I 7/16" diameter x 46" shaft



All Steel Tamper

One piece heavy-duty steel pipe construction with welded gussets for increased strength. Designed for professional rugged use. Base is used to flatten asphalt and other materials. 48" handle with rubber grip for comfort.

Size No. CC921 8"x8"

CC939 10"x10" NEW

Heavy-Duty Broom

Designed for heavy sweeping. Heavy-duty crimped orange poly bristles. Bristles hold up under the toughest of conditions. Comes with 54" tapered end wood handle (BL432).

No. Size

CC264 16" Broom 18" Broom CC195

24" Broom CC197 CC195-02 **Broom Bracket**

1-1/8" diam. 72" Tapered Handle CC107L

for Head Only

Add (01) to Part No.

GG877-01 BL432 CC107L

Coated steel wire bristles make this broom a perfect asphalt clean up tool. Great for hard to get spots. Comes with 54" tapered end wood handle (BL432).


No. Description

16" Round Wire Street GG877 Broom with Handle **Head ONLY**

54" Tapered Handle

Wide Diam. 72" Tapered Handle





No. GG966*

Asphalt Bander

Repl. Wear GG966-01* Plate

GG966-02* Repl. Wheels (pair)



steel pour pot is an easy way to fill asphalt cracks with hot or cold crack filler. The convenient stand up design is available with or without wheels. There is an adjustable 3-size pouring nozzle with fingertip control top valve (squeeze to open, release to close).

No. GG961*

Pour Pot Pour Pot with GG961-01*

Wheel Kit

GG961-02* Wheel Kit ONLY



Edging Brush

Apply sealer along concrete curbs, around poles and other edged areas. Heavyduty 10" plastic block with polypropylene bristles. Use with threaded wood handle No. BL433









B) 31" "D" Wood Handle

C) 48" Fiberglass Handle

D) 31" "D" Wood Handle

E) 48" Fiberglass Handle

E) 48" Wood Handle

C) 48" Wood Handle

CAUTION: Call before you dig for safety.

No. GG863

GG860

GG861

GG861F

GG864

GG864F

Round Point Shovels

Sledge Hammers

Double faced sledge hammer available in two sizes. Choice of fiberglass or wood handles. Replaceable 32" wood handle with wedges available.

Fiberglass Handle

No. GG638F* NEW 8 lb. GG640F* 10 lb. **NEW**

Wood Handle

Size No. GG638* GG640* 10 lb. GG638-01* Replacement

> Wood Handle with Wedges



General Purpose Hammer

20 oz. curved claw general purpose hammer with smooth face. 11" wood handle. No. GG219



Framing Hammer

Fiberglass handle with a comfortable grip and your choice of a smooth or milled face on this must-have framing hammer.

Style No.

Smooth Face GG641' GG642* Milled Face



Pro Caulk Gun

Professional caulking gun features all steel

construction. Easy-to-load barrel swivels to quickly change the angles on corners. Ladder hook keeps the tools handy on the jobsite.

Description No. GG279* 10 oz.

GG277* 1 qt.



DIY Caulk Gun

Lightweight, easy-to-load gun with spout cutter and puncture tool. Accommodates standard 10 oz. caulk cartridge.

No. GG278*



Squeegee Coater Brush 18" hardwood block includes squeegee,

brush and handle hole. Two rows of 2" palmyra bristles permits even distribution of coatings and asphalt sealers. Squeegee creates a smooth professional finish. Comes with 60" threaded handle (CC163).

No. GG876



3 Knot Brush

Durable bristles resist acids - ideal for applying roof sealants. Rounded design provides better coverage around pipes and other obstructions. Use with threaded broom handle (not included)

No. BL501



Snow Puller

With Wheels

Great for moving snow from roofs and hardto-reach areas. Wheels will not damage shingles. Blade measures 24"x13-3/4". Use with 1-3/4" button extension handle (not included).



Broom Handles

Telescoping Fiberglass® Handles

These handles fit all brooms that take a broom thread. Swivel twist lock loosens and tightens handles when extended to desired length.

No.

CC446 A) Fiberglass® with Aluminum Extensions 6'3" to 12' B) Fiberglass® with Aluminum Extensions 6'6" to 18' CC429 CC448

C) All Fiberglass® 6'3" to 12'

Wood Handles

No.

D) 5' Metal Thread Wood Broom Handle CC163 E) 6' Metal Thread Wood Broom Handle CC163L

F) 72" Wide Diameter Tapered Wood Jam Handle CC107L 54" Tapered Wood Jam Handle 1-1/8" diam. (not shown) BL432


Steel Handle

60" heavy-duty coated steel handle with broom threaded tip.

G) GG232 No.

3-Piece Aluminum Handle

3-piece snap-style 60" aluminum handle with broom threaded tip. H) CC263











No.	Size
GG013	7" Scraper
GG013-01	7" Repl blade (for GG013 only)
GG014	14" Scraper
GG014-01	14" Repl blade (for GG014 only)
GG018	18" Scraper
GG018-01	18" Repl blade (for GG018 only)
GG022	22" Scraper
GG022-01	22" Repl blade (for GG022 only)
GG023	36" Scraper
GG023-01	36" Repl blade (for GG023 only)
GG024	48" Scraper
GG024-01	48" Repl blade (for GG024 only)
GG014-04	54" Repl Handle with Handle Clamp Bracket (for all Floor/Form Scrapers)

Squeegees

All Neoprene squeegee blades come with metal head and aluminum bracket, requiring a broom threaded handle (not included).

Straight Blade Squeegee

Blade, head and bracket only

No. Size NEW GG223-01 18" GG224-01 24" GG236-01 36"

Curved Blade Squeegee

Blade, head and bracket only

No. Size GG224C-01 24" GG236C-01 36"

Squeegee Replacement Blades

No. Size GG223-03 18" NEW GG224-03 24" GG236-03 36'

GG232 60" Threaded Coated Steel Handle **NEV**

CC163 60" Threaded Wood Handle CC163L 72" Threaded Wood Handle GG224-04* Replacement Handle Bracket



SCRAPERS & SQUEEGEES

Heavy-Duty Floor Scrapers Ideal for after work clean up. Scraper

blades are firm but flexible. Comes with heavy-duty 5' shovel-type wood handle.

No.	Size
CC214	Floor scraper w/14" Blade
CC218	Floor scraper w/18" Blade
CC222	Floor scraper w/22" Blade
CC207	14" Replacement Blade
CC208	18" Replacement Blade
CC209	22" Replacement Blade
XHDW04	Wood Replacement Handle

T-Handle Floor Scrapers

54" long all steel floor scraper. All steel "T" handle with weighted head for extra leverage. Shaves all kinds of floor coverings on any type of floor. Fitted with 7" replaceable steel blade, 10" replacement blade also available.

Size No.

GG393 Floor scraper w/7" Blade GG394 7" Replacement Blade 10" Replacement Blade GG395

Right Angle Scrapers

18" scraper with 60" aluminum cushion grip handle. Right angle bracket gives extra strength. Heavy gauge, replaceable steel blade. Perfect clean up tool.

No. Size

GG012 18" Right Angle Scraper GG018-01 18" Replacement Blade



Big Floor ScraperFeatures an 8" wide heavy-duty

replaceable blade, and a twist-lock adjustable telescoping handle. Handle length adjusts from 39" to 59". The perfect tool for floor preparation.

No. **Description** Big Floor Scraper FC506

FC507 (5) 8" Replacement Blades

Heavy-Duty Rubber Floor Squeegee

Rugged heavy-duty floor squeegee with all steel construction. Pure gum rubber blade is replaceable and reversible for longer wear. Comes complete with 60" handle and ferrule (CC901-02).

No. Description

24" Rubber Floor Squeegee GG285 36" Rubber Floor Squeegee GG286

24" Rubber Refill GG287 GG288 36" Rubber Refill

Checkered Handle Utility Knife

Will not slip out of your hand. Blade can be adjusted, but does not retract. Storage for extra blades in handle. Includes 5 blades.

Description

DW199 Bulk Packed 48 per carton DW199C* with Display Card

3-Way Utility Knife

Blade will not slip. Retractable blade can be adjusted to 3 positions. Light but rugged aluminum body. Includes 3 blades.

No. Description

Bulk Packed 48 per carton DW042 with Display Card DW042C*

DW199C DW199



DW042

Replacement Utility Blades - see pg 122

(10 Pack) Dispenser DW078 DW079 (100 Pack) Dispenser

Chalk Box and Chalk

Traditional metal-looking plastic chalk box; use as chalk line or plumb line. Includes 100' of line. Can be used to snap lines and create grids.

No. Description GG319 Chalk Box GG303 White Chalk - 8 oz. Blue Chalk - 8 oz. GG304 Glo Orange Chalk - 8 oz GG305 GG306 Red Chalk - 8 oz. GG307 Yellow Chalk - 8 oz.



Kraft Pro Self Locking 25' Tape Measure

Enalish/Metric

Self-locking tape offers brake releases on top and bottom of tape. Blade printed with English and Metric on both sides for ease in reading. Durable, nylon coated blade resists fading and warping. Rugged and accurate.

No.

GG299* 25' (7.62m) x1"

Dust Mask

Industry accepted N95 disposable respirator mask with foam nose cushion and two elastic straps. Box of 20 masks.

No. GG435*



Orange Latex Gloves

Sturdy latex gloves are resistant to most caustic chemicals, paints and sealers. Provides protection for hands from liquids and other materials.

No. Size Length GG426-L* Large 12" GG426-XL* X-Large 12"



Professional Work Gloves

Lightweight yet durable. Features a neoprene cuff with Velcro® closure for a secure fit. Breathable spandex back provides ultimate comfort and fit.



Construction Boots

Excellent in wet/muddy conditions

Rugged, heavy-duty vinyl boots made of the finest materials and for the toughest construction work. Excellent in wet, muddy conditions. (boot height 16")

"Over The Sock" Black Boot

No.	Size
GG908	8
GG909	9
GG910	10
GG911	11
GG912	12
GG913	13



Ultra Rubber Knee Pads

Durable, accordion style rubber knee pads with comfortable foam pad insert. Replaceable, adjustable strap available. No.

WL084* (pair)



EZ-Kneeler[™] Kneeboard

No more sore knees. Comfortable, 1-1/2" thick foam cushion adhered to 14"x24" polypropylene tray, which protects cushion for long life. Cushion is washable and chemical resistant.

No. WL069

"Ner The Shoe" Vellow Root

UVEI	THE SHUE	IUII	TEIIUW DUUL			
No.	Size					
GG918	8				ı	
GG919	9	•			ı	
GG920	10	1	1	• •	ı	
GG921	11				ı	
GG922	12					
GG923	13	V				
GG924	14					
GG925	15			\	ı	
					١	

RECOMMENDATION: Buy "Over the Shoe" boots 1-2 sizes larger than your regular shoe size.

Standard Nylon Tool Bag

transport to and from the job site.

Size

No.

WL102*

Double layer of nylon and reinforced bottom make this light but strong. Large zippered

opening with 6 inside and 6 outside pockets.

Soft handles and shoulder strap for easy

20"x8-1/2"x13-1/2"

Large Bucket Bag

Heavy-duty construction-grade nylon. Fits over 5 gallon bucket. Organizes a wide range of tools for a job site. 42 exterior pockets, 10 interior pockets and tape holder.

No. WL104

Tools Not Included



Professional Nylon Tool Bag

Double layer of nylon with heavy reinforced bottom makes this a perfect bag for the professional tradesman. Extra large zippered opening for tools and supplies. 14 inside pockets, 6 outside pockets, heavy-duty handles and shoulder strap.

No. Size

WL103* 24"x10-1/2"x13-1/2"



Deluxe Canvas Tool BagsAn expertly made bag, deep and roomy,

built around a 12-gauge steel hinged frame. Leather handles, buckles and canvas are riveted into the frame. Lockstitched sewing assures long life. Inside is a 9"x11" pocket and a masonite bottom board provides waterproofing.

No. Size WL018 14"x18" 14"x20" WL020 14"x24" WL024



Professional Canvas Bag With Outside Pockets

24" large capacity heavy-duty canvas bag. Soft durable canvas, leather handles and lockedstitched sewing assures long life. Exterior pockets for extra storage.

No. Size WI 025 14"x24"



Deluxe Canvas Tool Bags With Leather Bottom

Our finest quality heavy-duty canvas and leather reinforced bags for masons, mechanics and linemen. Made with 12 gauge steel hinged frame and heavy #10 canvas, this bag is made for heavy work and long-lasting wear. Leather reinforcing on the bottom and 3" up on the sides. Inside is a 9"x11" pocket. Waterproof bottom board.

Size No. WL180 14"x18" WL200 14"x20" WL220 14"x22"

Professional Leather Bottom Bag

Heavy-duty, lightweight leather bottom canvas bag comes with tough nylon support handles. Convenient masonite bottom board holds the bag in shape and provides waterproofing.

No. WL224



Standard Tool Bag

Made of heavy canvas riveted to a metal frame. Handles and straps made of leather. Inside is a 9"x11" pocket for small tools.

Size No. WL108* 15"x20'



Economy Tool Bag

Economical 20" wide canvas tool bag. A lightweight but sturdy all-purpose bag. Two steel dowels are sewn into casings and a masonite bottom board holds the bag's shape. Two buckles secure top closed.

No. Size WL050



Double Prong Leather Work Belt

Double leather work belt. Belt adjusts from 30" to 54". Reinforced back with double roller buckles. Quality stitching with solid rivets.

No. WL049



Leather Work Belt

General purpose work belt for nail bags and tool pouches. Fits 29" to 46" waist.

Width Description No. WL099 2" Deluxe 1-3/4" WL098 Economy



Web Pistol Belt

Strong polypropylene web belt adjusts from 32" to 46" with hook-in fastener. No. WL052



Drywall Tool Pouch

loop, plus six other tool loops

and holders. Securely made with total rivet construction for heavy-duty use. No. WL077

The best heavy leather drywall tool pouch

on the market. Features a steel hammer

Deluxe 10-Pocket Tool Apron

Double tool pouch with 2 hammer loops and 10 pockets. Soft leather with 2" leather belt that adjusts to 54".

No. WL030



Double Pouch Style 11-Pocket Moccasin Leather Carpenter's Apron

Our top of the line leather apron made for the professional craftsman. Finest quality supple moccasin leather.

- Large double stitched nylon pockets
- Stress points rivet reinforced
- 2 large and 2 medium size nail pockets
- 6 small tool pockets 25' tape pocket
- 2 strap leather hammer loops
- 1-1/2" combination square holder
- Adjustable 2-1/4" polypropylene web belt No. WL028



Flat Type Drywall Tool Pouch

A flat 8-compartment drywall tool pouch features 4 flared front pockets that hold pencils, knives, etc. A strong leather clip

allows for any size tape to be carried. Also featured is a sharpening stone pocket and circle cutter pockets with a steel loop hammer holder. No. WL096



Promotional 10-Pocket Split Leather Carpenter's Apron

This outstanding value has top of the line features at a promotional price.

- Strong suede split leather
- 2 large and 2 medium size nail pockets
- 6 small tool pockets 25' tape pocket
- 2 strap leather hammer loops
- Adjustable 2" polypropylene web belt No. WL029





Deluxe 9-Pocket Nail Bag

A favorite of drywall installers. This deluxe 9-pocket drywall nail bag is made of the finest moccasin leather.

No. WL520

Deluxe 5-Pocket **Nail Bag**

Deluxe 5-pocket nail bag has 10" flared pocket, 4"x6" pouched pocket

with 2 nail slots and hammer holder. All pockets are fully bound for long wear and lock stitched with strong nylon thread. Rivet reinforced. Strong but supple leather makes this bag one of our best.

No. Description

WL044 Left Side Hammer Loop WI 045 Right Side Hammer Loop



3-Pocket Nail Bag

This fine quality, genuine cowhide nail bag has 3 pockets to hold even more tools and nails than a standard bag.

No. WL516

A) Steel Hammer Loop

Steel loop hammer holder made for easy insertion. Top grain leather is riveted for long wear. Fits easily on belt.


No. WL095

B) Hammer and Hatchet Holder

2"x2" steel loop. Loop swings freely to make carrying hammer easier. Made of heavy leather. **No.** WL403

C) Hammer Holder with Sheath

Ideal for snips and knife with hammer loop. No. WL093



1-Pocket **Nail Bag**

Popular priced nail bag made of soft but heavy chrome split leather.

Lockstitching and riveting make this bag extremely sturdy. Bag has a 10"x11" bellows flared pocket and wide tunnel belt loop.

No. WL046



PROFESSIONAL LEVELS



MADE IN USA

A Kraft Tool Co.® Brand

Professional Cast Aluminum Levels

Contractor's red, super hard professional surface



Durable cast aluminum Will not warp Will not rust

No.	Length	Vials
SL1212	12" (305mm)	4
SL1818	18" (457mm)	6
SL2424	24" (610mm)	6
SL2828	28" (711mm)	6
SL3030	30" (762mm)	6
SL4848	48" (1219mm)	6
SL18YA18	18" (457mm)	5 (45 Degree





Precision milled frame for accurate work surface



Solid Set Cat's Eye Yellow double bent vials for accuracy with protective lenses

Cast Aluminum Level Repair Kit

Includes: (6) lenses, (6) paper rings, (1) 8 oz. painter's putty and (1) aluminum putty tool No. SL010

Professional Cast Aluminum Plumber's Level




Vials Length SL2424P 24" (610mm)


Guaranteed accurate to .0004" per inch

Graduated 1/10" ruler on working surface on contractor's red edge


Durable cast aluminum Will not warp Will not rust



to adjust pitch









and twin plumb vials

Protective glass lenses with Cat's Eye Yellow double bent vials for accuracy

Precision milled frame for accurate work surface

Guaranteed accurate to .0004" per inch

Professional Top-Reading Magnetic Aluminum Extruded Levels

Top-reading

level




No. Length **Vials** SLPML18 18" (457mm) 3 SLPML24 24" (610mm) 3 SLPML36 3 36" (914mm) 48" (1219mm) SLPML48 3 72" (1829mm) SLPML72 5 SLPML96 96" (2438mm) 5



Heavy-duty extruded aluminum I-beam frame with strong magnetic strip



Special replaceable Solid Set acrylic Roto Vial® feature for accurate leveling in all directions



Shock absorbent end caps, Cat's Eye Yellow vials, top-reading window for the level vial, and two plumb vials

SLTMI-48

SANDS PROFESSIONAL LEVELS

Wood Level Repair Kit

Includes: (6) lenses, (1) 8 oz. painter's putty, (1) aluminum putty tool and (1) 2 oz. raw linseed oil

No. SL011

Professional Top-Reading Mahogany I-Beam Levels



Heavy-duty aluminum I-beam frame for extra strength



5

5 solid set Cat's Eye Yellow double bent vials with protective glass lenses

•

Adjustable top vial for accuracy

Professional Walnut/Maple Laminated Levels



Premium grade walnut/maple with flat stainless steel binding and wrap around end caps

Solid flat

 No.
 Length
 Vials

 SLWML24
 24" (610mm)
 6

 SLWML36
 36" (914mm)
 6

 SLWML42
 42" (1067mm)
 6

 SLWML48
 48" (1219mm)
 6

48" (1219mm)



Six Solid Set Cat's Eye Yellow double bent vials for accuracy

Guaranteed accurate to .0004" per inch



Two large hand holes and one hang hole



Double strength glass lenses

Guaranteed accurate to .0004" per inch

Professional Mahogany Flat Brass Levels



brass trim with screws makes it more durable

 No.
 Length
 Vials

 SL22BY24
 24" (610mm)
 6

 SL22BY36
 36" (914mm)
 6

 SL22BY42
 42" (1067mm)
 6

 SL22BY48
 48" (1219mm)
 6



Six Solid Set Cat's Eye Yellow double bent vials for accuracy



Two large hand holes and one hang hole



Shock absorbent rubber end caps and protective glass lenses

Guaranteed accurate to .0004" per inch

Professional Door Jamb Level

Use as a straightedge or for setting door jams



Length 77-3/4" (1975mm)



Vials



Heavy-duty aluminum I-beam frame for extra strength



Eight Solid Set Cat's Eye Yellow double bent vials



Large hand holes and shock absorbent rubber end caps



No.

Professional Mahogany I-Beam Levels





NO.	Length	viais
SLMA24	24" (610mm)	6 w/ hand grooves
SLMA36	36" (914mm)	6
SLMA42	42" (1067mm)	6
SLMA48	48" (1219mm)	6

72" (1829mm)

SLMA72

 Made from the finest selection of mahogany wood



Six Solid Set Cat's Eye Yellow double bent vials for accuracy with protective glass lenses



Two large hand holes and one hang hole



Shock absorbent rubber end caps

Guaranteed accurate to .0004" per inch

Professional Brass Bound Mahogany Levels



Angle bound brass binding embedded in wood for extra strength

No.	Length	Vials
SL12AB18	18" (457mm)	6 no hand holes
SL12AB24	24" (610mm)	6
SL12AB28	28" (711mm)	6
SL12AB36	36" (914mm)	6
SL12AB42	42" (1067mm)	
SL12AB48	48" (1219mm)	6

 Made from the finest selection of mahogany wood









Shock absorbent rubber end caps

Two large hand holes and one hang hole



Guaranteed accurate to .0004" per inch

Professional Stainless Steel Bound Mahogany Levels



Angle bound NO RUST stainless steel binding on all edges

No.	Length	Vials
SL44SB-24	24" (610mm)	6
SL44SB-36	36" (914mm)	6
SL44SB-42	42" (1067mm)	6
SL44SB-48	48" (1219mm)	6

- Made from the finest selection of mahogany wood
- No Rust Stainless Steel Bindings











Two large hand holes and one hang hole

Shock absorbent rubber end caps

Protective glass lenses


Professional Level Cases





Available in 6 sizes 24" to 96"

- Will protect and prolong the life of the level
- · Easy open/close end with peg hook for hanging
- Durable high-impact styrene
- Opening measures 1-1/4"x2-1/2"
- Available in 6 sizes
- · Fits most levels



Easy hang hook

SANDS PROFESSIONAL LEVELS



Professional Aluminum Extruded Levels

Contractor's red with machined edge



I-Beam construction strong and lightweight

No.	Length	Vials
SLHD18	18" (457mm)	6
SLHD24	24" (610mm)	6
SLHD28	28" (711mm)	6
SLHD30	30" (762mm)	6
SLHD36	36" (914mm)	6
SLHD42	42" (1067mm)	6
SLHD48	48" (1219mm)	6
SLHD72	72" (1829mm)	10 (NO END CAPS)
SLHD78	78" (1981mm)	10 (NO END CAPS)
SLHD96	96" (2438mm)	10 (NO END CAPS)



Heavy-duty extruded aluminum I-beam frame



Strong, lightweight frame with shock absorbent end caps





Adjustable Cat's Eye Yellow double bent vials for accuracy with replaceable protective plastic lenses and vials



Precision milled frame for accurate work surface

Professional Aluminum Box Levels

Top-reading vial



Waterproof for easy clean-up of wet trades like tile and plaster

Length **Vials** SLBX24* 24" (610mm) 3 3 SLBX48* 48" (1219mm) 3 SLBX72* 72" (1829mm)







Top-reading window for level vial, one horizontal and two plumb vials



Cat's Eye Yellow vials are accurate and consistent



Shock absorbent end caps



Protective plastic lenses

Professional Aluminum Box Levels with Hand Holes

· Soft cushioned, comfortable hand holes • Heavy-duty extruded aluminum frame Powder coated for long lasting finish

· Heavy-duty extruded aluminum frame Powder coated for long lasting finish

• Frame will not warp or twist

Top-reading vial



Waterproof for easy clean-up of wet trades like tile and plaster

Length **Vials** SLBX24HH* 24" (610mm) 3 3 SLBX48HH* 48" (1219mm) SLBX72HH* 72" (1829mm) 3





Top-reading window for level vial, one horizontal and two plumb vials

Guaranteed accurate to .02" per inch



Cat's Eye Yellow vials are accurate and consistent



Shock absorbent end caps



Protective plastic lenses



Sands Level & Tool Since 1895



PROFESSIONAL LEVELS

Professional Magnesium Extruded Levels



No.	Length	Vials
SL024	24" (610mm)	6
SL028	28" (711mm)	6
SL048	48" (1219mm)	6
SL060	60" (1524mm)	8
SL072	72" (1829mm)	10
SL096	96" (2438mm)	10




30% lighter than aluminum









accuracy

frame levels




Replaceable protective plastic lenses & vials

High quality Extru-Lite™ Magnesium I-beam frame is strong and 30% lighter than aluminum

Adjustable Cat's Eye Yellow double bent vials for

Professional Asphalt Mahogany I-Beam Level



No. SLAL48

Length 48" (1219mm)

· Designed to be used in asphalt

Made from the finest selection

of mahogany wood

construction - NO plastic parts

Vials 2



Heavy-duty aluminum I-beam frame for extra strength





Two top-reading Cat's Eye Yellow vials for

Two large hand holes and one hang hole for hanging



Guaranteed accurate to .0004" per inch



Professional Combo Packs

i i di doci dila dollisto i dokto		
Description		
48" Cast Aluminum Level w/ Case & Torpedo Level		
24" Cast Aluminum Level w/ Case		
48" Cast Aluminum Level w/ Case		
24" Brass Bound Level (w/ hand grooves) w/ Case 48" Brass Bound Level w/ Case		
24" Walnut/Maple Laminated Level w/ Case 48" Walnut/Maple Laminated Level w/ Case		



SANDS CONTRACTOR LEVELS




Contractor Extruded Aluminum Levels



No.	Length	Vials
SLSC2212	12" (305mm)	2
SLSC2418	18" (457mm)	4
SLSC3624	24" (610mm)	6
SLSC3628	28" (711mm)	6
SLSC3636	36" (914mm)	6
SLSC3648	48" (1219mm)	6
SLSC4872	72" (1829mm)	8




Strong, lightweight aluminum I-beam frame





Two large hand holes and one hang hole



Contractor Magnetic Extruded Aluminum Levels



Vials Length SLQML24 24" (610mm) 3 SLQML48 48" (1219mm) 3 SLQML72 72" (1829mm)

> · Good for use on metal studs and door jambs



Full length strong magnetic strip



Strong extruded aluminum I-beam frame



Replaceable Solid Set acrylic Roto Vial® feature for accuracy with replaceable protective plastic



Shock absorbing protective end caps

Contractor **Mahogany Carpenter Levels**





Solid Set Cat's Eye Yellow bent vials for accuracy with heavy protective glass lenses





Available with top-reading or 45 degree vials

Made from the finest selection of mahogany wood and double sealed with a smooth lacquer finish





(2) plumb vials SL11824A 24" (610mm) (2) level vials, (1) plumb vial and (1) 45 degree vial (not shown)

Guaranteed accurate to .0004" per inch



(1) plumb vial with hand grooves



No.	Length	Vials
SL2018 (not shown)	18" (457mm)	(1) level vial, (1) plumb vial and(1) 45 degree vial with hand grooves
SL2024	24" (610mm)	(1) level vial, (1) plumb vial and (1) 45 degree vial with hand holes
SL2048	48" (1219mm)	(1) level vial, (1) plumb vial and (1) 45 degree vial with hand holes



SANDS UTILITY LEVEL

Utility Aluminum Extruded Levels



No.	Length	Vials
SLPL218	18" (457mm)	2
SLPL318	18" (457mm)	3
SLPL224	24" (610mm)	2
SLPL324	24" (610mm)	3
SLPL336	36" (914mm)	3
SLPL348	48" (1219mm)	3

Lightweight extruded aluminum I-beam frame



Two large hand holes



"V" groove on bottom of frame for use on round pipe, conduit or flat surfaces



Replaceable vials (no lenses)

Professional Drywall T-Squares

45 45 44 43 42 41 40 39 38 37 38 35 34 33 32 31 30 29 28 27 26 25 24 23 22 21 20 10 11 • Available in 48" and 54" lengths, 1/8" and 3/16" thickness

16

1 2 3 4 5 8 7 8 9 10 11 12 13 14 15 16 17 18 19 20 21 22 23 24 25

- 16" arm for locating studs
- Bright clear anodized extruded aluminum

Engineered to meet the demands

of the home handyman

- Four rivet construction designed for strength
- Easy-to-read black graduations

No.	Description	Carton Qty
SL672	Aluminum 1/8" (3.175mm) Thick, 48" (1,219.2mm) Length	2
SL676	Aluminum 1/8" (3.175mm) Thick, 48" (1,219.2mm) Length	6
SL682	Heavy-Duty Aluminum 3/16" (4.76mm) Thick, 48" (1,219.2mm) Lengt	th 2
SL686	Heavy-Duty Aluminum 3/16" (4.76mm) Thick, 48" (1,219.2mm) Lengt	th 6
SL692	Heavy-Duty Aluminum 3/16" (4.76mm) Thick, 54" (1,371.6mm) Lengt	th 2

SLCS1

SLCS3

Professional Combination Squares

- Level vial in the head of the square
- Steel scribe and solid brass knurled thumb screw for adjustment
- Easy-to-read permanently etched graduations
- · Available with plastic or zinc head
- · Ideal for level, plumb and miter work

Description No. SLCS0

12" Plastic Head (304.8mm)

12" Zinc Head (304.8mm)

6" Zinc Head (152.4mm)

Professional Try and Mitre



Professional Sliding T-Bevel

- Chrome plated steel 8" (203.2mm) blade
- Solid plastic handle with hand groove and thumb locking screw for securing blade
- · Used for testing bevels, duplicating angles and rafter cuts

No. SL440*



SANDS LEVEL DISPLAY

- 2-Sided, Fast Assembly, Complete with Hooks and Sign
- 28 Popular Wood, Aluminum, Box and Cast Levels
- Level Cases also Included



Sands Level Display - SL900B

Displa	y dimensions:	80" Tall, 20" Wide, 16" Deep
Qty	No.	Description
2	SLPLC24	24" Level Case
2	SLPLC48	48" Level Case
2	SL2424	24" Cast Aluminum Level
2	SL4848	48" Cast Aluminum Level
2	SLBX24	24" Aluminum Box Level
2	SLBX48	48" Aluminum Box Level
2	SLBX24HH	24" Aluminum Box Level with Hand Holes
2	SLBX48HH	48" Aluminum Box Level with Hand Holes
2	SL12AB24	24" Brass Bound Mahogany Level
2	SL12AB48	48" Brass Bound Mahogany Level
2	SLTMI24	24" Top-Reading Mahogany I-Beam Level
2	SLTMI48	48" Top-Reading Mahogany I-Beam Level
2	SLPML24	24" Top-Reading Magnetic Alum. Extruded Level
2	SLPML48	48" Top-Reading Magnetic Alum. Extruded Level
2	SLMA24	24" Mahogany I-Beam Level
2	SLMA48	48" Mahogany I-Beam Level

Rapid Square®

- Flat finish to prevent glare
- Durable, lightweight aluminum
- Easy-to-read dark, permanent graduations
- 5 tools in 1 (try square, miter square, protractor, inscriber and saw guide)

Description No. Rapid Square® - 7" with Manual Rapid Square® - 7" SLRS45 SLRS45B (Bulk pk 30) without Manual

With Manual

T-Square Junior

- Bright, anodized extruded aluminum, 3/16" thick
- Riveted construction
- · Lip catches material for easy cutting and scoring
- Clear black 1/16", 1/8 markings
- Hang hole for easy storage
- · Ideal for carpentry and woodworking

Size No. SL698 24" x 16"



Professional Plumb Bobs



Brass Plumb Bob

- Includes 2 replaceable tips
- Removable cap for easy string installation
- Bright machined finish
- Ideal for finding vertical points Description

No. SL40* Brass Engineer Plumb Bob - 24 oz. SL41*

Brass Engineer Plumb Bob - 16 oz. SL43* Brass Engineer Plumb Bob - 8 oz.



Steel Plumb Bob

- Bright plated finish
- Machined hexagonal steel
- Removable cap for easy string installation
- Ideal for finding vertical points

Description No.

SL51* Hex Steel Plumb Bob - 12 oz. SL52* Hex Steel Plumb Bob - 8 oz.

SL51C* Hex Steel Plumb Bob - 12 oz. carded Hex Steel Plumb Bob - 8 oz. carded SL52C*

KEY TO FEATURES Features listed below by Squares



A. Rafter Framing Rule



B. Octagon Scale



C. Brace Measure



D. 1/100 Scale



E. Essex Board Measure



F. Reverse Reading Rule




G. Metric Equivalents



H. Wood Screw Drill Size

J. Protractor





M. Decimal Equivalents

N. Screw Thread Gauge

O. Board Foot Table

CARPENTER **SQUARES**



Etched Numbers

Long lasting, easy-to-read permanent etched numbers

الميلية المار

Features: A, B, C, D, E / Etched Multiple Features

Graduations: 1/16", 1/8", 1/10", 1/12" Sizo.

No.	Size	Description
SL100RC	16"x24"	Rafter Square - Steel - Copper
SL100RB	16"x24"	Rafter Square - Steel - Black
SL100RP	16"x24"	Rafter Square - Steel - Polished
SLA100R	16"x24"	Rafter Square - Aluminum

Features: Rafter. Metric / Etched **Graduations: Centimeters**

No.	Size	Description
SL200C	16"x24"	Rafter Square Metric - Steel - Copper
SL200P	16"x24"	Rafter Square Metric - Steel - Polished
SL800C	8"x12"	Rafter Square Metric - Steel - Copper

Features: A. Rafter / Etched

Graduations: 1/16", 1/8", Centimeters

E/M = Engish/Metric

No. Size Description

SI 300P 16"x24" E/M Rafter Square - Steel - Polished

Features: A, Rafter / Etched

Graduations: 1/8"

No.	Size	Description
SLSC2C	16"x24"	Rafter Square - Steel - Copper
SLSC2B	16"x24"	Rafter Square - Steel - Black

Features: H. K. L. O / Etched Multiple Features

Graduations: 1/8", 1/4"

No.	Size	Description
SL8C	8"x12"	Square - Steel - Copper
SL8B	8"x12"	Square - Steel - Black
SI 8P	8"x12"	Square - Steel - Polished

Features: F / Etched Graduations: 1/8", 1/4"

NO.	Size	Description
SLSC1C	16"x24"	Standard Square - Steel - Copper
SLSC1P	16"x24"	Standard Square - Steel - Polished
SLSC1A	16"x24"	Standard Square - Aluminum

No. SL460 - 2 Per Pkg

Printed Numbers

ANGLE - STAIR GAUGE

General purpose squares, with easy-to-read numbers

SL100RB

Black

Features: G, H, J, K, L, M, N, O / Printed Multiple Features Graduations: 1/8"

No. Description Size SLSC4P 16"x24" Printed Square - Steel - Polished SLSC4A 16"x24" Printed Square - Aluminum

Features: Standard / Printed Graduations: 1/16", 1/8"

No. Size **Description** SLSC7B 8"x12" Printed Square - Steel - Black

Features: A, B, C, E / Printed Multiple Features Graduations: 1/16", 1/12", 1/10", 1/8"

Description No. Size SLSC6B 16"x24" Printed Square - Steel - Black SLSC6A 16"x24" Printed Square - Aluminum

Etched Numbers

Long lasting, easy-to-read permanent etched numbers

E/M = Engish/Metric

Features: Etched Graduations: 1/8", millimeters

Description

No. Size SL400P 16"x24" English / Metric - Steel - Polished SL800P 8"x12" English / Metric - Steel - Polished

22 **Professional Meter Stick** - 39.37" Length

39.37" = 1 Meter

- Bright anodized extruded aluminum
- Easy-to-read black graduations
- Convenient metric conversion tables printed on back

No. Description SLM39 Meter Stick = 39.37"



- Bright anodized extruded aluminum
- Easy-to-read black graduations
- · Rules are reverse reading

No.	Description
SLAR12	Rule - 12"x1-

-1/8" (304.8mm x 28.575mm) SLAR18 Rule - 18"x1-1/8" (457.2mm x 28.575mm) SLAR24 **Rule** - 24"x1-1/8" (609.6mm x 28.575mm)

SLAYS36 **Yard Stick** 1 Sided - 36"x1-1/8" (914.4mm x 28.575mm) Yard Stick 2 Sided - 36"x1-1/8" (914.4mm x 28.575mm) SLAYS362




Professional Straightedges

- Bright anodized extruded aluminum
- Easy-to-read black graduations
- Reverse reading
 - 7 Sizes 18" 96"
 - •"T" Denotes THICK 3/16" Blade

No.	Description
SLASE18	18"x2"x1/8" (457.2mm x 50.8mm x 3.175mm)
SLASE18T	18"x2"x3/16" (457.2mm x 50.8mm x 4.76mm)
SLASE24	24"x2"x1/8" (609.6mm x 50.8mm x 3.175mm)
SLASE24T	24"x2"x3/16" (609.6mm x 50.8mm x 4.76mm)
SLASE36	36"x2"x1/8" (914.4mm x 50.8mm x 3.175mm)
SLASE36T	36"x2"x3/16" (914.4mm x 50.8mm x 4.76mm)
SLASE48	48"x2"x1/8" (1,219.2mm x 50.8mm x 3.175mm)
SLASE48T	48"x2"x3/16" (1,219.2mm x 50.8mm x 4.76mm)
SLASE60	60"x2"x1/8" (1,524mm x 50.8mm x 3.175mm)
SLASE72	72"x2"x1/8" (1,828.8mm x 50.8mm x 3.175mm)
SLASE72T	72"x2"x3/16" (1,828.8mm x 50.8mm x 4.76mm)
SLASE96	96"x2"x1/8" (2,438.4mm x 50.8mm x 3.175mm)

Professional Aluminum T-Squares



48"x2" (1,219.2mm x 50.8mm)

Professional Drywall Square with Lip



- · Perfect for jobs where a smaller tool is needed
- Lip catches board for easy placement and cutting of drywall board or sheet material

No. Description

SL694 16"x24" with Lip (406.4mm x 609.6mm)



SLATS48

All Torpedo Levels come with • One Level Vial • One Plumb Vial • One 45 Degree Vial

TORPEDO & SPECIALTY LEVELS

Professional 9" Aluminum Torpedo Level-3 Vial

SLSC50 9" (229mm)

Contractor 9" Magnetic Plastic Torpedo Level-3 Vial

No. SLPT12M* Size 9" (229mm)



Professional 9" Magnetic Aluminum Torpedo Level-3 Vial

No. SLSC50M Size 9" (229mm)



Utility (DIY) 9" Magnetic Plastic Torpedo Level-3 Vial

No. SLPT9M* Size 9" (229mm)





Magnetic Base

Contractor Dial Levels • Easy-to-read degree graduations for setting angles

Available magnetic and non-magnetic

Description No. SL410 Non-Magnetic SL420 Magnetic



Utility Magnetic Post Level

- High impact plastic body
- 90 degree bend
- Hooks quickly to any post

No. Vials SL470*

Professional Specialty Levels

A) Aluminum Line and Surface Level

Lenath Vials No. SLSC55 3" (76mm) B) Aluminum Pocket Level

No. Lenath Vials SL556 5" (127mm)





C) Plastic Line Level

Lenath No. Vials SLPLL3 3" (76mm)

D) Cross Check Level

No. Vials SL480*

E) Bull's Eve Level

No. SL400*



C

Contractor Carpenter Pencils



Description

Carded (2 per) Bulk Pack 72 (not carded)

Contractor Angle - Stair Gauge

• Attach to metal carpenter square for accurate, repeat angle cuts on rafters, stairs, etc.

No. Description **SL460** (2) per card



Contractor Clear Redwood Floats

No.

SL529 12"x5" (304.8mm x 127mm) SI 528 15"x3-1/2" (381mm x 88.9mm)



W. Rose™ Tools www.KraftTool.com



THE WORLD'S FINEST BRICKLAYER'S TOOLS

FORGED STEEL

The blade and shank are forged from a single piece of uniquely formulated carbon steel for extra toughness. Forging also assures product consistency.

HEAT TEMPERED

Blades are heat tempered with a special time-tested process to ensure uniform blade hardness.



FLEXIBILITY

W. Rose™ features a tapered ground blade for flexibility. Blades are made in standard or limber weights.



The forged steel blade and shank offer strength and integrity with no internal voids created by welding pieces together. Forged steel will not weaken or crack.

HAND POLISHED

Each blade is carefully hand polished to keep mortar centered on the blade and resist sliding.

SHANK ANGLE

The standard shank angle is specifically balanced to reduce wrist fatigue. Many of our popular trowel patterns are also available in low lift shanks.

INSPECTION

Every trowel is inspected, keeping in mind the high quality standards of the W. Rose™ legacy. They also undergo testing for blade hardness and consistent size.

HANDLE STYLES

Four styles of handles are available on most W. Rose™ trowels - ProForm® soft grip, leather, two sizes of wood and plastic. All handles are specially contoured for a comfortable grip.



Left: A hanging W. Rose[™] store sign from the 1930s **Right:** W. Rose[™] Book of Tools from 1929

ROSE TOOLS ENDURE

For over 200 years W. Rose[™] has been the premier brand for the highest quality of masonry tools. William Rose established the company in 1798 near Philadelphia in Blockley Township, Pennsylvania. This blacksmith shop spent much of the early 1800s making tools, cavalry sabers and officer swords for the U.S. Army. In 1864 W. Rose[™] began specializing in quality edged tools, knives and their signature brick trowel.

In 2001, Kraft Tool Co.® acquired W.Rose™ and remains dedicated to maintaining the legendary quality of its masonry products.

As they have for 216 years, Rose Tools Endure

NARROW LONDON PATTERN

This diamond-heeled blade carries mortar away from the handle. The narrow size is good for general masonry and brick projects. The Narrow London blade easily spreads mortar for projects such as veneering.

ProForm® Soft Grip Handle



Standard Shank - Narrow London				
No.	Blade	Heel Width		
RO116-9SH	9"	4-3/16"		
RO116-9-1/2SH	9-1/2"	4-1/4"		
RO116-10SH	10"	4-1/2"		
RO116-10-1/2SH	10-1/2"	4-5/8"		
RO116-11SH	11"	4-3/4"		
RO116-11-1/2SH	11-1/2"	4-7/8"		
RO116-12SH	12"	5"		
RO116-12-1/2SH	12-1/2"	5-1/4"		
RO116-13SH	13"	5-3/8"		

Wood Handle



vvoou 11aii	uic		
Standard Shank -	Narrow Lond	on	
No.	Blade	Heel Width	Handle Size
RO116-9	9"	4-3/16"	6"
RO116-9-1/2	9-1/2"	4-1/4"	6"
RO116-10	10"	4-1/2"	6"
RO116-10-1/2	10-1/2"	4-5/8"	6"
RO116-11	11"	4-3/4"	6"
RO116-11-1/2	11-1/2"	4-7/8"	6"
RO116-12	12"	5"	6"
RO116-12-1/2	12-1/2"	5-1/4"	6"
RO116-13	13"	5-3/8"	6"
RO416-9	9"	4-3/16"	5"
RO416-9-1/2	9-1/2"	4-1/4"	5"
RO416-10	10"	4-1/2"	5"
RO416-10-1/2	10-1/2"	4-5/8"	5"
RO416-11	11"	4-3/4"	5"
RO416-11-1/2	11-1/2"	4-7/8"	5"
RO416-12	12"	5"	5"
RO416-12-1/2	12-1/2"	5-1/4"	5"
RO416-13	13"	5-3/8"	5"

Leather Handle



Standard Shank - Narrow London				
No.	Blade	Heel Width		
RO316-9	9"	4-3/16"		
RO316-9-1/2	9-1/2"	4-1/4"		
RO316-10	10"	4-1/2"		
RO316-10-1/2	10-1/2"	4-5/8"		
RO316-11	11"	4-3/4"		
RO316-11-1/2	11-1/2"	4-7/8"		
RO316-12	12"	5"		
RO316-12-1/2	12-1/2"	5-1/4"		
RO316-13	13"	5-3/8"		

Plastic Handle



Standard Shank - Narrow London				
Blade	Heel Width			
9"	4-3/16"			
9-1/2"	4-1/4"			
10"	4-1/2"			
10-1/2"	4-5/8"			
11"	4-3/4"			
11-1/2"	4-7/8"			
12"	5"			
12-1/2"	5-1/4"			
13"	5-3/8"			
	Blade 9" 9-1/2" 10" 10-1/2" 11-1/2" 12" 12-1/2"	Blade Heel Width 9" 4-3/16" 9-1/2" 4-1/4" 10" 4-1/2" 10-1/2" 4-5/8" 11" 4-3/4" 11-1/2" 4-7/8" 12" 5" 12-1/2" 5-1/4"		

See page 87 for limber weight trowel blades





MADE IN THE USA SINCE 1798



Low Lift Shanks

Low lift shank trowels have a lower handle angle as preferred by some masons. Comfortable feel for your hand and wrist.

Low Lift Shank -	Wood Handle	Narrow Londo	n
No.	Blade	Heel Width	Handle Size
RO186-9	9"	4-3/16"	6"
RO186-9-1/2	9-1/2"	4-1/4"	6"
RO186-10	10"	4-1/2"	6"
RO186-10-1/2	10-1/2"	4-5/8"	6"
RO186-11	11"	4-3/4"	6"
RO186-11-1/2	11-1/2"	4-7/8"	6"
RO186-12	12"	5"	6"
RO186-12-1/2	12-1/2"	5-1/4"	6"
RO186-13	13"	5-3/8"	6"
RO486-9	9"	4-3/16"	5"
RO486-9-1/2	9-1/2"	4-1/4"	5"
RO486-10	10"	4-1/2"	5"
RO486-10-1/2	10-1/2"	4-5/8"	5"
RO486-11	11"	4-3/4"	5"
RO486-11-1/2	11-1/2"	4-7/8"	5"
RO486-12	12"	5"	5"
RO486-12-1/2	12-1/2"	5-1/4"	5"
RO486-13	13"	5-3/8"	5"

Low Lift Shank - Leather Handle Narrow London			
No.	Blade	Heel Width	
RO386-9	9"	4-3/16"	
RO386-9-1/2	9-1/2"	4-1/4"	
RO386-10	10"	4-1/2"	
RO386-10-1/2	10-1/2"	4-5/8"	
RO386-11	11"	4-3/4"	
RO386-11-1/2	11-1/2"	4-7/8"	
RO386-12	12"	5"	
RO386-12-1/2	12-1/2"	5-1/4"	
RO386-13	13"	5-3/8"	

Low Lift Shank - Plastic Handle Narrow London			
No.	Blade	Heel Width	
RO1486-9	9"	4-3/16"	
RO1486-9-1/2	9-1/2"	4-1/4"	
RO1486-10	10"	4-1/2"	
RO1486-10-1/2	10-1/2"	4-5/8"	
RO1486-11	11"	4-3/4"	
RO1486-11-1/2	11-1/2"	4-7/8"	
RO1486-12	12"	5"	
RO1486-12-1/2	12-1/2"	5-1/4"	
RO1486-13	13"	5-3/8"	

www.KraftTool.com W. Rose[™] Tools



WIDE LONDON **PATTERN**

The wide diamon-shaped blade carries the mortar towards the blade tip. The Wide London pattern holds more mortar making it a popular pattern for concrete block and stonework.



86

ProForm® Soft Grip Handle

Standard Shank - W	Vide London	
No.	Blade	Heel Width
RO112-9SH	9"	5-1/4"
RO112-9-1/2SH	9-1/2"	5-3/8"
RO112-10SH	10"	5-1/2"
RO112-10-1/2SH	10-1/2"	5-1/2"
RO112-11SH	11"	5-5/8"
RO112-11-1/2SH	11-1/2"	5-3/4"
RO112-12SH	12"	5-13/16"



Wood Handle

Standard Shank - V			
No.	Blade	Heel Width	Handle Size
RO112-9	9"	5-1/4"	6"
RO112-9-1/2	9-1/2"	5-3/8"	6"
RO112-10	10"	5-1/2"	6"
RO112-10-1/2	10-1/2"	5-1/2"	6"
RO112-11	11"	5-5/8"	6"
RO112-11-1/2	11-1/2"	5-3/4"	6"
RO112-12	12"	5-13/16"	6"
RO412-9	9"	5-1/4"	5"
RO412-9-1/2	9-1/2"	5-3/8"	5"
RO412-10	10"	5-1/2"	5"
RO412-10-1/2	10-1/2"	5-1/2"	5"
RO412-11	11"	5-5/8"	5"
RO412-11-1/2	11-1/2"	5-3/4"	5"
RO412-12	12"	5-13/16"	5"



Leather Handle

Deather Handle			
Wide Londor	1		
Blade	Heel Width		
9"	5-1/4"		
9-1/2"	5-3/8"		
10"	5-1/2"		
10-1/2"	5-1/2"		
11"	5-5/8"		
11-1/2"	5-3/4"		
12"	5-13/16"		
	Wide Londor Blade 9" 9-1/2" 10" 10-1/2" 11" 11-1/2"		



Plastic Handle

Standard Shank - Wide London			
No.	Blade	Heel Width	
RO1412-9	9"	5-1/4"	
RO1412-9-1/2	9-1/2"	5-3/8"	
RO1412-10	10"	5-1/2"	
RO1412-10-1/2	10-1/2"	5-1/2"	
RO1412-11	11"	5-5/8"	
RO1412-11-1/2	11-1/2"	5-3/4"	
RO1412-12	12"	5-13/16"	




MADE IN THE USA **SINCE 1798**




Low Lift Shanks

Low lift shank trowels have a lower handle angle as preferred by some masons. Comfortable feel for your hand and wrist.

		•	
Low Lift Shank - Wood Handle Wide London			
No.	Blade	Heel Width	Handle Size
RO182-9	9"	5-1/4"	6"
RO182-9-1/2	9-1/2"	5-3/8"	6"
RO182-10	10"	5-1/2"	6"
RO182-10-1/2	10-1/2"	5-1/2"	6"
RO182-11	11"	5-5/8"	6"
RO182-11-1/2	11-1/2"	5-3/4"	6"
RO182-12	12"	5-13/16"	6"
RO482-9	9"	5-1/4"	5"
RO482-9-1/2	9-1/2"	5-3/8"	5"
RO482-10	10"	5-1/2"	5"
RO482-10-1/2	10-1/2"	5-1/2"	5"
RO482-11	11"	5-5/8"	5"
RO482-11-1/2	11-1/2"	5-3/4"	5"
RO482-12	12"	5-13/16"	5"





PHILADELPHIA **PATTERN**

The square heel on this trowel holds the most mortar and has become the most popular trowel to use with block.



MADE IN THE USA **SINCE 1798**

Leather Handle

RO310-12





ProForm® Soft Grip Handle

Standard Shank - P	hiladelphia	
No.	Blade	Heel Width
RO110-9SH	9"	5-1/8"
RO110-9-1/2SH	9-1/2"	5-3/16"
RO110-10SH	10"	5-1/4"
RO110-10-1/2SH	10-1/2"	5-3/8"
RO110-11SH	11"	5-7/16"
RO110-11-1/2SH	11-1/2"	5-1/2"
RO110-12SH	12"	5-9/16"



6" Wood Handle

Standard Shank -	Philadelphia	
No.	Blade	Heel Width
RO110-9	9"	5-1/8"
RO110-9-1/2	9-1/2"	5-3/16"
RO110-10	10"	5-1/4"
RO110-10-1/2	10-1/2"	5-3/8"
RO110-11	11"	5-7/16"
RO110-11-1/2	11-1/2"	5-1/2"
RO110-12	12"	5-9/16"



Standard Shank - Philadelphia			
No.	Blade	Heel Width	
RO310-9	9"	5-1/8"	
RO310-9-1/2	9-1/2"	5-3/16"	
RO310-10	10"	5-1/4"	
RO310-10-1/2	10-1/2"	5-3/8"	
RO310-11	11"	5-7/16"	
RO310-11-1/2	11-1/2"	5-1/2"	



Plastic Handle

Standard Shank - Philadelphia			
No.	Blade	Heel Width	
RO1410-9	9"	5-1/8"	
RO1410-9-1/2	9-1/2"	5-3/16"	
RO1410-10	10"	5-1/4"	
RO1410-10-1/2	10-1/2"	5-3/8"	
RO1410-11	11"	5-7/16"	
RO1410-11-1/2	11-1/2"	5-1/2"	
RO1410-12	12"	5-9/16"	

W. ROSE LIMBER BLADES

NARROW LONDON

Standard Shanh Limber Blad

Standard Shank, Limber Blade		
ProForm® Soft Grip Handle		
Blade	Heel Width	
10"	4-1/2"	
11"	4-3/4"	
11-1/2"	4-7/8"	
12"	5"	
13"	5-3/8"	
Blade	Heel Width	
10"	4-1/2"	
11"	4-3/4"	
11-1/2"	4-7/8"	
12"	5"	
13"	5-3/8"	
Blade	Heel Width	
10"	4-1/2"	
11"	4-3/4"	
11-1/2"	4-7/8"	
12"	5"	
13"	5-3/8"	
	Handle Blade 10" 11" 11-1/2" 13" Blade 10" 11" 11-1/2" 13" Blade 10" 11" 11-1/2" 12"	

WIDE LONDON Neur

5-9/16"

Standard Shank, Limber Blade

,		
ProForm® Soft Grip I	Handle	
No. RO112-10LSH RO112-11LSH RO112-11 1/2LSH RO112-12LSH	Blade 10" 11" 11-1/2" 12"	Heel Width 5-1/2" 5-5/8" 5-3/4" 5-13/16"
<u>6" Wood Handle</u> <i>No</i> .	Blade	Heel Width

b vvood Handle		
No.	Blade	Heel Width
RO112-10L	10"	5-1/2"
RO112-11L	11"	5-5/8"
RO112-11 1/2L	11-1/2"	5-3/4"
RO112-12	12"	5-13/16"
T 4 TT 11		
<u>Leather Handle</u>		
No.	Blade	Heel Width
RO312-10L	10"	5-1/2"

12"

5-5/8"

5-3/4"

5-13/16"

RO312-11L

RO312-12L

RO312-11 1/2L

The same W. Rose™ quality with a more flexible blade. Available in our most popular blade patterns, sizes and handles.

PHILADELPHIA Veur

Standard Shank, Limber Blade

ProForm® Soft Grip Handle Blade Heel Width No.

RO110-10LSH	10"	5-1/4"
RO110-11LSH	11"	5-7/16"
RO110-11 1/2LSH	11-1/2"	5-1/2"
RO110-12LSH	12"	5-9/16"
6" Wood Handle		

o vvooa manaie		
No.	Blade	Heel Width
RO110-10L	10"	5-1/4"
RO110-11L	11"	5-7/16"
RO110-11 1/2L	11-1/2"	5-1/2"
RO110-12L	12"	5-9/16"

Blade Heel Width
0" 5-1/4"
1" 5-7/16"
1-1/2" 5-1/2"
2" 5-9/16"



WIDE HEEL **BLADE PATTERN**

Wide heel is useful when working on thick walls



ROUND HEEL BLADE PATTERN

Rounded heel has no corners to catch the mason's line



6" Wood Handle

Standard Shank -	Wide Heel	
No.	Blade	Heel Width
RO221-10	10"	6"
RO221-10-1/2	10-1/2"	6"
RO221-11	11"	6"
RO221-11-1/2	11-1/2"	6"
RO221-12	12"	6-1/8"



6" Wood Handle

Round Heel	
Blade	Heel Width
10"	5"
10-1/2"	5-1/16"
11"	5-1/8"
11-1/2"	5-1/4"
12"	5-5/16"
	Blade 10" 10-1/2" 11" 11-1/2"



Leather Handle

Standard Shank -	Wide Heel	
No.	Blade	Heel Width
RO321-10	10"	6"
RO321-10-1/2	10-1/2"	6"
RO321-11	11"	6"
RO321-11-1/2	11-1/2"	6"
RO321-12	12"	6-1/8"



Leather Handle

Standard Shank -	Round Heel	
No.	Blade	Heel Width
RO313-10	10"	5"
RO313-10-1/2	10-1/2"	5-1/16"
RO313-11	11"	5-1/8"
RO313-11-1/2	11-1/2"	5-1/4"
RO313-12	12"	5-5/16"



Plastic Handle

Standard Shank - Y		
No.	Blade	Heel Width
RO1421-10	10"	6"
RO1421-10-1/2	10-1/2"	6"
RO1421-11	11"	6"
RO1421-11-1/2	11-1/2"	6"
RO1421-12	12"	6-1/8"



Plastic Handle

Standard Shank - 1	Round Heel	
No.	Blade	Heel Width
RO1413-10	10"	5"
RO1413-10-1/2	10-1/2"	5-1/16"
RO1413-11	11"	5-1/8"
RO1413-11-1/2	11-1/2"	5-1/4"
RO1413-12	12"	5-5/16"

SPECIALTY TROWELS SOLD IN CARTONS OF 6

Blade and shank forged as one piece. Unique heat tempering process for hardness and strength. Hand polished for perfect flexiblity.

R075

RO55

Brick Weight Large Tang Pointing Trowel

Standard	Shank	8		RO50
No.	Blade	Heel Width	Handle	
RO50W	7"	3-3/8"	5" Wood	
RO50I	7"	3-3/8"	5-1/2" pat	her



Standard	d Shank		
No.	Blade	Heel Width	Handle
RO75	7"	3-3/16"	5" Wood
RO55	7-1/2"	4-7/16"	5" Wood

	0 0/0	_	.,_	
	Sewer Tro	wel		



<u>tandard Shan</u>	<u>k</u>			DO 407
/o.	Blade	Heel Width	Handle	RO427
0/127-0 1/2	0_1/2"	6"	5" Wood	

Pumpkin Seed Trowel

Standard :	Shank			RO414-9
No. RO414-9	Blade 9"	Heel Width 4-3/4"	<i>Handle</i> 5" Wood	

Mud Trowel

Standard	Shank			RO6302
No.	Blade	Heel Width	Handle	
RO6302	7-1/2"	5-3/8"	6" Wood	

Buttering Trowel

Standar	d Shank		
No.	Blade	Heel Width	Handle
RO74	7-1/2"	3-1/2"	5" Wood

RO74



Standard	Shank			RO6301
<i>N</i> ₀ . RO6301	Blade 8"	Heel Width 5-3/8"	<i>Handle</i> 6" Wood	

Gauging Trowel

Standard Shank		
No.	Blade	Handle
RO118-9 1/2	9-1/2"	5" Wood
RO118-10	10"	5" Wood

RO118

POINTING & MARGIN TROWELS

Forged from a single piece of uniquely formulated steel. Long lasting with a comfortable weight and flexibility to the blade. Heat treatment produces a uniform hardness for scraping and digging. Pointing and Margin trowels come with smooth wood or comfortable leather handles.

Margin Trowels

Wood Handle 5" x 2" RO58-5 RO58-6 6" x 2" 8" x 2" **RO58-8** Leather Handle Size RO58-5L 5" x 2" 6" x 2" RO58-6L RO58-8L 8" x 2"



Pointing Trowels

Wood Handle RO50-5 5" x 2-1/2" RO50-6 6" x 2-3/4" **RO50-7** 7" x 3-3/8" Leather Handle Size RO50-5L 5" x 2-1/2" RO50-6L 6" x 2-3/4"

End View

 \Box

7" x 3-3/8"

JOINTERS & SLED RUNNERS

Special heat tempering process for hardness and long wear. Hand polished for a smooth, perfect joint.

End View



Convex Jointer

- Creates an inverted rounded impression in the mortar joint
- Most popular joint in the US

Wiost popular joint in t	ile US
No.	Size
RO5121-3/8x1/2	3/8" x 1/2"
RO5121-1/2x5/8	1/2" x 5/8"
RO5121-5/8x3/4	5/8" x 3/4"
RO5121-3/4x7/8	3/4" x 7/8"
RO5121-7/8x1	7/8" x 1"
RO5121-1x1-1/8	1" x 1-1/8"
RO5121-1-1/8x1-1/4	1-1/8" x 1-1/4"



RO50-7L

Concave Jointer

- Creates a beaded protruding joint
- · Very weathertight

No.	Size
RO5321-3/8x1/2	3/8" x 1/2"
RO5321-1/2x5/8	1/2" x 5/8"
RO5321-5/8x3/4	5/8" x 3/4"
RO5321-3/4x7/8	3/4" x 7/8"
RO5321-7/8x1	7/8" x 1"
RO5321-1x1-1/8	1" x 1-1/8"



- Creates a smooth flush joint
- Prohibits moisture from entering the joint
- · Ideal for exteriors
- Great for tucking mortar into the joints.

/VO.	Size
RO5211-1/4x3/8	1/4" x 3/8"
RO5211-3/8x1/2	3/8" x 1/2"
RO5211-1/2x5/8	1/2" x 5/8"
RO5211-5/8x3/4	5/8" x 3/4"
RO5211-3/4x7/8	3/4" x 7/8"
RO5211-7/8x1	7/8" x 1"
RO5211-1x1-1/8	1" x 1-1/8"
RO5211-1-1/8x1-1/4	1-1/8" x 1-1/4"



Grapevine Jointer

- · Creates shallow joints with an indented line, making it appear deeper
- · Popular in colonial period brickwork and masonry restoration

No.	Size
RO5150	5/8" x 3/4"
RO5151	1/2" x 5/8"



 Great for touch-ups and compressing mortar arge End)

No.	Size (La
RO5042-1/4	1/4"
RO5042-3/8	3/8"
RO5042-1/2	1/2"
RO5042-5/8	5/8"
RO5042-3/4	3/4"
RO5042-7/8	7/8"



"V" Jointer

- Creates a rustic appearance on rough and matte finish brick
- V shape creates a sense of depth in the joint

No. Size 5/8" x 5/8" RO5121-5/8V


Sled Runners


- Creates an inverted rounded impression in the mortar joint
- Quickly and efficiently make long, straight and even joints

· Perfect for concrete block walls

A) Convex Loop		
No.	Size	Length
RO5140-3/8	3/8"	17"
RO5140-1/2	1/2"	17"
RO5140-5/8	5/8"	17"
RO5140-3/4	3/4"	17"

Sold in cartons of (6)





Professional Bonded Braided Nylon Line

Premium Quality

Super Tough - Will Not Sag W. Rose™ professional quality, super tough, super strong. Bonded for better knot holding and abrasion resistance. 35% stronger than regular mason's line. 216 lb. test.

Standard Shank - Wide Heel

No.	Size	Color
RO685	685'	Yellow & Black
RO686	685'	Orange & Black

"All American" Red, White & Blue RO687 685 **RO688** 685' "Camo" Green, Black & Brown

685' Orange, Black & Gold RO689



Yellow & Black Orange & Black



"All American" Red, White & Blue



"Camo" Green, Black & Brown



Orange, Black & Gold

Brick Hammer

Properly balanced for great leverage. Fitted with wood handle.

RO3131-24 24 oz. Head



Carbide-Tipped Tile Hammer 5/8" polished hammer head face on a 8 oz. hammer

head. Fitted with a smooth 10" solid wood handle.

Carbide-Tipped		
No.	Head Weight	Face Size
RO3122-5/8C	8 oz.	5/8"
Without Carbide		
No.	Head Weight	Face Size
RO3122-5/8	8 oz.	5/8"
RO3122-3/4	10 oz.	3/4"

Line Pins

Precision forged, heavy-duty steel line pins. Hand polished. Sold individually.

Description No. RO2122 Individual Steel Line Pin



Premium Professional Level with Case

Professional Quality

This classic masonry level is made in the USA by American craftsmen. This 3-piece Walnut/Maple framed level provides accuracy up to .015" per inch. Stainless steel binding and end caps surround the level and promote wear. Precisely set yellow, bent vials increase visibility and accuracy. Clear 1/8" thick tempered glass lenses are replaceable. Walnut/Maple level sold with protective case.

No.Size **RO24** 24" **RO48** 48"



Sold in cartons of (6)




W. Rose[™] Replacement Trowel Handles

ProForm® Handle - RO1000

Unique soft textured contoured 6" ProForm® handle. Tough, rugged and well-balanced, with hard urethane endcap for tamping. (US Patent #D508638)

6" Wood Handle - RO100 5" Wood Handle - RO400

Smooth comfortable second-growth hardwood handle fitted with steel ferrule.



5-1/2" seasoned wood handle wrapped with genuine leather to provide a smooth comfortable grip. Fitted with steel ferrule. Helps absorbs moisture from sweat.

Plastic Handle - RO1400

Clear amber colored 5-1/4" plastic handle. Tough and rugged handle will not mushroom from tamping bricks or concrete blocks.



RO316-10C




Professional Quality Kraft Tool Brick Trowels

- One-piece forging made from the highest grade trowel steel
- Taper ground for flexibility
- Precision balanced
- Fitted with hardwood handle

Narrow London **Blade Size**

BL703 10"x4-3/4" BL705 11"x5" BL707 12"x5"



Philadelphia

Blade Size No. BL750 10"x5-3/8" BL752 11"x5-1/2" BL754 12"x5-5/8"



Wide London

Blade Size No. BI 723 10"x5-1/2" 11"x5-1/2" BL729 BL772 12"x5-1/2"



Replacement Handle

Size BL101 6" Hardwood



No. BL104



Aluminum Solid Wheel Joint Raker

Solid steel wheels bridge the joint while an adjustable nail rakes ioints. The aluminum handle can also be used for tooling joints. No. BL209



PROFESSIONAL MASONRY TOOLS

Specialty Trowels

• One-piece forged for strength and flexibility • Tempered, ground and polished for perfect balance



Wood Handle

Blade Length Heel Width No. GG441 4-3/8"

ProForm® Handle

Heel Width No. **Blade Length** GG441PF 4-3/8"



Wood Handle

Heel Width No. **Blade Length** GG443 3-1/4"

ProForm® Handle

Cross-Joint

Trowel

Wood Handle

ProForm® Handle

No.

No. GG445PF

GG445

Heel Width No. **Blade Length** 3-1/4" GG443PF

Grapevine Jointer

Carefully forged from high carbon steel, this jointer with handle is especially convenient when the job calls for this special joint.



No. Size

BL401 Bit 1/8" wide on center of blade

with Wood handle

BL401PF Bit 1/8" wide on center of blade with ProForm® Handle



Blade Length

Blade Length

Heel Width

1-3/4"

Heel Width

1-3/4"

Wood Handle

Blade Length Heel Width No. GG444 2"

ProForm® Handle

Heel Width Blade Length No. GG444PF

Bucket Trowel

End of blade is cut off diagonally for scraping or mixing in buckets or mortar boxes.

No. BL700

Size





1-3/4" in diameter, mounted 2-1/4" apart. Overall width is 3-5/8". Has 8-1/2" aluminum handle that is squared off at

Masons love this

big wheeled joint

raker. Wheels are

the end so you can rod joints. Hardened nail is adjusted for depth.

No. BL210

92 Masonry Tools

www.KraftTool.com

Margin Trowels

GG433PF 8"x2"

- One-piece forged for strength and flexibility
- Tempered, ground and polished for perfect balance



Pointing Trowels

- One-piece forged for strength and flexibility
- Tempered, ground and polished for perfect balance

Wood Handle

Blade Size		
4"x2"		
4-1/2"x2-1/4		
5-1/2"x2-1/2		
5"x2-1/2"		
6"x2-3/4"		
7"x3"		
100		

ProForm® Handle		
No.	Blade Size	
GG420PF	4"x2"	
GG421PF	4-1/2"x2-1/4"	
GG422PF	5-1/2"x2-1/2"	
GG424PF	5"x2-1/2"	
GG427PF	6"x2-3/4"	
GG423PF	7"x3"	
	and the second	

Margin/ Pointing Trowel Leather Pouch

Convenient leather pouch easily snaps around belt. Fits Pointing and Margin Trowels (6" or smaller). **No.** AR100

See page 106 for Archaeology Tools.



Caulking Trowels

- One-piece forged for strength and flexibility
- Tempered, ground and polished for perfect balance
- Ideal for tuckpointing

Wood Handle

No.	Blade Size
BL761	6-5/8"x3/16"
BL762	6-5/8"x1/4"
BL763	6-5/8"x3/8"
BL764	6-5/8"x1/2"
BL765	6-5/8"x5/8"
BL766	6-5/8"x3/4"
BL767	6-5/8"x7/8"
BL768	6-5/8"x1"

_		
<u>ProForm</u> ®	<u>Handle</u>	
No.	Blade Size	
BL761PF	6-5/8"x3/16"	
BL762PF	6-5/8"x1/4"	
BL763PF	6-5/8"x3/8"	100
BL764PF	6-5/8"x1/2"	- 5 th
BL765PF	6-5/8"x5/8"	1.00
BL766PF	6-5/8"x3/4"	
BL767PF	6-5/8"x7/8"	
BL768PF	6-5/8"x1"	9

Deluxe Canvas Tool Bag *With Leather Bottom*

Our finest quality heavy-duty canvas and leather reinforced bag for masons, mechanics, and linemen. Made with 12-gauge steel hinged frame and heavy #10 canvas, this bag is made for heavy work and long-lasting wear. Leather reinforcing on the bottom and 3" up on the sides. Inside is a 9"x11" pocket. Waterproof bottom board.

No. Size
WL180 14"x18"
WL200 14"x20"
WL220 14"x22"



Deluxe Canvas Tool Bags

An expertly made bag, deep and roomy, built around a 12-gauge steel hinged frame. Leather handles, buckles and canvas are riveted into the frame. Lock-stitched sewing assures long life. A masonite bottom board provides waterproofing. 9"x11" inside pocket.

No. Size
WL018 14"x18"
WL020 14"x20"
WL024 14"x24"



Economy Canvas Tool Bag

Economical 20" wide canvas tool bag. A lightweight but sturdy all-purpose bag. Two steel dowels are sewn into casings and a masonite bottom board holds the bag's shape. Two buckles secure top closed.

No. Size WL050 13"x20"x12"



Standard Nylon Tool Bag

Double layer of nylon and a reinforced bottom make this light but strong. Large zippered opening with 6 inside and 6 outside pockets. Soft handles and shoulder strap for easy transport to and from the job site.

WL102* 20"x8-1/2"x13-1/2"



Professional Leather Bottom Bag

Heavy-duty, lightweight leather bottom canvas bag comes with tough nylon support handles. Convenient masonite bottom board holds the bag in shape and provides waterproofing.

No. Size WL224 24"





Double layer of nylon with heavy reinforced bottom make this a perfect bag for the professional tradesman. Extra large zippered opening for tools and supplies. Comes with 14 inside pockets, 6 outside pockets, and heavy-duty handles and shoulder strap.

No. Size

WL103* 24"x10-1/2"x13-1/2"



JOINTERS

Brick Jointers

Made of high carbon steel

Each end makes a different size concave joint. Overall length 10-1/2".

No.	Size
BL260	3/8"x1/2"
BL261	1/2"x5/8"
BL262	5/8"x3/4"
BL264	3/4"x7/8"
BL265	7/8"x1"



Brick and Stone Marker

A cutting tool for producing imitation brick and stone. Lightweight aluminum tool for cutting out mortar joints also. Heat treated blade is 1/2" wide. Overall length 10".

Description BL207 Cutter with Blade BL208 Extra Blade

Double **Blade** Slicker

Forged from the highest grade carbon steel. Each end makes a different size joint. Overall length 11-1/4".

No. Size 1/4"x3/8" BL201 BL202 1/2"x5/8"

Variable Convex Jointer Extra hard tempered steel **EXTRA** jointer for tile, brick and mortar **HARD** joints. Produces smooth half round sunken joints. Jointer tapers from 5/8" to 7/8" on curvature. Legs measure 3-1/2" and 4-1/4" long. Easy to handle tool adjusts to various joint widths. No. BL660

Diamond "V" Head Jointers

Really nice for striking head joints. Forged from carbon steel. Overall length 9".

No.	Size
BL290	1/2"
BL291	5/8"

Heavyweight Convex **Jointers**

Large at one end, tapered at the other to produce half round sunken joints.

No. Size BL270 9-1/2"x1/2" BL271 9-1/2"x5/8" 9-1/2"x3/4" BL272

Plexiglass Jointers

Will not discolor or leave black marks. Use this plexiglass jointer for white mortar. Overall length 11-1/4".

No.	Size
BL273	1/4"
BL274	3/8"
BL276	1/2"
BL277	5/8"
BL278	3/4"

Double End Grapevine Jointers

Forged from high quality tool steel. Overall length 8".

Width Center Groove No. BL402 1/2" 1/8" BL403 5/8" 1/8"

Combination Raker-Jointer

Rakerjointer is used on rough materials such as adobe brick, split stone and split block.

It has a 3/4" convex jointer on one end, and a 5/16" raker blade at the other end. Overall length 10". No. BL205

Stone & Brick Beader (Grapevine)

Produces 5/16" raised joints for that popular Southern look. Double end. Overall length 11-1/2".

No. Size BL405 5/16"

Lightweight **Concave Stone Beaders**

Produces raised half round beaded joints. Each beader provides 2 size beads. Overall length 10-1/2".

No. Size 3/8"x1/2" BL140 BL141 5/8"x3/4"

Low Cost Joint Raker

work where you can't with a wheeled jointer. The 5/16" joint raker is offset to throw out mortar as you rake. A 5/16" and 3/8" tab at the ends help you rake the corners. Overall length 8".

Lets you

No. BL103

Kraft (Ultra Hard)
"S" Jointers

The patented "S" curve allows you to approach or maintain different pitch angles while jointing the mortar. Long wearing steel. Overall length 9-1/4".

NO.	Size
BL160	3/8"x1/2"
BL161	1/2"x5/8"
BL162	5/8"x3/4"
BL164	3/4"x7/8"
BI 165	7/8"x1"



Masonry Tools www.KraftTool.com

JOINTERS & SLED RUNNERS

"The Original"

Hubbard Jointers

Hubbard Jointers

Hubbard Jointer was designed by a bricklayer in the business for 60 years. More knuckle clearance, replaceable blades, long lasting. Jointer comes assembled with one 1/2 blade, one 5/8" blade, one 3/4" blade, and one 7/8" blade is included in set. Keep the handle - replace the blades.

Overall length 8-1/2".







• The best tool you can get for making round sunken concave or rodded masonry joints

• High quality steel blade

• 14" blade turned up on one end only and 20" blade turned up on both ends

Wood		ProForm [®]
Handle		Handle
No.	Size	No.
BL215	14"x1/2"	BL215PF
BL216	14"x5/8"	BL216PF
BL217	14"x3/4"	BL217PF
BL229	20"x1/2"	BL229PF
BL226	20"x5/8"	BL226PF
BL227	20"x3/4"	BL227PF
	No. BL215 BL216 BL217 BL229 BL226	HandleNo.SizeBL21514"x1/2"BL21614"x5/8"BL21714"x3/4"BL22920"x1/2"BL22620"x5/8"



- High quality steel blade
- Very handy in block construction
- Makes perfect horizontal "V" joints

Wood Handle		ProForm [®] Handle
No.	Size	No.
BL214	14"x3/4"	BL214PF
BL220	20"x3/4"	BL220PF



Hubbard Sled Runners

"The Original"

- The ideal tool for making half-round sunken joints
- Hubbard sled runner operates the same way as the jointer. Keep the handle, replace the blade
- · Cast aluminum blade holder with wood handle
- Comes with 3/4" diameter blademade of case hardened steel
- Turning the blade during use helps distribute wear



No.	Size
BL286	14" Sled Runner with 3/4" Blade
BL285	5/8" Replacement Blade
BL287	3/4" Replacement Blade

7/8" Replacement Blade

BL288



Faster jointing • Even wear • Longer life

5/8"



- Round head joints in all directions
- Eliminates changing hand or wrist positions
- · Keeps knuckles away from wall
- When using fast setting mortar, the Masonry Barbell Jointer® allows you to apply more pressure with less effort
- Comes in package of 2

No. BL390





10-1/2"x24" Large WL013 3/8" Replacement WL015 Metal Tip

WL014 15"x28" Giant WL019 7/16" Replacement

Metal Tip



separately) Sold per box of 50. No. Size

WL009* 11"x16" (Box of 50) 3/8" Replacement Metal Tip WL015 WL019 7/16" Replacement Metal Tip



Curved Handle Wire Brush

Round tempered wire. Removes rust, metal burrs, paint and varnish. Great for cleaning tools. 14" overall length. 4 rows of bristles with 1-1/8" trim.

No. Size 14" **BL467**

Wire Duster Brush

Rounded tempered steel wire. Great for dusting and removing metal chips, 9-1/2" overall length. 2-5/8" trim.

No. Size **BL468** 9-1/2"

Finger Tape

Protect fingers from abrasions and cuts by wrapping individual fingers with cloth finger tape. 165' per roll. Size

No. BL400 1" x 165



Union Fiber Mason's Brush

General purpose construction cleaning brush. Combination of Palmyra and Tampico fibers set in wood block. Overall length is 8" with 2" long bristles.





Fortex® Pail

These popular Fortex® black rubber pails will not rust, dent, leak or chip. They aren't affected by heat or cold, acids, alkalis and most other chemicals.

No. Size

GG460 10 qt. Standard

12 qt. Heavy-Duty with Lip GG462

GG463 12 qt. Heavy-Duty GG464 18 gt. Utility with Lip



Contractor-quality centercut boltcutter for cutting concrete reinforcing rods, soft and medium hard bolts, rods forged jaws. One-half the weight of traditional boltcutters. One-piece handles attach directly to the jaws. (50) pounds of hand pressure at handle turns into 4,000 pounds of pressure at jaw.

Weight No. Length 14" GG114 3 lbs.

Capacities: soft, medium, hard metals: 1/4" (7mm)

6 lbs. 24"

Capacities: soft, medium, hard metals: 3/8" (10mm.)





For general heavy-duty cutting of all soft or hard metals, including concrete reinforcing rods, hard wire rope, chrome ball wire, cold drawn alloy steel, stainless steel and tempered spring wire up to Brinell 400 and Rockwell C42 hardness.

Weight Length No. GG124 6 lbs. 24"

Capacities: soft metal 7/16"; hard 5/16"

14 lbs. 36"

Capacities: soft metal 9/16"; hard 7/16"

GG142 18 lbs. 42"

Capacities: soft metal 11/16"; hard 1/2"

(Add "01" to part number for replacement jaws)

PROFESSIONAL MASON'S LINE

Braided Line



Professional Braided Mason's Nylon Line

Professional masons and contractors ask for this quality, long wearing, tough, braided line. Special braiding process aids elasticity and eliminates sagging. Solid bright colors make it easy to see and use on job sites. 170 lb. test, abrasion and alkali resistant.



Yellow

Orange

Yellow

Fluorescent Fluorescent White

Green

"Hunter"

Size and Color No. BC334T 250' Tube / Fluorescent Orange BC335T 250' Tube / Fluorescent Yellow 250' Tube / White 250' Tubes BC336T BC337T 250' Tube / Green BC338T 250' Tube / Yellow 250' Tube / Fluorescent Pink BC333T BC485T 250' Tube / "Patriot" Red, White & Blue 250' Tube / "Hunter" Green, Gold & Brown BC486T

500' Tube / Fluorescent Orange BC346 BC339 500' Tube / Fluorescent Yellow BC340 500' Tube / White BC341 500' Tube / Green

500' Tube / Yellow BC342 BC355 500' Tube / Fluorescent Pink

500' Tube / "Patriot" Red, White & Blue BC487 500' Tube / "Hunter" Green, Gold & Brown BC488 BC360 1000' Tube / Fluorescent Orange

BC359 1000' Tube / Fluorescent Yellow BC343 1000' Tube / White BC344 1000' Tube / Green

BC345 1000' Tube / Yellow 1000' Tube / Fluorescent Pink BC361

BC489 1000' Tube / "Patriot" Red, White & Blue 1000' Tube / "Hunter" Green, Gold & Brown BC490

Professional Mason's Line Winders

Free spinning plastic winder holds line in place for easy dispensing. Comes with high quality 18# solid braided mason's line. Easy to see bright colors. 170 lb. test.

No. Size and Color BC332W 250' Yellow 250' Flo. Orange BC331W 250' Green **BC330W** 100' Yellow BC329W **BC328W** 100' Flo. Orange BC327W 100' Green



Flo Orange

Braided Mason's Nylon Line with Winder

Braided nylon line on a plastic winder with metal line cutter. The 170 lb. test has built in elasticity and eliminates sagging.

"Patriot"

Size and Color No. BC336 250' Winder / White 250' Winder / Green BC337 250' Winder / Yellow BC338

Fluorescent

Pink

BC367 250' Winder / "Patriot" Red, White & Blue 250' Winder / "Hunter" Green, Gold & Brown BC368





Professional Quality 500' Braided Nylon Line EZ-Winder

"Hunter"



Ideal for: Concrete, Masonry, General Construction, Surveying, Fence **Building or Landscaping**

500' Winders

No. Color BC342W Yellow BC346W Fluorescent Orange BC352W White & Black

1.000' Winders No. Description

BC360W Fluorescent Orange



and winding a snap

EZ-Winder makes unwinding

500' Tubes

1000' Tubes

Display with 24 Winders Color No. BC342D Yellow

BC346D Fluorescent Orange BC352D White & Black





PROFESSIONAL Braided Line MASON'S LINE



www.KraftTool.com



PREMIUM Professional Bonded Braided Nylon Line

High Visibility Colors

This bright, fluorescent ultra strong bonded braided line is longer wearing. The extra elasticity helps eliminate sagging. The nylon has a black flecked braid. Special bonding process adds extra abrasion and alkali resistance.

1/U lb. test.	
No.	Size and Color
BC354	500' Tube / Green and Black
BC353	500' Tube / Orange and Black
BC352	500' Tube / White and Black

1000' Tube / White and Black

Winder White and Black No. Size BC351 250



PREMIUM Super Tough Professional Bonded Braided Nylon Line

BC350

High Visibility Colors

A Kraft Tool Co.® Brand

NO SAG LINE. . . Professional quality, super tough, super strong. Bonded for better knot holding and abrasion resistance. 35% stronger than regular mason's line. 216 lb. test.

No. Size and Color RO685 685' Yellow and Black RO686 685' Orange and Black RO687 685' "All American" Red. White & Blue 685' "Camo" Green, Black & Brown RO688 RO689 685' Orange, Black and Gold







"All American"




Orange, Black and Gold

PREMIUM Professional Bonded Braided Nylon Line (General Purpose)

Toughest in the business, withstands the punishing rigors of the Construction and Industrial Trades. Strong, all purpose, abrasive resistant braided cord. General utility cord for fishing, outdoors and construction applications. Hard braided & specially bonded to resist tangling. Reliable waterproof hand line. Available in 1/2 lb and 1 lb tubes (green).



9	(Approx.)	1 lb. Tube		(Approx.)
# Test	Yards	No.	# Test	Yards
132	160	SS102132	132	320
176	110	SS102176	176	220
240	85	SS102240	240	170
265	72	SS102265	265	144
315	60	SS102315	315	120
350	48	SS102350	350	96
	# Test 132 176 240 265 315	# Test Yards 132 160 176 110 240 85 265 72 315 60	# Test Yards No. 132 160 SS102132 176 110 SS102176 240 85 SS102240 265 72 SS102265 315 60 SS102315	# Test Yards No. # Test 132 160 SS102132 132 176 110 SS102176 176 240 85 SS102240 240 265 72 SS102265 265 315 60 SS102315 315







White Green Yellow Flo. Flo. Flo. Yellow Orange Pink

Contractor Twisted Mason's Nylon Line

This low-cost, twisted nylon line tests over 120 lbs. Not affected by mortar, oil or mildew.

Size & Color No. BC347 350' Tube / White BC348 350' Tube / Green 350' Tube / Yellow BC349

BC356 350' Tube / Fluorescent Yellow BC357 350' Tube / Fluorescent Orange BC358 350' Tube / Fluorescent Pink



Nylon Solid Braid Rope

Excellent multipurpose starter cord. tie down rope. Solid braid for extra strength.

No. GG250-8 250' x 1/4" diam.

Broom Handles

Description No.

BL431 14" Tapered Wood Jam Handle 54" Tapered Wood Jam Handle BL432 CC163 60" Metal Threaded Wood Handle

CC232 60" Metal Threaded Coated Steel Handle

CC263 60" Snap-Style 3-Piece Threaded Aluminum Handle

Heavy-Duty Acid Brush

Mason's like it because of the solid stock construction and greater holding capacity. Coarse 3" palmyra and tampico fibers securely attached to hardwood block. Uses tapered wood handle. (Order handle separately.)

No. Size

BL430 (Brush only) 8-1/2"x2"

Standard Acid Brush

Use to wash down new and old masonry surfaces with muriatic acid. White tampico fibers are 6" wide, 1-3/4" thick and 3-1/2" long. 14 rows wide, 5 rows thick.

No. BL422 (Brush only)

Heavy-Duty Acid Brush

Use this long wearing acid brush with any length handle. The smooth finished hardwood block has 18 x 7 rows of stiff white tampico fibers bristles 1-1/4" long. Use with tapered wood handle only.

Size No. BL525 8-1/4"x3"

Acid/Cleaning Brush

Ideal brush for cleaning equipment and other surfaces. 2-1/2" long plastic bristles are acid resistant. Use with threaded wood handle only. 10" plastic block.

No. BL433

Deck Brush

Stiff blue filament is resistant to chemicals and holds solutions. Not affected by solvents or acids. Smooth 10"x3" hardwood block with 2" long fibers. Accepts threaded or tapered handles.

No. BL529

Coating/Cleaning Brush

Perfect for applying coatings, rough scrubbing or acid cleaning. Smooth wood block with 9-1/2" brush surface and 2" tampico fibers. Accepts threaded handles.

No. BL503 NEW

10" Truck / Wash Brush

Black and white flagged soft polystyrene bristles. Soft scrubbing action ideal to prep floors or use on vehicles. Use with threaded handle.

Size No. **BL435** 10"











MASONRY BRUSHES

Jumbo **Utility Brush**

This red handle utility brush is a must for any professional. Long wearing, white tampico fibers can be used on masonry, brick, tile and stone. A truly versatile brush.

Size

BL526 6-1/2"x2"x4"





Long Arm Acid Brush

20" solid wood handle to keep your hands out of acid. 2" fiber gives just the right spring to the bristles. Brush face is 5"x6". Handle is smooth, tumbled block that is easy to grasp.

No. A) BL521 B) BL522 C) BL523

Fiber Palmyra White Tampico Plastic

Acid Brushes

Designed especially for use with acid and heavy scrubbing. 8-1/2" long overall. Wood handle is 5" long.

No. **Fiber**

A) BL119 Plastic B) BL120 White Tampico







Keeps your projects neat and clean. Made of medium soft hair.

Size No.

BL428 13" Medium Gray Flagg 13" Soft Horsehair BL427



for removing paint. 4x11 rows.

No. BL466







Brass Bound Mahogany Levels

Made of the best grade mahogany. High quality brass binding and accurate vials make this level the choice of many craftsmen.

Size No.

BL244 24" with Hand Holes 48" with Hand Holes BL248



Smith Levels

These handmade stainless steel bound walnut and maple laminated levels are used by the most discriminating craftsmen. Featuring metallic sealed vellow vials, handset in an unshrinkable compound. The exterior is sealed using raw linseed oil. Will not warp or delaminate.

No. Size

SMITH-18 18" with Hand Holes 24" with Hand Holes SMITH-24 SMITH-36 36" with Hand Holes 42" with Hand Holes SMITH-42 SMITH-48 48" with Hand Holes

Smith Recondition Kit

Includes (6) replacement lenses, (6) lens ring holders and linseed oil. No.







QUIK READ

Power Tape

- 25'x1" Tape Measure
- Easy to read vertical tape
- Numbers both in fractions and decimals
- Handy belt clip
- Top quality durable plastic case
- Heavy-duty spring

No. Size GG295* 25'x1'



- 200'x1/2" Tape measure
- Nylon coated steel tape
- Handy easy reel handle
- Top quality durable plastic case

No. Size

200'x1/2" (ft, 10ths, 100ths) GG297*

GG298* 200'x1/2" (ft, in)

Kraft Pro Self Locking 25'



Self-locking tape offers brake releases on top and bottom of tape for personal preference. Blade printed with English and Metric on both sides for ease in reading from all angles. Durable, nylon coated blade resists fading and warping. The riveted double end hook stands up to rugged use while providing accurate measurements.

No. Size GG299* 25' (7.5m) x1"

Walking Tape

Quickly and easily measure horizontal and vertical surfaces. Heavy-duty wheel is long-lasting. Convenient support keeps tool upright when not in use. Telescoping handle adjusts easily to correct working height. Measure up to 10,000' (2 miles) without resetting.

No. Description GG283* Feet/Inches GG283M* Metric

Magnetic Torpedo Level

This magnetic level is made of lightweight aluminum. Ideal for those small places and perfect to carry in the pocket.

No. Size GG450

3" Line Level



nished with two strong line clips. This level can be used on a line or as a surface level. No. GG513



Easy to read black markings on yellow steel tape. Top quality durable plastic case with handy belt clip. Choose the one you need.

No. Size GG292* 25'x1"

GG294* 25'x1" (Tenths)

25' Carpenter's **Tape Measure**



- 25'x1" large read blade with easy-to-use thumb lock
- Comfort grip outer casting
- End hook features multiple rivets for durability

No. Size 25'x1" GG284*

Chalk Box

Use either as a chalk line or plumb line. Comes with 100' line. Packaged (6) per box. No. GG319



Chalk

High quality chalk for use in

any chalk box.			
No.	Color	Weight	
GG303	White	8 oz.	
GG304	Blue	8 oz.	
GG305	Glo-Orange	8 oz.	
GG306	Red	8 oz.	
GG307	Yellow	8 oz.	
GG221	White	5 lbs.	
GG314	Blue	5 lbs.	
GG315	Glo-Orange	5 lbs.	
GG316	Red	5 lbs.	
GG317	Yellow	5 lbs.	





100 Masonry Tools www.KraftTool.com

TAPES & BRICK RULES

Modular Rule

Lists modular spacings on one side; feet, inches, eighths and sixteenths on the other side. Ruler features six scales. First section is short for butting rule on first 16" module. Legs have square ends.

No. Size BL512 6' Wood



Thick hardwood rule rists ten course spacing on one side; has inches, eighths and sixteenths on other side. Joints lubricated for smooth opening and closing.

No. Size BL167 6' Wood



This mason's spacing rule is for oversized brick. These brick rules have 2-3/4" height and spacings at 2-7/8" and go to 3-1/2" in 1/16" increments. This brick spacing rule is identified with black letter "A" through "K".

No. Size
BL169 6' Wood
BL656F* 6' Fiberglass


Engineer Folding Rule

Red end folding rule is the finest engineer rule made. Graduations: inside markings in feet, 10ths and 100ths of feet. Foot numbers in red, repeated each inch and 10th of a foot.

No. Size

GG320 6' (Feet, 10ths & 100ths)1066D GG322 6' (10ths & Metric)1066DM GG1066DF* 6' (Feet, 10ths & 100ths)

Fiberglass





16' Spacing Tape has space markings, and feet, inches on one edge of blade. Modular tape has modular markings for all common bricks; and feet, inches on one edge of blade.

No. Size

BL518* 16'x3/4" Spacing BL519* 16'x3/4" Modular



Estwing 16" All Steel Framing Hammer

Drive nails straight and fast with this powerful hammer. Milled face, nylon vinyl grip.

No. Size

GG417 22 oz. Steel Hammer

Framing Hammer

Fiberglass handle with a comfortable grip and your choice of a smooth or milled face on this must have framing hammer.





Non-slip lock down to unload quickly and easily. Will not damage bricks and is designed and built for long wear. Large wing nut makes for fast adjustment from 7 to 11 bricks. Made of malleable iron with smooth wood handle. A favorite with brick masons across the country.

No. BC281



Adjustable Tubular Brick Tong

This professional brick handler is built for long service. It is made of square tubing. Will not damage bricks. Handles 6 to 11 bricks.

No. BC384



Heavy-duty quick adjusting tong can carry 6 to 10 bricks. Will not damage bricks and is designed and built for long wear.

No. Size BC380 16" Long

Masonry Guides

The finest most versatile corner pole system available can be effectively used on all types of masonry brick veneer or solid load bearing wall and block work. The 9' pole and fittings are constructed entirely of high grade aluminum. The top and bottom fittings are completely adjustable and can be used at any height for quicker and more accurate set up.

One man can quickly and easily erect and align. Sturdy, rugged, practically indestructible, these corner poles will pay for themselves time and time again.

BC607 Outside Corner System

Complete with 9' guide pole (no pole markings) and fittings shown below:



BC617 Outside corner base



Top sliding attachment



BC615 Outside corner top fitting

BC608 Inside Corner System

Complete with 9' guide pole (no pole markings) and fittings shown below:



BC618 BC
Inside/intermediate Top sattace



Top sliding attachment



BC619 Inside/intermediate line holder

BC609** Guide Pole ONLY 9' pole (with no markings), weight 16 lbs.

9° pole (with no markings), weight

**Must ship via truck

Pole shown with outside fittings

Fittings may be ordered separately

PERSONALIZED Mason's Line Twigs / Trigs Line Blocks and Line Pins

Text only, no logos

Personalized Line Twigs/Trigs

- Two line maximum imprint
- Imprint area 3/8" high and 2" wide
- · Choice of black or red imprint color

Personalized Line Blocks

- Three line maximum imprint
- Imprint area 1/2" high and 2-1/2" wide
- · Choice of blue, black or red imprint color

Personalized Line Pins

- One line maximum imprint
- Imprint area is 18 spaces
- · Stamped into metal surface



Ask your helpful Customer Service Representative for a Special Imprint Order Form and for prices and quantities. Order forms also available online.



102 **Masonry Tools** www.KraftTool.com

MORTAR BOXES

Steel **Mortar Box**



#10 Gauge heavy-duty steel

6" forklift clearance

Heavy-duty reinforced top lip

 Joints lapped with continuous welds for extra strength

Weight: 166 lbs Dimensions:

57" Length, 22" Width, 24" Height Inside Bottom Dimensions:

39" Length, 22" Width

No. Size

10 Cu. Ft. Steel Mortar Box BC210



HEAVY-DUTY CU. FT. CAPACITY

Outside Dimensions: 45" Length, 22" Width, 18" Height Inside Bottom Dimensions: 34" Length, 22" Width

- Heavy-duty 10 gauge steel Weight: 260 lbs
- Easy turn heavy-duty 8" casters; two swivel with locking feature and two straight
- Reinforced 1" steel handle
- Joints lapped with continuous welds for extra strength

No.

BC211 10 Cu. Ft. Steel Mortar Box with Locking Casters BC211-01 10 Cu. Ft. Steel Mortar Box without Casters

Poly Mortar Box



HEAVY-DUTY CU. FT. CAPACITY

Outside Dimensions: 60" Length, 32" Width, 12" Height Inside Bottom Dimensions: 34"Length, 23" Width

- Heavy-duty 350 mil poly mortar box
- Heavy-duty reinforced top lip
- Easy to clean
- Weight: 26 lbs

BC218 9 Cu. Ft. Poly Mortar Box

Steel Mortar Boxes



Steel mortar boxes made of heavy-duty 16 gauge steel. Smooth interior makes mixing easier. Leakproof. (Must ship by truck).

No. BC206 50"x29"x12" (6 Cu. Ft.) 47 lbs. BC209 60"x32"x12" (9 Cu. Ft.) 65 lbs. BC215 78"x38"x12" (15 Cu. Ft.) 86 lbs.

Polyethylene Mortar Boxes



Available in two popular sizes; 7-1/2 cubic feet and 9 cubic feet Lightweight, but tough. Not affected by heat or cold; easy to clean. Will not rust. (Must ship by truck).

No. Wt. Size BL375 56"x33"x8" (7.5 cubic feet) 20 lbs. 60"x36"x12" (9 cubic feet) BL376 25 lbs.



Polyethylene Mortar Pan

One-piece construction. Outwears metal. Not affected by plaster,

mortar or water. Weighs less than 5 lbs. Easy to use, easy to clean. 30"x30 at the top, tapered to 16"x16" at bottom.

No. Size 30"x30"x7" BC492



All Steel Mortar Pan

16 gauge steel. Rounded edges for easy handling. Curved corners and sloped sides makes this pan ideal for mixing materials. Smooth interior makes mixing easier. Leakproof. Easy to use, and to clean.

No. Size BC212 30"x30"x8"



200 mil

Polyethylene Mortar Board

Will not splinter. Will not absorb water. Dry mortar will not stick. Lightweight polyethylene, easy to use, easy to clean.

Fiberglass® Mortar Board

Will not splinter. Will not absorb water. Dry

No. Size BC480 30"x30"



All Purpose Tub

Great for mixing a variety of materials. (6 per carton)

No. 26"x20"x6" BC217



Folding stand is made of tubular steel and can be used on scaffold or ground. Lightweight and easy to handle. Stand is 30" tall and has



Use on scaffold or ground. Made from tubular steel, 30" tall or 19" laying on side.

No. BC293*



Heavy-Duty Mortar Hoe

Mortar hoe has two holes for better mortar mixing. Comes with heavy-duty shovel type wood handle. Preferred by the pros.

No. Size

BC228 6"x10" Blade with 66" Handle 7"x5" Blade with 60" Handle BC230

Mortar Stand

(2) chains. Weight: 12 lbs.

No. BC291



Great tool for mixing concrete quickly in wheelbarrows, backhoe buckets and other mixing containers. Patented forged head easily mixes 60 to 90 lb. bags of concrete in less than a minute. Special design creates minimum splash with 50% less drag. Great in corners. Open bag with point of hoe. 7-1/2"x6" blade.

Description No.

Easy Mixer Hoe with 60" Handle CC211 Easy Mixer Hoe with 21" Handle CC212

Short Handle Mortar Hoe Mortar hoe has two holes for better mortar

mixing. Short 21" heavy-duty shovel type wood handle, ideal for working in tight areas. A must tool for every mason.

BC229 6-1/2"x4-3/4" Blade

No.



Size

Proudly Made In The USA *See page 145

US PATENT # 6,412,569

Concrete Chisels

Forged from the finest tool steel, well tempered, properly balanced for a comfortable hold.

No. CC654 10"x1-7/8" CC671 10"x2-1/2" CC655 10"x2-7/8"



English Pattern Plugging ChiselPlugging chisel has 10" grooved blade forged in

England from the best steel available. Blade is 4-1/2" long; tapers from 1" down to 1/2".

Overall length 10". No. BL377*

Plugging ChiselForged from the finest tool steel, well tempered, properly balanced for a comfortable hold. Blade length

4-1/2". Overall length 10" No. Size

10"x4-1/2"x1-3/16" BL576

Cold Chisels

Forged from the finest tool steel, well tempered, properly balanced for a comfortable hold.

No. Size GG362 7-3/8"x3/4" GG363 12"x3/4" GG364 8-1/8"x1" GG365 12"x1"

Stone Splitting Wedge

Drill hole in stone and insert shims and wedge. Hammer the wedge to force stone apart. Measures 4-3/4"x1/2"

No. BL389

Carbide Tipped Hand Tracer

Hand tracer makes straight lines on stone. Continued tracing will cause stone to split along this line. 2" beveled blade, 1-1/2' diameter and 8-1/2" overall length.

Weight No. **BL388** 3 lbs.

Carbide Tipped Brick/Stone Hammer

Special designed head with wood handle gives extra striking force with 7/8" wide durable carbide tip.

Weight No. BL150 2 lbs.

Carbide Tipped Chipping Hammer

Forged and tempered. Vertical cutting edge has carbide tip for perfect angle to remove stone.

Weight No. BL149 2 lbs.

Rubber Grip Enalish Bolster Chisel

Rubber grip English chisel is easier to hold while using. Forged and heat treated for longer life. Overall length of 8-3/4", 5" handle, 4" wide cutting

No. BL426*

Bricklayer's Set

Forged from the finest tool steel, well tempered, properly balanced for a comfortable hold.

No.	Size
BL232	8"x2-1/2"
BL233	8"x3"
BL234	8"x4"
BL235	8"x5"



Plain Stone Mason's Chisels

Forged from the finest tool steel, well tempered, properly balanced for a comfortable hold.

Size
8"x5/8"x1-1/4"
8"x3/4"x1-3/4"
8"x3/4"x2-1/4"
8"x7/8"x2-3/4"

Tooth Stone Mason's Chisels

Forged from the finest tool steel, well tempered, properly balanced for a comfortable hold.

NO.	Size
BL412	8"x5/8"x1-1/4"
BL413	8"x3/4"x1-3/4"
BL414	8"x3/4"x2-1/4"
BL415	8"x7/8"x2-3/4"

A) Hand Stone Chipper

Use to chip a straight edge on a smooth building stone.

Diameter No. Bit 2" BL385 7/8" BL386 1" 2-1/2" **BL387** 1-1/8" 3"

B) Hand Stone Tracer Marks a straight line on stone.

Continued tracing will cause stone to split along this line. Great for shaping and cutting.

No. Diameter Bit BL382 7/8" 2" BL383 2-1/2" 3" 1-1/8" BL384

C) Hand Stone Pitching Tool

Use to trim stone on edge to put on a facing. No.

Diameter Bit 7/8" 2" **BL378** BL379 1" 2-1/21 1-1/8" BL381



Kraft Brick Hammer

This heavy-duty brick hammer is available in three sizes. Forged from high quality tool steel. Comes with a smooth comfortable 11-1/4" wood handle.

> No. Description BL155 24 oz. BL153 28 oz. BL152 32 07 32 oz. with 15" Handle BL152L

BL155-01 11-1/4" Replacement Handle with Wedges

Bricklayer's Brick HammerThis heavy-duty brick hammer is available in two sizes.

Forged from high quality tool steel. Comes with a smooth comfortable 11-1/4" wood handle.

> Weight No. BL255* 16 oz. BL256* 24 oz.

BL255-01 Replacement Handle with Wedges

Dead Blow Hammer

Dampens vibration when striking surface. Compacted head design with flared and extruded handle for easy gripping.

No. Weight BL275* 2 lbs.

Toothed Bush Hammer

Has milled teeth on square face for shaping and texturing masonry materials.

> No. Size Weight BL344 1-1/2" Square Face 3 lbs. BL444 1-3/4" Square Face 4 lbs.

Deluxe Toothed Bush Hammer

8-1/2" long head with 1" square face. Teeth are precision cut to a sharp point for superior cutting action and wear. Comes with smooth wood handle.

No. Weight **BL151** 2 lbs. Replacement Handle BL155-01 with Wedges

Stone Mason's Hammer

A heavy-duty hammer made of forged and tempered steel. One end used for splitting and breaking stone, and the other end for trimming. Comes with 36" long handle.

Weight No. BL336 16 lbs. BL338 20 lbs.

MASONRY HAMMERS

Mash Hammer

Forged steel head. Comes with 10-1/4" wood or fiberglass handle. Used by the professional bricklayer.

Weight

BL453* 3 lbs. (Wood Handle) BL453F* 3 lbs. (Fiberglass Handle)



Sledge Hammer With Fiberglass Handle

4 lb. sledge style head with strong fiberglass handle. Overall length 14". Ideal for working with forms, stakes and other general construction jobs.

Weight BL454F* 4 lbs.



One-Piece Estwing Mash Hammer

Made of steel with nylon-vinyl cushion grip. Polished face and bevel, painted finish.

Weight No. BL352 2 lbs BL353 3 lbs BL354 4 lbs



Scaling Brick Hammer

Scaling hammer is used for cleaning in preparation for refinishing old brick. Can also be used for chipping mortar in a variety of ways.

No. Weight GG334 16 oz.



Built to really take punishment. Rugged steel handle will not break, fly off, dent or get chewed up. Exceptionally well balanced.

Mason Hammer

Weight No. BL312 12 oz. BL320 20 oz. BL324 24 oz.



Stone Mason's Hammer

Made of forged and tempered steel for trimming and splitting stone. Comes with 16" wood handle.

No. Weight BL333 3 lbs. BL334 4 lbs. BL337

BL332 16" Replacement Handle with Wedges



chaeology Tools 3 Handle Styles 8,9

Leather Pouch with rivets and belt loop made to fit these trowels. No. AR100 Add "P" after part number of Pointing Trowel or Margin Trowel to add Pouch

Specialty trowel made from high grade steel. Thicker, beveled blade makes these trowels ideal for digging and scraping. Handles are placed at just the right angle to reduce wrist fatigue and provide knuckle clearance. Available in wood, leather or ProForm® soft grip handles.



Pointing Trowels

Wood Handle

No. **Blade Size** 4-1/2"x2-1/4" AR421 AR424 5"x2-1/2"

Leather Handle

No. Blade Size AR421L 4-1/2"x2-1/4" AR424L 5"x2-1/2"

ProForm® Handle

Blade Size No. AR421PF 4-1/2"x2-1/4" AR424PF 5"x2-1/2"

Margin Trowels

Wood Handle

No. **Blade Size AR431** 5"x1-1/2" AR432 5"x2"

Leather Handle

No. **Blade Size** AR431L 5"x1-1/2"" 5"x2" AR432L

ProForm® Handle **Blade Size** No. AR431PF 5"x1-1/2"

AR432PF 5"x2"

Mini Brick Splitter



At only 39 lbs this brick splitter easily travels from jobsite to jobsite. The opening is a full 5" high fitting a standard brick standing up at an angle. The lever action increases your arm strength, making cuts with minimum effort. The blades are 4-1/2" wide, so it cuts most bricks now in use. A 12" rule and square is built right into the Mini Splitter for accurate cuts.

Description No. BC582 Mini Brick Splitter

BC582-01 Set of Replacement Blades

Brick and Block Cart



Heavy-duty all terrain cart allows user to move straps of bricks. Comes with 7-1/2" prongs and a heavy-duty 3 piece hub with 2 ply tube type tires. Rubber sealed heavy-duty ball bearings. All steel wheels with grease fittings. Constructed for a lifetime of service. 800 lb. capacity. Must ship by truck (only).

Weight: 112 lbs. No.

BC205 Cart: 29" wide, 54" high BC205-01 **Short Replacement Prongs (Pair)**

7-1/2" (Brick)

BC205-02 Long Replacement Prongs (Pair)

15" (Block)

Professional Work Gloves

Lightweight yet durable professional work gloves. Comfortable neoprene cuff with Velcro® closure for a secure fit. Breathable spandex back provides ultimate comfort and fit.




Concrete Block Line Stretchers

Stretches line tight between blocks. Can also be used as a winder to store line when not in use. Sold only in pairs. No. Size 4" to 6" BL343 6" to 8" BL342 BL341 8" to 12"

Adjustable Line Stretchers

These aluminum line stretchers work on various size blocks





Aluminum Bricklayer's Corner

These aluminum corner blocks grip the wall tightly and will not break. Line wraps around stem, feeds through slot at the fork, then brick and groove on face of block. The line pull holds block at right angles to the brick. 2-3/4" stem lets you easily move the line up. Sold only in pairs.

No. BL253

Tenite Line Blocks

Blocks grip the wall tightly and will not split or break. Made of hard tenite (plastic). Sold only in pairs.

Size No.

BL348 4-1/4" Bagged (Pairs) 4-1/4" Bulk (Pairs) BL349

Bricklayer's Line Pins



Made of tempered steel; stiff and long enough to hold the line. Each pin measures 4-1/2" long.

No. Quantity **Imprint** Kraft Tool Co.® **BL158** BL159 200 "Build With Masonry"



Mason's Wood Line Blocks

Size: 4"x1-1/8"

· Made of hard wood · Grips the wall tightly

No. SLLB2

Snap-Over Line Twigs / Trigs



Manufactured from spring steel. They snap around the mason's line and eliminate sagging. Package of (14).

No. Size BL156 4"x5/8"

Front to Left or right

U.S. Patent #5,125,162

Over Sized Line Block

Designed for use on bull nosed block. Can also be used on other types of block and





Wood Line Blocks

Size 4"x1-1/4" Bulk (pairs) BL350



Brick Clips and Block Clips

This patented design on brick and block alignment clips are the quickest for setup and most portable line guides ever developed. The front of the clip has an irregular toothed surface and a thumb screw in the rear helps secure the clip.

Description No. BL250 4" Brick Clips (Pair) BL251 2" Block Clips (Pair)

PLASTER **FLOATS**




Molded Rubber Floats

- Molded black sponge rubber
- Very dense texture
- Comes with comfortable wood handle

No. Size PL395 8"x4"x5/8" PL398 10"x4"x5/8"

Add "P" to part number for Plastic Handle



Green Texture Floats

- Special coarse green foam
- Does an excellent job on any sand surface
- Comes with comfortable wood handle

No. Size PL602 10"x4"x3/4"

PL601 12"x4"x3/4"

12"x5"x3/4" **NEW** PL607

PL603 12"x5"x1"

Green Replacement Pads

10"x4"x3/4" PL702 12"x4"x3/4" PL703

12"x5"x3/4" **NEW** PL707

PL701 12"x5"x1"



"Sandsucker" Float

- · Perfect for exterior sand finishing
- Pulls the sand right out of the mud
- Pad is made of thick textured red sponge rubber mounted on a metal reinforced flexible rubber back
- · Comes with comfortable wood handle

No. Size 10"x4"x3/4" PL350

Add "P" to part number for Plastic Handle



Coarse Cell Rubber Floats

- Rubber float pad is securely cemented to flat aluminum back
- Comes with comfortable wood handle

No. PL374

Size 8"x4"x5/8" 10"x4"x3/4" PL382

Add "P" to part number for Plastic Handle



Fine Cell Rubber Floats

- Rubber pad securely cemented to flat aluminum back
- · Comes with comfortable wood handle

No.

Size 8"x4"x5/8" PL371 10"x4"x3/4" PL372

Add "P" to part number for Plastic Handle

Red Rubber **Floats**

- Sponge rubber securely cemented to flat aluminum back
- · Comes with comfortable wood float handle

No. Size PL373 Fine

8"x5"x1" PL383 Coarse 8"x5"x1"

Add "P" to part number for Plastic Handle



Lightweight Rubber Float

- Sponge rubber of correct density, lightweight red float that covers more surfaces
- Comes with comfortable wood handle

No. Size

PL384 12"x4"x1/2" Add "P" to part number for Plastic Handle

Plasterer's Rubber Sponge

- Pure sponge rubber
- Oval shaped to fit hand
- One of the finest sponges made

No. Size

PL069 6-3/4"x4"x1-3/4"





Replacement Float Handles

Your choice of wood or plastic handle.

Description No.

CF263 7-1/4" Wood Float Handle CF263P 7-1/4" Plastic Float Handle

Float Pads

Replacement pads available for all floats.

Contact Cement

PL379 Replacement Pad Adhesive (1 pint)



Super Poly-Foam Floats• White poly-foam that looks and wears

- like rubber
- Does not disintegrate like most foams
- · Comes with comfortable wood handle

No. Size PL606 10"x4"x3/4" 12"x4"x3/4" PL605

PL604

Add "P" to part number for Plastic Handle

12"x5"x1" Poly-Foam Replacement Pads

PL706 10"x4"x3/4" 12"x4"x3/4" PL705 PL704 12"x5"x1'



Jumbo Red Rubber Float • Popular on the West Coast and Arizona

- Sponge density is the most popular used
- No. Size PI 310

12"x5"x3/4"


Add "P" to part number for Plastic Handle



Go Devils

- Applies stucco and other materials fast
- · Available in lightweight aluminum or magnesium

-	No.	Size	Material
-	PL267	22"x8"	Magnesium
-	PL268	22"x10"	Magnesium
-	PL529	22"x8"	Aluminum
	PL530	22"x10"	Aluminum



Magnesium Hawks

30% Lighter than aluminum

Corners are rounded for safety, comfort and long service. Has 4" flange reinforcing the center. Comes with a special 1/2" thick sponge rubber hand protector. Blade is machine scored to control material.

	11	
Wood	ProForm ®	
No.	No.	Size
PL260	PL260PF	8"x8"
PL261	PL261PF	10"x10"
PL262	PL262PF	12"x12"
PL263	PL263PF	13"x13"
PL265	PL265PF	13-1/2"x13-1/2"
PL264	PL264PF	14"x14"
PL266	PL266PF	16"x16"
PL250	Replacemen	t Wood Handle
PL250PF	Replacemen	t ProForm® Handle

PL249 Replacement Callous Preventer **Scratcher**

Great for scratching plaster or stucco. Fitted with a smooth camel back wood handle. Features a 1/2" x 1/2" "V" notch.

Trowel

No.	Size
PL631	12"x5"
PL630	16"x5"

Mitre Rod

Knife edge is ideal for cutting cornices on plaster walls. Durable steel construction.

All rods	are 4"	wide.
No.	Size	
PL106	6"	
PL108	8"	
PL110	10"	
PL112	12"	
PL116	14"	
PL120	20"	
PL124	24"	

Flat Wire Texture Broom

Produces a uniform groove surface. Tine row is 11-1/8" long. Flatwire tines measure 3-5/8" in length on 1/2" spacing. Perfect for small jobs.

No. Size CC201



Aluminum Hawks

Heavy-Duty .080" Thickness

Heavy-duty aluminum hawk. Smooth straight edges with rounded corners. Detachable handle with threaded bolt and sponge rubber callous preventer. Blade is machine scored to control material.

Wood	<u>ProForm</u> ®	
No.	No.	Size
PL510	PL510PF	10"x10"
PL512	PL512PF	12"x12"
PL513	PL513PF	13"x13"
PL524	PL524PF	13-1/2"x13-1/2"
PL528	PL528PF	14"x14"
PL250	0 Replacement Wood Handle	
PL250PF	F Replacement ProForm® Handl	
PL249	Replacement Callous Prevent	

PLASTER HAWKS

Contractor Aluminum Hawks

- High strength, lightweight aluminum
- Blade thickness .060"
- Comes with wood handle and callous



No.	Size
SL518	8"x8" (203.2mm x 203.2mm)
SL517	9"x9" (228.6mm x 228.6mm)
SL522	10"x10" (254mm x 254mm)
SL519	12"x12" (304.8mm x 304.8mm)
SL520	13"x13" (330.2mm x 330.2mm)
SL521	13-1/2"x13-1/2"
	(342.9mm x 342.9mm)

PROFESSIONAL PLASTER TROWELS

View more Plaster Trowels on Pages 5, 9-10

Golden Stainless Steel

Trowels are made of heat treated golden stainless steel. This special alloy will not rust, pit or stain. A great, long-wearing tool with just the right balance.

Wood Handle ProForn			
No.	Size	No.	
PL452	10-1/2"x4-1/2"	PL452PF	
PL454	11"x4-1/2"	PL454PF	
PL455	11"x4-3/4"	PL455PF	
PL453	11-1/2"x4-1/2"	PL453PF	
PL457	11-1/2"x4-3/4"	PL457PF	
PL459	12"x5"	PL459PF	
PL460	13"x5"	PL460PF	



Swedish Stainless Steel

All Swedish stainless steel trowels are made of heat treated stainless steel. This special alloy will not rust, pit, or stain.

Wood H	ProForm [©]	
No.	Size	No.
PL525	10-1/2"x4-1/2"	PL525PF
PL551	11"x4-1/2"	PL551PF
PL556	11-1/2"x4-1/2"	PL556PF
PL547	11"x4-3/4"	PL547PF
PL548	11-1/2"x4-3/4"	PL548PF
PL568	12"x5"	PL568PF
PL570	13"x5"	PL570PF



Packed 3 per carton



Featheredge Makes it easy to scrape off mud while following a plastering machine.

Perfectly balanced for fingertip control. Width is 4-1/2".

1 01100119	Daianio	a for imgorup control. Water to 1
No.	Size	
PC004	4'	
PC005	5'	
PC006	6'	
PC007	7'	
PC008	8'	
PC010	10'	
PC012	12'	
N/I		V


Magnesium Slicker

Ideal for straightening and slicking ceilings. No water needed. Designed with an angle at the top for strength, rigidity and ease of operation. Weighs only 22 oz.

No. Size PL695

Wedge-Shape Darby Nedge shape magnesium darby is made of tempered magnesium alloy. It is the choice of

the trade. Gives fine smooth finish to plaster. Size PC036 36" PC042 42" 48" PC048



Lightweight magnesium darby with double knob handle.

Raised edge for strength. 1/2"x1/2" "V" notch.

No.

PL694 42" Magnesium Scratcher Darby

42" Mag Darby



Reinforced for strength and straightness

Lightweight magnesium darby. Long wearing sharp serrations. Special end wedges provide strong support. 15" long rib handle.

No.

PL413 42" Smooth Edge PL413D 42" Double Serrated **PL413S** 42" Single Serrated

End View

Reinforced for extra strength

and straightness

Packed 3

per carton

TRU-LITE™



Packed 3 per carton

Darby

Very popular and preferred by most plasterers. Lightweight magnesium darby is very strong. Has raised ridges on each side for extra strength. 15" long rib handle.

SMOOTH EDGE

No. Size PL400 42"x3-1/2" 48"x3-1/2" PL401

DOUBLE SERRATED EDGE No. Size PL402 42"x3-1/2"

48"x3-1/2" PI 403 SINGLE SERRATED EDGE

No. Size PL404 42"x3-1/2" PL405 48"x3-1/2"

Darby With Double Knob Handle

Lightweight magnesium darby is very strong. Has raised ridges on each side for extra strength.

SMOOTH EDGE Size

No. 42"x3-1/2" PL410

DOUBLE SERRATED EDGE Size No.

PL412 42"x3-1/2"

SINGLE SERRATED EDGE No. Size 42"x3-1/2" PL414

Ornamental Tools



The plasterer's delight! Forged and tempered.

No.		Size	Length
PL188*	Trowel & Square	3/8"	8-3/4"
PL189*	Trowel & Square	1/2"	9-1/2"
PL190*	Trowel & Square	5/8"	10-1/2"
PL191*	Trowel & Square	3/4"	10-1/2"
PL192*	Trowel & Square	1"	10-1/2"
PL193*	Leaf & Square	3/8"	8-1/2"
PL194*	Leaf & Square	1/2"	8-1/2"
PL195*	Leaf & Square	5/8"	9-1/4"
PL196*	Leaf & Square	3/4"	9-1/2"
PL197*	Leaf & Leaf	1/2"	8-1/2"



Shaping Tools

Forged and tempered ornamental tools for long life. 9" length.

Description No. PL186* Cut and Shape Tool PL187* Radius Shaping Tool

Packed 3 per carton



Darby with 24" Rib Handle

Lightweight magnesium darby is very strong. Fitted with 24" long wood handle. Has raised ridges on each side for extra strength. Design preferred by many plasterers.

SMOOTH EDGE No. Size

PL400-24 42"x3-1/2" PL401-24 48"x3-1/2" DOUBLE SERRATED EDGE No. Size

PL402-24 42"x3-1/2" PL403-24 48"x3-1/2"

SINGLE SERRATED EDGE No. Size PL404-24 42"x3-1/2" PL405-24 48"x3-1/2"

DOUBLE SINGLE **SMOOTH SERRATED** SERRATED **EDGE EDGE EDGE**



Stucco Dash Brush

Stucco dash brush has 8 rows x 4 rows on 5"x2-1/4" block.

No. Size

PL114 Bassine 4" Brown Bristles
PL115 Plastic 5-1/2" Yellow Bristles



Thin Coat Angle Trowel Made of flexible stainless steel. Has 90°

Made of flexible stainless steel. Has 90° angle. 4" wide blades are tapered back from 5" at center to 4-1/4" at outside edge. **No.** PL320



Blister Brush

Just the tool to easily apply water or pick water up off newly finished surfaces. Also handy for cement

finishing. Has removable hardwood handle with steel ferrule. Insert felt pads into a 1-1/4"x7-1/2" aluminum channel with sturdy 1/8" sidewalls. Comes with two 4"x8-7/8" felt pads.

No. Description
PL224 Blister Brush
PL225 Extra Pair Felt Pads



The very best angle floats are lightweight. This float has square side edges and tapered angles on both ends. Perfect for brown coating. 3/4" high side walls.

No.	Size	Material
PL061	9"x4"	Magnesium
PL063	10"x5"	Magnesium
PL065	9"x4"	Stainless Steel

Regular Dutch Brush

Used by plasterers, painters, stucco workers and cement finishers. Made of Tynex® nylon set in rubber.

No. Size

PL101 7"x1-5/8" (4-1/8" Bristle Length)



Jumbo Dutch Brush

Plaster, paint and wall brush. 2-1/4" wide for maximum material holding and coverage. Soft nylon bristles with stainless steel binding.

No. Size

PL103 7"x2-1/4" (4-1/8" Bristle Length)



Angle Plane

Use this handy tool instead of your

trowel blade to work down high spots, scrape walls and clean angles. It has 7 blue steel blades, 1-1/4" deep.

No. Size PL300 4"x10"



Trapezoid shape stainless steel finish trowels. Designed for finishing and polishing decorative plaster and stucco. Machined edge with smooth bright finish.

Camel Back Wood Handle

No. Size

PL627 8"x3" (203mmx76mm) (small) PL628 9-1/2"x3-1/2" (241mmx89mm) (med.)

ProForm® Handle

No. Size

PL627PF 8"x3" (203mmx76mm) (small)

PL628PF 9-1/2"x3-1/2" (241mmx89mm) (med.)



Universal wall, paint and plaster finish brush. Pure China bristles set in epoxy makes this brush ideal for plastering, painting, stucco and texturing projects. Smooth wood handle with rubber grip for comfort.

No.	Block Size	Bristle
PL130*	5-3/4"x1-3/4"	3-1/4"
	(146mmx44mm)	
PL131*	5-3/4"x2-1/4"	3-1/4"
	(146mmx57mm)	
PL132*	6-1/2"x2-1/2"	3-1/2"
	(165mmx64mm)	



Plasterer's Scarifier

Used to easily scratch undercoats so finish coat will bond and not separate. Has light, flexible steel tines, all welded construction. Available with a steel handle or comfortable ProForm® handle. End of ProForm® handle accepts broom threaded handles (sold separately, see page 68).

ProForm®	Wood	
Handle	Handle	
No.	No.	Size
PL206PF	PL206	6"
PL208PF	PL208	8"
PL212PF	PL212	12"
PL214PF	PL214	14"
PL216PF	PL216	16"



Stainless Steel Outside Corner Trowels - 90°

Great for detailing outside corners for EIFS, stucco and plaster. Leaves a clean, smooth corner, Trowels have 90 degree angle.

No.	Size	No.	Size
PL590PF	3-1/8"x1/2"	PL593PF	4"x1-1/2"
PL591PF	3-1/8"x3/4"	PL594PF	4"x2"
PL592PF	3-1/8"x1"		

Stainless Steel Inside Corner Trowels - 90°

Great for detailing inside corners for EIFS, stucco and plaster. Leaves a clean, smooth corner. Trowels have 90 degree angle

= care a cream, critectin comment mane co degree angle.			
No.	Size	No.	Size
PL580PF	3-1/8"x1/2"	PL583PF	4"x1-1/2"
PL581PF	3-1/8"x3/4"	PL584PF	4"x2"
PL582PF	3-1/8"x1"		

Stainless Steel Rounded Detail and Pointing Detail Trowels

100% Stainless Steel Blade

Great for detailing plaster and EIFS. No. Size Description PL585PF 6" Rounded Detail PI 586PF 6" Pointing Detail

Rounded Detail Pointing

Detail

Miter Snips

Accurately cuts angles in seconds up to 1" wide x 1/2" thick (replaceable blade). Cuts plastic, decorative moldings and tile edges/trim. Adjustable miter fence with built in protractor. 7 preset angles from 45°-135°. Safety lock handle with no slip grip. To easily change angle, slide the self-indexing metal guide to desired angle.

Description No. LA355* Miter Snips

LA355-01* Top Cutting Replacement Blade

US Patent #6.973.725 B2

Stainless Steel Outside Corner Tool

Stainless steel, each side measures 3-1/2"x2-1/2"

No.	Radiu
PL011	1/8"
PL013	1/4"
PL015	3/8"
PL017	1/2"
PL019	90°
PL021	3/4"



Grips nail tightly. Lets you work in tight places. 12-1/2" handle. Weighs 25 oz.

No.

PL258SG Soft Grip Handle

Magnetic Nail Drivers

Stainless steel nail driver, Grips nails tightly. Lets you reach really tight spots. Has 5/8" hexagonal shank, giving you a good grip.

No. Description

PL252 5-1/2" long, 3/4" diam. nose 8" long, 9/16" diam. nose PL256

Multi-Master

Extra long 3" blades for easier faster cutting. Compound action cutting system cuts twice as long as standard snips.

Cuts up to #20 gauge steel.

No. LA375



Drop forged. Offset blades keep hands clear of metal. Blades individually hand edged for maximum cutting. Rust resistant blades.



Sheet Metal Cutting Shears

A favorite with sheet metal, lath and tile professionals. Cuts sheet metal, tile, asphalt, wire, plastic, shingling, carpets. Forged snips are contoured for easier cutting, less fatigue.

No. Size LA292* 12"



Perfect for metal lath work. Double action. Plastic color coded grips for safety/comfort.

No.

LA205 Left Cutting (Red) LA207 Right Cutting (Green)

Straight and Combination (Yellow) LA350



Comfortable, lightweight tool cuts up to #22 gauge steel and stainless steel up to #26 gauge. Great for vinyl, aluminum siding, vinyl flooring, and roofing materials.

No. Size LA377* 12"

End Cut Nippers

Comfortably cut wire all day long with these steel lather's nippers. 8" and 9" nippers have plastic handle grips.

No. Size LA407* LA408* 8" LA409*



EIFS Sanding Rasps



These giant sanding rasps have very coarse #12 grit sandpaper faces for use on EIFS wall finish systems. Sandpaper glued to face of aluminum back. Comes with wood float handle for comfortable grip.

No.	Size
PL514	8"x14" Rasp
PL520	6"x14" Rasp
PL515	4"x14" Rasp
PL516	2"x14" Rasp
PL517	8"x14" Replacement Adhesive Sheet
PL521	6"x14" Replacement Adhesive Sheet
PL518	4"x14" Replacement Adhesive Sheet
PL519	2"x14" Replacement Adhesive Sheet
PL379	Contact Cement (One Pint)
	for Sandpaper Replacement



EIFS Corner Tools

Stainless steel blade with rust-resistant tang and hardwood handle. Ideal tool for finishing corners, grooves, inset/offset trim lines, around doors and windows.

No.	Size
PL504	3"x1" Outside
PL505	3"x1" Inside
PL506	3"x1-1/2" Outside
PL507	3"x1-1/2" Inside
PL508	3"x2" Outside
PL509	3"x2" Inside
	<u> </u>

Bucket Trowel

Stainless steel tapered blade allows user to eliminate wasted material left in bucket. Comes with wood handle and special tang to hang on side of bucket.

No. Size


*See page 145

PL800* 7"x4-1/2"x3"

EIFS NOTCH TROWELS 12"x5"

Stainless Steel **Notched Trowels**

Stainless steel notched trowels allow accurate application of EIFS materials. Comes with camel back wood handle for comfort.





PL626 3/16"x3/8"x1-7/8"



Plastic Corner Tools

Durable plastic tools for inside and outside corners. Choice of 1/2" or 3/4" radius. Great tool for pool, plaster or stucco jobs. No worry of carbon marks. Size: 3"x1-3/4".

No.	Size
PL010	1/2" Radius InsideTool
PL012	1/2" Radius Outside Tool
PL014	3/4" Radius Inside Tool
PL016	3/4" Radius Outside Tool



Made of 4" long white tampico. Great for tool clean up and many other uses. Hang device allows brush to be stored on bucket away from material. 7" Plastic handle.

No. Size

6-1/2"x1-3/4" (Block) BL527



EIFS Tools


Smooth non-marking ABS blade with comfortable handle grip. Ideal for specialty coating and materials.

Please Note: Drawings at left

represent only shape of the notches. See measurements for exact sizes.

Size No. PL799* 11"x5"

Exterior Finishing Trowel



No. PL801* 11"x5-1/2"



Bucket Scoop

Galvanized steel scoop; great for loading trowels and transferring mortar, plaster or stucco material. Comes with wood handle and bucket hanger. Inside of scoop is tapered from 7" to 3-1/2".

No. PL804*



Lid Claw

Remove lids from plastic buckets quickly and easily. Made of strong durable plastic.

No. Size DW110 8" Length

Texture Rollers

Now in just minutes you can create a unique finish on walls and ceilings. Simply roll this texture roller over fresh textured surfaces to provide a beautiful uniform pattern. Hides blemishes and defects in old walls.

Fits standard 9" paint roller.

No.	Description
DW180	Crowsfoot

DW180R Crowsfoot with Roller Frame

DW181 Basket Weave

DW181R Basket Weave with Roller Frame

DW182 Monterrey

Monterrey with Roller Frame DW182R

DW183 Poinsettia

Poinsettia with Roller Frame DW183R

DW184 Tree Bark

DW184R Tree Bark with Roller Frame

DW185 Vine

DW185R Vine with Roller Frame

DW186 Palm Leaf

DW186R Palm Leaf with Roller Frame

Comes with or without roller frame


Outstanding decorations for walls

 Economically applied and simple to use



Poinsettia

Tree Bark











Palm Leaf

Roller **Frame** Only

Poinsettia

(Actual photo)

9" roller frame with soft style handle, threaded end for extension handle.

No. DW179*

Roller Tray

18" Plastic No. DW189



Lexan® Knock Down Knife

Clear, durable and flexible. Used for drywall, EIFS and acoustical jobs. Threaded end plastic handle can be used with extension handle for longer reach. Packaged 6 per carton.

No. Size DW193 18"x12" DW194 24"x12"



Handy and efficient tool for acoustic repairs, remodeling and patching. Great for spot retouching.

No. DC196* DC196-01*

Description Patch Gun Replacement Rotary

Wheel

DC196-02* Replacement Lid



Spray Shield

High impact super-flexible plastic, lightweight easy to clean. Keeps paint off window frames and floors. Ideal to control spray for acoustical ceilings. Threaded end plastic handle.


No. Size DC192 12"x36"



Glitter Gun

Plastic glitter gun used to apply glitter to ceilings and walls. Easily operated by turning handle to apply a steady flow of glitter to surface.

No. DC615*




Glitter Gives sparkling

effect to ceiling. Covers about 500 sq. ft. per pound. Glitter is applied by blowing on with glitter gun to wet surface of texture. Fade

and tarnish resistant. Not recommended for outside use. 1/16" cut silver and gold glitter.

No.	Description
DC452	A) 1 lb. Silver glitter
DC492	B) 1 lb. Gold glitter
DC456	C) 1 lb. Glaschip#20 size
DC462	D) 1 lb. Multi glitter
DC472	E) 1 lb. Iris glitter



Apply joint compound or drywall mud. Sturdy handle for easy reach. Comes with replaceable lambs wool cover and threaded end plastic handle.

No.	Desription
DC265	6" w/ 19" handle corner roller
DC266	6" lamb's wool cover replacement
DC267	4" w/ 14" handle corner roller
DC268	4" lamb's wool cover replacement

GUNS, HOPPERS & TEXTURE COMPRESSORS

PC501

Standard Texture Gun & Hopper

Ideal for spraying walls, ceilings, fireproofing and stucco

PC501 Standard Texture Gun & Hopper

- Texture guns made of cast aluminum for long wear
- Top hopper handle for control of hopper
- Hopper angle great for walls and ceilings
- Sprays a variety of textures

PC506 PC507

Gun ONLY Repair Kit for Standard Gun



Standard Texture Gun & **Hopper with Compressor** (Complete Unit)

Flexible

neck for

variable



PC301

Super-Pro® Texture Gun & Hopper

Sprays a variety of textures and materials

PC301 Super-Pro® Texture Gun & Hopper

- Large 2.5 gal hopper with built in control handle, 40 degree hopper angle for easy spraying
- Easy pull full grip bronze trigger for less fatigue
- · Special orifice adjusting nut makes orifice selection quick and easy
- Patented Super-Pro® gun cylinder and shut off valve



PC401

EZY Deck Pro Gun & Hopper

Sprays overlay and decking material

PC401 EZY Deck Pro Gun & Hopper

- Built-in downward hopper angle ideal for decks and floors with flexible neck
- positions Control hopper with built-in finger tip
 - Full grip trigger for ease and comfort
 - · Remove nozzle and tip for quick and easy cleaning

PC406 Gun ONLY PC407 Nozzle Repair Kit PC409 Flexible Neck ONLY

PC400

EZY Deck Pro Gun & Hopper with Compressor (Complete Unit)



PC201

ProForm® Texture Gun & Hopper

Sprays a variety of textures and materials

PC201 ProForm® Texture Gun & Hopper

- · Built-in hopper angle easily lets user direct spray for walls and ceilings
- · Built-in easy grip hopper handle
- Full grip trigger for ease and comfort
- Remove nozzle and tip for quick and easy cleaning

PC406 Gun ONLY PC407 Nozzle Repair Kit

PC200

ProForm® Texture Gun & **Hopper with Compressor** (Complete Unit)



Ideal for Spraying

Walls & Ceilings, Fire Proofing, Stucco, Decking, Waterproofing

- Unit is equipped with a 1 H.P. capacitor-start electric motor with manual re-set thermal overload protector
- Rotary vane compressor delivers 6.2 C.F.M. free air at 25 P.S.I.
- Two-wheel cart is 19" wide, 34" high and measures 15" front to back
- Heavy-Duty 200 P.S.I hose, resists kinking
- The 8"x1.75" wheel and tire have a load rating of 100 lbs. each. Shipping weight is 103 lbs



EZ-GRIP Mud Pan

Stainless Steel

Mud pans have tapered ends and sides. Sides are sheared to clean knife easily. Pan resists rust and is easy to clean.



EZ-Grip Mud Pans feature a non-slip textured surface which provides the professional finisher with a more secure grip with less hand fatique.



Heli-Arc Stainless Steel

These heli-arc welded mud pans have tapered ends and sides. Pan resists rust and is easy to clean. Sides are sheared to clean knife easily. Measures 3-1/4" deep.

Weasures 3-1/4		
No.	Size	
DW710	10"x3"	
DW712	12"x3"	
DW714	14"x3"	
DW718	18"x3"	



These heavy-duty plastic mud pans have tapered ends and sides with one replaceable steel wiping blade. Resists chemicals and will not break if dropped.

No.	Size
DW210	10"x3"x3" deep
DW212	12"x3"x3-1/4" deep
DW214	14"x3"x3-1/4" deep

Plastic Double Bladed Mud Pan

12" double bladed plastic is more pliable than our standard mud pan. Designed so you can wipe your knife clean on both sides.

Sturdy, 22" blue steel blade scrapes excess mud from walls and ceilings.

Easy-to-change replacement blade

and 48" replaceable wood handle is

22" Replacement Blade

48" Replacement Handle

Description

Wallscraper

No. Size

available

DC386

DC388

DC318

No.

DW312 12"x3"x3-1/4" deep

Wallscraper



Smooth tapered ends with contoured corners. Sides sheared to clean knife easily. Natural contour for comfortable, non-slip grip.

No. Size

Rounded Edge

DW723 10"x3"x3" deep DW725 12"x3"x3-1/4" deep DW726 14"x3"x3-1/4" deep



Drywall Mud Holder

Stainless steel mud holder is designed mainly for plaster or drywall work. Comfortable detachable handle fastens securely to blade. Comes with sponge rubber callous preventer.

No. Size

DW460 12"x6" with 1-1/2" Lip



n Holder Mud Mashers

Has 5" square head; durable wood handle. 25" inches tall.
Made of heavy steel wire. Mixes small batches quickly and easily
No. DW103*





Mud Pan Holder

This lightweight mud pan holder leaves your hands free to work. All aluminum, hooks to your belt to hold your mud pan where you can easily get at it. Has a hook below the pan to hold a roll of tape.

No. DW207



not included

Jiffler Mixers

- Unique wheel design evenly mixes drywall mud, pigment and other materials
- Dispersal wheels engineered to evenly mix materials and eliminate lumps
- Zinc-plated steel wheels will stand up to a long life of use
- Adjustable wheels adapt to many different containers and materials
- Flats on shaft prevent slipping in drill chuck on large size mixers
- Removable wheels make clean up easy



2-1/2" Wheels attach to a 1/4"x11" shaft. Great for small containers and thinner materials such as paint and powdered materials. Use with a 1/4" drill

Chuck Shaft

with 3-Sided Non-Slip

or larger. No. DC342

3-1/2" Wheels adjust along the 3/8"x16" shaft. Use a minimum 450 rpm power depending on the amount and thickness of material. Use with 1/4" drill or larger.

No. DC343

5" Wheels attach to the 3/8"x24" shaft for use with a 1/2" drill. Easily mixes drywall mud, thin set mortar, grout and other powdered materials.

No. DC310

6-1/2" Wheels adjust these large wheels on the 1/2"x24" shaft to mix larger containers of material. Blend a two-sack batch in one minute. Perfect for use with a 12" to 16" diameter container. Use with 1/2" drill mixer.

No. DC312



(3) adjustable wheels with 3-Sided Non-Slip Chuck Shaft

Three 5" mixing wheels can be adjusted on the 3/8"x24" shaft for use with a 1/2" drill mixer. Design thoroughly mixes components for smoothness. Mix 5 gallons of drywall mud in less than 2 minutes with this mixer.

No. DC311




DRYWALL MUD MIXERS

Junior Mud Mixer

Mud mixer has a cast aluminum paddle 8-1/2"x5" deep. 7/16" steel shaft works in slow speed 1/2" drill. Rounded end design for better balance when mixing. Ideal for mixing drywall mud and texture materials.

No.	Size
DC713	7/16" diam. x 30" shaft
DC714	7/16" diam. x 36" shaft

DC714I 7/16" diam. x 46" shaft **NEW**



Mixers fitted with

7/16" steel

Hexagon Shaft

Fast-Mixers

Heavy-duty mixer is ideal for mixing drywall mud, acoustic or blending paint. Mixer has an aluminum paddle 8-1/2"x4" deep. 7/16" diam. steel shaft fits any 1/2" or larger slow-speed drill.

No. Size

DC307 7/16" diameter, 28" shaft DC308 7/16" diameter, 36" shaft

Spiffy Mixers

Double or triple 5" diam. fan blade mixer, zincplated adjustable or welded blades. Ideal for small pigment mixes and other materials. Non-slip 3/8" steel hexagon shaft for durability. Fits 1/2" slow speed drill.

No.

DC302 2-wheel, 24" adjustable shaft DC303 3-wheel, 24" adjustable shaft DC304 2-wheel, 24" shaft welded DC305 3-wheel, 24" shaft welded

Unomixers

Ideal for fast mixing of all kinds of materials, from paint to cement. For use in a 1/2" drill.

No. Size

DC362* 2-1/2" diameter, 16" shaft DC363* 3-1/4" diameter, 16" shaft DC365* 4-3/4" diameter, 30" shaft DC367* 5-1/2" diameter, 30" shaft

Round Shaft

Deluxe Mud Mixer

Mixes all kinds of drywall mud and texture materials fast and completely. Works in 5 to 55 gallon drums. Mixer works in slow speed 1/2" or larger drill. Paddle head is 9-5/8" wide, and 6-1/4" deep.

No. Size DC715

7/16" diameter 30" hexagon shaft



7/16" steel hex shaft. 30" overall length. Plated solid steel. For use in a 1/2" drill or larger. Use to mix thin set, grout and concrete products. Easy to use, easy to clean. No. DC716*

Stainless Steel Jiffy Mud and Paint Mixers

Fits containers 3 gallons or larger. 21" long, 1/2" shaft, top diameter 4-1/2", bottom diameter 5" depth 5"

No. DC409



For small containers, 2 gallons or less. 10-1/2" long, 1/4" shaft, top diameter 2-3/8", bottom diameter 2-5/8", head depth 2-1/2". No. DC408





Deluxe Taping

Knives

Features soft grip ProForm® handle. Each taping knife has a lightweight aluminum mounting. The blade is balanced and flexible for just the right feel. Choose a blue steel blade for additional flexibility.

 Blue Steel
 Size

 No.
 8"x3"

 DW808PF
 8"x3"

 DW810PF
 10"x3"

 DW812PF
 12"x3"

 Stainless Steel

 No.
 Size

 DW808PFSS
 8"x3"

 DW810PFSS
 10"x3"

 DW812PFSS
 12"x3"

Standard Flexible Taping Knives *Blue Steel or Stainless Steel*

Choice of Blue Steel or Stainless Steel blade is securely attached to a durable blue plastic handle which has been carefully shaped for comfort. This knife is balanced for effortless taping and finishing.

Blue Steel	Stainless Steel		
No.	Size	No.	Size
DW548	8"x3"	DW548SS	8"x3"
DW550	10"x3"	DW550SS	10"x3"
DW552	12"x3"	DW552SS	12"x3"

Rosewood Handle Wall Scraper

Tough, flexible scraper is great for multiple applications in drywall, painting and other surface preparations. Stainless steel, broken-in blade with rosewood handle.

No. Blade Width DW437* 4"

Blue Steel or Stainless Steel

Wide flexible blue spring steel or stainless steel blade in lightweight rustproof aluminum mounting.

Blue Steel

ProForm®	Handle
No.	Size
DWOUGDE	6">3"

DW906PF 6"x3" DW908PF 8"x3" DW910PF 10"x3" DW912PF 12"x3" DW914PF 14"x3"

Stainless Steel ProForm® Handle

No. Siz

DW906PFSS 6"x3"
DW908PFSS 8"x3"
DW910PFSS 10"x3"
DW912PFSS 12"x3"
DW914PFSS 14"x3"

Long Handle Taping Knives

Ine
16" long
wood
handle
makes these
knives popular on
the job. Blade is made
of flexible blue spring steel.

No. Size
DW628 18"x4"
DW630 20"x4"
DW634 24"x4"

Professional Hammer End Joint/Taping Knives



Flexible blade is ground and polished for a professional finish. Comfortable handle with convenient metal hammer end.

With Convenient motal name			
No.	Blade Width		
DW527*	1-1/2"		
DW528*	2"		
DW529*	4"		
DW530*	5"		
DW533*	6"		



A) Aluminum 6' button handle (CC336) attached to broad knife for extra long reach. **No.**

DW283 9" Broad Knife with 6' Button Handle

B) Choice of 7" or 9" wide spring steel blade with rounded corners attached to an aluminum handle. Over all length 17-1/2". Reinforced where the blade attaches to handle. Easy to change replaceable blade.

No. Size

DW281 7" Broad Knife

DW281-01 7" Replacement Blade

DW277 7" Broad Knife with 28" Handle

DW282 9" Broad Knife DW282-01 9" Replacement Blade

Flexible Non Rust Stainless Steel Putty and Drywall Knives A Finisher's Favorite!

Non-rust stainless steel blade and handle, one-piece construction for strength and longevity. These knives come in 6 sizes and are ideal for scraping, painting and drywall applications. Contoured handle is comfortable and easy to grip also available with a soft grip.

Stainless Steel Handle

No	Blad	e Width
DW727*	1-1/2	2"
DW728*	2"	
DW729*	4"	
DW730*	5"	
DW733*	6"	
DW736*	10"	NEW
Sure Grip	Handle	,

No **Blade Width** DW727PF 1-1/2" DW728PF* DW729PF* DW730PF* 5" DW733PF* 6"

10" NEW DW736PF*

Add "L" after part number for a more flexible limber blade. Available only on 4", 5", 6" and 10" knives. **NEW**





Rosewood Handle Joint Knives

Flexible putty and drywall knives. Carbon steel with mirror polished blade. Rosewood handle fitted with metal hammer end for setting nails.

No.	Blade Width
DW427*	1-1/2"
DW428*	2"
DW429*	4"
DW430*	5"
DW433*	6"



Bucket Scoop

Scoops drywall mud, stucco and other similar material. Stainless steel blade with non-slip ProForm® handle. Curved radius blade sized to fit bucket for easy removal of material.

No. DC421



Drywall Trowels

This trowel has a curved, high carbon or stainless steel blade for finishing drywall joints. A lightweight, flexible tool with perfect balance.

Wood Handle		ProForm® Handle
No.	Size	No.
DW521	12"x4-1/2"	DW521PF
DW541	14"x4-1/2"	DW541PF
DW516	16"x4-1/2"	DW516PF



K.C. Taper

K.C. taper is made exactly like the Kraft drywall taper, except without the top handle making it more compact.

Description No. DC402 Right Hand



Drywall Taper

Taper is made of lightweight aluminum with separate mud and tape compartments. Holds up to 500' roll of tape. Easy to adjust mud metering blade. Comes with wood and nvlon strap handles.

No. HC540*

DRYWALL



Kraft Drywall Taper

Aluminum construction won't rust and is easy to clean up. Features large mud capacity and holds all 500' rolls of tape. Adjustable slide/blade moves to regulate mud and cuts tape quickly and accurately.

No. Description DC401 Right Hand DC401L Left Hand

View more Hi-Craft™

Drywall Tools on 63



A) Standard **Wide Handle Taping Knives**

Blue Steel or Stainless Steel

Strong lightweight handle. Fitted with a flexible lightweight blue steel blade and balanced for effortless taping and finishing.

No. Size DW648 8"x3" DW650 10"x3" 12"x3" DW652

Add "SS" to part no. for Stainless Steel

B) Standard Strong Handle Taping Knives

Blue Steel or Stainless Steel

Reinforced high strength yellow plastic handle. Fitted with a flexible lightweight blue steel blade. Well balanced

and easy to use.

No. Size DW008 8"x3" DW010 10"x3" DW012 12"x3'

Outside

Inside

Bullnose Corner Tools

Bullnose corner tools

are made of lightweight flexible stainless steel. Blade angles flex to 90 degrees when used. Blades are 5" long with 2-1/2" sidewalls. Fitted with smooth wood handle.

No.

DW451 (Outside) DW450 (Inside)




Flexible 2"x3" stainless steel blade. Will not rust or pit. Overall length 13". Great for finishing around windows and hard-to-reach areas.

No. Size DW519 2"x3'



Adjustable Wipe Down Knife

Two knives in one. A flexible rubber taping and wipe down knife for inside 90 degree angles. Then loosen the wing nut and turn the pad around, for angles over 90 degrees. No. DW453





Just loosen nut and rotate for less than 90 degrees or...over 90 degree angles



Round It Tool

Flexes for just the right angle!

With just a push of the thumb you can adjust the angles as you go for smooth professional outside

angles and round corners.


No. Size

6-1/2"x4-1/2" diameter





Flexible rubber knife for taping and cleaning excess mud from inside angles. Ideal for splay and angles that are wider than 90 degrees. Lightweight and easy to clean. Can be used by hand or with any 1" diameter pole. No. DW438





Outside Corner Tool

Made of stainless steel. Will not rust or pit. 80 degree angle flexes to 90 degree when used. 5" long at center and tapers to 4-1/4" at outside edge.

Size **Blade Depth** No. DW619 2-1/2" 4"x5" 4"x5" DW621



Corner tool blade is formed from flexible stainless steel. Its 103 degree angle flexes to 90 degree for perfect corners. This is a lightweight, perfectly balanced tool.

No. Size DW520 4"x5"





Compound leverage permits ease of punch through two layers of 22 gauge metal. Made of forged and hardened steel. Nickel plated to resist corrosion.

No. DC273*



Clinch-On Tool

Clinch-On tool is operated by a spring loaded arm. A sharp blow from a rubber mallet (sold separately) drives the cornerbead on tight, centers it and clinches it in position without nails or screws.

NO.	Size
DC806	1-1/8" Bead (less Mallet)
DC807	1-1/4" Bead (less Mallet)
DC808	Repair Kit
DC809*	Black Rubber Mallet 32 oz.
FC551*	White Rubber Mallet 22 oz.

Circle Cutter

8-1/2" long calibrated steel shaft enables sharp, clean cuts up to 16" in diameter. Hardened steel cutting blade and center point remain sharp. Chrome plated for long wear.

No. DW241*



Stud Crimping Tool

A specially designed tool for setting light gauge metal studs and track, furr downs, door and window headers. Use on .025 gauge or lighter galvanized metal. Secures metal to metal. Weighs only 14 oz.; 10" long.

Description GG163 Stud Crimping Tool GG163-01 1/4" Replacement Crimper GG163-02 1/4" Replacement Bushing

1/8" Rivet Hole Punch

Designed specifically for acoustical grid systems. Cuts perfect 1/8" holes for painted or aluminum rivets. Reduces installation time up to 30%. High strength alloy weighs only 14 oz.; 10" long.

Description No. GG159 Punch

GG159-01 1/8" Replacement Punch GG159-02 1/8" Replacement Bushing

Combination Tool

Five heavy-duty tools in one: scraper, seam opener, spreader, putty remover, cutout removes paint from rollers. Wood handle with brass rivets.

Size No. DW027 2-1/4"

Flexible Putty Knives

Industrial quality stainless steel flexible blades. Wood handles with brass rivets.

No. Size DW015 1-1/2" DW002

DW015

DW002

Heavy "Chisel" Scraper

Extra thick (.095) stainless steel, single bevel blade with brass riveted wood handle.

No. Size DW025 1-1/2"



Stiff Scrapers

Wood handle, stainless steel 3" wide, stiff blade scraper of the best quality. Double bevel on standard and long handle models. Single bevel on bent model.

No. Type DW033 Standard DW034 Long Handle DW035 Bent Blade



Crows Foot Texture Brush

Brush is made with white tampico fiber set in hardwood block 1-3/8"x6-3/8". Threaded

handle hole in center. Single brush measures 8-1/2" wide, 13-1/2" long when flattened.

No. Description DW118 Single Brush DW118D Double Brush


Drywall Texture Brush

The perfect brush for texturing. Use it in your hand or with a threaded handle (sold separately, see page 68). Comes in two sizes and also available as a double brush unit. These brushes are made of horsehair and fiber bristles and are available in 2 sizes.

Description No.

DW116 2-1/2" long bristles, 6" diameter DW117 3-1/2" long bristles, 9" diameter





Drywall Patch

The ideal way to repair holes or surface damage. Self-adhesive drywall patch is permanent and made from rustproof aluminum. Easy to cut to any size or shape. Apply over damaged area, cover with a finishing compound, sand and paint...it's that simple.

No. **Description** DC418 4"x4"/50 Pack DC419 6"x6"/50 Pack 8"x8"/25 Pack DC420



Lightweight aluminum back. Available with wood or plastic handle. Clamps lock sandpaper tight to base. Sander face is 9-1/2"x3-1/4".

No. Description

DW442 Wood Handle (not shown) DW442P Black Plastic Handle

Drywall Tape Holder

An excellent tool for the drywall finisher. Made of steel for longer life. Holds all standard size drywall tape as well as our metal corner tape. Hangs from belt for easy access. Pull wire for easy refilling. No. DW224

Metal **Corner Tape**

Rolled corner bead fits any corner. Work on outside or inside corners. Applies easily with joint cement.

No. **Description** DC701

100'x2-1/16" Rolls (Carton of 10)



Kraft pole sander makes it easy to reach hard-to-get places high on walls and ceilings. Pole sander base is made of lightweight sturdy aluminum; with a bonded 9-3/8"x3-1/4" rubber pad and two positive lock clamps. Swivel head permits sanding anywhere. Comes with 48" wood handle.

Description No.

DC317 Sander with Wood Handle DC318 48" Replacement Wood Handle

DC317ASM Sander with Wood Handle Assembled (pk 6 only)

Extension Handle

Made of lightweight aluminum. Extends from 4'8" to 8' for sanding ceilings and high walls.

DC319

Handle Adapter

Female fitting for pole sanders.

No. DC349



Professional Cast Aluminum Drywall Hand Sander

Cast aluminum lightweight base with foam pad and screw clamps keeps sandpaper tight to sander base. High lift wood handle designed for knuckle clearance and balance. Also available with black plastic handle. Sander face is 9-1/2"x3-1/4".

No. **Description** DW441 Wood Handle

DW441P Plastic Handle (not shown)



Ideal for sanding down drywall joint mud or drywall board. Sheet size 11"x4-3/16".

No.	Grit	Pkg./Sheets
DC080	80	100
DC100	100	100
DC083	120	100
DC084	150	100
DC082	80	10
DC102	100	10
DC103	120	10
DC104	150	10

Utility Knife Replacement Blades with Dispensers

Blades come with convenient plastic dispenser. Fits most standard knives. Steel blade with 2 notches on top (.025" thickness). 100 Pack has hang holes for easy storage.

Description

DW078* 10 Pack Dispenser (carded) DW079* 100 Pack Dispenser (carded)





Change Blade Utility Knife

An adjustable blade on a non-slip comfort handle features storage for extra blades.



This open weave silicon carbide sanding cloth practically cleans itself. It lasts longer,

cuts joint mud faster than regular sandpaper

Pkg/Sheets.

50

50

10

10

and will not easily clog.

Grit

120

220

120

220

No.

DC120

DC220

DC122

DC222

Easy

No. DW040*



Drywall T-Squares Our 48" 4-rivet construction T-Square with black easy-to-read markings will outwear all others. Has stud locator markings, a notched head and is reverse ruled to read from either edge. Blade width 2". No. DW221 Packed (2)

Color **Thickness** Silver Anodized 1/8" 1/8" (metric) DW221M Silver Anodized DW222 Silver Anodized 3/16" DW225 Bright Yellow Painted 3/16"



Professional Drywall Square with Lip

Bright, clear anodized aluminum. Easy to read black numbers and graduations. Perfect for jobs where a smaller tool is needed. Lip catches board for easy placement and cutting of drywall board or sheet material.

No. **Description**

16"x24" with Lip (406.4mm x 609.6mm) SL694



Packed (4) per carton



Drywall Hammers

Heavy-Duty

per carton

Chrome checkered face makes nailing easy, prevents breaking the surface of wallboard. Checkered head is securely attached to a wood handle for a perfect balance.

No.

DW254 18 oz. Head / 14" Handle DW264 18 oz. Head / 16" Handle

Lightweight

Beautifully balanced chrome head has a crowned face to make nailing easy. Lightweight durable checkered head is attached to a wood handle for a perfect balance.

No.

DW354 13 oz. Head / 14" Handle 13 oz. Head / 16" Handle DW364

Checkered Handle Utility Knife

Will not slip out of your hand. Blade can be adjusted, but does not retract. Storage for extra blades in handle. Includes 5 blades.

No. Description

DW199 Bulk Packed 48 per Carton DW199C* with Display Card



3-Way Utility KnifeBlade will not slip. Retractable blade can

be adjusted to 3 positions. Light but rugged aluminum body. Includes 3 blades.

Description No.

DW042 Bulk Packed 48 per Carton DW042C* with Display Card



Soffit Square

Used in metal stud framing to square soffit track and studs. Special 2" wide notch in square fits over stud track to allow correct

alignment with no track lip interference. No. DW242



Drywall Hammer

Checkered face 14oz. polished head attached to a 16" handle for perfect balance





This drywall saw blade is hardened and tempered for long wear. Large, specially designed teeth cut quickly through wallboard, 15" blade with wood handle No. DW811*



15" blade with specially designed teeth cuts quickly through wallboard. Hardened and tempered blade with soft plastic handle. No. DW814*



Rugged constructed with sharp point for easy penetration. Heat treated aggressive 6" blade is anchored into hardwood handle with steel ferrule to prevent splitting.

No. DW243*

Can ship


UPS

Sands Top-Reading Magnetic Aluminum Extruded Levels

Heavy-duty extruded aluminum I-beam frame with strong magnetic strip. Special replaceable Solid Set acrylic Roto Vial® feature for accurate leveling in all directions. Shock absorbent end caps, Cat's Eye Yellow vials, top reading window for the level vial, and two plumb vials

101 1110 10 101	viai, alia tivo piaili	o viaio
No.	Length	Vials
SLPML18	18" (457mm)	3
SLPML24	24" (610mm)	3
SLPML36	36" (914mm)	3
SLPML48	48" (1219mm)	3
SLPML72	72" (1829mm)	5
SLPML96	96" (2438mm)	5





Drywall PanelLift®

Panellift® is excellent for fast and easy installation of drywall. One person can easily load and operate. Takes only seconds to assemble or disassemble with no tools required. Load capacity 150 lbs. Maximum height 11'. Maximum height with 6' extension is 15'. Weight: 115 lbs.

Description No. DC164 Panell ift 18" Extension DC166

6' Extension with Cable

Drywall Dolly

All steel structure of welded tubing. Rounded corners for safety. Bed is sloped to carry boards at proper angle. Phenolic resin wheels, resist corrosion from most materials and provide exceptional service in cold and wet conditions. Comes with four heavy-duty casters; two locking swivel casters and two straight casters. 48" long by 24" wide and 48" tall. Goes through most doorways. Weight: 112 lbs.

No. DC323**

**Must ship via truck



Lift 'n' Carry Panel Mover

One person can carry up to 150 lbs. of drywall, panel board, plywood, or wallboard with this lightweight molded plastic tool. Handle is angled away from hands. Rubber pads to prevent shifting. No. HC545*



Drywall Lifter and Carrier

This is a combination tool. Carry a full sheet of board and then use it as a lifter. Step down on it and lift the board into place for nailing. Made of cast aluminum. Weighs only 2 lbs. No. DC170



Drywall Stirrup Footlift

Drywall stirrup footlift is made of cast aluminum, correctly balanced with lip always on floor. Just kick under board and lift. Stirrup allows moving of lifter without bending over.

No. DW273



Drvwall Roll Lifter

Rigid steel construction, ribbed back weighted nose and roller-wheel for moving ease. Permits one man to raise drywall up to 3". Weighs 2 lbs, 8 oz.

No. DC171



Can ship

UPS

All steel construction. 44"x12" sloped bed. 2 straight and 2 locking 8" casters. 22" width easily fits through doorways. Bright orange easy to spot on jobsite. Ships flat unassembled. Weight: 99 lbs.

No. DC323E*



Rasp is the ideal tool to shave and form wood, vinyl, drywall and many other materials. Handy tool to carry in the pocket or pouch. Only 5-1/2" long. No.

DC135*

Rasp

DC136* Replacement Blade

Mini Lifter

Junior mini foot-lift is only 9" long. Very strong, yet lightweight.

No. DC175





Since 1930, Superior Tile Cutter®, Inc. has been a trailblazer in making professional quality tile cutters, chisels and scribes. These quality tools are known to last a professional tile setter a lifetime. In 2003, Kraft Tool Co.® acquired this company and expanded this brand to include everything you need for tile, carpet, wood and vinyl flooring.





CERAMIC TILE CUTTERS

The Choice of Professional Tile Setters Around The World

Superior Tile Cutters are designed to score and evenly cut most types of bull nose, shoe-base, quarter rounds, wall tile, thin vitreous tile, quarry, porcelain and sheet ceramic tiles without moving the material. All Superior Tile Cutters feature the "A" type handle with automatic spring tension keeping the handle adjusted to the bar.

Small


6"x11"

WT. 4.0 lbs

- · Cuts 6" tiles straight and 4-1/2" tiles diagonally.
- Includes adjustable angle gauge
- 4" working table on the right side of the breaker bar and 2' working table on the left side

ST001 (#00) W/3 Wheel Turret (ST050)

STOO2 (#00-400) W/#400 Carbide Wheel (ST048)



Medium

12"x12" WT. 8.0 lbs

- Cuts 6" tiles straight and 4-1/2' tiles diagonally
- Includes adjustable angle gauge
- 6" working table on each side of the breaker bar and

ST003 (#1A) W/6 Wheel Turret (ST049)

ST004 (#1A-400) W/#400 Carbide Wheel (ST048)



All Tile Cutter Replacement Parts on Page 126

Large

15"x15"

WT. 9.0 lbs

- Cuts 10" tiles straight and 7" tiles diagonally
- Includes adjustable angle gauge
- 7-1/4" working table on each side of the breaker bar



W/6 Wheel Turret (ST049)

ST006 (#2A-400) W/#400 Carbide Wheel (ST048)



Jumbo

16"x21-1/2"

WT. 13.0 lbs

- Cuts 16" tiles straight and 10" tiles diagonally.
- Includes adjustable angle gauge
- 10" working table on the right side of the breaker bar and 4" working table on the left side
- Scores tile up to 1-1/2" in thickness

ST007 (#3)

W/#400 Carbide Wheel (ST048)



Superior Tile Cutter® Replacement Parts



#400 Wheel

#200 Wheel

Carbide Scoring Wheels

- · Each are fitted with bushing, washer, screw and locknut.
- Carbide wheels fit all Superior Tile Cutters® and can be sharpened, thus increasing the life of the wheel.

No. Description

ST048 #400 1/2" Carbide Scoring Wheel #200 1/2" Carbide Scoring Wheel



6 Wheel Turret

3 Wheel Turret

Brass Turrets

- Low cost 1/2" replacement brass turrets with carbon steel cutting wheels.
- Rotate turret to move cutting wheel into position.

No. Description

(6) Wheel 1/2" Brass turrets (2 ea.) ST049 ST050

(3) Wheel 1/2" Brass turrets (2 ea.)



"A" Type Replacement Handle

- · Insert and spring automatically keep the handle adjusted to the bar.
- Unique spring tension provides automatic adjustment for straight cuts.

Description No. ST070

Replacement Handle (Fits all tile cutters)

Contractor Dual Rail Manual Tile Cutter With Carrying Case

Adjustable measuring guide with English and Metric. All metal body with chrome plated handle and rails. Cuts 19" (48.26cm) ceramic tile straight and 13-3/4" (35cm) ceramic tile diagonally. Comes with 1/2" thick cutting wheel.

No. Description

ST015* Dual Rail Manual Tile Cutter with Carrying Case ST015-02* 1/2" Carbide Replacement Cutting Wheel

Professional 14" Dual Rail Tile Cutter With Carrying Case

All metal body with chrome plated handle and rails. Heavy-duty steel base with anti skid pads. Adjustable measuring guide with English and Metric measurements. Cuts 14" (35.5cm) ceramic tile straight and cuts 10" (25.4cm) ceramic tile diagonally. Comes with 7/8" thick cutting wheel.

No. Description

ST017* 14" Dual Rail Tile Cutter with Carrying Case ST017-02* 7/8" Carbide Replacement Cutting Wheel





6" Rod / Coping Saw

Quality steel framed rod saw with 6" blade. Easy-to-change blade held in place by angled steel posts. Rubber grip adds comfort and prevents slippage.



Tile Hole Saw

Tungsten carbide-tipped hole saw cuts clean holes fast and easy. The tungsten carbide edges cut a 1-3/8" diameter hole. Works well on both ceramic and quarry tile. Ideal for faucet and shower head pipes. Fits electric drills.



Carbide Scoring and Cutting Tool


All-purpose tool for scoring and cutting countertop laminates, roof tiles and floor tiles, WonderBoard, Durock, etc. The unique design features three tungsten carbide blades. Rubber handle cover assures a firm grip. Length 7-1/2".

No. TL137*





Superior 8" Carbide Tungsten Tile Nippers



ST021 #40 Carbide Nippers with 1/2" Offset Jaws

- Carbide-tipped jaws
- 1/2" biting surface area
- · Both cutting edges straight



ST020 #80 Carbide Nippers with 5/8" Offset Jaws

- · Carbide-tipped jaws
- 5/8" biting surface area
- · Both cutting edges straight





- Carbide-tipped jaws
- 5/8" biting surface area
- One jaw convex for easy bite action







TILE **NIPPERS**



ST023 #85C1 Carbide Nippers with 5/8" Centered Jaws

- Carbide-tipped jaws
- 5/8" biting surface area
- Both jaws convex for more accurate cutting of glass, glass mosaic and porcelain tile

Cuts glass, mosaic & porcelain tile

ST024 #Quarry Carbide Nippers with 5/8" Offset Jaws

- Carbide-tipped jaws
- 5/8" biting surface area
- 3/8" Opening for cutting thicker tile

Cuts thicker man-made or quarry tiles including porcelain



ST025 #Thin Tile Carbide Nippers with 5/8" Offset Jaws

- · Carbide-tipped jaws
- 5/8" biting surface area
- 1/8" Opening for cutting thin tile
- Both cutting edges straight

Cuts wall (thin) tile



Opening refers to gap when jaws are closed

Glass Mosaic Cutter

Cut glass, mosaic, terrazzo and thin tile. Cuts thicknesses from 1/32" to 1/4" by handle adjustment of replaceable carbide cutting wheels. Safety - always use proper eye protection.

No. Description

ST026 Glass Mosaic Cutters Replacement Cutting Wheels ST026-01



Tile Cutter

Score the tile with the tungsten carbide wheel then use the strong plastic breaker bar to break ceramic tile. Soft comfortable textured plasic grips. Tool measures 8" long.

No. TL410 **Description** Tile Cutters





Notch Trowels


Easy-to-use notch trowels. Great for enclosed or small areas. Comes with comfortable wood handle.



Margin and Pointing Trowels Professional trowel grade steel, 1-piece forging; ProForm® soft grip handle for added comfort. No. Type Size GG422PF Pointing 5-1/2" GG434PF Margin 6"x2" AR100 Leather Pouch for Margin and Pointing Trowels (6" or less)


Gizmo Snap-On Trowel

Ideal for applying solid wood flooring and engineered wood flooring adhesive moisture barrier. Disposable notched steel blades allow you to trowel the perfect amount of adhesive each time. Use a new clip for each bucket of material. After use, simply discard the blade for easy clean up. It clips firmly on to any of our 11" notch trowels or finishing trowels. Two notch styles are available for various flooring thicknesses. Each style includes 10 blades per carton. Individual blades are 11" long by 1.5" tall.



No. Notch Type
ST430 A) Wave Notch
Use for flooring 3/8" thick or less
1/32" (.8mm) Deep
3/32" (2.4mm) Groover Width

ST431 B) Modified V-Notch
Use for flooring 3/8" to 3/4" thick.
3/8" (10mm) Deep
3/16" Width, 3/8" Flat





Drawings not to scale





NOTCH TROWELS







Add "CC" to part # for case cut displays

Drawings not to scale

11"x4½" Add "CC" to part # for case cut displays

- Professional Tile Installation Trowels
- 16 Different Notch Sizes
- Soft Gripping Patented ProForm® Handle
- Hardened, Tempered Blade with Stainless Steel Rivets
- Order Individually or in Case Cut Displays



Notch: SQ

Spreading adhesives for carpet, tile, sheet vinyl, vinyl tile, VCT rubber and cork.

(2mm x 2mm x 2mm)



No.
ST404PF
Notch: SQ

Spreading thinset mortar for ceramic floor tile and laminated wood plank flooring. (6mm x 6mm x 6mm)



No. ST406PF

Notch: U

Spreading adhesives for carpet to cushion in double glue installations.

(3mm x 2.2mm x 3mm)



No. ST408PF

Notch: V

Spreading adhesives for glue-down engineered wood flooring. (5mm x 4mm)



No. ST401PF Notch: SQ

Spreading adhesives for vinyl and rubber cove base and glue-down parquet wood flooring. (3mm x 3mm x 3mm)



No. ST411PF

Spreading thinset for ceramic and quarry tile.

ST416PF 16"x4-1/2" (6mm x 9mm x 6mm)



No. ST407PF

Spreading adhesives for double glue carpet. (3mm x 5mm x 3mm)



No. ST409PF Notch: V

Spreading adhesives for attached foam and smooth backed carpet.
(2.2mm x 2.2mm x 2.2mm)



Spreading adhesives for glue-down engineered and solid wood flooring.
(5mm x 5mm x 5mm)



Spreading thinset and mortar for large format ceramic and quarry tile. (12mm x 12mm x 12mm)



Spreading thinset, full contact mortars and thick-bed mortars. (19mm x 14mm x 9mm)




ST410PF
Notch: V
Spreading adhesives for

No.

Spreading adhesives for textured and rough backed carpets. (3mm x 3mm x 2mm)



Spreading adhesives for glue-down engineered wood flooring. (6mm x 3mm x 6mm)



No. ST405PF

Spreading adhesives for carpet tile, smooth backed carpet, VCT, felt-back sheet vinyl and vinyl plank.

(2mm x 1mm x 1mm)



No. ST417PF Notch: U

Spreading of thinset for floor or wall tiles and spreads adhesive and mastic. (6mm x 9mm x 6mm)



No. ST414PF Notch: V

Spreading mastic for wall tile.

(6mm x 5mm)

PROFESSIONAL SPONGES

Sponges (Medium Fine Pore) Durable polyester-based

sponges retain water like natural sponges. Package contains three different semi-oval sponges. No. PL060



Grout Sponge

Large water holding capacity. Soft to prevent digging, scratching or marring of grout.





Scouring Pad Holder

Kraft Tool's ProForm® soft grip handle is mounted to the plastic backing plate. Bottom hook strip attaches to scouring pad. Helps protect hands when scrubbing. (Must purchase pad separately.)

No. Size ST140PF 3-1/4"x9-1/4"

Scouring Pad

Available in non-abrasive or medium abrasive. Ideal for cleaning tile tools.

Description

No. ST134 10"x4-3/8"x1"

10"x4-3/8"x1"

(Blue) Medium abrasive (White) Non-abrasive



Turtle Back Sponge

General purpose, durable cellulose sponge. Keeps its shape and conforms to hand. Holds water exceptionally well, washes clean.

No. Size

PL600 6-3/4"x3"x2"

PL600-25 6-3/4"x3"x2" (Box of 25)

PI 6001 * 7-1/2"x3-1/2"x2"

PL600L-25* 7-1/2"x3-1/2"x2" (Box of 25)



Cellulose Sponge

ST133

Durable cellulose keeps its shape. Great for cleaning and all around use.

No. Size

5-3/4"x4"x2" PL370

(Sold 24 per Case Cut Carton)



Grout Scrubber SpongeHydra sponge on one side to wipe off excess

grout. Coarse plastic foam scrubber on opposite side to remove grout haze.

No.

ST137 7-1/2"x5"x2"

(Case Cut Carton of 24)

ST137-125 7-1/2"x5"x2"

(Display Box of 125)

ST137BALE 7-1/2"x5"x2'

(Bale of 200)



Rubber Sponge

Cleaning sponge made of pure natural rubber. Rectangular-shaped to fit your hand.

Size No. PL369

7"x2-3/4"x1-5/8"



White Rubbing Stone

Top quality rubbing stone is preferred by many tile setters. Will not mark or stain.

No.	Size	Grit
ST281	8"x2"x1"	60
ST282	8"x2"x1"	80



Tile Setter's Rub Brick

Smooth out and dress down tile, marble, granite or concrete with these high quality 6"x2"x1" silicon carbide rub bricks.

No.	Grit	No.	Grit
ST370	46 grit	ST373	120 grit
ST371	60 grit	ST374	150 grit
ST372	80 arit		•



GROUT FLOATS

Toe Grout Floats

The pure gum rubber face is bonded to a molded rubber pad, then cemented to a non-marring backing. The offset position of the handle and its special narrow width makes it possible to work in tight corners. Now available with a non-marring float back. Fitted with wood or ProForm® soft grip float handle.

 No.
 Size
 Handle

 ST127
 3"x12"
 Wood

 ST127PF
 3"x12"
 ProForm®

Epoxy Grout Floats

Long-wearing, lightweight float with non-marring plastic handle and back. Dense 1/2" float face ideal for using with epoxy grouts.

No Size ST362* 10"x3-3/4"



Tile Grouter's Floats

This float is excellent for tile grouting but has been adapted for many uses. The pure gum rubber face is bonded to a molded rubber pad, then cemented to a non-marring backing. Fitted with wood or ProForm® soft grip float handle.

No. Size Handle No. Size Handle ST126PF 9-1/2"x4" 9-1/2"x4" ProForm® ST126 Wood ST132 12"x4" Wood ST132PF 12"x4" ProForm®



Non-Porus Grout Floats


The very best non-porus, hard synthetic rubber-faced float for brown coat and tile grout. Fitted with wood float handle.

No. Size
ST128 12"x5" Add "P" to part no. for plastic handle



Super Grout Floats

A medium weight, firm float for grouting glazed tile on walls or floors. Can also be used for grouting mosaics and plain or abrasive quarry tile. Now available with a non-marring float back. Fitted with wood or ProForm® soft grip float handle.



Margin Grout Float

Professional quality margin grout float with contoured wood handle.



Grout Cleaning Brush

Contoured plastic handle with sturdy 5/8" long nylon bristles in 2 by 9 rows. For scrubbing grout and grout lines. Hang hole at the end of handle.




Grout Saw

The preferred tool among tile professionals. Long-lasting carbide-edged blade. Durable ProForm® soft grip handle. Use two blades on wide grout joints.

No. Description
ST147 Grout Saw
ST148* (2) Replacement
Blades

Carbide-Tipped Chisels & Scribe

Carbide-tipped chisels and scribe are 6" in length. Designed for removing chipped or broken tile. Chisels are shaped to prevent damage to adjacent tiles. Scribe has pencil point to ensure precision.



A) Chisel with 1/4" wide tip ST030 B) Chisel with 3/8" wide tip ST031 ST032 C) Chisel with 1/2" wide tip D) Scribe with 1/4" shank ST033

Carbide-Tipped Tile Hammer

5/8" polished hammer head face on a 8 oz. hammer head. Fitted with a smooth 10" solid wood handle.

No.

Description RO3122-5/8C Hammer with Carbide-Tipped RO3122-5/8 Hammer without Carbide-Tipped





Chalk Box and Chalk

Traditional metal-looking plastic chalk box; use as chalk line or plumb line. Includes 100' of line. Can be used to snap lines and create arids.

No.	Description
GG319	Chalk Box
GG303	White Chalk - 8 oz.
GG304	Blue Chalk - 8 oz.
GG305	Glo Orange Chalk - 8 oz
GG306	Red Chalk - 8 oz.
GG307	Yellow Chalk - 8 oz.

Kraft Pro Self Locking 25' Tape Measure

Self-locking tape Blade printed with English/ Metric on both sides. Blade resists fading and warping, 25' long. No. GG299*



Industry accepted N95 disposable respirator mask with foam nose cushion and two elastic straps.

Box of 20 masks. No. GG435*

Tile / China Markers

Quality tile markers. Package of six includes two of each: yellow, black, and red.

No. Size ST157* 6-1/2"



Professional Work Gloves

Lightweight yet durable professional work gloves. Comfortable neoprene cuff with Velcro® closure for a secure fit. Breathable spandex back provides ultimate comfort and fit.

Size No. GG488-M* Medium GG488-L* Large GG488-XL* X-Large

Sold 12 per Case Cut Carton

Orange Latex Gloves

Sturdy latex gloves are resistant to most caustic chemicals, paints and sealers. Provides protection for hands from liquids and other materials.

No.	Size	Length
GG426-L*	Large	12"
GG426-XL*	X-Large	12"

Sold 12 per Case Cut Carton

Ultra Rubber Knee Pads

Durable, accordion style rubber knee pads with comfortable foam pad insert. Adjustable, replaceable strap.

No. WL084* (pair)



EZ-Kneeler™ Kneeboard

Comfortable, 1-1/2" thick foam cushion adhered to 14"x24" polypropylene tray, which protects cushion for long life.

No. WL069



13"x23" Poly Grout Bag

Soft 3/8" tip molded into this poly-lined grout bag. Size of tip can be increased by cutting small amount of the point off with anv scissors.

No. WL010



Cone-Shaped Heavy-Duty Vinyl Grout Bag

Cone-shaped, heavy-duty vinyl bag comes complete with replaceable metal tip.

No. Size

WL013 Large 10-1/2"x24"

WL015 Large 3/8" Replacement Metal Tip

WL014 Giant 15"x28"

WL019 Giant 7/16" Replacement Metal Tip



BACK

Plastic Bucket and Pail

Durable 90 mil 5 gal. translucent bucket and 10 qt. pail for general uses such as mixing or moving various materials. Lid for 5 gallon bucket sold separately.

5 Gal. Plastic Bucket

Liters. Quarts. Gallons measurements

Description No.

GG468 5 Gal. Plastic Bucket

GG468-01 Plastic Lid

(For GG468 5 Gal. Bucket) GG468-02 Plastic Lid w/ Spout

(For GG468 5 Gal. Bucket)

10 Qt. Plastic Pail

Ounces, Liters, Quarts measurements No. Description

GG470 10 Qt. Plastic Pail

Lid Claw

Open buckets with ease. Durable plastic lid claw - one piece plastic construction.

No. DW110



Stainless Steel Bucket Trowel

Stainless steel blade is tapered to align with sides and bottom of bucket. Special tang to hang trowel on rim of bucket.

No. PI 800* 7"x4-1/2"x3"



5 Gallon



Easily move heavy buckets. Strong polypropylene construction can be used with standard 3-1/2 to 5 gallon buckets. 5 non-marring rubber wheels with 2 locking casters make this dolly perform well even on unlevel surfaces. 3 thumbscrews secure bucket. (Bucket not included.)

No. ST379

Unomixer

Ideal for fast mixing of all kinds of materials, from paint to cement. For use in a 1/2" drill chuck. 16" shaft, 3-1/4" diameter. No. DC363*



Round Shaft

Stainless Steel Jiffy Mud and Paint Mixers

Fits containers 3 gallons or larger. 21" long, 1/2" shaft, top diameter 4-1/2". bottom diameter 5". depth 5". For use in a 1/2"

drill. No. DC409

Round Shaft

For small containers, 2 gallons or less. 10-1/2" long, 1/4" shaft, top diameter 2-3/8", bottom diameter

2-5/8", head depth

2-1/2". For use in a 3/8"

drill. No. DC408

Round Shaft

Egg Beater Mixer

7/16" steel hex shaft. 30" overall length. Plated solid steel. For use in a 1/2" drill or larger. Use to mix thinset, grout and concrete products.

Easy to use, easy to clean.

No. DC716*

Hex Shaft

Triangle Blade Mixer

Multi-purpose triangle blade mixer. Measures 24" long. Use with all concrete-based products. For use in a 1/2" drill

No. DC721

Hex Shaft

Epoxy Mixing Paddle

Flat steel blade with slots so material flows through and around mixer. Ideal for mixing epoxies, mortars, resins and other construction materials. Plated to resist wear and corrosion. Fits most 1/2" drill motors. 7/16" hex shaft. Overall length 18".

No. DC719

Hex Shaft

Double Bent Mixer

Bent mixing blades provide a bottom-to-top mixing action. Mix urethane and other materials smoothly. Plated to reduce wear and corrosion. Fits most 1/2" drill motors. 18" hex shaft. 4"x3" blades. No. DC720

> Hex Shaft

Proudly Made In The USA

Tile Spacers

Constructed of tough durable plastic. Evenly spaces tile for uniform grout lines.

opaces the for armorning roat mice.			
	No.	Size	Quantity
()-	ST324*	1/16" Spacer	Bag of 300
-1	ST325*	1/16" Spacer	Box of 3000
0-	ST326*	1/8" Spacer	Bag of 200
35	ST327*	1/8" Spacer	Box of 1600
Do	ST328*	3/16" Spacer	Bag of 150
2	ST329*	3/16" Spacer	Box of 850
Do	ST330*	1/4" Spacer	Bag of 100
9	ST331*	1/4" Spacer	Box of 550
0	ST332*	3/8" Spacer	Bag of 50
1			




Tile Wedges

Use these durable plastic wedges for installing wall tiles. Avoid tile slippage on vertical surfaces while maintaining a horizontal grout line. Tapered, textured grip makes installation and removal easy.

No. Description


ST340* Bag of 500 Tile Wedges



Tile Bridge *Revolutionary Tile Support System*

Tile Support System for setting tile and marble around fireplaces. Eliminates need for wood braces to hold tile in place. One step installation saves time and money. Made of high strength lightweight aluminum and galvanized steel. Weighs only 4 pounds. Easy to adjust telescoping legs with built-in screw locks. Legs extend up to 41". Leg supports fitted with non-marring rubber caps

No. ST114





L Shape Screeds / Straightedges

Straightedge set L shape, 3-1/2" wide x 1-1/4" high. Made of high strength lightweight aluminum.

No. Description Sizes ST295 5 Piece Set 1-1/2'

ST295 5 Piece Set 1-1/2', 2', 3', 4', 6' ST296 6 Piece Set 1-1/2', 2', 2-1/2', 3', 4', 6





Aluminum Screed Set

Screed set 1" wide x 4" high. Made of high strength lightweight gold anodized aluminum.

No. Description Sizes

ST294AL 5 Piece Set 30", 2', 3', 4-1/2', 6'

zed aluminum.

4" Heavy-Duty Scraper

12" long handle allows for easy access of hard-to-reach areas. Easily remove vinyl, ceramic tile and adhesive with less effort. 3 tightening screws for stability, comes with 4" blade. Carded for easy display.

No. Description

ST298* 4" Heavy-Duty Scraper ST299* 4" Repl. Wall Scraper

Blades (Pkg 5)

Heavy-Duty Scraper

Large metal handle is weighted to produce inertia, for easier scraping. Heavy-duty blade carrier has (3) tightening crews. 15" hammer-end handle ideal for rubber mallet use. Includes (1) 5" blade

No. Description

Blades

FC520 Heavy-duty Scraper FC521 (5) 5" Replacement

Big Floor Scraper

Features an 8" wide heavy-duty replaceable blade, and a twist-lock adjustable telescoping handle. Handle length adjusts from 39" to 59". The perfect tool for floor preparation.

No. Description

FC506 Big Floor Scraper FC507 (5) 8" Replacement Blades

Forged Floor and Wall Scraper

54" Äll Steel

Scraper for extra tough scraping and cleaning jobs. Steel handle welded to solid forged 4" blade. Pry tile, wood flooring and other materials.

No. ST175






HI-CRAFT" FLOOR COVERING TOOLS

Hi-Craft™ Notch Trowels

Hardened and tempered 11"x4-1/2" steel blade for wearability. Comes with soft grip or camel back wood handle. Packed in case cut boxes of 6.





SQ 1/4"x1/4"x1/4" Soft Grip HC404PFCC*

> Wood HC404CC*



1/4"x3/8"x1/4" Soft Grip HC411PFCC* Wood

HC411CC*



SQ 1/2"x1/2"x1/2" Soft Grip HC412PFCC*

> Wood HC412CC*



3/16"x5/32" Soft Grip HC408PFCC*

Wood HC408CC*



9/16

3/4"x9/16"x3/8" Soft Grip HC420PFCC*

> Wood HC420CC*



Hi-Craft™ Grout Floats

Closed cell pad with gum rubber face. Non-marring top with beveled edges.

Size HC394P*

9"x4" Econo Tile Grouter's Float

Dense solid molded rubber grout float.

No.

HC395P* 9"x4" Econo Molded

Rubber Float

Closed cell foam rubber pad with plastic handle and non-marring top.

No.

HC396P* 9"x3" Econo Grout Float



Order in Case Cut cartons of (6) each.



Economy stainless steel adhesive spreader with 9" cold rolled steel blade.

Notch	Size
SQ	1/4"x3/8"x1/4"
SQ	1/16"x1/16"x1/16"
SQ	1/4"x1/4"x1/4"
V	3/16"x5/32"
	SQ SQ SQ

Tile Pliers/Nipper
Made of forged tool steel with 5/8" wide offset jaws. Carbide-tipped edges assure easy and accurate cutting of tile every time. Rubber coated handles for comfortable grip. Cuts wall tile, thin vitreous, and quarry tile. 8" length

No. HC210*

Order in Case Cut cartons of (6) each.

Grout Saw

Non-slip comfort handle. Fitted with two blades. Use one blade for thin grout joints and two blades for thicker grout joints.

No. HC174*

Order in Case Cut cartons of (6) each.

Economy Notch Trowel

Economy notch trowel with 9"x4" steel blade mounted to contoured plastic handle.

Size No. Notch HC167P* SQ 1/4"x3/8"x1/4" 1/16"x1/16"x1/16" HC168P* SQ HC169P* SQ 1/4"x1/4"x1/4" HC170P* 3/16"x5/32"

HC166P* No Notch

Order in Case Cut cartons of (12) each.



Vinvl Knife

Hook axe knife with extra heavy, curved carbon steel sharp point for making even, accurate cuts in vinyl and linoleum. Comfortable, contoured soft grip handle.

No. HC300*



VINYL FLOORING

Comes with convenient carrying case

Folding Triangle w/ Case

Used for framing, tile, drywall and tile layout. Square easily folds for storage in protective cover. English and metric measurements.

Size No. ST283* 24"

Checkered Handle Utility Knife

Will not slip out of your hand. Blade can be adjusted, but does not retract. Storage for extra blades in handle. Includes 5 blades.

Description No.

DW199 Bulk Packed 48 per carton DW199C* with Display Card



DW199C

3-Way Utility Knife

Blade will not slip. Retractable blade can be adjusted to 3 positions. Light but rugged aluminum body. Includes 3 blades.

Description No.

DW042 Bulk Packed 48 per carton DW042C* with Display Card



DW042

DW042C

Replacement Utility Blades - see pg 122

(10 Pack) Dispenser DW078 (100 Pack) Dispenser DW079

12" Sheet Metal **Cutting Snips**

Forged cutting shears are contoured for easier cutting, less fatigue. Cuts sheet metal, tile, asphalt, carpet, wire, plastic, and more. Rubberized grip for comfort.

No. LA292*



Vinvl Roller

Solid steel consruction.Rollers have smooth surfaces, and rounded corners to protect flooring materials from indentations. Each roller section "floats" independently and automatically compensates for subfloor irregularities. Handle yoke detaches for easy carrying and storage. Diameter 5-1/4", Width 16", Height 39". No. FC511

Miter Snips

Accurately cuts angles in seconds up to 1" wide x 1/2" thick (replaceable blade). Cuts plastic, decorative moldings and tile edges/ trim. Adjustable miter fence with built in protractor, 7 preset angles from 45°-135°. Safety lock handle with no slip grip. To change angle, slide the self-indexing metal guide to desired angle.

Description No. LA355* Miter Snips

LA355-01* Top cutting Replacement Blade



Vinyl Floor Roller

Great tool for rolling vinyl floor covering, carpet and cove base. Handle telescopes from 17" to 27". Three (3) non-marking

rollers are 7-3/8" wide. No. FC543*



Economy Vinyl Tile Cutter Heavy cutting frame with casters, moveable

cutting guide and marked measuring guide. Cuts 12" tiles straight or 9" tiles diagonally. No. FC512E*



Vinyl Seam Roller

Weighted steel seam roller with 6" wood handle. Roller is flat on shaft side, rounded on outside edge; 2" diameter and 2" wide. Great for finishing work in vinyl installations.

No. FC542*



Tapping Block

Black plastic tapping block with female groove on one side and end to mate with tongue in tongue-and-groove planks. Large plastic handle for quick and easy placement.

No. FC550

General Purpose Hammer

20 oz. curved claw general purpose hammer with smooth face. 11" wood handle.

No. GG219



White Rubber Mallet

22 oz. white rubber mallet head on 10-1/4" solid wood handle; non-marring. Use with tapping block to ensure boards are installed tightly in place.

No. FC551*



WOOD FLOORING

Small Flat Pry Bar

15" long forged steel pry bar. 30° claw at one end for reaching tight spots and curved pry claw at the other end for superior leverage. Use for pulling nails or prying materials. 3 nail slots for pulling different sizes of nails. Great for removing tile and boards in glue-down wood flooring installations.

No. GG636

Pro Caulk Gun

Professional caulking gun vmade of all steel

construction. Easy-to-load barrel swivels to quickly change the angles on corners. Ladder hook keeps the tools handy on the jobsite.

No. Description GG279* 10 oz. GG277* 1 qt.



DIY Caulk Gun

Lightweight, easy-to-load gun with spout cutter and puncture tool. Accommodates standard 10 oz. caulk cartridge.

No. GG278*



Bearcat Stripper Machine

Easily remove flooring products for replacement. Patented cam-driven oscillating cutting system is quieter than previous systems. The shearing blade is directly linked to the 3/4 h.p. motor for few parts to wear out. 110 volt Stripper. 10 Amps. No. Description

FC700ZZ FC701ZZ FC705ZZ **Description**Bearcat Stripper Machine
4"x6" Bearcat Stripper Blade
3"x10" Bearcat Stripper Blade



Blades

Door Jamb Super Saw

Powerful 13 amp., 110V motor. Saw allows undercutting of doors, door jambs, inside corners and walls. Blade height adjusts from flush to maximum 1-1/4". Cuts doors 1-3/4" without removal. Complete with (1) combination and (1) masonry blade, detailed instructions and durable plastic carrying case. Weight 14 lbs.

No. Description FC537 Door Jamb Saw

FC538 Carbide-Tipped Blade (use only with FC537 Door Jamb

Super Saw)



Multi-Undercut Saw

Saw cuts along walls, door jambs, toe spaces and inside corners. Height adjusts from flush to 1" above the floor. Comes with 36-tooth carbide blade made specifically for Multi-Undercut Saw. Carrying case included. 110V motor. Weight 11 lbs.

No. Description
FC527 Multi-Undercut Saw

FC527 Multi-Undercut Saw FC528 Replacement Carbide Blade (use only with FC527 Multi-Undercut Saw)



Undercut Door Jamb Saw

This is the perfect tool for cutting door jambs and other hard-to-reach areas. 12" long replaceable blade.

No. Description

FC518* Undercut Door Jamb Saw FC518-01* Replacement Blade



CARPET FLOORING



Constructed of tough, durable alloy steel to withstand hammering. The blade is ground to a perfect taper so as not to cut the carpet. Nickel plating will not rust.

Size No. FC510* 3-1/2"x8"



Knife is made of cast aluminum, with a bright polished surface. Rear-loading blade storage for quick access to extra blades. Includes five blades.

No. **Description** FC504 Carpet Knife

(10) Replacement Blades (slotted)



Uses standard slotted carpet blades. Press button on handle for fast change and access to blade storage. Knurled handle for sure grip. Perfect for cutting carpet, foam, padding, etc. 3 steel heavy-duty blades included. Carded for easy display.

Description No.

FC547* Push Button Carpet Knife FC548* (10) Replacement Blades (slotted)





Economy Adjustable Knee

Adjusts from 17-1/2" to 21-1/2" long. Steel pins adjusts to Cdepth of carpet.



Carpet Seam Roller 5" wide head helps press

backing into adhesive for stronger seams. No. FC532*



Powerful 11 amp. tool drives staples into hardwoods. Jamb-proof magazine holds 100 staples. Features a built-in trigger-lock for safety. The stapler height fits under stepraisers for easy stapling and features a uniquely designed pointed tip.

No. Description

FC535 Stapler Gun

Staples - 9/16" length divergent FC536

points with 3/16" crown. Packed 5,000 per box.

Heat Iron

Low profile tool glides easily under carpets and permits the seams to be joined on the iron, while the adhesive is still hot. "U" shaped handle provides strength and is tapered to slide easily by the seam edges. Heat settings are adjustable from 250° to 350°, for fast seaming. Built-in heat shield protects sensitive pile fibers and synthetic backings

Weight No. FC501 3-1/2 lbs.



Create a professional seam every time. Ideal for both commercial and residential use. Use a special heat seaming iron (FC501) to melt the glue providing a strong durable adhesion to the carpet. 66' long roll.

No. FC530



- Kits feature all the tools to get started in the trade
- Designed in cooperation with trade associations, schools and unions
- Instructors: Contact Kraft for more information on program support

APPRENTICE KITS

Masonry



Masonry Apprentice Kit #BC901AK

Qty	Part No.	Description
1	RO116-10-1/2	10-1/2" Rose™ Narrow London Trowe
1	RO3131-24	W. Rose™ Brick Hammer 24oz
1	RO5121-3/8x1/2	3/8"x1/2" W. Rose™ Convex Jointer
1	RO5121-5/8x3/4	5/8"x3/4" W. Rose™ Convex Jointer
1	BC334T	250' Tube Flo. Orange Braided Line
1	BL167	Wood Spacing Rule
1	BL210	Skate Joint Raker
1	BL234	4" Bricklayer's Set
1	BL350	Wooden Line Block Pair
1	BL526	Utility Brush
1	GG432	5"x2" Margin Trowel
1	SL12AB48	48" Brass Bound Mahogany Level
1	WL050	20" Canvas Tool Bag

Plaster



Plaster Apprentice Kit #PL700AK

Qty	Part No.	Description
1	BL526	Utility Brush
1	PL101	7"x1-5/8" Stainless Steel Bound Brus
1	PL194	Leaf & Square Ornamental Tool
1	PL208	8" Plasterer's Scarifier
1	PL263PF	13"X13" Magnesium Hawk
		w/ ProForm® Handle
1	PL372	10"x4"x3/4"Fine Cell Rubber Floa
1	PL453PF	11-1/2"x4-1/2" Gold Stainless
		Steel Trowel w/ ProForm® Handle
1	GG284	25'x1" Tape
1	GG432	5"x2" Margin Trowel
1	SL2424	24" Cast Aluminum Level
1	WL050	20" Canvas Tool Bag

Concrete



Concrete Apprentice Kit #CC900AK

Qty	Part No.	Description
1	CF217PF	14"x4" Trowel w/ ProForm® Handl
1	CF285PF	16"x4" Rnd Front SQ Back Trowe
		w/ ProForm® Handle
1	CF016PF	16"x3-1/4" Magnesium Float
		w/ ProForm® Handle
1	CF256	15"x3-1/2" Beveled Redwood Flo
1	CF118PF	6"x3" Groover, 1/2" Bit
		w/ ProForm® Handle
1	CF138PF	6"x6" Edger, 3/8" R, 1/2" Lip
		w/ ProForm® Handle
1	CF164PF	6"x3-1/2" Edger, 3/8" R, 1/2" Lip
		w/ ProForm® Handle
1	CF173PF	6"x4" Edger, 3/8" R, 1/2" Lip
		w/ ProForm® Handle
1	BL526	Utility Brush
1	GG284	25'x1" Tape
1	GG432	5"x2" Margin Trowel
1	PL374	8"x4"x5/8" Coarse Rubber Float
1	SL4848	48" Cast Aluminum Level
1	WL080	Poly Knee Pads
1	WL050	20" Canvas Tool Bag

Tile



Tile Apprentice Kit #ST100AK

Qty	Part No.	Description
1	SLSC3624	24" Contractor Extruded Alum. Level
1	ST005	Large Tile Cutter 15" x 15"
1	ST020	#80 Carbide Nipper 5/8" Offset
1	ST031	Carbide Chisel 3/8" Tip
1	ST126	Grout Float 9" x 4"
1	ST135	Grout Sponge
1	ST137	Grout Scrubber Sponge
1	ST371	Tile Setters Rub Brick 60 Grit
1	ST411PF	SQ Notch Trowel 1/4"x3/8"x1/4" w/PF Hdl
1	WL050	20" Canvas Tool Bag
1	WL080	Poly Knee Pads

Drywall



Drywall Apprentice Kit #DC902AK

	πι	DUJUZAN
Qty	Part No.	Description
1	DC317	Drywall Pole Sander
1	DW243	Utility Drywall Saw
1	DW254	18 oz Drywall Hammer
1	DW441	Hand Sander
1	DW520	Inside Corner Tool
1	DW533	6" Brass Hammer End Knife
1	DW722	12" EZ-Grip Mud Pan
1	DW810PF	10" Wide Handle Taping Knife
1	DW811	15" Drywall Saw
1	GG284	25'x1" Tape
1	SL671	48" T-Square
1	WL050	20" Tool Bag
1	WL077	Drywall Tool Pouch

Registered Trademarks of Kraft Tool Co.®

EZY-Tilt®, EZY-Tilt® II, Knucklehead®, Knucklehead® II, Kraft Tool Co.®, Kumalong®, Masonry Barbell Jointer®, ProForm®, Rapid Square®, Roto-Vial®, Sands Level & Tool Co.® Inc., Sands Levels Tell the Truth®, Solid Set Vials®, Step-Saver®, Super-Pro®, Superior Tile Cutter® Inc., Bronco™ Tilt Bracket, Buckaroo™ Straightedge, Buckeye™ Straightedge, Cardinal™ Placer, Elite Series Five Star Trowel™, EZ-Kneeler™, EZ-Shooter™, Flipper Tilt Bracket™, Gold Standard™, Hi-Craft™, Mag-150™, Mega Mover Concrete Placer™, Multi-Twist™, Orbit-er™, Redwood Striker™, Right Angle Placer™, Silverback™ Professional Series, Striker™ Screed, W.Rose™

Registered Patents of Kraft Tool Co.®

ProForm® Trowel Handle, US Patent #6,247,204 B1, Elite Series Wood Handle #D584,126, Knucklehead™ II, Bull Float Bracket, US Patent #4,335,485, Bronco™ Tilt Bracket, US Patent #4,856,932, ProForm® Float Handle, US Patent #6,473,939 B1, US Patent #6,821,468 B2, W.Rose™ ProForm® Trowel Handle #D508638, Super-Pro® Gun Cylinder, US Patent #5,415,351, Beveler Floats US Patent #6,183,237, Step-Saver® Tools US Patent #D-333,600 & US Patent #5,098,278, Squeegee Trowel Handle US Patent #D614,471S

Ask for Special Forms to order or visit www.KraftTool.com (General Information): Imprinted Line Blocks, Line Twigs, or Line Pins

TOOL DISPLAYS

Complete Flooring Display #ST900C



Complete W. Rose™ **Masonry Display** #R0900



Five Star Elite Trowel™ Concrete Display #CC900E



Choose from any of Kraft's displays highlighting Concrete, Masonry, Drywall or Tile products. Target the professional concrete contractor with the Elite Series Five Star Trowel[™] display or the professional mason with the W. Rose[™] masonry tool display. Kraft displays are an excellent way to highlight your currect product offering or expand your selection into a new product category. Each display features an assortment of the most popular products to assure that products will sell. Each display also includes a header sign, hooks and catalogs to feature the tools.



For complete listings and photos of the other Kraft Tool Co® Tool Displays please visit www.KraftTool.com and go to the "General Information" tab.

TOOL DISPLAYS

Complete Concrete Display #CC900



Oty Part No	Description

O(L)	, i ditit	. Description
6	CF064PF	16"x3-1/8" ThinLine Pro Mag Hand Float W/PF Hd
6	CF141PF	6"x3" 1/4"R Curved End Edger W/PF Hdl
6	CF165PF	6"x4" 1/2"R Cement Edger W/PF Hdl
6	CF173PF	6"x4" 3/8"R Cement Edger W/PF Hdl
6	CF175PF	6"x6" 1/2"R Cement Edger W/PF Hdl
3	CF217PF	14"x4" Cement Trowel W/PF Hdl
3	CF222PF	16"x4" Cement Trowel W/PF Hdl
3	CF227PF	18"x4" Cement Trowel W/PF Hdl
6	CF256	15"x3-1/2" Redwood Hand Float
5	CF283	20 Grit 6"x3"x1" Rub Brick
2	CF304PF	6"x4-1/2" Big Bit Bronze Groover W/PF Hdl
2	CF305PF	6"x4-1/2" Narrow Bit Bronze Groover W/PF Hdl
2	CF314PF	6"x4-1/2" Deep Bit Bronze Groover W/PF Hdl
3	CF438PF	16"x4" Carbon Steel Pool Trowel W/PF Hdl
6	GG422	5-1/2" Pointing Trowel
6	GG432	5"x2" Margin Trowel
6	PL374	8"x4" Red Rubber Float w/ Wood Handle
4	WL069	EZ-Kneeler™ Kneeboard

Complete Masonry Display #BC901



θtν	Part	No.	Description

BC338T

ь	BC342	Yellow Braided Line - 500' Tube
2	BC380	Yellow Brick Tongs
3	BL147	Adjustable Line Stretchers
4	BL155	24 oz Brick Hammer
4	BL156	Snap-Over Line Twigs (Pkg 14)
4	BL158	Bricklayer's Line Pins (Pkg 4)
6	BL167	6' Lufkin® Wood Spacing Rule
3	BL210	Skate Wheel Joint Raker
6	BL216	14" x 5/8" Half Round Convex Sled Runner
4	BL234	4" Bricklayer's Set
1	BL244	24" Brass Bound Mahogany Level
1	BL248	48" Brass Bound Mahogany Level
6	BL261	1/2" x 5/8" Brick Jointer
6	BL262	5/8" x 3/4" Brick Jointer
6	BL280	Hubbard Jointer w/ 4 Blades
4	BL348	4-1/4" Tenite Line Blocks (Carded Pair)
6	BL512	6' Lufkin® Wood Modular Rule
6	BL526	6-1/2"x2"x4" Jumbo Utility Brush W/Red Hdl
6	BL703	10" Narrow London Brick Trowel w/Wood Hdl
6	BL705	11" Narrow London Brick Trowel w/Wood Hdl
6	GG422	5-1/2" Pointing Trowel
	GG432	5" x 2" Margin Trowel

Yellow Braided Line - 250' Tube

Complete Drywall Display #DC902



Qty	Part	No.	Description
-----	-------------	-----	-------------

5-1/2" Rasp

DC102

DC135

2 PL512

2	DC171	Drywall Roll Lifter
2	DC317	Pole Sander w/ Wood Handle
1	DC401	Drywall Taper W/Wood & Web Handle
2	DC713	Jr. Mud Mixer w/ 30" Hex Shaft
2	DW221	48"x1/8" Drywall T-Square
3	DW241	Circle Cutter
6	DW243	Utility Drywall Saw
2	DW264	18oz Checked Face Heavy Duty Hammer
2	DW281	7" Broad Knife
6	DW312	Plastic Double Blade Mud Pan
6	DW441	Hand Sander
2	DW520	4"x5" Inside Drywall Corner Tool
5	DW533	6" Brass Hammer-End Taping Knife
6	DW548	8"x3" Flexible Taping Knife
6	DW550	10"x3" Flexible Taping Knife
6	DW552	12"x3" Flexible Taping Knife

DW712 12" Heli-Arc Stainless Steel Mud Pan PC201 ProForm® Texture Gun & Hopper

12" Aluminum Hawk

100 Grit Diecut Sandpaper (Pkg 10)



- 144" Wide -

	•		177	WIUG	·
Qty	Part No	Description	Qty	Part No	Description
6	BC342	Yellow Braid Line - 500' Tube	2	CF292BPF	18"x5" Blue Steel Cement Trowel w/ProForm® Handle
6	BC352	Bonded Braid (White & Black) Line - 500' Tube	2	CF295BPF	20"x5" Blue Steel Cement Trowel w/ProForm® Handle
4	BC380	Yellow Brick Tongs	4	CF304PF	6"x4-1/2" Big Bit Bronze Groover w/ ProForm® Handle
3	BL147	Adjustable Line Stretchers (Pair)	4	CF305PF	6"x4-1/2" Narrow Bit Bronze Groover w/ProForm® Handle
6	BL167	6' Lufkin® Wood Spacing Rule	2	CFE222	16"x4" Elite Series Five Star™ Cement Trowel w/Wood Handle
6	BL169	6' Lufkin® King Size Brick Rule	2	CFE222L	16"x4" Elite Series Five Star™ Cement Trowel w/Leather Handle
3	BL210	Skate Wheel Joint Raker	2	CFE222PF	16"x4" Elite Series Five Star™ Cement Trowel w/ProForm® Handle
4	BL280	Hubbard Jointer with 4 Blades	2	CFE227	18"x4" Elite Series Five Star™ Cement Trowel w/Wood Handle
6	BL348	4-1/4" Tenite Line Blocks (Carded Pair)	2	CFE227L	18"x4" Elite Series Five Star™ Cement Trowel w/Leather Handle
6	BL512	6' Lufkin® Wood Modular Rule	2	CFE227PF	18"x4" Elite Series Five Star™ Cement Trowel w/ProForm® Handle
12	BL526	6-1/2"x2"x4" Jumbo Utility Brush with Red Handle	6	GG310	Tie Wire Twister
6	BL763PF	7"x 3/8" Caulking Trowel with ProForm® Handle	6	GG320	6' Lufkin® Engineer Folding Rule
6	BL764PF	7"x 1/2" Caulking Trowel with ProForm® Handle	6	GG422PF	5-1/2" Pointing Trowel w/ProForm® Handle
1	CC152	Denver Slider/Knee Boards (Pair)	6	GG432PF	
1	CC153	30"x10" Concrete Sliders (Pair)	6	R0116-11	5"x2" Margin Trowel w/ProForm® Handle
3	CC177	36" Aluminum Medium Cement Finish Broom			11" Narrow London Brick Trowel w/Wood Handle
3	CC178	48" Aluminum Medium Cement Finish Broom	6	R0116-11SH	11" Narrow London Brick Trowel w/ProForm® Soft Handle
6	CC226	6' Thread Magnesium Handle 1-3/4" Dia.	6	R01416-11	11" Narrow London Brick Trowel w/Plastic Handle
6	CC285	Button/Female Thread Plug Handle Adapter	4	R03131-24	24 oz. Head Brick Hammer
6	CC286	Button/Male Thread Plug Handle Adapter	6	R0316-11	11" Narrow London Brick Trowel w/Leather Handle
6	CC289S	6' Swaged Button Alum Handle 1-3/4" Dia (Anodized)	12	R05121-1/2x5/8	Convex Jointer
2	CC294	EZY-Tilt® II Float Bracket - 6 Hole	12	R05121-5/8x3/4	Convex Jointer
6	CC295	Fresno/Broom Adapter for Double Button Handle	2	SL2424C	24" Cast Aluminum Level w/Case
2	CC296	Knucklehead® II Tilt Float Bracket - 6 Hole	2	SL4848C	48" Cast Aluminum level w/Case
4	CC421L	4'x 1-3/8"x 2" Buckaroo Straightedge™ w/Level Vial Hdl	6	SLMA48	48" Professional Mahogany I-Beam Level (6 Vials)
4	CC623	1/2" Bronze Groover Fresno Attachment	12	SLSC55	3" Aluminum Line Level
4	CC625	3/4" Bronze Groover Fresno Attachment	*10	WL069	EZ-Kneeler™ Kneeboard Foam Rubber Knee Pads (Pair) 12" Display Hook 4" Standard Loop Hook Opisplay (A) offers a variety of our mos Display (A) offers a variety of our mos opisplay (B) opisplay (B) offers a variety of our mos opisplay (B) opispl
6	CC662	Fresno Trowel Adapter	4	WL135	Foam Rubber Knee Pads (Pair)
3	CC802-01	48"x8" Square End Mag Bull Float w/o Bracket	7	KH00K12	12" Display Hook 4" Standard Loop Hook 6" Display Hook Display Hook Display (A) offers a variety of our index oncrete, and masonry tools. Display measures one popular concrete, and masonry tools.
3	CC803-01	48"x8" Round End Mag Bull Float w/o Bracket	5	KH00K4L	4" Standard Loop Hook 6" Display Hook 6" Chandard Loop Hook
2	CC851	36"x5" Rouund End Fresno w/All Angle Bracket	3	KH00K6	6" Display Hook popular of Display measure 69" tall.
5	CC905	19-1/2"x4" Concrete Spreader w/Hook w/Handle	4	KH00K6L	
6	CC940	3/4" Bronze Bull Float Groover Attachment	18	KH00K8	8" Display Hook 144 Wishington Complete (10) catalog
6	CC941	1" Bronze Bull Float Groover Attachment	18	KH00K8L	8" Display Hook 8" Standard Loop Hook 12" Masonry Hook (6 Loop) 12" Masonry Hook (6 Loop)
6	CF118PF	6"x3" 1/2"D Universal Hand Groover w/ ProForm® Handle	4	KTC019	12" Masonry Hook (6 Loop) header signs
6	CF150PF	16"x3-1/2" Mag-150™ Float w/ProForm® Handle	2	KTC026	Multi-Tier Trowel Holder
6	CF164PF	6"x3-1/2" 3/8" R Cement Edger w/ProForm® Handle	4	KTCBOARD	Display board
6	CF165PF	6"x4" 1/2" Radius Cement Edger w/ ProForm® Handle	1	KTCBSKTSIGN	Sign For Tool Display Basket
6	CF173PF	6"x4" 3/8" Radius Cement Edger w/ ProForm® Handle	4	KTCHDLHOLDER	
2	CF212PF	12"x4" Cement Trowel w/ProForm® Handle	4	KTCHOLDER	Universal Bracket
2	CF222PF	16"x4" Cement Trowel w/ProForm® Handle	4	KTCSIGN	Kraft Tool Co.® Sign
2	CF227PF	18"x4" Cement Trowel w/ProForm® Handle	1	KTCTOOLBSKT	Tool Display Basket
2 5	CF279BPF CF283	16"x4" Blue Steel Pool Trowel w/ProForm® Handle 20 Grit 6"x3"x1" Rub Brick			Z-Kneeler [™] Kneeboards, but will come with a box of 10.

DISPLAY ACCESSORIES, SHIRTS & HATS



KRAFT TOOL CO.º

"Hand Krafted" Tools for the Construction Trades





KTCSIGN Plastic 36"x9 Sign



KTCTOOLBSKT*

Basket

KTCBSKTSIGN Sign

KTCHDLHOLDER*

Extension handle holder (Holds 12)

KTCHDLHOLDER18*

Extension handle holder (Holds 18)



KTRWLBR* Trowel Bar

KHOOK6* 6" Display Hook

KHOOK12* 12" Display Hook

KHOOK4* 4" Display Hook

KHOOK8*

8" Display Hook

KHOOK4L*



6" Loop Holder



KTC018*

Brick Trowel Hanger (Blue)

KTC015*

Brick Trowel Hanger (Orange) Trowels not included



KTC026*

Multi-tier trowel holder Trowels not included





KTC019* Holder (Holds 6)

Holder (holds 4)H Trowels not included



KHOOK8L* 8" Loop Holder

4" Loop Holder



KTCCTLGHOLDER*

Catalog holder for displays





No.

KTCSHIRT-C* KTCSHIRT-D*

KTCSHIRT-E* KTCSHIRT-A*

KTCSHIRT-B* KTCSHIRT-F* Description

Kraft Tool Co.® Shirt - Blue (L) Kraft Tool Co.® Shirt - Blue (XL)

Kraft Tool Co.® Shirt - Blue (XXL)

Kraft Tool Co.® Shirt - Ash Grey (L) Kraft Tool Co.® Shirt - Ash Grey (XL) Kraft Tool Co.® Shirt - Ash Grey (XXL)



KTCSQHOLDER* Square holder for displays

Holds up to 15 Squares!





Description

KTCSHIRT ROSE-C* W. Rose™ Shirt - Brown (L)
KTCSHIRT ROSE-D* W. Rose™ Shirt - Brown (XL) KTCSHIRT ROSE-E* W. Rose™ Shirt - Brown (XXL)

KTCSHIRT ROSE-A* W. Rose™ Shirt - Ash Grey (L) KTCSHIRT ROSE-B* W. Rose™ Shirt - Ash Grey (XL) KTCSHIRT ROSE-F* W. Rose™ Shirt - Ash Grey (XXL)




KTCCAP* Kraft Ball Cap



KTCCAP-ROSE* W.Rose™ Ball Cap



KTCCAP-CAMO* Kraft Camo Ball Cap



KTCHOLDER* (above) Multi-Purpose holder for displays (1-1/2" Space)

KTCBIGDHLDR* (right) Big "D" Bull Float holder for displays (3" Space)

KTCLVLHOLDER* (below) Level holder for displays







3 Knot Brush	68	Edging	66	Convex Jointer 89, 93	F
A	00	Finish	33, 58	Coping Saw 126	Featheredge 110
ADA Mats	E4	Grout Cleaning	131	Corner Tape 122	Finger Tape 95
Adapter Bar	51 28	Masonry	95, 98	Corner Tools	Flat Wire Texture Broom 34, 109
Adhesive Spreader	135	Squeegee Coater	65, 68	Plastic 113	Flipper Tilt Bracket [™] 33
Aluminum Handles	16-17, 55	Stucco	111	Stainless Steel 112, 113, 120	Float and Broom Combo 33
Angle Floats	111	Texture Duckerse™ Ctraightedge	121	Countertop Tools 58	Float Hook 11
Angle Plane	111	Buckaroo™ Straightedge Bucket Bags	27, 58 71	Cross Check Level 83 Curb & Gutter Tools 48	Float Pans 30 Floats
Apparel	143	Buckets	58, 133	Curb Forming Tool 26	Beveler 13
Apprentice Kits	139	Bucket Scoop	113, 119	Curb Tools	Brackets 15-16
Archaeology Tools	106	Buckeye [™] Straightedge	27	Blue Steel 46	Button Handle 14, 15
Asphalt Banding Machine		Bull Floats		Stainless Steel 49	Threaded Handle 14, 15
Asphalt Tools Aussie Combo	64-66 23	Aluminum	18	D	Bull 18-19
_	23	Brackets	14, 15	Darbies	Canvas-Resin 13,19
В		Bronze Groover Bit	18	Canvas-Resin 13, 22	Channel 19
Banjos	119	Canvas-Resin	19	Magnesium 22	Drain 13
Barbell Jointer	94	Channel Converter Plate	19 15	Mahogany 23	Epoxy Grout Float 131
Barrel, Mixing	55 e 137	Groover Bit	18	Scratcher 110	Float & Broom Combo 33 Foam 108
Bearcat Stripper Machine Big "D" Bull Float	137	Handles	16-17	Decorative Concrete Tools 19, 50-54	Grout 131, 135
Blister Brush	111	Magnesium	18-19	Denver Sliders 59	Groover Bit 18
Bolt Cutters	95	Multi-Trac	21	Dial Levels 83	Hand 11
Boots	70	Weight	19	Diamond-Shaped Joint Knife 63	Handles 11, 16, 17, 108
Border Tools	50	Wood	18	Diamond "V" Head Jointers 93 Displacers 24-25	Hi-Craft [™] 61-62
Brackets		Bull's Eye Level	83	Displacers 24-25 Display Accessories 81, 143	Mag-150 [™] 12
Adapters	14, 16			Displays 80, 140-142	Magnesium 11, 12, 13, 18, 19
Broom	66	C		Door Jamb Super Saw 137	Mini Mag Float 11
Bull Float	14,15	Cardinal Placer	24	Double Notch Rake 56	Plaster 108
Converter Plate	15	Carpenter Pencils	83	Driveway Approach Tool 48	Rubber 108 Sand Cast 12
Double Tilt Action	15	Carpenter Aprons	72 81	Drywall Dolly 124	Sand Cast 12 Texture 63, 108
Fresno Quick Change Convert	14 ter 38	Carpenter Squares Carpet Puller	138	Drywall Knives 118-120	ThinLine 12
Single Tilt Action	14	Carpet Seam Roller	138	Drywall Lifters 124	Walking 18, 19, 23
Brass Turrets	126	Carpet Stapler	138	Drywall PanelLift® 124	Wide 12
Brick/Block Clips	107	Carpet Stretcher	138	Drywall Patch 122	Wood 13, 18, 83
Brick and Stone Marker	93	Carpet Tools	138	Drywall Saw 123 Drywall Squares 82, 123	Floorcovering Tools 125-138, 140
Brick Cart	106	Caulk Guns	58, 137	Drywall Tape Holder 122	Fortex® Pail 95
Brick Splitters	106	Epoxy Guns (Dual Cartric		Drywall Tapers 119	Fresnos 20,21
Brick Tongs	101	Caulking Trowels	62, 92	Drywall Tools 114-124, 139, 141	Adapters 16,21
Brick Trowels	91, 85-88		70, 99, 132	Dust Mask 70, 132	Brackets 14,15, 20, 21
Limber Handles	87 90	Chalk Box 65, 70, 9 Chamfer Tools	99, 100, 132 45	E	Bronze Groover Bit 20 Center Line Groover 20
Bricklayer's Set	104	Chamfer Tube Edgers	38	Edger Pans 30	Curved Shotcrete 35
Big "D" Bull Float	19	Channel Floats	19	Edger/Groovers 42, 44, 50	Edger 21
Broadcast Gun	50	Channellock®	10	Edgers	Hi-Craft™ 61
Bronco™ Tilt Bracket	15	Ironworker's Pliers	31	All Steel 45	Multi-Trac 21
Broom Cover/Protector	33	Check Rod	27	Blue Steel 46, 47	Weight 21
Brooms			53, 104, 132	Bronze 38-39	G
Adapters	33	Circle Cutter	121	Deco 50	Gauge Rake 55, 57
Asphalt	66	Clinch-On Tool	121	Hi-Craft™ 61	General Construction Tools 68-72
Brackets	32	Clipped Angle Joint Knife	e 63 50	Stainless Steel 43, 44, 45, 50	Gizmo Snap-On Trowel 128
Broom Cover Finish	33 32-33	Color Hardener Color Release	50 50	Step-Saver® 36 Walking 39, 45, 47, 50	Glitter 114
Float & Broom	32-33	Color Release Agents	50	EIFS Tools 113	Glitter Gun 114
Handles	33, 55, 98	Combination Squares	79	Elite Series Five Star Trowels [™] 4, 5,	Gloves (Latex) 58, 70, 132
Wire Texture	34, 109	Combination Tool	63, 121	140	Gloves (Work) 58, 70, 106, 132
Bronco™ Tilt Bracket	15	Compressor	115	End Cut Nippers 112	Go Devils 108 Gold Standard™ Placer 24
Bronze Tools	37-39	Concrete Chute	34	Epoxy Gun 58	Gold Standard [™] Placer 24 Gold Standard [™] Tools 17, 24
Brushes		Concrete Chute Tool	34	EZ-Kneeler™ Kneeboard 59, 70, 132	Grinding Stone 29
3 Knot	68	Concrete Restoration	55-58	EZY Deck	Groover/Edgers 42, 44, 50
Bucket	113 33	Concrete Tools 4-61, 13 Construction Boots		Pro Gun & Hopper 52, 115	Groovers
Curb Dutch	33 111	Concave Jointer	70 89, 93	EZY-Tilt® Bracket 15 EZY-Tilt® II Bracket 15	Airplane 36, 40
Duton	111	OUTIOUVO UUTITUT	00, 00	LZ I IIIL II DIQUNGL IJ	

All Charl	littorhug E4	Line Dine 00 101 107	Dovor's Croover
All-Steel 36 Aluminum 36, 53	Jitterbug 54 Jointers	Line Pins 90, 101, 107 Line Stretchers 107	Paver's Groover 40 Paver's Straightedge 26-27
Bits 18	Barbell 94	Line Twigs 101, 107	Personalized Items 101
Bronze 37-39	Brick 93	Linoleum Knife 135	Placers 24-25
Deco 53	Bullhorn 89	Liquid Release 51	Plaster Floats 108
Hand 36, 37, 38, 41, 42, 44, 50	Concave 89, 93	Lutes 64	Plaster Hawks 109
Hi-Craft [™] 61	Convex 89, 93	M	Plaster Tools 108-112, 139
Iron 38	Deco "V" 53	Mag-150™ Float 12	Pliers 31
Magnesium 40	Grapevine 89, 91, 93	Magnesium Handles 16-17	Plumb Bobs 80
Ramp Groover 44	Hubbard 94 Plexiglass 93	Mallet, Rubber 137, 121	Pointing Trowels 62, 89, 92, 128
Rocker 38 Safety 44, 49	Plexiglass 93 Rake 93	Margin Grout Float 131	Pour Pot 66 Power Troweler Blades 28-29
Stainless Steel 40, 41, 50	S 93	Margin Trowels 62, 89, 92, 128	ProForm® Float Pans 30
Step-Saver® 36	V 89, 94	Mask (Dust) 70, 132	ProForm® Heavy-Duty
Straight Arrow 53	Variable Convex 93	Masonry Barbell Jointer® 94	Gold Trowler Blades 29
Ultra Hard 38	Joint Knives 63, 118-119	Masonry Brushes 95, 98	ProForm® Ultra Blue
Walking 36, 39, 40, 41, 44, 50	Joint Rakers 91, 93	Masonry Guides 101 Masonry Tools 91-107, 139,	Trowler Blades 29
Grout Bags 95, 133	Joint Touch-Up Rollers 53	140-141	Pry Bars 31, 137
Grout Floats 131, 135	K	Mason's Line 90, 96-97	Pull Bar
Grout Saw 131	Keyhole Screeds 26	Mason's Tape 100	Pullers 138
Gun & Hoppers 52, 115 Hi-Craft [™] 62	Knee Kicker 138	Measuring Pitcher 55	Putty Knives 63, 118-119, 121
Gunite Shoes 35, 55, 57	Knee Pads 60, 62, 70, 132	Measuring Tapes 70, 99	R
Gunite Tools 35, 35, 37	Kneeboards & Sliders 59	Mega Mover Concrete Placer™ 24	Radius Bender 35
H	Knives	Meter Stick 82	Rapid Square® 80
	Broad 118	Mini Lifter 124	Rakes 25, 64, 66
Hammer Loops 72 Hammers	Carpet 138 Joint 63, 118-119	Miter Snips 112, 136 Mitre Rod 109	Rasps 113, 124 Rebar Cutter/Bender 31
Brick 90, 104, 105	Linoleum 63, 135	Mixers 57, 66, 117, 133	Rebar Lifter 31
Drywall 123	Putty 63, 118-119, 121	Mortar Boards 103	Redwood Striker [™] 23
Framing 68, 100	Taping 118-120	Mortar Boxes 102	Right Angle Placer [™] 24
General Purpose 68, 137	Utility 70, 122-123, 136	Mortar Hoe 103	Rocker Head Pry Bar 310
Magnetic 112	Vinyl 135	Mortar Pans 103	Rod/Coping Saw 126
Miscellaneous 105	Wipe Down 120	Mortar Stands 103	Roller Tray 56
Sledge 68	Knock Down Knife 114	Mosaic Nippers 127	Rollers
Tile 90, 132	Knucklehead® II Bracket 15	Mud Dobber 102	Carpet Seam 138 Corner 114
Handles Adapters 16	Knucklehead [®] II Rebuild Kit 15 Kumalong [®] 25	Mud Holder 116 Mud Mashers 116	Corner 114 Double 54
Bull Float 16	3	Mud Mixers 57, 66, 117	Frame 56, 114
Broom 33, 55, 66, 68, 98	L	Mud Pan Holder 116	Joint Touch-Up 53
Cleaning Brush 17	Laminated Float 13, 18	Mud Pans 116	Nap Covers 56
Extension 16, 34, 68, 122	Levels Aluminum Box 76	Multi-Trac Groover 21	Safety 54
Float 11, 108	Aluminum Box 76 Aluminum Extruded 73, 76,	Multi-Twist™ Bracket 14,23	Salt 51
Trowel	78-79, 124	Multi-Undercut Saw 137	Single 54
Brick 90	Bull's Eye 83	N	Spiked 56
Concrete 5, 7 Wood Clevis 40, 47	Cases 75, 77	Nail Bags 72	Tamp 54 Texture 114
Hand Tracer 104	Cast Aluminum 73	Nail Drivers 112	Vinyl 136
Hawks 109	Cross Check 83	Name Stamp 39	Rope 97
Heat Iron 138	Door Jamb 74	Neptune Line 97	Round It Tool 120
Heat Seaming Tape 138	Line 83, 99 Magnesium Extruded 77	New Products 3, 5, 10, 27, 33, 48, 54, 56, 63, 66, 67, 68, 69, 87,	Rubbing Stone 130
Heavy-Duty Broom 66	Magnesium Extruded 77 Magnetic 73, 78, 99, 124	98, 108, 111, 112, 117, 119, 127	Rub Bricks 35, 130
Hi-Craft [™] Tools 61-62,	Mahogany 74-75, 77, 99	Notch Trowels 128, 129	Rules 100
119, 123, 124, 135	Post 83	Economy 135	S
Hickey See Rebar Bender	Smith 99	Nylon Line 96-97	Safety Rod Style Float Pans 30
Hoes Asphalt Crack 64	Torpedo 83, 99	0	Salt Roller 51
Easy Mixer Concrete 34, 103	Walnut/Maple 74	Orbit-er™ Bracket 15	Sanders 63, 122
Mortar 103	W. Rose [™] 90	Ornamental Tools 110	*PRODUCTS OF FOREIGN ORIGIN
Hoppers 52, 62, 115	Lid Claw 113, 133	Oval Mixer 55, 57	are noted with an (*) in the product description and could also be
Hubbard Jointers 94	Line 96-97 Line Blocks	P	assembled in the USA
J	Aluminum Corner 107	Pail 59, 95, 133	with foreign parts. Kraft Tool Co.® will bring to you the best quality
Jiffy Mixer 57, 117, 133	Plastic 62, 107	Panel Carrier 63, 124	possible in order to offer a wide variety of professional hand tools.
Jiffler Mixers 57, 117	Wood 101, 107	Patch Gun 114	-variety of professional flatid tools.
	, -		

Sanding Rasps 11	3	Spray Shield	114	Brio
Sandpaper 12		Spreaders	24-25	Din
Sands Level & Tool Co® 73-83	3,	Squares	79, 80, 82, 123	
109, 123, 12		Squeegees		
	11	Asphalt	65, 68	
	13	Crack	65	Buo
	'9 13	Floor Notched	55, 69 55	Bur But
Drywall Squares 79, 82, 12		Trowel	55	Cai
Hawks 10		Stair Gauge	81	Cer
	5	Stair Tool	138	Chr
Levels 73-79, 12		Stamps		Cor
Line Blocks 10		Bronze Concre		
	12	Utility	51 10p 72	
	10 13	Steel Hammer Lo Step-Saver®	36	
	12	Step Tools	50	
Stair Gauge 81, 8		Blue Steel	46, 47	Cro
	13	Plastic	50	Dry
	13	Stainless Steel		Duc
	12	Step-Saver® To		EIF
Sandsucker 10 Saws 123, 13		Stone Splitting W Straight Arrow G		EIF: Elit
Scarifier 11			26, 27, 82, 134	Exte
Scoops 66-6		Striker™ Screed	26	Fin
Scoring/Cutting Tool 12		Stripper Machine	137	Flex
Scoring Wheels 12		Stud Crimpers	121	Fur
Scouring Pad Holder 13		Super-Pro® Gun		Gau
Scouring Pads 13		Superior Tile Cut	ter® 125-138	Giz
Scrapers 63, 69, 116 118, 121, 13		Т		Gui Hi-
Screeds	' '	Tampers	54, 66	Insi
Aluminum 26, 13	4	Tape Measures	70, 99, 132	Ma
	23	Tapers Taping Knives	119 118-120	
	26	Tapping Block	137	Mic
Magnesium 26, 11 Redwood 2	U !3	Texture Broom	34	Mu Not
Scribes 13		Texture Compres		Out
Scoops 66-6		Texture Guns	115	Pip
•	i1	Texture Mats	52	Pla
	5	Texture Rollers Texture Skins	114 53	
Shears 11		Tie Wire Reel	31	
	5 7	Tie Wire Twister	31	
	9	Tile Bridge	134	
Sled Runners 89, 9		Tile Cutters	125-126	Ple
	8	Tile Hole Saw	126	Poi
Slickers 89, 93, 11		Tile Kit Tile Markers	128 132	Poi
	9	Tile Nippers	127, 135	
	9	Tile Spacers	134	Pod
Smith Level 9 Smoother 55, 5	19 18	Tile Tools	125-138, 139, 140	
	8	Tile Wedges	134	
Snips 112, 13		Tine Broom	34	
Soffit Square 12		Tool Bags Tool Displays	71, 92 80, 140-142	
	57	Tool Pouches	72, 92, 128	Pur
	8	Tri Level Placer	25	Rep
Spiked Shoes 35, 55, 5 Sponges 13		Triangle (Folding	136	
Cellulose 13		Troweler Blades	28-29	Rou
Grout 13		Trowels	444	Rou
Polyester 13	0	Angle Asphalt	111 65	Rou
Rubber 13		Aspriari Barrier	34	Sev
Sprayer 5	1	Darriol	04	Scr

Brick	91
Limber	87
	i, 91
	', 91
	, 31 5, 91
	1, 31 122
	133
Burn 62 00	01
Buttering 62, 88	
Caulking 62, 68	
Ceremonial	90
Chrome (No Burn)	9
Concrete	
Blue Steel 5, 7, 9	
Carbon Stainless Steel	9
	5, 10
Golden Stainless Steel	5, 7
Swedish Stainless Steel	7
Cross-Joint	91
Drywall	119
Duck Bill	91
EIFS Notch	113
EIFS Plastic	113
Elite Series Five Star	4-5
Exterior Finish	113
	1-10
Flexible Radius Trowel	10
Funny Trowel	10
Gauging 62, 88	
Gizmo Snap-On	128
Gunite	35
Hi-Craft™	61
Margin 62, 89, 92,	
	128
Midget	7
Mud	88
Notch 128,	
Outside Corner 112,	
Pipe Trowel	10
Plaster	
Carbon Steel	5,9
Golden	
Stainless Steel 5, 9,	109
Swedish	
Stainless Steel 9,	109
Plexi-Plastic	10
Pointed Sword	61
Pointing 62, 89, 92,	128
	128
Pool	
Blue Steel	5,8
Carbon Steel	8
Golden Stainless Steel	8
Mini Pool	7
Swedish Stainless Steel	8
Pumpkin Seed	88
Replacement Handle	00
	00
Brick	90
Concrete	7
Round End Burn	7
Rounded Detail	112
Round Front/Square Back	9
Sewer	88
Scratcher	109

Sharpener Silo Squeegee Sword Tile Trowel Bracket Venetian 10 Try & Mitre T-Square 79, 80, 82	10 10 55 61 88 10 , 111 79
Undercut Door Jamb Saw Utility Knife 70, 122-123 Utility Stamps	137 3 136 51
Vinyl Floor Roller	136 , 135 136 136 136 136
Whiskey Stick Wipe Down Knives	71 , 132 4-90.
Yard Sticks	82
Z-Clip Style Float Pans	30

FOLLOW US














Kraft Tool Co.® established in 1981, manufactures quality Trowel Trade Tools for concrete, masonry, asphalt, drywall, plaster, and tile professionals. As a trusted name in the hand tool industry, Kraft Tool is proud of the "Hand Krafted" workmanship attributed to every product.

Our goal is simple: Maintain quality, provide good service and offer new and innovative products.

W. Rose™, Sands Level & Tool Co.®, Inc., and Superior Tile Cutter®, Inc. are Kraft Tool Co.® Brands



For over 200 years W. Rose™ has been known for the highest quality of masonry tools. William Rose established the company in 1798 in Blockley Township, Pennsylvania near Philadelphia. This blacksmith shop spent much of the early 1800s making cavalry sabers and officer swords for the U.S. Army. In 1864, W. Rose began specializing in quality edged tools, knives, and their signature brick trowel. In 2001, Kraft acquired this legendary company and remains dedicated to maintaining the superior craftsmanship of its tools. Rose Tools Endure. Find W. Rose™ brick trowels and masonry tools on pages 84-90 in this catalog.





This Contact Saber was manufactured by William Rose in 1807.

Julius Sands, a bricklayer by trade, invented Sands's "solid set" vials. In 1895, he started the J. Sands & Sons business in Detroit, Michigan. His company originated the lightweight aluminum level that is a mainstay of tradesmen around the world and grew it to become one of the largest level manufacturers in the world. Kraft Tool Company purchased the Sands Level & Tool Co.® in 2005. The levels, squares, and rules are all still made here in the United States. As they have for over 100 years, "Sands Levels Tell the Truth." Find Sands levels and tools on pages 73-83 of this catalog.



This wood level was manufactured when Sands was J. Sands & Son's (Detroit, MI) in 1900.



Superior Tile Cutter®, Inc. and Tools brand was established in 1930 as a trailblazer making professional quality tile cutters, chisels and scribes. Superior prides itself on tools that will last a professional tilesetter a lifetime. In 2003, the Kraft Tool Company purchased Superior and has continued the excellence that has made it the choice of professionals around the world. Over eighty years later the product line includes not just tile cutters, but everything you need for tile, carpet, wood and vinyl flooring. Find Superior Tile Cutter® tools on pages 125-134 of this catalog.




Kraft Tool Co.® continues to expand its tool family by offering "Value-Priced Trade Tools" called Hi-Craft™. These are additions to the already extensive line of tools for tradesmen, offering homeowner tools at a value price. Find Hi-Craft™ tools on pages 61-63 & 135 of this catalog.



KRAFT TOOL CO.® SIGNATURE BRANDS









Kraft Tool Co.®

8325 Hedge Lane Terrace Shawnee, KS 66227 USA

Phone: 800-422-2448 • 913-422-4848

Fax: 800-985-7238 • 913-422-1018

www.KraftTool.com