


FIGURE 7899 - Insulation Couplings



Catalog Number	Clamp ID	C	Weight
	Tube OD		
FNW7899D0050	1/2" NOM	2.025	0.49
FNW7899D0062	5/8" OD	1.785	0.46
FNW7899D0075	3/4" NOM	2.285	0.5
FNW7899D0087	7/8" OD	2.025	0.49
FNW7899D0100	1" NOM	2.500	0.57
FNW7899D0112	1-1/8" OD	2.285	0.52
FNW7899D0125	1-1/4" NOM	2.845	0.63
FNW7899D0137	1-3/8" OD	2.500	0.58
FNW7899D0150	1-1/2" NOM	3.285	0.68
FNW7899D0162	1-5/8" OD	2.845	0.63
FNW7899D0212	2-1/8" OD	3.285	0.73

Catalog Number	Clamp ID	C	Weight
	Tube OD		
NW7899G0050	1/2" NOM	3.008	0.65
FNW7899G0062	5/8" OD	3.008	0.63
FNW7899G0075	3/4" NOM	4.138	0.72
FNW7899G0087	7/8" OD	3.008	0.67
FNW7899G0112	1-1/8" OD	3.008	0.73
FNW7899G0125	1-1/4" NOM	3.638	0.79
FNW7899G0137	1-3/8" OD	3.638	0.76
FNW7899G0150	1-1/2" NOM	3.950	0.8
FNW7899G0162	1-5/8" OD	3.638	0.78
FNW7899G0200	2" NOM	4.648	0.89
FNW7899G0212	2-1/8" OD	4.138	0.86
FNW7899G0250	2-1/2" OD	5.138	0.97
FNW7899G0262	2-5/8" OD	4.648	0.95
FNW7899G0300	3" NOM	5.75	1.207
FNW7899G0312	3-1/8" OD	5.138	1.05
FNW7899G0362	3-5/8" OD	5.69	1.234
FNW7899G0412	4-1/8" OD	6.87	1.234
FNW7899G0512	5-1/8" OD	7.870	1.234

Catalog Number	Clamp ID	C	Weight
	Tube OD		
FNW7899J0050	1/2" NOM	4.138	0.81
FNW7899J0075	3/4" NOM	4.138	0.84
FNW7899J0087	7/8" OD	4.138	0.84
FNW7899J0100	1" NOM	4.648	0.94
FNW7899J0112	1-1/8" OD	4.138	0.86
FNW7899J0125	1-1/4" NOM	5.138	0.97
FNW7899J0137	1-3/8" OD	4.648	0.93
FNW7899J0150	1-1/2" NOM	5.138	1.01
FNW7899J0162	1-5/8" OD	5.138	0.95
FNW7899J0212	2-1/8" OD	5.138	1.05
FNW7899J0262	2-5/8" OD	5.690	1.234
FNW7899J0300	3" NOM	6.870	1.234
FNW7899J0312	3-1/8" OD	6.870	1.234
FNW7899J0362	3-5/8" OD	6.870	1.234
FNW7899J0412	4-1/8" OD	7.870	1.234

Catalog Number	Clamp ID	C	Weight
	Tube OD		
FNW7899K0062	5/8" OD	4.648	0.63
FNW7899K0087	7/8" OD	5.138	0.995
FNW7899K0112	1-1/8" OD	5.138	0.995
FNW7899K0137	1-3/8" OD	5.698	1.234
FNW7899K0162	1-5/8" OD	5.698	1.234
FNW7899K0212	2-1/8" OD	6.870	1.234
FNW7899K0262	2-5/8" OD	6.87	1.234
FNW7899K0312	3-1/8" OD	7.87	1.234
FNW7899K0362	3-5/8" OD	7.87	1.234

For use with fiberglass insulation

- 1" wall thickness
Sizes 7/8" to 1-1/8"
- 1-1/2" wall thickness
Sizes 7/8"

